

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912370

Luminaire Tested: DFN2DIP-SQ4F0-120D160US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912370
REPORT IS A COMBINATION OF REPORTS P900216 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D160US850-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 27016.3 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 239.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912370

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912370

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3859	3859	3859
5°	3865	3799	3824
10°	3827	3725	3700
15°	3774	3603	3509
20°	3705	3434	3274
25°	3633	3244	3047
30°	3537	3050	2758
35°	3443	2841	2505
40°	3348	2624	2214
45°	3237	2384	1950
50°	3122	2141	1693
55°	3002	1882	1446
60°	2863	1610	1191
65°	2703	1335	1073
70°	2510	1077	973
75°	2267	951	887
80°	1915	801	773
85°	1333	539	589

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 4416 cd/sqm

TEST NUMBER: P912370

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.5	1.9
10°-20°	1415.1	5.2
20°-30°	1986.8	7.4
30°-40°	2165.7	8.0
40°-50°	1990.5	7.4
50°-60°	1563.2	5.8
60°-70°	1017.5	3.8
70°-80°	523.8	1.9
80°-90°	149.6	0.6
90°-100°	347.3	1.3
100°-110°	1103.4	4.1
110°-120°	1888.3	7.0
120°-130°	2483.4	9.2
130°-140°	2787.5	10.3
140°-150°	2733.5	10.1
150°-160°	2293.0	8.5
160°-170°	1520.7	5.6
170°-180°	531.5	2.0
0°-30°	3917.3	14.5
0°-40°	6083.0	22.5
0°-60°	9636.8	35.7
0°-90°	11327.7	41.9
90°-120°	3339.0	12.4
90°-150°	11343.4	42.0
90°-180°	15689.0	58.1
0°-180°	27016.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5500	5500	5500	5500	5500	
5°	5500	5475	5410	5455	5440	522
15°	5231	5176	5008	4913	4863	1474
25°	4749	4589	4261	4057	3982	2184
35°	4092	3838	3400	3086	2976	2561
45°	3345	3011	2489	2135	2016	2583
55°	2543	2155	1618	1319	1225	2273
65°	1717	1314	866	697	682	1703
75°	916	567	398	363	358	969
85°	214	109	94	94	94	246
90°	5	61	166	156	161	27
95°	247	294	303	303	294	275
105°	1018	1032	1042	1051	1051	1075
115°	1895	1922	1914	1908	1895	1874
125°	2756	2798	2785	2770	2765	2463
135°	3565	3617	3628	3622	3609	2756
145°	4328	4362	4389	4394	4375	2704
155°	4949	4962	4978	5001	4986	2278
165°	5384	5379	5379	5412	5389	1519
175°	5602	5588	5578	5612	5583	532
180°	5612	5612	5612	5612	5612	

TEST NUMBER: P912370

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5500.2	5500.2	5500.2	5500.2	5500.2
2.5°	5525.0	5500.2	5445.3	5495.4	5485.3
5°	5500.2	5475.4	5410.4	5455.3	5440.5
7.5°	5455.3	5425.7	5356.0	5375.5	5350.7
10°	5395.6	5360.8	5261.4	5246.1	5216.6
12.5°	5321.1	5276.3	5141.5	5112.0	5057.2
15°	5231.4	5176.5	5007.5	4912.9	4863.3
17.5°	5126.8	5047.1	4837.9	4728.7	4648.9
20°	5007.5	4907.7	4658.9	4534.8	4424.9
22.5°	4878.0	4763.5	4474.6	4305.6	4231.2
25°	4748.7	4589.2	4260.7	4056.8	3981.9
27.5°	4594.5	4424.9	4061.6	3827.7	3713.0
30°	4430.2	4240.7	3842.5	3588.9	3454.3
32.5°	4270.8	4041.5	3633.9	3335.0	3210.3
35°	4091.8	3837.7	3399.9	3086.2	2976.3
37.5°	3917.4	3643.4	3180.7	2836.9	2712.8
40°	3733.1	3434.8	2951.6	2598.3	2468.9
42.5°	3544.0	3225.6	2722.9	2354.3	2230.2
45°	3345.0	3011.3	2488.9	2135.2	2015.7
47.5°	3155.9	2802.7	2265.0	1911.3	1801.9
50°	2946.8	2593.5	2045.9	1702.1	1598.1
52.5°	2742.4	2369.0	1836.7	1508.2	1413.8
55°	2543.4	2155.2	1617.6	1319.2	1224.7
57.5°	2339.4	1941.3	1423.7	1144.9	1065.2
60°	2130.4	1732.1	1219.3	965.9	886.2
62.5°	1926.6	1528.3	1045.1	806.5	766.8
65°	1717.4	1313.9	866.1	697.1	681.8
67.5°	1518.3	1114.8	697.1	612.1	597.3
70°	1309.2	921.0	577.2	527.6	507.5
72.5°	1110.1	741.5	482.6	443.0	433.1
75°	915.7	567.1	398.2	363.3	358.5
77.5°	722.0	402.9	313.7	293.7	283.6
80°	542.4	288.9	238.7	219.1	219.1
82.5°	378.2	194.3	164.2	154.2	154.2
85°	213.9	109.3	94.5	94.5	94.5
87.5°	79.7	39.6	39.6	34.8	34.8
90°	5.1	60.9	165.8	155.7	160.7
92.5°	104.9	142.2	147.2	152.3	152.3
95°	247.0	294.4	302.9	302.9	294.4
97.5°	411.1	455.1	473.8	473.8	473.8
100°	600.6	639.6	653.1	653.1	648.0
102.5°	800.3	829.1	847.6	852.7	847.6
105°	1018.5	1032.0	1042.2	1050.7	1050.7
107.5°	1235.1	1255.4	1255.4	1258.8	1235.1
110°	1444.9	1472.0	1472.0	1472.0	1458.4

TEST NUMBER: P912370

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1671.6	1700.4	1695.3	1681.8	1671.6
115°	1894.9	1922.0	1913.6	1908.5	1894.9
117.5°	2116.6	2153.8	2130.2	2116.6	2103.1
120°	2340.0	2377.1	2340.0	2340.0	2324.7
122.5°	2542.9	2590.4	2566.7	2553.1	2542.9
125°	2756.2	2798.5	2784.9	2769.7	2764.6
127.5°	2964.2	3016.7	2998.1	2977.8	2964.2
130°	3158.9	3219.8	3211.3	3201.1	3182.5
132.5°	3377.1	3424.5	3427.8	3404.2	3390.7
135°	3564.9	3617.3	3627.5	3622.4	3608.9
137.5°	3774.7	3817.0	3825.5	3822.1	3801.8
140°	3959.1	4001.4	4025.1	4025.1	4006.5
142.5°	4148.7	4190.9	4204.4	4209.5	4190.9
145°	4328.0	4361.8	4388.9	4394.0	4375.3
147.5°	4488.7	4531.0	4551.3	4559.8	4541.1
150°	4654.5	4683.3	4701.9	4717.1	4701.9
152.5°	4801.7	4830.5	4854.2	4872.7	4854.2
155°	4948.9	4962.4	4977.6	5001.4	4986.2
157.5°	5075.8	5086.0	5094.4	5128.2	5104.6
160°	5189.1	5199.3	5204.4	5233.1	5212.9
162.5°	5294.0	5294.0	5299.1	5331.3	5307.6
165°	5383.8	5378.6	5378.6	5412.5	5388.9
167.5°	5464.9	5449.7	5449.7	5483.6	5459.8
170°	5525.8	5512.3	5507.3	5541.1	5512.3
172.5°	5568.2	5554.6	5549.5	5583.4	5554.6
175°	5602.0	5588.5	5578.3	5612.2	5583.4
177.5°	5620.6	5607.1	5596.9	5625.7	5596.9
180°	5612.2	5612.2	5612.2	5612.2	5612.2

TEST NUMBER: P912370

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.05	11.82	12.08	12.85	14.23	7.01	7.78	8.04	8.81	10.19
	3H	12.72	13.41	13.76	14.45	15.86	8.19	8.88	9.23	9.92	11.32
	4H	13.33	13.98	14.38	15.03	16.44	8.64	9.29	9.69	10.33	11.75
	6H	13.75	14.35	14.82	15.40	16.82	8.96	9.56	10.02	10.60	12.03
	8H	13.88	14.45	14.95	15.51	16.93	9.05	9.62	10.11	10.68	12.10
	12H	13.94	14.48	15.01	15.54	16.98	9.09	9.63	10.16	10.69	12.13
4H	2H	11.06	11.71	12.12	12.75	14.16	7.60	8.25	8.66	9.29	10.70
	3H	12.89	13.43	13.95	14.50	15.92	8.94	9.48	10.01	10.56	11.98
	4H	13.58	14.07	14.65	15.14	16.58	9.49	9.98	10.56	11.05	12.49
	6H	14.09	14.52	15.18	15.61	17.05	9.91	10.33	10.99	11.42	12.86
	8H	14.27	14.67	15.35	15.75	17.20	10.03	10.43	11.11	11.51	12.96
	12H	14.37	14.72	15.46	15.82	17.28	10.10	10.46	11.19	11.55	13.01
8H	4H	13.54	13.94	14.62	15.02	16.47	9.77	10.16	10.85	11.24	12.70
	6H	14.11	14.44	15.21	15.56	17.01	10.28	10.61	11.39	11.73	13.19
	8H	14.33	14.62	15.44	15.72	17.19	10.48	10.76	11.59	11.87	13.34
	12H	14.47	14.72	15.58	15.82	17.33	10.59	10.85	11.71	11.94	13.46
12H	4H	13.49	13.85	14.59	14.94	16.40	9.77	10.13	10.87	11.22	12.68
	6H	14.09	14.37	15.20	15.48	16.95	10.33	10.62	11.44	11.72	13.20
	8H	14.31	14.56	15.42	15.66	17.17	10.54	10.80	11.66	11.89	13.41

END OF REPORT