

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912372

Luminaire Tested: DFN2DIP-SQ4F0-140D060US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912372
REPORT IS A COMBINATION OF REPORTS P900073 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D060US850-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21259.5 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912372

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912372

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US850-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	81	79	76	74	72	68	66	65
2	94	86	80	74	89	82	76	71	74	69	65	66	63	60	60	57	55
3	85	76	68	62	81	72	65	60	65	60	55	59	54	51	53	49	46
4	78	67	59	52	74	64	56	51	58	52	47	52	48	44	47	43	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	35	31	27
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4239	4239	4239
5°	4246	4181	4209
10°	4211	4125	4153
15°	4149	4058	4066
20°	4066	3965	3976
25°	3982	3853	3871
30°	3878	3748	3739
35°	3779	3626	3598
40°	3657	3501	3464
45°	3536	3377	3328
50°	3403	3246	3169
55°	3264	3095	3024
60°	3107	2916	2858
65°	2936	2731	2661
70°	2717	2504	2450
75°	2415	2234	2258
80°	2051	1890	1886
85°	1483	1293	1268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3536 cd/sqm

TEST NUMBER: P912372

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	568.6	2.7
10°-20°	1599.8	7.5
20°-30°	2351.1	11.1
30°-40°	2730.7	12.8
40°-50°	2727.3	12.8
50°-60°	2378.1	11.2
60°-70°	1757.9	8.3
70°-80°	994.6	4.7
80°-90°	268.5	1.3
90°-100°	130.2	0.6
100°-110°	413.7	1.9
110°-120°	708.0	3.3
120°-130°	931.2	4.4
130°-140°	1045.3	4.9
140°-150°	1025.0	4.8
150°-160°	859.8	4.0
160°-170°	570.2	2.7
170°-180°	199.3	0.9
0°-30°	4519.6	21.3
0°-40°	7250.2	34.1
0°-60°	12355.7	58.1
0°-90°	15376.7	72.3
90°-120°	1252.0	5.9
90°-150°	4253.5	20.0
90°-180°	5883.0	27.7
0°-180°	21259.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6041	6041	6041	6041	6041	
5°	6041	6018	5954	6001	5990	573
15°	5751	5716	5641	5664	5635	1620
25°	5205	5159	5060	5071	5060	2395
35°	4491	4433	4340	4304	4275	2804
45°	3654	3614	3526	3462	3439	2820
55°	2766	2730	2661	2591	2562	2472
65°	1865	1830	1772	1720	1691	1844
75°	976	965	935	900	912	1042
85°	238	232	227	209	203	265
90°	2	23	62	58	60	20
95°	93	110	114	114	110	103
105°	382	387	391	394	394	403
115°	710	721	718	716	710	703
125°	1034	1049	1044	1039	1037	924
135°	1337	1356	1360	1358	1353	1033
145°	1623	1636	1646	1648	1641	1014
155°	1856	1861	1866	1875	1870	854
165°	2019	2017	2017	2030	2021	569
175°	2101	2096	2092	2104	2094	200
180°	2104	2104	2104	2104	2104	

TEST NUMBER: P912372

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6041.3	6041.3	6041.3	6041.3	6041.3
2.5°	6076.3	6047.4	5983.3	6041.3	6030.2
5°	6041.3	6018.4	5954.3	6000.6	5989.5
7.5°	6000.6	5966.1	5902.0	5948.8	5937.0
10°	5937.0	5896.4	5826.8	5873.0	5855.7
12.5°	5849.5	5815.0	5745.4	5774.3	5762.7
15°	5750.9	5716.5	5640.6	5664.1	5635.1
17.5°	5629.0	5594.5	5518.6	5547.6	5518.6
20°	5495.2	5460.7	5379.3	5396.6	5373.8
22.5°	5362.0	5309.7	5233.8	5233.8	5222.2
25°	5204.9	5158.6	5060.0	5071.1	5060.0
27.5°	5030.4	4989.8	4914.6	4897.3	4868.4
30°	4856.6	4809.8	4722.9	4705.7	4682.2
32.5°	4670.6	4636.1	4542.9	4507.9	4484.4
35°	4490.6	4432.7	4339.5	4304.5	4275.4
37.5°	4287.2	4234.8	4141.7	4101.1	4072.0
40°	4078.2	4031.4	3938.3	3886.6	3863.1
42.5°	3874.8	3828.0	3735.6	3677.0	3642.5
45°	3654.2	3613.6	3526.1	3462.5	3439.1
47.5°	3439.1	3398.4	3305.4	3241.3	3206.8
50°	3212.3	3183.4	3102.0	3020.6	2991.6
52.5°	2991.6	2950.9	2875.7	2811.6	2771.1
55°	2765.5	2730.4	2660.7	2591.1	2562.1
57.5°	2538.6	2509.7	2433.9	2364.3	2340.8
60°	2311.8	2289.1	2207.7	2143.6	2126.3
62.5°	2091.2	2050.5	1992.5	1934.7	1911.3
65°	1865.0	1829.8	1772.0	1719.5	1690.6
67.5°	1632.7	1603.1	1551.3	1510.6	1487.2
70°	1417.5	1394.1	1341.8	1301.1	1278.2
72.5°	1196.9	1173.4	1144.5	1103.9	1086.6
75°	975.7	964.6	935.0	900.5	912.2
77.5°	778.4	755.0	743.3	726.1	708.8
80°	581.2	575.0	563.4	546.1	534.3
82.5°	395.0	395.0	389.5	366.1	366.1
85°	237.9	232.3	226.8	208.9	203.4
87.5°	104.8	93.0	81.4	64.1	57.9
90°	1.9	22.8	62.2	58.3	60.2
92.5°	39.4	53.3	55.2	57.1	57.1
95°	92.6	110.3	113.6	113.6	110.3
97.5°	154.2	170.7	177.7	177.7	177.7
100°	225.2	239.8	244.9	244.9	243.0
102.5°	300.1	310.9	317.8	319.7	317.8
105°	381.9	387.0	390.8	394.0	394.0
107.5°	463.1	470.8	470.8	472.0	463.1
110°	541.9	551.9	551.9	551.9	546.8

TEST NUMBER: P912372

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	626.8	637.6	635.7	630.6	626.8
115°	710.5	720.7	717.5	715.6	710.5
117.5°	793.7	807.7	798.7	793.7	788.6
120°	877.4	891.4	877.4	877.4	871.7
122.5°	953.5	971.3	962.4	957.4	953.5
125°	1033.5	1049.3	1044.2	1038.6	1036.7
127.5°	1111.6	1131.2	1124.2	1116.7	1111.6
130°	1184.5	1207.4	1204.2	1200.4	1193.4
132.5°	1266.4	1284.1	1285.3	1276.5	1271.4
135°	1336.8	1356.4	1360.2	1358.3	1353.2
137.5°	1415.4	1431.3	1434.5	1433.2	1425.6
140°	1484.6	1500.5	1509.3	1509.3	1502.4
142.5°	1555.6	1571.5	1576.6	1578.4	1571.5
145°	1622.9	1635.6	1645.8	1647.6	1640.7
147.5°	1683.1	1699.0	1706.6	1709.7	1702.8
150°	1745.3	1756.1	1763.1	1768.7	1763.1
152.5°	1800.5	1811.3	1820.2	1827.2	1820.2
155°	1855.7	1860.8	1866.4	1875.4	1869.7
157.5°	1903.3	1907.1	1910.3	1923.0	1914.1
160°	1945.9	1949.6	1951.5	1962.3	1954.7
162.5°	1985.1	1985.1	1987.0	1999.1	1990.2
165°	2018.7	2016.8	2016.8	2029.6	2020.7
167.5°	2049.2	2043.6	2043.6	2056.2	2047.3
170°	2072.1	2067.0	2065.1	2077.7	2067.0
172.5°	2087.9	2082.8	2080.9	2093.6	2082.8
175°	2100.6	2095.6	2091.7	2104.4	2093.6
177.5°	2107.5	2102.6	2098.7	2109.4	2098.7
180°	2104.4	2104.4	2104.4	2104.4	2104.4

TEST NUMBER: P912372

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.15	15.25	14.89	16.01	16.93	13.70	14.81	14.44	15.57	16.48
	3H	15.83	16.82	16.58	17.59	18.54	15.34	16.33	16.09	17.10	18.05
	4H	16.43	17.37	17.20	18.15	19.10	15.94	16.88	16.71	17.65	18.61
	6H	16.85	17.71	17.63	18.50	19.47	16.35	17.21	17.13	18.00	18.97
	8H	16.96	17.79	17.75	18.59	19.56	16.46	17.28	17.25	18.09	19.06
	12H	17.02	17.81	17.82	18.61	19.60	16.51	17.30	17.31	18.10	19.09
4H	2H	14.64	15.58	15.41	16.36	17.31	14.28	15.22	15.06	16.00	16.96
	3H	16.53	17.31	17.32	18.13	19.10	16.12	16.91	16.91	17.72	18.69
	4H	17.26	17.97	18.06	18.78	19.78	16.83	17.55	17.64	18.36	19.36
	6H	17.79	18.41	18.61	19.25	20.25	17.36	17.98	18.18	18.81	19.82
	8H	17.95	18.53	18.77	19.36	20.38	17.51	18.09	18.33	18.92	19.94
	12H	18.04	18.56	18.88	19.41	20.43	17.59	18.11	18.43	18.96	19.98
8H	4H	17.47	18.05	18.30	18.89	19.90	17.10	17.68	17.92	18.51	19.53
	6H	18.12	18.60	18.97	19.47	20.49	17.74	18.22	18.59	19.09	20.11
	8H	18.35	18.77	19.21	19.64	20.68	17.95	18.38	18.82	19.25	20.29
	12H	18.49	18.87	19.36	19.73	20.82	18.08	18.46	18.95	19.32	20.41
12H	4H	17.47	17.99	18.31	18.85	19.87	17.10	17.62	17.95	18.48	19.50
	6H	18.15	18.58	19.01	19.45	20.49	17.78	18.21	18.64	19.08	20.11
	8H	18.41	18.78	19.27	19.65	20.74	18.03	18.40	18.89	19.27	20.36

END OF REPORT