

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912398

Luminaire Tested: DFN2DIP-SQ4F0-140D120US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912398
REPORT IS A COMBINATION OF REPORTS P900182 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D120US850-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24974.6 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 233.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912398
CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US850-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P912398

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	43	47	45	43	39
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	34	31	29	34	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	31	28	26	31	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4503	4503	4503
5°	4510	4432	4461
10°	4465	4346	4317
15°	4403	4203	4094
20°	4322	4006	3819
25°	4239	3785	3554
30°	4127	3558	3218
35°	4017	3314	2922
40°	3906	3061	2583
45°	3776	2781	2276
50°	3642	2498	1975
55°	3502	2195	1686
60°	3340	1879	1389
65°	3154	1557	1252
70°	2928	1257	1135
75°	2644	1110	1035
80°	2234	934	903
85°	1555	628	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3776 cd/sqm



TEST NUMBER: P912398

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	601.4	2.4
10°-20°	1651.0	6.6
20°-30°	2317.9	9.3
30°-40°	2526.6	10.1
40°-50°	2322.3	9.3
50°-60°	1823.8	7.3
60°-70°	1187.1	4.8
70°-80°	611.1	2.4
80°-90°	167.9	0.7
90°-100°	260.4	1.0
100°-110°	827.5	3.3
110°-120°	1416.1	5.7
120°-130°	1862.4	7.5
130°-140°	2090.5	8.4
140°-150°	2050.0	8.2
150°-160°	1719.6	6.9
160°-170°	1140.4	4.6
170°-180°	398.6	1.6
0°-30°	4570.2	18.3
0°-40°	7096.9	28.4
0°-60°	11242.9	45.0
0°-90°	13209.0	52.9
90°-120°	2504.0	10.0
90°-150°	8506.9	34.1
90°-180°	11766.0	47.1
0°-180°	24974.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6417	6417	6417	6417	6417	
5°	6417	6388	6312	6365	6347	608
15°	6103	6039	5842	5732	5674	1720
25°	5540	5354	4971	4733	4646	2548
35°	4774	4477	3967	3601	3472	2988
45°	3902	3513	2904	2491	2352	3014
55°	2967	2514	1887	1539	1429	2651
65°	2004	1533	1010	813	795	1986
75°	1068	662	465	424	418	1130
85°	250	128	110	110	110	286
90°	4	46	124	117	120	25
95°	185	221	227	227	221	206
105°	764	774	782	788	788	806
115°	1421	1442	1435	1431	1421	1406
125°	2067	2099	2089	2077	2073	1847
135°	2674	2713	2720	2717	2706	2066
145°	3246	3271	3291	3295	3281	2028
155°	3711	3722	3733	3751	3739	1708
165°	4038	4034	4034	4059	4041	1139
175°	4201	4191	4184	4209	4187	399
180°	4209	4209	4209	4209	4209	



TEST NUMBER: P912398

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6416.9	6416.9	6416.9	6416.9	6416.9
2.5°	6445.8	6416.9	6352.8	6411.4	6399.6
5°	6416.9	6388.0	6312.1	6364.6	6347.3
7.5°	6364.6	6330.0	6248.7	6271.5	6242.6
10°	6294.9	6254.2	6138.4	6120.5	6086.0
12.5°	6208.0	6155.6	5998.5	5964.0	5900.0
15°	6103.3	6039.2	5842.0	5731.8	5673.9
17.5°	5981.3	5888.2	5644.3	5516.7	5423.7
20°	5842.0	5725.5	5435.4	5290.6	5162.5
22.5°	5691.1	5557.4	5220.4	5023.2	4936.4
25°	5540.1	5354.0	4970.9	4733.0	4645.5
27.5°	5360.2	5162.5	4738.5	4465.6	4332.0
30°	5168.6	4947.5	4482.9	4187.1	4030.0
32.5°	4982.5	4715.1	4239.5	3890.8	3745.4
35°	4773.7	4477.4	3966.6	3600.6	3472.4
37.5°	4570.4	4250.6	3710.8	3309.8	3165.0
40°	4355.4	4007.3	3443.4	3031.3	2880.4
42.5°	4134.8	3763.3	3176.7	2746.7	2601.8
45°	3902.5	3513.1	2903.8	2490.9	2351.7
47.5°	3681.9	3269.8	2642.5	2229.8	2102.2
50°	3437.9	3025.8	2386.8	1985.8	1864.3
52.5°	3199.5	2763.8	2142.8	1759.7	1649.3
55°	2967.2	2514.3	1887.2	1539.1	1428.7
57.5°	2729.4	2264.8	1661.1	1335.8	1242.7
60°	2485.4	2020.8	1422.6	1126.9	1033.8
62.5°	2247.6	1783.1	1219.3	940.8	894.6
65°	2003.6	1532.9	1010.4	813.2	795.4
67.5°	1771.3	1300.6	813.2	714.1	696.8
70°	1527.3	1074.5	673.4	615.5	592.1
72.5°	1295.1	865.0	563.2	516.9	505.3
75°	1068.3	661.7	464.6	423.9	418.3
77.5°	842.3	470.1	366.0	342.6	330.8
80°	632.8	337.0	278.5	255.7	255.7
82.5°	441.2	226.7	191.6	179.9	179.9
85°	249.5	127.5	110.2	110.2	110.2
87.5°	93.0	46.2	46.2	40.7	40.7
90°	3.8	45.7	124.3	116.8	120.5
92.5°	78.6	106.6	110.3	114.2	114.2
95°	185.2	220.8	227.1	227.1	220.8
97.5°	308.3	341.4	355.3	355.3	355.3
100°	450.5	479.6	489.7	489.7	486.0
102.5°	600.2	621.7	635.7	639.6	635.7
105°	763.9	774.0	781.6	787.9	787.9
107.5°	926.2	941.5	941.5	944.0	926.2
110°	1083.6	1103.9	1103.9	1103.9	1093.8



TEST NUMBER: P912398

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US850-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1253.6	1275.2	1271.4	1261.3	1253.6
115°	1421.1	1441.5	1435.0	1431.3	1421.1
117.5°	1587.3	1615.3	1597.5	1587.3	1577.2
120°	1754.9	1782.7	1754.9	1754.9	1743.5
122.5°	1907.1	1942.6	1924.9	1914.7	1907.1
125°	2067.0	2098.7	2088.6	2077.2	2073.3
127.5°	2223.1	2262.4	2248.4	2233.2	2223.1
130°	2368.9	2414.6	2408.3	2400.7	2386.7
132.5°	2532.6	2568.2	2570.7	2552.9	2542.8
135°	2673.5	2712.8	2720.5	2716.6	2706.5
137.5°	2830.8	2862.6	2868.9	2866.3	2851.1
140°	2969.1	3000.8	3018.6	3018.6	3004.6
142.5°	3111.3	3143.0	3153.1	3156.9	3143.0
145°	3245.7	3271.1	3291.4	3295.3	3281.3
147.5°	3366.3	3398.0	3413.3	3419.6	3405.6
150°	3490.7	3512.2	3526.2	3537.6	3526.2
152.5°	3601.0	3622.5	3640.4	3654.4	3640.4
155°	3711.4	3721.6	3733.0	3750.7	3739.3
157.5°	3806.6	3814.2	3820.5	3845.9	3828.2
160°	3891.6	3899.2	3903.0	3924.6	3909.3
162.5°	3970.2	3970.2	3974.1	3998.2	3980.4
165°	4037.5	4033.8	4033.8	4059.1	4041.3
167.5°	4098.4	4087.0	4087.0	4112.4	4094.6
170°	4144.1	4133.9	4130.1	4155.5	4133.9
172.5°	4175.8	4165.6	4161.9	4187.3	4165.6
175°	4201.2	4191.0	4183.5	4208.8	4187.3
177.5°	4215.2	4205.0	4197.3	4219.0	4197.3
180°	4208.8	4208.8	4208.8	4208.8	4208.8



TEST NUMBER: P912398
 CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.65	13.51	13.59	14.46	15.69	8.61	9.47	9.55	10.42	11.65
	3H	14.34	15.10	15.29	16.06	17.32	9.80	10.57	10.75	11.53	12.78
	4H	14.95	15.67	15.91	16.64	17.90	10.26	10.98	11.22	11.94	13.21
	6H	15.38	16.04	16.35	17.01	18.29	10.58	11.24	11.55	12.21	13.49
	8H	15.50	16.14	16.49	17.12	18.40	10.67	11.30	11.65	12.29	13.56
	12H	15.57	16.17	16.56	17.15	18.45	10.72	11.32	11.70	12.30	13.59
4H	2H	12.67	13.40	13.64	14.36	15.62	9.21	9.94	10.18	10.90	12.16
	3H	14.51	15.11	15.49	16.10	17.38	10.57	11.17	11.55	12.16	13.44
	4H	15.21	15.75	16.19	16.74	18.04	11.12	11.66	12.11	12.65	13.95
	6H	15.73	16.20	16.73	17.21	18.51	11.54	12.01	12.54	13.02	14.32
	8H	15.91	16.34	16.91	17.35	18.66	11.67	12.11	12.67	13.11	14.43
	12H	16.00	16.40	17.02	17.42	18.74	11.73	12.13	12.75	13.15	14.47
8H	4H	15.18	15.62	16.18	16.62	17.93	11.40	11.84	12.40	12.85	14.16
	6H	15.75	16.11	16.77	17.16	18.47	11.92	12.28	12.95	13.33	14.64
	8H	15.97	16.29	17.00	17.32	18.65	12.11	12.43	13.15	13.47	14.80
	12H	16.11	16.39	17.15	17.42	18.79	12.23	12.52	13.27	13.54	14.92
12H	4H	15.13	15.53	16.15	16.55	17.87	11.41	11.80	12.43	12.82	14.14
	6H	15.72	16.04	16.76	17.08	18.41	11.97	12.29	13.01	13.33	14.66
	8H	15.95	16.23	16.98	17.26	18.63	12.19	12.47	13.22	13.49	14.87