

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914915

Luminaire Tested: DFN2DIP-SQ4F0-070D140US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914915
REPORT IS A COMBINATION OF REPORTS P901708 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D140US927-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15693.1 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 167.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914915

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914915

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1608	1608	1608
5°	1611	1583	1593
10°	1595	1552	1542
15°	1573	1501	1462
20°	1544	1431	1364
25°	1514	1352	1269
30°	1474	1271	1149
35°	1435	1184	1044
40°	1395	1093	922
45°	1349	993	813
50°	1301	892	705
55°	1251	784	602
60°	1193	671	496
65°	1126	556	447
70°	1046	449	405
75°	945	396	370
80°	798	334	322
85°	555	225	246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2006 cd/sqm

TEST NUMBER: P914915

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	1.4
10°-20°	589.7	3.8
20°-30°	827.9	5.3
30°-40°	902.4	5.8
40°-50°	829.4	5.3
50°-60°	651.4	4.2
60°-70°	424.0	2.7
70°-80°	218.2	1.4
80°-90°	62.3	0.4
90°-100°	123.4	0.8
100°-110°	460.1	2.9
110°-120°	1220.2	7.8
120°-130°	2023.8	12.9
130°-140°	2149.8	13.7
140°-150°	1998.0	12.7
150°-160°	1606.3	10.2
160°-170°	1035.1	6.6
170°-180°	356.3	2.3
0°-30°	1632.3	10.4
0°-40°	2534.7	16.2
0°-60°	4015.5	25.6
0°-90°	4720.0	30.1
90°-120°	1803.7	11.5
90°-150°	7975.4	50.8
90°-180°	10973.0	69.9
0°-180°	15693.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2282	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	2	32	54	68	73	15
95°	176	86	106	119	116	208
105°	823	905	165	195	206	880
115°	1557	1603	1671	417	222	1533
125°	2202	2237	2289	2308	2316	1964
135°	2725	2768	2792	2820	2814	2105
145°	3161	3158	3204	3223	3209	1977
155°	3480	3456	3488	3505	3483	1604
165°	3667	3651	3659	3678	3659	1036
175°	3751	3732	3737	3756	3729	357
180°	3743	3743	3743	3743	3743	

TEST NUMBER: P914915

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.9	2291.9	2291.9	2291.9	2291.9
2.5°	2302.2	2291.9	2269.0	2289.9	2285.7
5°	2291.9	2281.5	2254.5	2273.2	2267.0
7.5°	2273.2	2260.8	2231.8	2239.9	2229.6
10°	2248.3	2233.8	2192.4	2186.0	2173.7
12.5°	2217.2	2198.5	2142.5	2130.1	2107.2
15°	2179.8	2157.0	2086.5	2047.2	2026.5
17.5°	2136.3	2103.1	2015.9	1970.3	1937.1
20°	2086.5	2044.9	1941.3	1889.6	1843.8
22.5°	2032.7	1984.9	1864.5	1794.1	1763.1
25°	1978.7	1912.2	1775.4	1690.4	1659.2
27.5°	1914.5	1843.8	1692.4	1595.0	1547.2
30°	1846.0	1767.0	1601.1	1495.5	1439.4
32.5°	1779.6	1684.1	1514.2	1389.6	1337.7
35°	1704.9	1599.1	1416.7	1286.0	1240.2
37.5°	1632.4	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.9	1082.7	1028.7
42.5°	1476.8	1344.1	1134.6	981.0	929.3
45°	1393.8	1254.7	1037.1	889.7	839.9
47.5°	1315.0	1167.8	943.8	796.4	750.8
50°	1227.9	1080.7	852.5	709.2	665.9
52.5°	1142.7	987.1	765.3	628.4	589.1
55°	1059.8	898.0	674.0	549.7	510.3
57.5°	974.9	808.9	593.3	477.1	443.9
60°	887.7	721.8	508.1	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.6	547.5	360.9	290.5	284.1
67.5°	632.6	464.5	290.5	255.0	248.9
70°	545.5	383.7	240.5	219.8	211.4
72.5°	462.6	309.0	201.1	184.7	180.5
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.1	45.6	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	2.5	32.5	54.0	67.9	73.0
92.5°	67.9	57.0	65.0	70.4	73.0
95°	175.9	86.5	105.5	119.3	116.5
97.5°	316.8	94.9	138.0	146.3	148.9
100°	479.5	108.4	154.4	175.9	181.4
102.5°	658.0	652.8	159.9	189.4	197.8
105°	823.3	904.7	165.3	194.9	205.8
107.5°	1015.7	1083.1	170.8	200.3	211.3
110°	1199.9	1256.6	474.0	203.3	213.9

TEST NUMBER: P914915

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1373.2	1421.8	1375.9	208.4	216.7
115°	1557.3	1603.2	1671.1	417.2	222.2
117.5°	1717.1	1771.1	1817.4	1429.9	720.4
120°	1895.9	1936.4	1985.3	2017.8	1652.1
122.5°	2047.4	2090.8	2145.1	2161.2	2164.2
125°	2201.8	2237.1	2288.6	2307.5	2315.6
127.5°	2342.6	2380.6	2421.4	2448.4	2451.0
130°	2475.4	2518.9	2548.4	2578.4	2575.8
132.5°	2610.9	2646.2	2675.8	2700.2	2697.7
135°	2724.7	2768.1	2792.2	2819.5	2814.1
137.5°	2843.7	2876.2	2903.5	2930.5	2922.5
140°	2960.1	2982.0	3011.6	3036.0	3022.5
142.5°	3057.9	3076.8	3111.9	3133.5	3119.9
145°	3160.8	3157.9	3203.9	3222.9	3209.4
147.5°	3249.9	3241.8	3287.9	3301.3	3290.7
150°	3336.7	3317.7	3361.1	3377.2	3363.8
152.5°	3409.7	3388.2	3428.7	3445.1	3426.1
155°	3480.1	3456.0	3488.5	3504.6	3483.1
157.5°	3537.1	3515.5	3540.0	3559.0	3537.1
160°	3586.0	3569.6	3586.0	3602.0	3583.1
162.5°	3629.1	3613.0	3626.5	3645.5	3621.1
165°	3667.0	3650.9	3659.0	3677.9	3659.0
167.5°	3697.0	3680.6	3688.9	3707.9	3683.4
170°	3721.4	3705.0	3710.4	3729.4	3705.0
172.5°	3737.4	3721.4	3726.8	3745.8	3721.4
175°	3751.0	3732.0	3737.4	3756.4	3729.4
177.5°	3756.4	3737.4	3740.4	3759.3	3734.9
180°	3742.9	3742.9	3742.9	3742.9	3742.9

TEST NUMBER: P914915

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.59	7.28	7.71	8.39	9.92	2.55	3.24	3.67	4.35	5.88
	3H	8.26	8.88	9.38	9.99	11.54	3.73	4.35	4.85	5.46	7.01
	4H	8.86	9.45	10.00	10.57	12.12	4.17	4.76	5.31	5.87	7.43
	6H	9.28	9.82	10.43	10.94	12.51	4.49	5.03	5.63	6.14	7.71
	8H	9.41	9.92	10.55	11.05	12.61	4.57	5.09	5.72	6.22	7.78
	12H	9.47	9.95	10.62	11.08	12.66	4.61	5.10	5.76	6.23	7.81
4H	2H	6.59	7.18	7.73	8.29	9.85	3.13	3.72	4.27	4.83	6.39
	3H	8.41	8.90	9.56	10.04	11.61	4.47	4.96	5.62	6.10	7.66
	4H	9.10	9.55	10.25	10.68	12.27	5.01	5.46	6.16	6.59	8.18
	6H	9.61	10.00	10.77	11.15	12.73	5.42	5.81	6.58	6.96	8.54
	8H	9.79	10.15	10.94	11.29	12.88	5.55	5.91	6.70	7.05	8.65
	12H	9.88	10.20	11.05	11.36	12.96	5.61	5.93	6.78	7.09	8.69
8H	4H	9.06	9.42	10.21	10.56	12.15	5.28	5.64	6.44	6.79	8.38
	6H	9.62	9.92	10.80	11.11	12.70	5.80	6.09	6.97	7.28	8.87
	8H	9.84	10.10	11.02	11.27	12.88	5.99	6.25	7.17	7.41	9.02
	12H	9.98	10.20	11.16	11.37	13.01	6.10	6.33	7.29	7.49	9.14
12H	4H	9.00	9.33	10.17	10.49	12.08	5.28	5.61	6.45	6.76	8.36
	6H	9.60	9.86	10.78	11.02	12.63	5.85	6.11	7.03	7.27	8.88
	8H	9.82	10.04	11.00	11.21	12.85	6.05	6.28	7.24	7.44	9.09

END OF REPORT