

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915007

Luminaire Tested: DFN2DIP-SQ4F0-100D090US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915007
REPORT IS A COMBINATION OF REPORTS P901642 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D090US927-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13791.8 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 159.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915007

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915007

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	35	30	51	40	33	29	35	29	26	30	26	22	25	22	19
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2297	2297	2297
5°	2301	2261	2276
10°	2278	2217	2203
15°	2247	2145	2089
20°	2205	2044	1949
25°	2163	1931	1814
30°	2106	1815	1642
35°	2050	1691	1491
40°	1993	1562	1318
45°	1927	1419	1161
50°	1858	1275	1008
55°	1787	1120	860
60°	1704	959	709
65°	1609	795	639
70°	1494	641	579
75°	1349	566	528
80°	1139	477	461
85°	793	320	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1927 cd/sqm

TEST NUMBER: P915007

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.9	2.2
10°-20°	842.4	6.1
20°-30°	1182.6	8.6
30°-40°	1289.2	9.3
40°-50°	1184.9	8.6
50°-60°	930.5	6.7
60°-70°	605.7	4.4
70°-80°	311.8	2.3
80°-90°	83.8	0.6
90°-100°	79.3	0.6
100°-110°	295.8	2.1
110°-120°	784.4	5.7
120°-130°	1301.0	9.4
130°-140°	1382.0	10.0
140°-150°	1284.4	9.3
150°-160°	1032.6	7.5
160°-170°	665.4	4.8
170°-180°	229.0	1.7
0°-30°	2331.9	16.9
0°-40°	3621.0	26.3
0°-60°	5736.5	41.6
0°-90°	6737.8	48.9
90°-120°	1159.5	8.4
90°-150°	5127.0	37.2
90°-180°	7054.0	51.1
0°-180°	13791.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3274	3274	3274	3274	3274	
5°	3274	3259	3221	3247	3238	310
15°	3114	3081	2981	2924	2895	878
25°	2827	2732	2536	2415	2370	1300
35°	2436	2284	2024	1837	1772	1524
45°	1991	1792	1482	1271	1200	1538
55°	1514	1283	963	785	729	1353
65°	1022	782	516	415	406	1014
75°	545	338	237	216	213	577
85°	127	65	56	56	56	146
90°	2	21	35	44	47	13
95°	113	56	68	77	75	134
105°	529	582	106	125	132	566
115°	1001	1031	1074	268	143	986
125°	1415	1438	1471	1483	1489	1262
135°	1752	1780	1795	1813	1809	1353
145°	2032	2030	2060	2072	2063	1271
155°	2237	2222	2243	2253	2239	1031
165°	2357	2347	2352	2364	2352	666
175°	2411	2399	2403	2415	2398	229
180°	2406	2406	2406	2406	2406	

TEST NUMBER: P915007

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3274.1	3274.1	3274.1	3274.1	3274.1
2.5°	3288.8	3274.1	3241.4	3271.2	3265.3
5°	3274.1	3259.3	3220.6	3247.4	3238.5
7.5°	3247.4	3229.7	3188.2	3199.9	3185.1
10°	3211.8	3191.1	3132.0	3122.9	3105.3
12.5°	3167.5	3140.8	3060.6	3043.0	3010.3
15°	3114.1	3081.3	2980.7	2924.5	2894.9
17.5°	3051.8	3004.3	2879.9	2814.8	2767.3
20°	2980.7	2921.3	2773.3	2699.4	2634.0
22.5°	2903.7	2835.5	2663.6	2563.0	2518.7
25°	2826.7	2731.8	2536.2	2414.9	2370.3
27.5°	2734.9	2634.0	2417.7	2278.5	2210.3
30°	2637.2	2524.3	2287.3	2136.4	2056.3
32.5°	2542.3	2405.8	2163.1	1985.2	1911.0
35°	2435.6	2284.5	2023.9	1837.1	1771.7
37.5°	2331.9	2168.8	1893.4	1688.8	1614.9
40°	2222.2	2044.6	1757.0	1546.7	1469.7
42.5°	2109.7	1920.1	1620.9	1401.4	1327.5
45°	1991.1	1792.5	1481.6	1271.0	1199.9
47.5°	1878.7	1668.3	1348.3	1137.7	1072.6
50°	1754.1	1543.8	1217.8	1013.2	951.3
52.5°	1632.4	1410.2	1093.4	897.8	841.5
55°	1513.9	1282.9	962.9	785.3	729.0
57.5°	1392.7	1155.6	847.6	681.5	634.1
60°	1268.1	1031.1	725.9	575.0	527.5
62.5°	1146.8	909.7	622.1	480.1	456.5
65°	1022.3	782.1	515.6	414.9	405.8
67.5°	903.8	663.6	414.9	364.3	355.5
70°	779.3	548.3	343.6	314.0	302.1
72.5°	660.8	441.3	287.3	263.7	257.8
75°	545.1	337.6	237.0	216.3	213.4
77.5°	429.8	239.9	186.7	174.8	168.8
80°	322.8	172.0	142.1	130.5	130.5
82.5°	225.1	115.7	97.8	91.8	91.8
85°	127.3	65.0	56.2	56.2	56.2
87.5°	47.5	23.6	23.6	20.8	20.8
90°	1.7	20.9	34.7	43.6	46.9
92.5°	43.6	36.6	41.7	45.3	46.9
95°	113.1	55.6	67.8	76.7	74.9
97.5°	203.7	61.0	88.7	94.0	95.7
100°	308.2	69.7	99.3	113.1	116.6
102.5°	423.0	419.7	102.7	121.8	127.1
105°	529.3	581.6	106.2	125.3	132.3
107.5°	652.9	696.3	109.8	128.8	135.9
110°	771.3	807.8	304.8	130.6	137.5

TEST NUMBER: P915007

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	882.8	914.0	884.5	134.0	139.3
115°	1001.1	1030.6	1074.3	268.2	142.8
117.5°	1103.8	1138.6	1168.3	919.2	463.1
120°	1218.8	1244.8	1276.3	1297.1	1062.1
122.5°	1316.2	1344.1	1379.0	1389.3	1391.2
125°	1415.4	1438.1	1471.2	1483.4	1488.6
127.5°	1505.9	1530.3	1556.6	1574.0	1575.6
130°	1591.3	1619.3	1638.3	1657.5	1655.9
132.5°	1678.4	1701.1	1720.1	1735.9	1734.2
135°	1751.6	1779.5	1795.0	1812.6	1809.1
137.5°	1828.1	1849.0	1866.5	1883.9	1878.7
140°	1902.9	1917.0	1936.0	1951.7	1943.1
142.5°	1965.8	1978.0	2000.5	2014.4	2005.7
145°	2031.9	2030.0	2059.7	2071.9	2063.2
147.5°	2089.2	2084.1	2113.6	2122.3	2115.4
150°	2145.1	2132.9	2160.8	2171.1	2162.4
152.5°	2192.0	2178.1	2204.2	2214.7	2202.5
155°	2237.3	2221.8	2242.6	2253.0	2239.1
157.5°	2273.9	2260.0	2275.7	2287.9	2273.9
160°	2305.2	2294.7	2305.2	2315.6	2303.4
162.5°	2333.0	2322.6	2331.3	2343.5	2327.8
165°	2357.4	2347.0	2352.2	2364.4	2352.2
167.5°	2376.6	2366.1	2371.4	2383.6	2367.9
170°	2392.3	2381.8	2385.3	2397.5	2381.8
172.5°	2402.7	2392.3	2395.8	2408.0	2392.3
175°	2411.3	2399.1	2402.7	2414.8	2397.5
177.5°	2414.8	2402.7	2404.5	2416.7	2401.0
180°	2406.2	2406.2	2406.2	2406.2	2406.2

TEST NUMBER: P915007

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.94	10.76	10.91	11.74	13.04	5.90	6.72	6.88	7.71	9.00
	3H	11.62	12.36	12.61	13.35	14.66	7.09	7.82	8.07	8.82	10.13
	4H	12.23	12.93	13.23	13.92	15.24	7.54	8.23	8.54	9.23	10.55
	6H	12.66	13.30	13.67	14.30	15.63	7.86	8.50	8.87	9.50	10.83
	8H	12.79	13.39	13.80	14.41	15.74	7.95	8.56	8.97	9.58	10.91
	12H	12.85	13.43	13.87	14.44	15.79	8.00	8.57	9.01	9.58	10.94
4H	2H	9.96	10.65	10.96	11.65	12.97	6.50	7.19	7.50	8.19	9.51
	3H	11.79	12.37	12.80	13.39	14.73	7.85	8.43	8.86	9.45	10.78
	4H	12.49	13.01	13.51	14.03	15.39	8.40	8.92	9.42	9.94	11.30
	6H	13.01	13.46	14.04	14.50	15.85	8.82	9.27	9.85	10.31	11.66
	8H	13.18	13.61	14.22	14.64	16.01	8.95	9.37	9.98	10.40	11.77
	12H	13.28	13.66	14.33	14.71	16.08	9.01	9.39	10.06	10.44	11.81
8H	4H	12.45	12.88	13.49	13.91	15.28	8.68	9.10	9.71	10.13	11.50
	6H	13.02	13.37	14.08	14.45	15.81	9.20	9.55	10.25	10.62	11.99
	8H	13.24	13.55	14.31	14.61	16.00	9.39	9.70	10.45	10.76	12.14
	12H	13.39	13.66	14.45	14.71	16.14	9.51	9.78	10.58	10.83	12.26
12H	4H	12.41	12.79	13.46	13.84	15.21	8.68	9.07	9.73	10.11	11.49
	6H	13.00	13.31	14.06	14.37	15.75	9.25	9.56	10.31	10.62	12.00
	8H	13.22	13.49	14.29	14.55	15.98	9.46	9.73	10.53	10.78	12.21

END OF REPORT