

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915026

Luminaire Tested: DFN2DIP-SQ4F0-100D160US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915026
REPORT IS A COMBINATION OF REPORTS P900212 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D160US927-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17951.6 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 214.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915026

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P915026

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2297	2297	2297
5°	2301	2261	2276
10°	2278	2217	2203
15°	2247	2145	2089
20°	2205	2044	1949
25°	2163	1931	1814
30°	2106	1815	1642
35°	2050	1691	1491
40°	1993	1562	1318
45°	1927	1419	1161
50°	1858	1275	1008
55°	1787	1120	860
60°	1704	959	709
65°	1609	795	639
70°	1494	641	579
75°	1349	566	528
80°	1139	477	461
85°	793	320	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3155 cd/sqm

TEST NUMBER: P915026

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.9	1.7
10°-20°	842.4	4.7
20°-30°	1182.6	6.6
30°-40°	1289.2	7.2
40°-50°	1184.9	6.6
50°-60°	930.5	5.2
60°-70°	605.7	3.4
70°-80°	311.8	1.7
80°-90°	91.0	0.5
90°-100°	248.1	1.4
100°-110°	788.2	4.4
110°-120°	1348.9	7.5
120°-130°	1774.0	9.9
130°-140°	1991.2	11.1
140°-150°	1952.6	10.9
150°-160°	1637.9	9.1
160°-170°	1086.2	6.1
170°-180°	379.7	2.1
0°-30°	2331.9	13.0
0°-40°	3621.0	20.2
0°-60°	5736.5	32.0
0°-90°	6744.9	37.6
90°-120°	2385.1	13.3
90°-150°	8102.8	45.1
90°-180°	11207.0	62.4
0°-180°	17951.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3274	3274	3274	3274	3274	
5°	3274	3259	3221	3247	3238	310
15°	3114	3081	2981	2924	2895	878
25°	2827	2732	2536	2415	2370	1300
35°	2436	2284	2024	1837	1772	1524
45°	1991	1792	1482	1271	1200	1538
55°	1514	1283	963	785	729	1353
65°	1022	782	516	415	406	1014
75°	545	338	237	216	213	577
85°	127	65	56	56	56	146
90°	4	44	118	111	115	18
95°	176	210	216	216	210	196
105°	728	737	744	750	750	768
115°	1354	1373	1367	1363	1354	1339
125°	1969	1999	1989	1978	1975	1759
135°	2546	2584	2591	2588	2578	1968
145°	3092	3116	3135	3139	3125	1932
155°	3535	3545	3556	3573	3562	1627
165°	3846	3842	3842	3866	3849	1085
175°	4002	3992	3985	4009	3988	380
180°	4009	4009	4009	4009	4009	

TEST NUMBER: P915026

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3274.1	3274.1	3274.1	3274.1	3274.1
2.5°	3288.8	3274.1	3241.4	3271.2	3265.3
5°	3274.1	3259.3	3220.6	3247.4	3238.5
7.5°	3247.4	3229.7	3188.2	3199.9	3185.1
10°	3211.8	3191.1	3132.0	3122.9	3105.3
12.5°	3167.5	3140.8	3060.6	3043.0	3010.3
15°	3114.1	3081.3	2980.7	2924.5	2894.9
17.5°	3051.8	3004.3	2879.9	2814.8	2767.3
20°	2980.7	2921.3	2773.3	2699.4	2634.0
22.5°	2903.7	2835.5	2663.6	2563.0	2518.7
25°	2826.7	2731.8	2536.2	2414.9	2370.3
27.5°	2734.9	2634.0	2417.7	2278.5	2210.3
30°	2637.2	2524.3	2287.3	2136.4	2056.3
32.5°	2542.3	2405.8	2163.1	1985.2	1911.0
35°	2435.6	2284.5	2023.9	1837.1	1771.7
37.5°	2331.9	2168.8	1893.4	1688.8	1614.9
40°	2222.2	2044.6	1757.0	1546.7	1469.7
42.5°	2109.7	1920.1	1620.9	1401.4	1327.5
45°	1991.1	1792.5	1481.6	1271.0	1199.9
47.5°	1878.7	1668.3	1348.3	1137.7	1072.6
50°	1754.1	1543.8	1217.8	1013.2	951.3
52.5°	1632.4	1410.2	1093.4	897.8	841.5
55°	1513.9	1282.9	962.9	785.3	729.0
57.5°	1392.7	1155.6	847.6	681.5	634.1
60°	1268.1	1031.1	725.9	575.0	527.5
62.5°	1146.8	909.7	622.1	480.1	456.5
65°	1022.3	782.1	515.6	414.9	405.8
67.5°	903.8	663.6	414.9	364.3	355.5
70°	779.3	548.3	343.6	314.0	302.1
72.5°	660.8	441.3	287.3	263.7	257.8
75°	545.1	337.6	237.0	216.3	213.4
77.5°	429.8	239.9	186.7	174.8	168.8
80°	322.8	172.0	142.1	130.5	130.5
82.5°	225.1	115.7	97.8	91.8	91.8
85°	127.3	65.0	56.2	56.2	56.2
87.5°	47.5	23.6	23.6	20.8	20.8
90°	3.6	43.5	118.4	111.2	114.8
92.5°	74.9	101.6	105.1	108.8	108.8
95°	176.4	210.3	216.3	216.3	210.3
97.5°	293.7	325.1	338.4	338.4	338.4
100°	429.0	456.9	466.5	466.5	462.9
102.5°	571.6	592.2	605.5	609.1	605.5
105°	727.5	737.2	744.5	750.5	750.5
107.5°	882.3	896.7	896.7	899.2	882.3
110°	1032.1	1051.5	1051.5	1051.5	1041.8

TEST NUMBER: P915026

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1194.1	1214.7	1211.0	1201.3	1194.1
115°	1353.6	1372.9	1366.9	1363.3	1353.6
117.5°	1512.0	1538.5	1521.6	1512.0	1502.3
120°	1671.5	1698.0	1671.5	1671.5	1660.6
122.5°	1816.5	1850.4	1833.4	1823.8	1816.5
125°	1968.8	1999.0	1989.3	1978.5	1974.8
127.5°	2117.4	2154.9	2141.6	2127.1	2117.4
130°	2256.4	2299.9	2293.9	2286.6	2273.3
132.5°	2412.4	2446.2	2448.6	2431.7	2422.0
135°	2546.5	2583.9	2591.2	2587.6	2577.9
137.5°	2696.3	2726.5	2732.6	2730.2	2715.7
140°	2828.1	2858.3	2875.2	2875.2	2861.9
142.5°	2963.5	2993.7	3003.3	3007.0	2993.7
145°	3091.6	3115.7	3135.1	3138.7	3125.4
147.5°	3206.4	3236.6	3251.1	3257.1	3243.8
150°	3324.8	3345.4	3358.7	3369.5	3358.7
152.5°	3430.0	3450.5	3467.5	3480.7	3467.5
155°	3535.1	3544.8	3555.6	3572.6	3561.7
157.5°	3625.7	3633.0	3639.0	3663.2	3646.3
160°	3706.7	3714.0	3717.6	3738.1	3723.6
162.5°	3781.6	3781.6	3785.3	3808.3	3791.3
165°	3845.7	3842.1	3842.1	3866.2	3849.4
167.5°	3903.7	3892.9	3892.9	3917.0	3900.1
170°	3947.2	3937.5	3934.0	3958.1	3937.5
172.5°	3977.5	3967.8	3964.2	3988.3	3967.8
175°	4001.6	3992.0	3984.7	4008.9	3988.3
177.5°	4014.9	4005.3	3998.0	4018.6	3998.0
180°	4008.9	4008.9	4008.9	4008.9	4008.9

TEST NUMBER: P915026

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.76	9.50	9.83	10.56	12.00	4.72	5.46	5.79	6.52	7.96
	3H	10.44	11.10	11.51	12.17	13.63	5.91	6.57	6.98	7.64	9.10
	4H	11.05	11.67	12.13	12.74	14.21	6.35	6.98	7.44	8.05	9.52
	6H	11.47	12.04	12.56	13.12	14.59	6.67	7.24	7.76	8.32	9.80
	8H	11.59	12.14	12.69	13.23	14.70	6.76	7.30	7.85	8.40	9.87
	12H	11.65	12.17	12.75	13.26	14.75	6.80	7.32	7.90	8.40	9.90
4H	2H	8.77	9.40	9.86	10.47	11.93	5.31	5.94	6.40	7.01	8.47
	3H	10.60	11.12	11.69	12.22	13.69	6.65	7.17	7.75	8.27	9.75
	4H	11.29	11.76	12.39	12.85	14.35	7.20	7.68	8.30	8.76	10.26
	6H	11.80	12.21	12.91	13.32	14.82	7.61	8.02	8.72	9.13	10.63
	8H	11.98	12.36	13.09	13.46	14.97	7.74	8.12	8.85	9.23	10.74
	12H	12.07	12.42	13.20	13.53	15.05	7.80	8.15	8.93	9.26	10.78
8H	4H	11.25	11.63	12.36	12.74	14.24	7.47	7.86	8.58	8.96	10.47
	6H	11.82	12.13	12.95	13.28	14.78	7.99	8.31	9.12	9.45	10.96
	8H	12.04	12.31	13.17	13.44	14.96	8.18	8.46	9.32	9.59	11.11
	12H	12.17	12.42	13.31	13.54	15.10	8.30	8.54	9.44	9.66	11.23
12H	4H	11.20	11.54	12.32	12.66	14.17	7.48	7.82	8.60	8.94	10.45
	6H	11.79	12.07	12.93	13.19	14.72	8.04	8.32	9.18	9.44	10.97
	8H	12.01	12.25	13.15	13.38	14.94	8.25	8.49	9.39	9.61	11.18