

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915030

Luminaire Tested: DFN2DIP-SQ4F0-110D060US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915030
REPORT IS A COMBINATION OF REPORTS P900070 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D060US927-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11613.4 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 150.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915030

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P915030

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	94	90	95	92	88	85	81	78	76	71	69	67	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	40	37	34
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2527	2527	2527
5°	2531	2487	2504
10°	2506	2439	2423
15°	2471	2359	2298
20°	2426	2248	2144
25°	2379	2124	1995
30°	2316	1997	1806
35°	2255	1860	1640
40°	2192	1718	1450
45°	2119	1561	1277
50°	2044	1402	1109
55°	1966	1232	946
60°	1875	1054	780
65°	1770	874	703
70°	1643	705	637
75°	1484	623	581
80°	1253	524	507
85°	873	353	386

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2119 cd/sqm

TEST NUMBER: P915030

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.5	2.9
10°-20°	926.6	8.0
20°-30°	1300.9	11.2
30°-40°	1418.1	12.2
40°-50°	1303.4	11.2
50°-60°	1023.6	8.8
60°-70°	666.3	5.7
70°-80°	343.0	3.0
80°-90°	91.8	0.8
90°-100°	93.0	0.8
100°-110°	295.6	2.5
110°-120°	505.8	4.4
120°-130°	665.2	5.7
130°-140°	746.6	6.4
140°-150°	732.2	6.3
150°-160°	614.2	5.3
160°-170°	407.3	3.5
170°-180°	142.4	1.2
0°-30°	2565.1	22.1
0°-40°	3983.1	34.3
0°-60°	6310.1	54.3
0°-90°	7411.2	63.8
90°-120°	894.4	7.7
90°-150°	3038.4	26.2
90°-180°	4202.0	36.2
0°-180°	11613.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3602	3602	3602	3602	3602	
5°	3602	3585	3543	3572	3562	341
15°	3426	3390	3279	3217	3184	965
25°	3109	3005	2790	2656	2607	1430
35°	2679	2513	2226	2021	1949	1677
45°	2190	1972	1630	1398	1320	1691
55°	1665	1411	1059	864	802	1488
65°	1124	860	567	456	446	1115
75°	600	371	261	238	235	634
85°	140	72	62	62	62	161
90°	1	16	44	42	43	11
95°	66	79	81	81	79	74
105°	273	276	279	282	282	288
115°	508	515	512	511	508	502
125°	738	750	746	742	740	660
135°	955	969	972	970	967	738
145°	1159	1168	1176	1177	1172	724
155°	1326	1329	1333	1340	1336	610
165°	1442	1441	1441	1450	1443	407
175°	1500	1497	1494	1503	1496	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P915030

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3601.5	3601.5	3601.5	3601.5	3601.5
2.5°	3617.7	3601.5	3565.5	3598.4	3591.8
5°	3601.5	3585.3	3542.7	3572.1	3562.4
7.5°	3572.1	3552.7	3507.1	3519.9	3503.6
10°	3533.0	3510.2	3445.2	3435.1	3415.8
12.5°	3484.3	3454.9	3366.7	3347.3	3311.3
15°	3425.5	3389.5	3278.8	3217.0	3184.4
17.5°	3357.0	3304.8	3167.9	3096.2	3044.0
20°	3278.8	3213.5	3050.6	2969.3	2897.4
22.5°	3194.2	3119.1	2930.0	2819.3	2770.5
25°	3109.4	3005.0	2789.9	2656.4	2607.3
27.5°	3008.5	2897.4	2659.5	2506.3	2431.3
30°	2900.9	2776.8	2516.0	2350.0	2261.8
32.5°	2796.5	2646.4	2379.4	2183.7	2102.1
35°	2679.2	2512.9	2226.3	2020.9	1948.9
37.5°	2565.2	2385.7	2082.7	1857.6	1776.4
40°	2444.4	2249.1	1932.7	1701.3	1616.6
42.5°	2320.6	2112.1	1783.0	1541.6	1460.3
45°	2190.3	1971.7	1629.8	1398.0	1319.9
47.5°	2066.5	1835.2	1483.1	1251.4	1179.9
50°	1929.5	1698.2	1339.7	1114.5	1046.4
52.5°	1795.7	1551.2	1202.7	987.6	925.7
55°	1665.3	1411.2	1059.1	863.8	801.9
57.5°	1531.9	1271.1	932.2	749.7	697.4
60°	1395.0	1134.2	798.4	632.5	580.3
62.5°	1261.5	1000.8	684.4	528.1	502.1
65°	1124.5	860.3	567.1	456.5	446.4
67.5°	994.2	730.0	456.5	400.8	391.1
70°	857.2	603.1	377.9	345.5	332.3
72.5°	726.8	485.5	316.1	290.1	283.5
75°	599.6	371.4	260.7	237.9	234.8
77.5°	472.7	263.9	205.4	192.3	185.7
80°	355.1	189.2	156.3	143.5	143.5
82.5°	247.6	127.2	107.6	101.0	101.0
85°	140.1	71.6	61.9	61.9	61.9
87.5°	52.2	25.9	25.9	22.8	22.8
90°	1.3	16.3	44.4	41.7	43.0
92.5°	28.1	38.1	39.5	40.8	40.8
95°	66.1	78.8	81.1	81.1	78.8
97.5°	110.1	121.9	126.9	126.9	126.9
100°	160.9	171.3	174.9	174.9	173.6
102.5°	214.4	222.0	227.0	228.4	227.0
105°	272.8	276.5	279.2	281.5	281.5
107.5°	330.8	336.3	336.3	337.2	330.8
110°	387.1	394.3	394.3	394.3	390.6

TEST NUMBER: P915030

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US927-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	447.7	455.4	454.1	450.4	447.7
115°	507.6	514.8	512.5	511.2	507.6
117.5°	567.0	576.9	570.5	567.0	563.3
120°	626.8	636.8	626.8	626.8	622.7
122.5°	681.1	693.8	687.5	683.9	681.1
125°	738.2	749.6	745.9	741.9	740.5
127.5°	794.0	808.0	803.0	797.6	794.0
130°	846.1	862.4	860.2	857.5	852.5
132.5°	904.6	917.3	918.1	911.8	908.2
135°	954.9	968.9	971.6	970.3	966.6
137.5°	1011.1	1022.4	1024.7	1023.7	1018.3
140°	1060.5	1071.8	1078.2	1078.2	1073.2
142.5°	1111.2	1122.5	1126.2	1127.5	1122.5
145°	1159.3	1168.3	1175.6	1176.9	1172.0
147.5°	1202.3	1213.6	1219.1	1221.3	1216.3
150°	1246.7	1254.4	1259.4	1263.4	1259.4
152.5°	1286.1	1293.9	1300.2	1305.2	1300.2
155°	1325.6	1329.2	1333.2	1339.7	1335.5
157.5°	1359.5	1362.3	1364.5	1373.6	1367.3
160°	1390.0	1392.7	1394.0	1401.7	1396.3
162.5°	1418.0	1418.0	1419.4	1428.0	1421.6
165°	1442.0	1440.7	1440.7	1449.8	1443.4
167.5°	1463.8	1459.8	1459.8	1468.8	1462.4
170°	1480.1	1476.5	1475.1	1484.2	1476.5
172.5°	1491.4	1487.8	1486.4	1495.5	1487.8
175°	1500.5	1496.9	1494.1	1503.2	1495.5
177.5°	1505.5	1501.9	1499.1	1506.8	1499.1
180°	1503.2	1503.2	1503.2	1503.2	1503.2

TEST NUMBER: P915030

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.58	12.54	12.42	13.39	14.45	7.54	8.50	8.38	9.35	10.41
	3H	13.27	14.13	14.12	14.99	16.08	8.74	9.60	9.59	10.46	11.55
	4H	13.89	14.70	14.76	15.57	16.67	9.20	10.00	10.06	10.87	11.97
	6H	14.32	15.07	15.20	15.94	17.06	9.52	10.27	10.40	11.15	12.26
	8H	14.45	15.16	15.34	16.06	17.17	9.62	10.33	10.51	11.22	12.33
	12H	14.52	15.19	15.41	16.08	17.22	9.67	10.34	10.56	11.23	12.37
4H	2H	11.61	12.42	12.48	13.29	14.39	8.15	8.96	9.02	9.83	10.93
	3H	13.46	14.13	14.34	15.03	16.15	9.52	10.19	10.40	11.09	12.21
	4H	14.16	14.77	15.05	15.67	16.81	10.07	10.68	10.96	11.58	12.72
	6H	14.69	15.21	15.59	16.13	17.28	10.50	11.02	11.41	11.95	13.09
	8H	14.87	15.36	15.78	16.27	17.43	10.63	11.12	11.54	12.04	13.19
	12H	14.97	15.41	15.90	16.35	17.51	10.70	11.14	11.63	12.08	13.24
8H	4H	14.14	14.63	15.05	15.55	16.70	10.36	10.85	11.27	11.77	12.93
	6H	14.71	15.12	15.65	16.08	17.23	10.89	11.29	11.82	12.25	13.41
	8H	14.93	15.29	15.88	16.24	17.42	11.08	11.44	12.03	12.39	13.56
	12H	15.08	15.40	16.03	16.34	17.56	11.21	11.52	12.15	12.46	13.69
12H	4H	14.10	14.54	15.02	15.47	16.63	10.37	10.82	11.30	11.75	12.91
	6H	14.69	15.05	15.64	16.00	17.17	10.94	11.30	11.88	12.25	13.42
	8H	14.92	15.23	15.87	16.18	17.40	11.16	11.47	12.10	12.41	13.64

END OF REPORT