

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920481

Luminaire Tested: DFN2DIP-SQ4F0-100D160US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920481
REPORT IS A COMBINATION OF REPORTS P901731 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D160US935-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22162.1 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 214.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920481

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920481

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2351	2351	2351
5°	2354	2318	2334
10°	2335	2288	2303
15°	2301	2250	2255
20°	2254	2199	2205
25°	2208	2137	2147
30°	2150	2079	2073
35°	2096	2011	1995
40°	2028	1942	1921
45°	1961	1873	1845
50°	1887	1800	1758
55°	1810	1717	1677
60°	1723	1617	1585
65°	1628	1514	1476
70°	1507	1389	1359
75°	1339	1239	1252
80°	1138	1048	1046
85°	822	717	703

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2493 cd/sqm

TEST NUMBER: P920481

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.3	1.4
10°-20°	887.2	4.0
20°-30°	1303.8	5.9
30°-40°	1514.3	6.8
40°-50°	1512.4	6.8
50°-60°	1318.8	6.0
60°-70°	974.9	4.4
70°-80°	551.6	2.5
80°-90°	153.8	0.7
90°-100°	153.3	0.7
100°-110°	571.5	2.6
110°-120°	1515.7	6.8
120°-130°	2513.9	11.3
130°-140°	2670.3	12.0
140°-150°	2481.8	11.2
150°-160°	1995.3	9.0
160°-170°	1285.7	5.8
170°-180°	442.5	2.0
0°-30°	2506.3	11.3
0°-40°	4020.6	18.1
0°-60°	6851.8	30.9
0°-90°	8532.1	38.5
90°-120°	2240.5	10.1
90°-150°	9906.5	44.7
90°-180°	13630.0	61.5
0°-180°	22162.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3350	3350	3350	3350	3350	
5°	3350	3338	3302	3328	3322	318
15°	3189	3170	3128	3141	3125	898
25°	2886	2861	2806	2812	2806	1328
35°	2490	2458	2406	2387	2371	1555
45°	2026	2004	1955	1920	1907	1564
55°	1534	1514	1476	1437	1421	1371
65°	1034	1015	983	954	938	1023
75°	541	535	518	499	506	578
85°	132	129	126	116	113	147
90°	3	40	67	84	91	20
95°	218	108	131	148	145	259
105°	1023	1124	205	242	256	1093
115°	1934	1991	2076	518	276	1904
125°	2735	2779	2843	2866	2876	2439
135°	3384	3438	3468	3502	3496	2614
145°	3926	3922	3980	4003	3986	2456
155°	4323	4293	4333	4353	4326	1992
165°	4555	4535	4545	4568	4545	1287
175°	4659	4636	4642	4666	4632	443
180°	4649	4649	4649	4649	4649	

TEST NUMBER: P920481

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3350.2	3350.2	3350.2	3350.2	3350.2
2.5°	3369.7	3353.6	3318.0	3350.2	3344.0
5°	3350.2	3337.6	3302.0	3327.7	3321.5
7.5°	3327.7	3308.5	3272.9	3298.9	3292.5
10°	3292.5	3269.9	3231.2	3256.9	3247.3
12.5°	3243.9	3224.8	3186.1	3202.2	3195.7
15°	3189.2	3170.1	3128.0	3141.0	3125.0
17.5°	3121.5	3102.4	3060.3	3076.4	3060.3
20°	3047.3	3028.2	2983.1	2992.7	2980.0
22.5°	2973.5	2944.5	2902.4	2902.4	2896.0
25°	2886.4	2860.8	2806.1	2812.2	2806.1
27.5°	2789.6	2767.1	2725.4	2715.8	2699.7
30°	2693.3	2667.3	2619.1	2609.5	2596.5
32.5°	2590.1	2570.9	2519.3	2499.8	2486.8
35°	2490.3	2458.1	2406.5	2387.0	2370.9
37.5°	2377.5	2348.4	2296.8	2274.2	2258.1
40°	2261.6	2235.6	2184.0	2155.3	2142.3
42.5°	2148.8	2122.8	2071.6	2039.1	2020.0
45°	2026.4	2003.9	1955.3	1920.1	1907.2
47.5°	1907.2	1884.6	1833.0	1797.4	1778.3
50°	1781.4	1765.3	1720.2	1675.1	1659.1
52.5°	1659.1	1636.5	1594.7	1559.3	1536.7
55°	1533.6	1514.2	1475.5	1436.8	1420.8
57.5°	1407.8	1391.7	1349.7	1311.1	1298.1
60°	1282.0	1269.4	1224.3	1188.7	1179.1
62.5°	1159.7	1137.1	1105.0	1072.9	1059.9
65°	1034.2	1014.8	982.7	953.6	937.5
67.5°	905.4	889.0	860.3	837.8	824.7
70°	786.1	773.1	744.1	721.5	708.9
72.5°	663.7	650.7	634.7	612.2	602.5
75°	541.1	534.9	518.5	499.4	505.8
77.5°	431.7	418.7	412.2	402.6	393.0
80°	322.3	318.9	312.4	302.8	296.4
82.5°	219.1	219.1	216.0	203.0	203.0
85°	131.9	128.9	125.8	115.9	112.8
87.5°	58.1	51.6	45.1	35.6	32.1
90°	3.2	40.4	67.1	84.3	90.7
92.5°	84.3	70.7	80.7	87.5	90.7
95°	218.5	107.5	131.0	148.2	144.6
97.5°	393.5	117.9	171.3	181.8	184.9
100°	595.6	134.7	191.7	218.5	225.3
102.5°	817.3	811.0	198.5	235.3	245.6
105°	1022.7	1123.8	205.3	242.1	255.6
107.5°	1261.5	1345.5	212.1	248.9	262.4
110°	1490.5	1560.8	588.8	252.4	265.6

TEST NUMBER: P920481

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1705.8	1766.2	1709.0	258.9	269.2
115°	1934.3	1991.4	2075.7	518.1	276.0
117.5°	2132.9	2199.9	2257.5	1776.2	894.8
120°	2355.0	2405.3	2466.0	2506.4	2052.2
122.5°	2543.1	2597.0	2664.5	2684.5	2688.1
125°	2734.9	2778.8	2842.8	2866.3	2876.3
127.5°	2909.8	2957.0	3007.7	3041.3	3044.5
130°	3074.9	3128.8	3165.5	3202.7	3199.5
132.5°	3243.0	3286.9	3323.7	3354.1	3350.9
135°	3384.4	3438.4	3468.4	3502.3	3495.5
137.5°	3532.2	3572.6	3606.5	3640.1	3630.1
140°	3676.9	3704.0	3740.8	3771.2	3754.4
142.5°	3798.3	3821.9	3865.4	3892.2	3875.4
145°	3926.2	3922.5	3979.7	4003.2	3986.5
147.5°	4036.8	4026.8	4084.0	4100.8	4087.5
150°	4144.7	4121.1	4175.1	4195.0	4178.3
152.5°	4235.3	4208.6	4258.9	4279.3	4255.7
155°	4322.8	4292.8	4333.2	4353.2	4326.4
157.5°	4393.6	4366.8	4397.1	4420.7	4393.6
160°	4454.3	4433.9	4454.3	4474.3	4450.7
162.5°	4507.8	4487.9	4504.6	4528.2	4497.9
165°	4554.9	4535.0	4544.9	4568.5	4544.9
167.5°	4592.1	4571.7	4582.1	4605.6	4575.3
170°	4622.4	4602.1	4608.8	4632.4	4602.1
172.5°	4642.4	4622.4	4629.2	4652.8	4622.4
175°	4659.2	4635.6	4642.4	4666.0	4632.4
177.5°	4666.0	4642.4	4646.0	4669.6	4639.2
180°	4649.2	4649.2	4649.2	4649.2	4649.2

TEST NUMBER: P920481

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.09	9.85	10.14	10.91	12.33	8.64	9.41	9.69	10.46	11.89
	3H	10.74	11.43	11.80	12.50	13.94	10.25	10.94	11.31	12.00	13.45
	4H	11.33	11.98	12.40	13.05	14.50	10.84	11.49	11.91	12.55	14.01
	6H	11.73	12.33	12.81	13.40	14.86	11.23	11.83	12.31	12.90	14.36
	8H	11.83	12.40	12.92	13.49	14.95	11.33	11.90	12.42	12.99	14.45
	12H	11.88	12.42	12.97	13.50	14.98	11.37	11.91	12.46	12.99	14.47
4H	2H	9.54	10.19	10.62	11.25	12.71	9.18	9.83	10.26	10.90	12.35
	3H	11.40	11.94	12.48	13.04	14.50	10.99	11.54	12.08	12.63	14.09
	4H	12.11	12.61	13.20	13.69	15.18	11.69	12.19	12.78	13.27	14.76
	6H	12.63	13.06	13.73	14.16	15.64	12.19	12.62	13.29	13.73	15.21
	8H	12.78	13.18	13.88	14.27	15.77	12.34	12.74	13.44	13.84	15.33
	12H	12.85	13.21	13.96	14.32	15.82	12.40	12.76	13.51	13.87	15.37
8H	4H	12.30	12.70	13.40	13.80	15.30	11.93	12.33	13.02	13.42	14.92
	6H	12.93	13.26	14.06	14.41	15.90	12.55	12.88	13.67	14.02	15.51
	8H	13.16	13.45	14.28	14.57	16.08	12.76	13.05	13.89	14.18	15.69
	12H	13.29	13.54	14.42	14.66	16.21	12.88	13.13	14.01	14.25	15.80
12H	4H	12.28	12.65	13.40	13.76	15.26	11.92	12.28	13.03	13.39	14.89
	6H	12.96	13.25	14.09	14.37	15.89	12.59	12.88	13.72	14.00	15.52
	8H	13.20	13.46	14.34	14.58	16.13	12.82	13.08	13.96	14.20	15.75