

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920499

Luminaire Tested: DFN2DIP-SQ4F0-110D090US935-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P920499  
REPORT IS A COMBINATION OF REPORTS P901644 AND P898471  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-110D090US935-RLLONL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15721.8 lumens  
Efficiency: N/A  
Efficacy: 91.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 171.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P920499  
CATALOG NUMBER: DFN2DIP-SQ4F0-110D090US935-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P920499  
 CATALOG NUMBER: DFN2DIP-SQ4F0-110D090US935-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	46	44	42	38
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	37	34	32	28
5	70	58	51	45	64	54	48	42	47	42	37	40	36	33	34	31	28	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25	31	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2747	2747	2747
5°	2751	2704	2721
10°	2724	2651	2633
15°	2686	2564	2497
20°	2637	2444	2330
25°	2586	2309	2168
30°	2517	2170	1963
35°	2451	2022	1783
40°	2383	1868	1576
45°	2304	1696	1388
50°	2222	1524	1205
55°	2136	1339	1029
60°	2038	1146	848
65°	1924	950	764
70°	1786	767	692
75°	1613	677	632
80°	1362	570	551
85°	949	383	419

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2304 cd/sqm



TEST NUMBER: P920499

CATALOG NUMBER: DFN2DIP-SQ4F0-110D090US935-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	366.9	2.3
10°-20°	1007.1	6.4
20°-30°	1413.9	9.0
30°-40°	1541.3	9.8
40°-50°	1416.6	9.0
50°-60°	1112.5	7.1
60°-70°	724.2	4.6
70°-80°	372.8	2.4
80°-90°	99.8	0.6
90°-100°	86.2	0.5
100°-110°	321.5	2.0
110°-120°	852.6	5.4
120°-130°	1414.1	9.0
130°-140°	1502.1	9.6
140°-150°	1396.0	8.9
150°-160°	1122.4	7.1
160°-170°	723.2	4.6
170°-180°	248.9	1.6
0°-30°	2787.9	17.7
0°-40°	4329.1	27.5
0°-60°	6858.3	43.6
0°-90°	8054.9	51.2
90°-120°	1260.3	8.0
90°-150°	5572.4	35.4
90°-180°	7667.0	48.8
0°-180°	15721.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3914	3914	3914	3914	3914	
5°	3914	3897	3850	3882	3872	371
15°	3723	3684	3564	3496	3461	1049
25°	3380	3266	3032	2887	2834	1554
35°	2912	2731	2420	2196	2118	1823
45°	2381	2143	1771	1520	1435	1838
55°	1810	1534	1151	939	872	1617
65°	1222	935	616	496	485	1212
75°	652	404	283	259	255	689
85°	152	78	67	67	67	175
90°	2	23	38	47	51	15
95°	123	60	74	83	81	146
105°	575	632	116	136	144	615
115°	1088	1120	1168	291	155	1071
125°	1538	1563	1599	1612	1618	1372
135°	1904	1934	1951	1970	1966	1471
145°	2208	2206	2239	2252	2242	1381
155°	2432	2415	2437	2449	2434	1121
165°	2562	2551	2557	2570	2557	724
175°	2621	2608	2611	2625	2606	249
180°	2615	2615	2615	2615	2615	



TEST NUMBER: P920499

CATALOG NUMBER: DFN2DIP-SQ4F0-110D090US935-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3914.4	3914.4	3914.4	3914.4	3914.4
2.5°	3932.0	3914.4	3875.3	3911.0	3903.9
5°	3914.4	3896.7	3850.5	3882.4	3871.9
7.5°	3882.4	3861.3	3811.7	3825.7	3807.9
10°	3840.0	3815.1	3744.5	3733.5	3712.5
12.5°	3786.9	3755.0	3659.2	3638.1	3599.0
15°	3723.0	3684.0	3563.7	3496.4	3461.0
17.5°	3648.7	3591.9	3443.0	3365.2	3308.5
20°	3563.7	3492.6	3315.6	3227.3	3149.1
22.5°	3471.6	3390.0	3184.5	3064.2	3011.2
25°	3379.5	3266.0	3032.3	2887.2	2833.8
27.5°	3269.8	3149.1	2890.5	2724.0	2642.5
30°	3152.9	3018.0	2734.6	2554.2	2458.3
32.5°	3039.4	2876.2	2586.1	2373.4	2284.7
35°	2912.0	2731.2	2419.7	2196.4	2118.2
37.5°	2788.0	2592.9	2263.6	2019.0	1930.7
40°	2656.8	2444.5	2100.6	1849.1	1757.0
42.5°	2522.2	2295.6	1937.8	1675.5	1587.2
45°	2380.6	2143.0	1771.3	1519.5	1434.6
47.5°	2246.0	1994.6	1612.0	1360.1	1282.4
50°	2097.1	1845.7	1456.0	1211.3	1137.3
52.5°	1951.7	1686.0	1307.2	1073.4	1006.1
55°	1810.0	1533.8	1151.2	938.8	871.6
57.5°	1665.0	1381.6	1013.2	814.8	758.0
60°	1516.1	1232.8	867.8	687.4	630.7
62.5°	1371.1	1087.7	743.8	573.9	545.7
65°	1222.2	935.0	616.4	496.1	485.2
67.5°	1080.6	793.4	496.1	435.6	425.1
70°	931.7	655.5	410.8	375.5	361.2
72.5°	790.0	527.7	343.5	315.3	308.2
75°	651.7	403.6	283.4	258.6	255.2
77.5°	513.8	286.8	223.3	209.0	201.8
80°	386.0	205.6	169.9	156.0	156.0
82.5°	269.1	138.3	116.9	109.8	109.8
85°	152.2	77.8	67.2	67.2	67.2
87.5°	56.7	28.2	28.2	24.8	24.8
90°	1.8	22.7	37.7	47.4	51.0
92.5°	47.4	39.8	45.4	49.2	51.0
95°	123.0	60.4	73.7	83.3	81.4
97.5°	221.4	66.3	96.4	102.2	104.0
100°	335.0	75.8	107.9	123.0	126.7
102.5°	459.8	456.2	111.7	132.3	138.2
105°	575.2	632.1	115.5	136.2	143.8
107.5°	709.6	756.8	119.3	140.0	147.7
110°	838.4	878.0	331.2	142.0	149.5



TEST NUMBER: P920499

CATALOG NUMBER: DFN2DIP-SQ4F0-110D090US935-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	959.5	993.4	961.3	145.6	151.4
115°	1088.0	1120.2	1167.6	291.4	155.2
117.5°	1199.7	1237.5	1269.8	999.1	503.3
120°	1324.6	1353.0	1387.2	1409.8	1154.3
122.5°	1430.5	1460.9	1498.8	1510.0	1512.1
125°	1538.3	1563.1	1599.0	1612.3	1617.9
127.5°	1636.8	1663.3	1691.9	1710.7	1712.5
130°	1729.6	1760.0	1780.6	1801.5	1799.7
132.5°	1824.2	1848.9	1869.6	1886.7	1884.9
135°	1903.8	1934.1	1950.9	1970.0	1966.3
137.5°	1986.9	2009.6	2028.7	2047.5	2041.9
140°	2068.2	2083.5	2104.2	2121.2	2111.9
142.5°	2136.6	2149.8	2174.3	2189.3	2180.0
145°	2208.5	2206.4	2238.6	2251.9	2242.4
147.5°	2270.7	2265.1	2297.2	2306.7	2299.2
150°	2331.4	2318.2	2348.5	2359.7	2350.3
152.5°	2382.4	2367.3	2395.6	2407.1	2393.8
155°	2431.6	2414.8	2437.4	2448.7	2433.6
157.5°	2471.4	2456.3	2473.4	2486.6	2471.4
160°	2505.5	2494.1	2505.5	2516.8	2503.5
162.5°	2535.6	2524.4	2533.8	2547.1	2530.0
165°	2562.2	2550.9	2556.6	2569.8	2556.6
167.5°	2583.1	2571.6	2577.4	2590.7	2573.6
170°	2600.1	2588.7	2592.5	2605.7	2588.7
172.5°	2611.4	2600.1	2603.9	2617.2	2600.1
175°	2620.8	2607.5	2611.4	2624.6	2605.7
177.5°	2624.6	2611.4	2613.4	2626.6	2609.6
180°	2615.2	2615.2	2615.2	2615.2	2615.2



TEST NUMBER: P920499  
 CATALOG NUMBER: DFN2DIP-SQ4F0-110D090US935-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.78	11.63	11.74	12.59	13.85	6.75	7.59	7.70	8.55	9.81
	3H	12.47	13.22	13.43	14.19	15.47	7.94	8.69	8.90	9.66	10.94
	4H	13.08	13.79	14.06	14.77	16.06	8.39	9.10	9.37	10.07	11.36
	6H	13.51	14.16	14.50	15.14	16.44	8.71	9.36	9.70	10.35	11.65
	8H	13.63	14.26	14.63	15.26	16.55	8.80	9.42	9.80	10.42	11.72
	12H	13.70	14.29	14.70	15.28	16.60	8.84	9.44	9.84	10.43	11.75
4H	2H	10.80	11.51	11.79	12.49	13.78	7.34	8.05	8.33	9.03	10.32
	3H	12.64	13.23	13.63	14.24	15.54	8.70	9.29	9.69	10.29	11.60
	4H	13.34	13.87	14.34	14.87	16.20	9.25	9.79	10.25	10.79	12.11
	6H	13.86	14.32	14.87	15.34	16.66	9.67	10.13	10.68	11.15	12.48
	8H	14.03	14.47	15.05	15.48	16.82	9.80	10.23	10.81	11.25	12.58
	12H	14.13	14.52	15.16	15.55	16.90	9.86	10.25	10.89	11.28	12.63
8H	4H	13.30	13.74	14.32	14.75	16.09	9.53	9.96	10.54	10.98	12.32
	6H	13.88	14.23	14.91	15.29	16.63	10.05	10.41	11.09	11.47	12.80
	8H	14.09	14.41	15.14	15.45	16.81	10.24	10.56	11.29	11.60	12.95
	12H	14.24	14.51	15.29	15.55	16.95	10.36	10.64	11.41	11.68	13.07
12H	4H	13.26	13.65	14.29	14.68	16.02	9.54	9.93	10.57	10.96	12.30
	6H	13.85	14.17	14.90	15.21	16.56	10.10	10.41	11.15	11.46	12.81
	8H	14.08	14.35	15.12	15.39	16.79	10.31	10.59	11.36	11.63	13.02