

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915111

Luminaire Tested: DFN2DIP-SQ4F0-140D080US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915111
REPORT IS A COMBINATION OF REPORTS P901630 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D080US927-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15701.0 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 203.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915111

CATALOG NUMBER: DFN2DIP-SQ4F0-140D080US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915111

CATALOG NUMBER: DFN2DIP-SQ4F0-140D080US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	57	56
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	32	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3216	3216	3216
5°	3221	3166	3186
10°	3189	3104	3084
15°	3145	3002	2924
20°	3087	2862	2728
25°	3028	2704	2539
30°	2948	2542	2299
35°	2870	2367	2087
40°	2790	2187	1845
45°	2697	1987	1625
50°	2602	1784	1411
55°	2502	1568	1205
60°	2386	1342	992
65°	2253	1112	894
70°	2092	898	811
75°	1889	793	740
80°	1595	667	645
85°	1111	448	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2697 cd/sqm

TEST NUMBER: P915111

CATALOG NUMBER: DFN2DIP-SQ4F0-140D080US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.6	2.7
10°-20°	1179.3	7.5
20°-30°	1655.7	10.5
30°-40°	1804.8	11.5
40°-50°	1658.8	10.6
50°-60°	1302.8	8.3
60°-70°	848.0	5.4
70°-80°	436.5	2.8
80°-90°	115.2	0.7
90°-100°	70.5	0.4
100°-110°	262.9	1.7
110°-120°	697.3	4.4
120°-130°	1156.5	7.4
130°-140°	1228.4	7.8
140°-150°	1141.7	7.3
150°-160°	917.9	5.8
160°-170°	591.5	3.8
170°-180°	203.6	1.3
0°-30°	3264.6	20.8
0°-40°	5069.5	32.3
0°-60°	8031.0	51.1
0°-90°	9430.7	60.1
90°-120°	1030.7	6.6
90°-150°	4557.3	29.0
90°-180°	6270.0	39.9
0°-180°	15701.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4584	4584	4584	4584	4584	
5°	4584	4563	4509	4546	4534	435
15°	4360	4314	4173	4094	4053	1229
25°	3957	3824	3551	3381	3318	1820
35°	3410	3198	2833	2572	2480	2134
45°	2788	2510	2074	1779	1680	2153
55°	2120	1796	1348	1099	1021	1894
65°	1431	1095	722	581	568	1419
75°	763	473	332	303	299	807
85°	178	91	79	79	79	205
90°	2	18	31	39	42	15
95°	100	49	60	68	66	119
105°	470	517	94	111	118	503
115°	890	916	955	238	127	876
125°	1258	1278	1308	1319	1323	1122
135°	1557	1582	1596	1611	1608	1203
145°	1806	1804	1831	1842	1834	1130
155°	1989	1975	1993	2003	1990	916
165°	2096	2086	2091	2102	2091	592
175°	2143	2133	2136	2146	2131	204
180°	2139	2139	2139	2139	2139	

TEST NUMBER: P915111

CATALOG NUMBER: DFN2DIP-SQ4F0-140D080US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4583.7	4583.7	4583.7	4583.7	4583.7
2.5°	4604.4	4583.7	4537.9	4579.8	4571.4
5°	4583.7	4563.0	4508.9	4546.3	4534.0
7.5°	4546.3	4521.6	4463.5	4479.9	4459.2
10°	4496.6	4467.5	4384.8	4372.0	4347.3
12.5°	4434.5	4397.1	4284.8	4260.2	4214.5
15°	4359.7	4313.9	4173.1	4094.3	4053.0
17.5°	4272.5	4206.1	4031.8	3940.7	3874.2
20°	4173.1	4089.9	3882.6	3779.2	3687.7
22.5°	4065.2	3969.8	3729.0	3588.2	3526.2
25°	3957.4	3824.5	3550.8	3380.9	3318.4
27.5°	3828.9	3687.7	3384.8	3189.9	3094.4
30°	3692.0	3534.1	3202.2	2991.0	2878.7
32.5°	3559.1	3368.1	3028.4	2779.3	2675.4
35°	3409.9	3198.3	2833.4	2572.0	2480.4
37.5°	3264.7	3036.3	2650.7	2364.3	2260.8
40°	3111.1	2862.5	2459.7	2165.3	2057.5
42.5°	2953.6	2688.2	2269.2	1962.0	1858.5
45°	2787.6	2509.5	2074.2	1779.3	1679.9
47.5°	2630.0	2335.7	1887.6	1592.8	1501.7
50°	2455.8	2161.4	1704.9	1418.5	1331.7
52.5°	2285.4	1974.3	1530.7	1257.0	1178.1
55°	2119.6	1796.0	1348.1	1099.4	1020.6
57.5°	1949.6	1617.8	1186.5	954.2	887.7
60°	1775.4	1443.5	1016.2	804.9	738.5
62.5°	1605.5	1273.7	871.0	672.0	639.1
65°	1431.2	1095.0	721.8	580.9	568.2
67.5°	1265.3	929.1	580.9	510.1	497.7
70°	1091.0	767.5	481.0	439.7	422.9
72.5°	925.1	617.9	402.3	369.2	360.9
75°	763.1	472.7	331.8	302.8	298.8
77.5°	601.7	335.8	261.4	244.7	236.3
80°	452.0	240.7	198.9	182.7	182.7
82.5°	315.1	161.9	136.9	128.5	128.5
85°	178.2	91.1	78.7	78.7	78.7
87.5°	66.5	33.0	33.0	29.1	29.1
90°	1.5	18.5	30.9	38.7	41.7
92.5°	38.7	32.6	37.2	40.2	41.7
95°	100.5	49.4	60.3	68.2	66.5
97.5°	181.0	54.2	78.8	83.7	85.1
100°	274.0	61.9	88.2	100.5	103.6
102.5°	376.0	373.0	91.3	108.2	113.0
105°	470.5	517.0	94.4	111.4	117.6
107.5°	580.4	618.9	97.6	114.5	120.7
110°	685.7	718.0	270.9	116.1	122.2

TEST NUMBER: P915111

CATALOG NUMBER: DFN2DIP-SQ4F0-140D080US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	784.7	812.5	786.2	119.1	123.9
115°	889.9	916.2	954.9	238.4	127.0
117.5°	981.2	1012.1	1038.5	817.1	411.7
120°	1083.4	1106.5	1134.5	1153.0	944.0
122.5°	1169.9	1194.8	1225.8	1235.0	1236.7
125°	1258.1	1278.3	1307.7	1318.6	1323.2
127.5°	1338.6	1360.3	1383.7	1399.1	1400.6
130°	1414.5	1439.3	1456.3	1473.4	1471.9
132.5°	1491.9	1512.1	1529.1	1543.0	1541.5
135°	1557.0	1581.7	1595.5	1611.2	1608.0
137.5°	1625.0	1643.5	1659.1	1674.6	1670.0
140°	1691.5	1704.0	1720.9	1734.9	1727.1
142.5°	1747.4	1758.2	1778.2	1790.6	1782.8
145°	1806.2	1804.5	1830.8	1841.7	1833.9
147.5°	1857.1	1852.5	1878.7	1886.5	1880.4
150°	1906.7	1895.8	1920.6	1929.8	1922.1
152.5°	1948.4	1936.1	1959.2	1968.6	1957.8
155°	1988.7	1974.9	1993.4	2002.6	1990.4
157.5°	2021.2	2008.9	2022.8	2033.7	2021.2
160°	2049.1	2039.8	2049.1	2058.3	2047.5
162.5°	2073.8	2064.6	2072.3	2083.1	2069.2
165°	2095.5	2086.3	2090.9	2101.7	2090.9
167.5°	2112.5	2103.2	2107.9	2118.8	2104.8
170°	2126.5	2117.1	2120.3	2131.1	2117.1
172.5°	2135.7	2126.5	2129.6	2140.5	2126.5
175°	2143.4	2132.6	2135.7	2146.5	2131.1
177.5°	2146.5	2135.7	2137.3	2148.2	2134.2
180°	2138.8	2138.8	2138.8	2138.8	2138.8

TEST NUMBER: P915111

CATALOG NUMBER: DFN2DIP-SQ4F0-140D080US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.11	13.03	12.98	13.92	15.04	8.07	8.99	8.94	9.88	11.00
	3H	13.80	14.62	14.68	15.52	16.67	9.27	10.09	10.15	10.99	12.14
	4H	14.41	15.19	15.32	16.09	17.25	9.72	10.50	10.62	11.40	12.56
	6H	14.84	15.56	15.76	16.47	17.64	10.05	10.76	10.96	11.67	12.84
	8H	14.97	15.65	15.90	16.58	17.75	10.14	10.82	11.06	11.75	12.92
	12H	15.04	15.69	15.97	16.61	17.81	10.19	10.83	11.11	11.76	12.95
4H	2H	12.14	12.91	13.04	13.82	14.98	8.68	9.46	9.59	10.36	11.52
	3H	13.98	14.63	14.90	15.56	16.73	10.04	10.68	10.95	11.62	12.79
	4H	14.68	15.27	15.61	16.20	17.40	10.59	11.18	11.52	12.11	13.31
	6H	15.20	15.71	16.15	16.66	17.86	11.02	11.52	11.96	12.48	13.68
	8H	15.38	15.86	16.33	16.80	18.02	11.15	11.62	12.09	12.57	13.78
	12H	15.49	15.91	16.45	16.88	18.09	11.22	11.64	12.18	12.61	13.83
8H	4H	14.65	15.13	15.60	16.08	17.29	10.88	11.35	11.82	12.30	13.51
	6H	15.23	15.62	16.20	16.61	17.82	11.40	11.79	12.37	12.78	14.00
	8H	15.45	15.79	16.43	16.77	18.00	11.60	11.94	12.57	12.92	14.15
	12H	15.59	15.90	16.57	16.87	18.15	11.72	12.02	12.70	12.99	14.27
12H	4H	14.61	15.04	15.57	16.00	17.22	10.89	11.31	11.85	12.28	13.50
	6H	15.20	15.55	16.18	16.53	17.76	11.45	11.80	12.43	12.78	14.01
	8H	15.43	15.74	16.41	16.71	17.99	11.67	11.97	12.65	12.95	14.22