

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920539

Luminaire Tested: DFN2DIP-SQ4F0-120D100US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920539
REPORT IS A COMBINATION OF REPORTS P901664 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D100US935-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17306.1 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920539

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920539

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42	42	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	36	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	32	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	28	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	25	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	22	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	20	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	18	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2996	2996	2996
5°	3001	2949	2969
10°	2971	2892	2873
15°	2930	2797	2724
20°	2876	2666	2542
25°	2821	2519	2365
30°	2746	2368	2141
35°	2673	2205	1945
40°	2599	2037	1719
45°	2513	1851	1514
50°	2424	1662	1314
55°	2331	1461	1122
60°	2223	1250	925
65°	2099	1036	833
70°	1949	836	755
75°	1760	739	689
80°	1486	621	600
85°	1035	418	457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2513 cd/sqm

TEST NUMBER: P920539

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.2	2.3
10°-20°	1098.7	6.3
20°-30°	1542.5	8.9
30°-40°	1681.4	9.7
40°-50°	1545.4	8.9
50°-60°	1213.7	7.0
60°-70°	790.0	4.6
70°-80°	406.7	2.3
80°-90°	108.9	0.6
90°-100°	95.8	0.6
100°-110°	357.2	2.1
110°-120°	947.3	5.5
120°-130°	1571.2	9.1
130°-140°	1669.0	9.6
140°-150°	1551.1	9.0
150°-160°	1247.1	7.2
160°-170°	803.6	4.6
170°-180°	276.6	1.6
0°-30°	3041.3	17.6
0°-40°	4722.7	27.3
0°-60°	7481.7	43.2
0°-90°	8787.3	50.8
90°-120°	1400.3	8.1
90°-150°	6191.6	35.8
90°-180°	8519.0	49.2
0°-180°	17306.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4270	4270	4270	4270	4270	
5°	4270	4251	4200	4235	4224	405
15°	4062	4019	3888	3814	3776	1144
25°	3687	3563	3308	3150	3091	1696
35°	3177	2980	2640	2396	2311	1988
45°	2597	2338	1932	1658	1565	2006
55°	1975	1673	1256	1024	951	1764
65°	1333	1020	672	541	529	1322
75°	711	440	309	282	278	752
85°	166	85	73	73	73	191
90°	2	25	42	53	57	16
95°	137	67	82	93	90	162
105°	639	702	128	151	160	683
115°	1209	1245	1297	324	172	1190
125°	1709	1737	1777	1792	1798	1524
135°	2115	2149	2168	2189	2185	1634
145°	2454	2452	2487	2502	2492	1535
155°	2702	2683	2708	2721	2704	1245
165°	2847	2834	2841	2855	2841	804
175°	2912	2897	2902	2916	2895	277
180°	2906	2906	2906	2906	2906	

TEST NUMBER: P920539

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4270.2	4270.2	4270.2	4270.2	4270.2
2.5°	4289.5	4270.2	4227.6	4266.5	4258.7
5°	4270.2	4250.9	4200.5	4235.3	4223.9
7.5°	4235.3	4212.3	4158.3	4173.4	4154.1
10°	4189.0	4162.0	4084.8	4073.0	4050.0
12.5°	4131.2	4096.4	3991.8	3968.9	3926.2
15°	4061.5	4018.9	3887.7	3814.2	3775.7
17.5°	3980.3	3918.4	3756.0	3671.2	3609.3
20°	3887.7	3810.2	3617.1	3520.7	3435.4
22.5°	3787.2	3698.2	3474.0	3342.7	3285.0
25°	3686.8	3562.9	3307.9	3149.6	3091.4
27.5°	3567.0	3435.4	3153.3	2971.7	2882.7
30°	3439.5	3292.4	2983.2	2786.4	2681.8
32.5°	3315.7	3137.7	2821.2	2589.2	2492.4
35°	3176.7	2979.5	2639.6	2396.1	2310.7
37.5°	3041.4	2828.6	2469.4	2202.5	2106.2
40°	2898.3	2666.7	2291.5	2017.2	1916.8
42.5°	2751.5	2504.3	2114.0	1827.8	1731.5
45°	2596.9	2337.9	1932.3	1657.7	1564.9
47.5°	2450.1	2175.9	1758.5	1483.8	1398.9
50°	2287.8	2013.5	1588.4	1321.5	1240.7
52.5°	2129.2	1839.3	1426.0	1171.0	1097.6
55°	1974.6	1673.3	1255.9	1024.2	950.8
57.5°	1816.3	1507.2	1105.3	888.9	827.0
60°	1654.0	1344.8	946.7	749.9	688.0
62.5°	1495.7	1186.5	811.4	626.1	595.3
65°	1333.3	1020.1	672.4	541.2	529.3
67.5°	1178.8	865.5	541.2	475.2	463.7
70°	1016.4	715.1	448.1	409.6	394.0
72.5°	861.9	575.7	374.7	344.0	336.2
75°	710.9	440.3	309.2	282.1	278.4
77.5°	560.5	312.8	243.6	228.0	220.2
80°	421.1	224.3	185.3	170.1	170.1
82.5°	293.6	150.8	127.5	119.7	119.7
85°	166.1	84.9	73.4	73.4	73.4
87.5°	61.9	30.7	30.7	27.0	27.0
90°	2.0	25.2	41.9	52.7	56.7
92.5°	52.7	44.2	50.5	54.7	56.7
95°	136.6	67.2	81.9	92.6	90.4
97.5°	245.9	73.6	107.1	113.6	115.6
100°	372.3	84.1	119.9	136.6	140.9
102.5°	510.8	506.9	124.1	147.1	153.5
105°	639.2	702.3	128.4	151.3	159.8
107.5°	788.5	840.9	132.6	155.6	164.0
110°	931.5	975.5	368.0	157.8	166.0

TEST NUMBER: P920539

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1066.1	1103.8	1068.2	161.8	168.3
115°	1208.9	1244.7	1297.4	323.8	172.5
117.5°	1333.0	1375.0	1410.9	1110.1	559.3
120°	1471.9	1503.3	1541.3	1566.5	1282.6
122.5°	1589.5	1623.2	1665.3	1677.8	1680.1
125°	1709.3	1736.8	1776.8	1791.5	1797.7
127.5°	1818.7	1848.1	1879.8	1900.8	1902.8
130°	1921.7	1955.5	1978.5	2001.6	1999.7
132.5°	2026.9	2054.3	2077.3	2096.3	2094.3
135°	2115.3	2149.0	2167.7	2188.9	2184.7
137.5°	2207.7	2232.9	2254.1	2275.1	2268.8
140°	2298.0	2315.1	2338.0	2357.0	2346.5
142.5°	2373.9	2388.7	2415.9	2432.6	2422.2
145°	2453.8	2451.6	2487.3	2502.1	2491.6
147.5°	2523.0	2516.8	2552.4	2562.9	2554.8
150°	2590.4	2575.7	2609.4	2621.9	2611.4
152.5°	2647.1	2630.3	2661.9	2674.5	2659.8
155°	2701.8	2683.0	2708.3	2720.8	2704.0
157.5°	2746.0	2729.3	2748.2	2762.9	2746.0
160°	2784.0	2771.2	2784.0	2796.4	2781.7
162.5°	2817.4	2804.9	2815.4	2830.1	2811.2
165°	2846.8	2834.3	2840.6	2855.3	2840.6
167.5°	2870.1	2857.3	2863.9	2878.6	2859.5
170°	2889.0	2876.3	2880.6	2895.3	2876.3
172.5°	2901.5	2889.0	2893.3	2908.0	2889.0
175°	2912.0	2897.3	2901.5	2916.3	2895.3
177.5°	2916.3	2901.5	2903.8	2918.5	2899.5
180°	2905.8	2905.8	2905.8	2905.8	2905.8

TEST NUMBER: P920539

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.04	11.88	12.00	12.85	14.11	7.01	7.84	7.96	8.81	10.07
	3H	12.73	13.48	13.70	14.45	15.74	8.20	8.94	9.16	9.92	11.21
	4H	13.34	14.05	14.32	15.03	16.32	8.65	9.35	9.63	10.33	11.63
	6H	13.76	14.42	14.76	15.40	16.71	8.97	9.62	9.96	10.61	11.91
	8H	13.89	14.51	14.89	15.52	16.82	9.06	9.68	10.06	10.68	11.98
	12H	13.96	14.55	14.96	15.54	16.87	9.10	9.69	10.11	10.69	12.02
4H	2H	11.06	11.77	12.05	12.75	14.05	7.60	8.31	8.59	9.29	10.59
	3H	12.90	13.49	13.90	14.50	15.80	8.96	9.54	9.95	10.55	11.86
	4H	13.59	14.13	14.60	15.13	16.47	9.50	10.04	10.51	11.04	12.38
	6H	14.11	14.58	15.13	15.60	16.93	9.93	10.39	10.94	11.41	12.74
	8H	14.29	14.72	15.31	15.74	17.09	10.05	10.49	11.07	11.50	12.85
	12H	14.39	14.78	15.43	15.81	17.16	10.12	10.51	11.16	11.54	12.89
8H	4H	13.56	13.99	14.58	15.01	16.36	9.79	10.22	10.81	11.24	12.58
	6H	14.13	14.49	15.18	15.55	16.89	10.31	10.66	11.35	11.73	13.07
	8H	14.35	14.67	15.40	15.71	17.07	10.50	10.81	11.55	11.86	13.22
	12H	14.50	14.77	15.55	15.81	17.22	10.62	10.90	11.67	11.94	13.34
12H	4H	13.51	13.90	14.55	14.94	16.29	9.79	10.18	10.83	11.22	12.57
	6H	14.11	14.42	15.16	15.47	16.83	10.36	10.67	11.41	11.72	13.08
	8H	14.33	14.61	15.39	15.65	17.05	10.57	10.85	11.62	11.89	13.29