

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920575

Luminaire Tested: DFN2DIP-SQ4F0-140D100US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920575
REPORT IS A COMBINATION OF REPORTS P901666 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D100US935-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18769.8 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 218.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920575

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920575

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3496	3496	3496
5°	3501	3441	3463
10°	3467	3374	3351
15°	3419	3263	3178
20°	3356	3110	2965
25°	3291	2938	2759
30°	3204	2762	2498
35°	3119	2573	2269
40°	3032	2377	2005
45°	2932	2159	1767
50°	2828	1939	1533
55°	2719	1705	1309
60°	2593	1459	1079
65°	2449	1209	972
70°	2273	976	881
75°	2053	862	804
80°	1734	725	701
85°	1207	488	533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2932 cd/sqm

TEST NUMBER: P920575

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	466.9	2.5
10°-20°	1281.8	6.8
20°-30°	1799.5	9.6
30°-40°	1961.6	10.5
40°-50°	1802.9	9.6
50°-60°	1415.9	7.5
60°-70°	921.6	4.9
70°-80°	474.4	2.5
80°-90°	126.2	0.7
90°-100°	95.8	0.5
100°-110°	357.2	1.9
110°-120°	947.3	5.0
120°-130°	1571.2	8.4
130°-140°	1669.0	8.9
140°-150°	1551.1	8.3
150°-160°	1247.1	6.6
160°-170°	803.6	4.3
170°-180°	276.6	1.5
0°-30°	3548.2	18.9
0°-40°	5509.8	29.4
0°-60°	8728.7	46.5
0°-90°	10251.0	54.6
90°-120°	1400.3	7.5
90°-150°	6191.6	33.0
90°-180°	8519.0	45.4
0°-180°	18769.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4982	4982	4982	4982	4982	
5°	4982	4959	4900	4941	4928	472
15°	4738	4689	4536	4450	4405	1335
25°	4301	4157	3859	3675	3607	1978
35°	3706	3476	3080	2795	2696	2320
45°	3030	2728	2254	1934	1826	2340
55°	2304	1952	1465	1195	1109	2059
65°	1556	1190	784	631	618	1542
75°	829	514	361	329	325	877
85°	194	99	86	86	86	222
90°	2	25	42	53	57	18
95°	137	67	82	93	90	162
105°	639	702	128	151	160	683
115°	1209	1245	1297	324	172	1190
125°	1709	1737	1777	1792	1798	1524
135°	2115	2149	2168	2189	2185	1634
145°	2454	2452	2487	2502	2492	1535
155°	2702	2683	2708	2721	2704	1245
165°	2847	2834	2841	2855	2841	804
175°	2912	2897	2902	2916	2895	277
180°	2906	2906	2906	2906	2906	

TEST NUMBER: P920575

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4981.9	4981.9	4981.9	4981.9	4981.9
2.5°	5004.4	4981.9	4932.1	4977.6	4968.5
5°	4981.9	4959.4	4900.5	4941.3	4927.8
7.5°	4941.3	4914.4	4851.3	4869.0	4846.6
10°	4887.2	4855.6	4765.7	4751.8	4725.0
12.5°	4819.7	4779.1	4657.1	4630.3	4580.6
15°	4738.4	4688.6	4535.6	4450.0	4405.0
17.5°	4643.7	4571.5	4382.0	4283.0	4210.8
20°	4535.6	4445.2	4219.9	4107.5	4008.0
22.5°	4418.4	4314.6	4053.0	3899.9	3832.5
25°	4301.2	4156.7	3859.3	3674.6	3606.6
27.5°	4161.5	4008.0	3678.9	3467.0	3363.2
30°	4012.8	3841.1	3480.4	3250.8	3128.8
32.5°	3868.3	3660.7	3291.4	3020.7	2907.8
35°	3706.2	3476.1	3079.5	2795.4	2695.9
37.5°	3548.3	3300.0	2881.0	2569.6	2457.2
40°	3381.4	3111.1	2673.4	2353.5	2236.3
42.5°	3210.1	2921.7	2466.3	2132.4	2020.0
45°	3029.8	2727.5	2254.4	1933.9	1825.8
47.5°	2858.5	2538.6	2051.6	1731.1	1632.1
50°	2669.1	2349.1	1853.0	1541.7	1447.4
52.5°	2484.0	2145.8	1663.6	1366.1	1280.5
55°	2303.7	1952.1	1465.2	1194.9	1109.2
57.5°	2119.0	1758.3	1289.6	1037.1	964.8
60°	1929.6	1568.9	1104.5	874.9	802.6
62.5°	1745.0	1384.3	946.7	730.4	694.6
65°	1555.6	1190.1	784.5	631.4	617.5
67.5°	1375.2	1009.8	631.4	554.4	541.0
70°	1185.8	834.2	522.8	477.9	459.7
72.5°	1005.5	671.6	437.2	401.3	392.3
75°	829.4	513.8	360.7	329.1	324.8
77.5°	653.9	365.0	284.1	266.0	256.8
80°	491.3	261.7	216.2	198.5	198.5
82.5°	342.5	176.0	148.8	139.7	139.7
85°	193.7	99.0	85.6	85.6	85.6
87.5°	72.2	35.9	35.9	31.6	31.6
90°	2.0	25.2	41.9	52.7	56.7
92.5°	52.7	44.2	50.5	54.7	56.7
95°	136.6	67.2	81.9	92.6	90.4
97.5°	245.9	73.6	107.1	113.6	115.6
100°	372.3	84.1	119.9	136.6	140.9
102.5°	510.8	506.9	124.1	147.1	153.5
105°	639.2	702.3	128.4	151.3	159.8
107.5°	788.5	840.9	132.6	155.6	164.0
110°	931.5	975.5	368.0	157.8	166.0

TEST NUMBER: P920575

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1066.1	1103.8	1068.2	161.8	168.3
115°	1208.9	1244.7	1297.4	323.8	172.5
117.5°	1333.0	1375.0	1410.9	1110.1	559.3
120°	1471.9	1503.3	1541.3	1566.5	1282.6
122.5°	1589.5	1623.2	1665.3	1677.8	1680.1
125°	1709.3	1736.8	1776.8	1791.5	1797.7
127.5°	1818.7	1848.1	1879.8	1900.8	1902.8
130°	1921.7	1955.5	1978.5	2001.6	1999.7
132.5°	2026.9	2054.3	2077.3	2096.3	2094.3
135°	2115.3	2149.0	2167.7	2188.9	2184.7
137.5°	2207.7	2232.9	2254.1	2275.1	2268.8
140°	2298.0	2315.1	2338.0	2357.0	2346.5
142.5°	2373.9	2388.7	2415.9	2432.6	2422.2
145°	2453.8	2451.6	2487.3	2502.1	2491.6
147.5°	2523.0	2516.8	2552.4	2562.9	2554.8
150°	2590.4	2575.7	2609.4	2621.9	2611.4
152.5°	2647.1	2630.3	2661.9	2674.5	2659.8
155°	2701.8	2683.0	2708.3	2720.8	2704.0
157.5°	2746.0	2729.3	2748.2	2762.9	2746.0
160°	2784.0	2771.2	2784.0	2796.4	2781.7
162.5°	2817.4	2804.9	2815.4	2830.1	2811.2
165°	2846.8	2834.3	2840.6	2855.3	2840.6
167.5°	2870.1	2857.3	2863.9	2878.6	2859.5
170°	2889.0	2876.3	2880.6	2895.3	2876.3
172.5°	2901.5	2889.0	2893.3	2908.0	2889.0
175°	2912.0	2897.3	2901.5	2916.3	2895.3
177.5°	2916.3	2901.5	2903.8	2918.5	2899.5
180°	2905.8	2905.8	2905.8	2905.8	2905.8

TEST NUMBER: P920575

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.93	12.80	12.85	13.73	14.94	7.89	8.76	8.81	9.70	10.90
	3H	13.61	14.39	14.55	15.34	16.57	9.08	9.86	10.02	10.81	12.04
	4H	14.23	14.96	15.18	15.91	17.15	9.53	10.27	10.48	11.22	12.46
	6H	14.65	15.33	15.62	16.29	17.54	9.86	10.53	10.82	11.49	12.74
	8H	14.78	15.43	15.75	16.40	17.65	9.95	10.59	10.92	11.57	12.82
	12H	14.85	15.46	15.82	16.43	17.70	10.00	10.61	10.97	11.57	12.85
4H	2H	11.95	12.69	12.91	13.64	14.88	8.49	9.23	9.45	10.18	11.42
	3H	13.79	14.40	14.75	15.38	16.63	9.85	10.46	10.81	11.44	12.69
	4H	14.49	15.04	15.46	16.02	17.30	10.40	10.95	11.37	11.93	13.21
	6H	15.01	15.49	15.99	16.48	17.76	10.82	11.30	11.81	12.30	13.57
	8H	15.19	15.63	16.17	16.63	17.92	10.95	11.40	11.94	12.39	13.68
	12H	15.29	15.69	16.29	16.70	17.99	11.02	11.42	12.02	12.43	13.72
8H	4H	14.46	14.90	15.45	15.90	17.19	10.68	11.13	11.67	12.12	13.41
	6H	15.03	15.40	16.04	16.43	17.72	11.20	11.57	12.22	12.61	13.90
	8H	15.25	15.57	16.27	16.60	17.90	11.40	11.72	12.42	12.74	14.05
	12H	15.39	15.68	16.42	16.69	18.05	11.52	11.80	12.54	12.82	14.17
12H	4H	14.41	14.81	15.42	15.82	17.12	10.69	11.09	11.70	12.10	13.40
	6H	15.01	15.33	16.03	16.35	17.66	11.25	11.58	12.28	12.60	13.91
	8H	15.23	15.52	16.25	16.53	17.88	11.47	11.75	12.49	12.77	14.12