

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920581

Luminaire Tested: DFN2DIP-SQ4F0-140D120US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920581
REPORT IS A COMBINATION OF REPORTS P901701 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D120US935-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22162.1 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 233.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920581

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920581

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	52	50
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	38	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	28	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3291	3291	3291
5°	3296	3246	3268
10°	3269	3203	3225
15°	3221	3151	3156
20°	3156	3078	3087
25°	3092	2991	3006
30°	3011	2910	2902
35°	2934	2815	2793
40°	2839	2718	2690
45°	2745	2622	2584
50°	2642	2520	2461
55°	2534	2403	2348
60°	2412	2264	2219
65°	2279	2120	2066
70°	2110	1944	1903
75°	1875	1734	1753
80°	1593	1467	1464
85°	1151	1004	984

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2745 cd/sqm

TEST NUMBER: P920581

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US935-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	441.4	2.0
10°-20°	1242.1	5.6
20°-30°	1825.4	8.2
30°-40°	2120.0	9.6
40°-50°	2117.4	9.6
50°-60°	1846.3	8.3
60°-70°	1364.8	6.2
70°-80°	772.2	3.5
80°-90°	209.9	0.9
90°-100°	115.0	0.5
100°-110°	428.6	1.9
110°-120°	1136.8	5.1
120°-130°	1885.4	8.5
130°-140°	2002.8	9.0
140°-150°	1861.3	8.4
150°-160°	1496.5	6.8
160°-170°	964.3	4.4
170°-180°	331.9	1.5
0°-30°	3508.9	15.8
0°-40°	5628.9	25.4
0°-60°	9592.6	43.3
0°-90°	11939.6	53.9
90°-120°	1680.4	7.6
90°-150°	7429.9	33.5
90°-180°	10223.0	46.1
0°-180°	22162.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4690	4690	4690	4690	4690	
5°	4690	4672	4623	4659	4650	445
15°	4465	4438	4379	4398	4375	1257
25°	4041	4005	3928	3937	3928	1859
35°	3486	3441	3369	3342	3319	2177
45°	2837	2806	2738	2688	2670	2189
55°	2147	2120	2066	2012	1989	1920
65°	1448	1421	1376	1335	1312	1432
75°	758	749	726	699	708	809
85°	185	180	176	162	158	206
90°	2	30	50	63	68	20
95°	164	81	98	111	108	194
105°	767	843	154	182	192	820
115°	1451	1494	1557	389	207	1428
125°	2051	2084	2132	2150	2157	1829
135°	2538	2579	2601	2627	2622	1961
145°	2945	2942	2985	3002	2990	1842
155°	3242	3220	3250	3265	3245	1494
165°	3416	3401	3409	3426	3409	965
175°	3494	3477	3482	3500	3474	333
180°	3487	3487	3487	3487	3487	

TEST NUMBER: P920581

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4690.3	4690.3	4690.3	4690.3	4690.3
2.5°	4717.5	4695.0	4645.3	4690.3	4681.7
5°	4690.3	4672.5	4622.8	4658.7	4650.1
7.5°	4658.7	4631.9	4582.1	4618.5	4609.4
10°	4609.4	4577.8	4523.8	4559.7	4546.2
12.5°	4541.4	4514.6	4460.6	4483.0	4474.0
15°	4464.9	4438.1	4379.2	4397.5	4374.9
17.5°	4370.2	4343.4	4284.5	4307.0	4284.5
20°	4266.3	4239.6	4176.4	4189.8	4172.1
22.5°	4162.9	4122.3	4063.4	4063.4	4054.4
25°	4040.9	4005.0	3928.5	3937.1	3928.5
27.5°	3905.5	3874.0	3815.6	3802.2	3779.7
30°	3770.6	3734.2	3666.7	3653.4	3635.1
32.5°	3626.1	3599.3	3527.0	3499.8	3481.5
35°	3486.4	3441.4	3369.1	3341.9	3319.3
37.5°	3328.4	3287.8	3215.5	3184.0	3161.4
40°	3166.2	3129.9	3057.6	3017.5	2999.2
42.5°	3008.3	2972.0	2900.2	2854.7	2827.9
45°	2837.0	2805.5	2737.5	2688.2	2670.0
47.5°	2670.0	2638.4	2566.2	2516.4	2489.7
50°	2494.0	2471.5	2408.3	2345.1	2322.6
52.5°	2322.6	2291.0	2232.7	2182.9	2151.4
55°	2147.1	2119.8	2065.7	2011.6	1989.2
57.5°	1970.9	1948.4	1889.6	1835.6	1817.3
60°	1794.8	1777.2	1714.0	1664.2	1650.8
62.5°	1623.6	1592.0	1547.0	1502.0	1483.8
65°	1447.9	1420.6	1375.7	1335.0	1312.5
67.5°	1267.6	1244.6	1204.4	1172.8	1154.6
70°	1100.5	1082.4	1041.7	1010.1	992.4
72.5°	929.3	911.0	888.5	857.0	843.6
75°	757.5	748.9	725.9	699.1	708.2
77.5°	604.3	586.2	577.0	563.7	550.3
80°	451.2	446.4	437.4	424.0	414.8
82.5°	306.7	306.7	302.4	284.2	284.2
85°	184.7	180.4	176.1	162.2	157.9
87.5°	81.4	72.2	63.2	49.8	44.9
90°	2.4	30.2	50.4	63.2	68.0
92.5°	63.2	53.0	60.5	65.6	68.0
95°	163.8	80.6	98.2	111.2	108.5
97.5°	295.2	88.4	128.5	136.3	138.7
100°	446.7	101.0	143.8	163.8	169.0
102.5°	613.0	608.2	148.9	176.5	184.3
105°	767.0	842.8	154.0	181.6	191.7
107.5°	946.2	1009.1	159.1	186.7	196.8
110°	1117.8	1170.6	441.6	189.3	199.2

TEST NUMBER: P920581

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1279.4	1324.6	1281.8	194.2	201.9
115°	1450.7	1493.6	1556.8	388.6	207.1
117.5°	1599.6	1650.0	1693.2	1332.0	671.1
120°	1766.3	1804.0	1849.5	1879.8	1539.1
122.5°	1907.4	1947.8	1998.5	2013.4	2016.1
125°	2051.2	2084.1	2132.1	2149.7	2157.2
127.5°	2182.4	2217.8	2255.8	2281.0	2283.4
130°	2306.1	2346.6	2374.1	2402.0	2399.6
132.5°	2432.2	2465.2	2492.8	2515.6	2513.2
135°	2538.3	2578.8	2601.2	2626.7	2621.7
137.5°	2649.2	2679.4	2704.9	2730.1	2722.6
140°	2757.7	2778.0	2805.6	2828.4	2815.8
142.5°	2848.7	2866.4	2899.1	2919.1	2906.6
145°	2944.6	2941.9	2984.7	3002.5	2989.8
147.5°	3027.6	3020.1	3063.0	3075.6	3065.7
150°	3108.5	3090.8	3131.3	3146.3	3133.7
152.5°	3176.5	3156.4	3194.2	3209.5	3191.8
155°	3242.1	3219.6	3249.9	3264.9	3244.8
157.5°	3295.1	3275.1	3297.9	3315.5	3295.1
160°	3340.7	3325.4	3340.7	3355.7	3338.0
162.5°	3380.9	3365.9	3378.5	3396.1	3373.4
165°	3416.2	3401.2	3408.7	3426.4	3408.7
167.5°	3444.1	3428.8	3436.6	3454.2	3431.5
170°	3466.8	3451.6	3456.6	3474.3	3451.6
172.5°	3481.8	3466.8	3472.0	3489.6	3466.8
175°	3494.4	3476.7	3481.8	3499.5	3474.3
177.5°	3499.5	3481.8	3484.5	3502.2	3479.5
180°	3487.0	3487.0	3487.0	3487.0	3487.0

TEST NUMBER: P920581

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.77	12.67	12.70	13.61	14.83	11.33	12.23	12.25	13.17	14.38
	3H	13.44	14.25	14.38	15.20	16.44	12.95	13.76	13.89	14.71	15.95
	4H	14.03	14.80	14.98	15.75	17.00	13.54	14.30	14.49	15.26	16.50
	6H	14.44	15.14	15.40	16.10	17.36	13.94	14.64	14.90	15.60	16.86
	8H	14.55	15.21	15.51	16.19	17.45	14.04	14.71	15.01	15.69	16.95
	12H	14.60	15.23	15.57	16.21	17.49	14.09	14.72	15.06	15.70	16.98
4H	2H	12.24	13.00	13.19	13.96	15.20	11.89	12.65	12.84	13.60	14.85
	3H	14.11	14.75	15.08	15.73	17.00	13.71	14.34	14.67	15.33	16.59
	4H	14.83	15.41	15.81	16.39	17.68	14.41	14.99	15.38	15.97	17.25
	6H	15.35	15.86	16.34	16.86	18.14	14.92	15.42	15.91	16.43	17.71
	8H	15.51	15.97	16.50	16.97	18.27	15.07	15.54	16.06	16.53	17.83
	12H	15.58	16.01	16.59	17.02	18.32	15.13	15.56	16.14	16.57	17.87
8H	4H	15.03	15.50	16.02	16.50	17.80	14.66	15.12	15.64	16.12	17.42
	6H	15.67	16.06	16.68	17.10	18.39	15.29	15.67	16.30	16.71	18.01
	8H	15.89	16.24	16.92	17.26	18.58	15.50	15.84	16.52	16.87	18.18
	12H	16.03	16.33	17.06	17.35	18.71	15.62	15.92	16.65	16.94	18.30
12H	4H	15.02	15.44	16.03	16.45	17.76	14.65	15.07	15.66	16.09	17.39
	6H	15.70	16.04	16.72	17.07	18.38	15.33	15.67	16.35	16.70	18.01
	8H	15.95	16.25	16.97	17.27	18.63	15.57	15.87	16.59	16.89	18.25