

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917610

Luminaire Tested: DFN2DIP-SQ4F0-060D160US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917610
REPORT IS A COMBINATION OF REPORTS P900204 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D160US930-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15703.4 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 172.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917610

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917610

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	30
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22
4	71	61	53	48	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1419	1419	1419
5°	1421	1396	1405
10°	1407	1369	1360
15°	1387	1324	1290
20°	1362	1262	1203
25°	1336	1192	1120
30°	1300	1121	1014
35°	1266	1044	921
40°	1231	965	814
45°	1190	876	717
50°	1148	787	622
55°	1103	692	531
60°	1052	592	438
65°	994	491	394
70°	923	396	358
75°	833	350	326
80°	703	294	284
85°	490	198	216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3246 cd/sqm

TEST NUMBER: P917610

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	1.2
10°-20°	520.2	3.3
20°-30°	730.3	4.7
30°-40°	796.1	5.1
40°-50°	731.7	4.7
50°-60°	574.6	3.7
60°-70°	374.0	2.4
70°-80°	192.5	1.2
80°-90°	60.9	0.4
90°-100°	255.3	1.6
100°-110°	811.2	5.2
110°-120°	1388.2	8.8
120°-130°	1825.7	11.6
130°-140°	2049.3	13.0
140°-150°	2009.6	12.8
150°-160°	1685.7	10.7
160°-170°	1117.9	7.1
170°-180°	390.8	2.5
0°-30°	1439.9	9.2
0°-40°	2236.0	14.2
0°-60°	3542.3	22.6
0°-90°	4169.7	26.6
90°-120°	2454.7	15.6
90°-150°	8339.3	53.1
90°-180°	11534.0	73.4
0°-180°	15703.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	4	45	122	114	118	16
95°	182	216	223	223	216	202
105°	749	759	766	772	772	790
115°	1393	1413	1407	1403	1393	1378
125°	2026	2057	2047	2036	2032	1811
135°	2621	2659	2667	2663	2653	2026
145°	3182	3207	3226	3230	3217	1988
155°	3638	3648	3659	3677	3666	1675
165°	3958	3954	3954	3979	3962	1117
175°	4118	4108	4101	4126	4105	391
180°	4126	4126	4126	4126	4126	

TEST NUMBER: P917610

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	3.8	44.8	121.9	114.5	118.1
92.5°	77.1	104.5	108.2	111.9	111.9
95°	181.6	216.5	222.7	222.7	216.5
97.5°	302.2	334.6	348.3	348.3	348.3
100°	441.6	470.2	480.1	480.1	476.4
102.5°	588.3	609.5	623.1	626.9	623.1
105°	748.8	758.7	766.2	772.4	772.4
107.5°	908.0	922.9	922.9	925.4	908.0
110°	1062.3	1082.1	1082.1	1082.1	1072.2

TEST NUMBER: P917610

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1228.9	1250.1	1246.3	1236.4	1228.9
115°	1393.1	1413.0	1406.8	1403.0	1393.1
117.5°	1556.1	1583.4	1566.0	1556.1	1546.1
120°	1720.3	1747.6	1720.3	1720.3	1709.0
122.5°	1869.5	1904.4	1886.9	1877.0	1869.5
125°	2026.3	2057.3	2047.4	2036.2	2032.5
127.5°	2179.2	2217.8	2204.1	2189.2	2179.2
130°	2322.3	2367.1	2360.9	2353.4	2339.7
132.5°	2482.7	2517.6	2520.0	2502.6	2492.7
135°	2620.8	2659.3	2666.8	2663.1	2653.1
137.5°	2775.0	2806.1	2812.4	2809.8	2794.9
140°	2910.6	2941.7	2959.1	2959.1	2945.4
142.5°	3049.9	3081.0	3091.0	3094.7	3081.0
145°	3181.8	3206.6	3226.5	3230.3	3216.6
147.5°	3299.9	3331.1	3346.0	3352.2	3338.5
150°	3421.8	3443.0	3456.7	3467.9	3456.7
152.5°	3530.1	3551.2	3568.6	3582.3	3568.6
155°	3638.3	3648.2	3659.4	3676.8	3665.7
157.5°	3731.5	3739.0	3745.2	3770.1	3752.7
160°	3814.9	3822.4	3826.1	3847.2	3832.3
162.5°	3892.0	3892.0	3895.7	3919.4	3901.9
165°	3957.9	3954.2	3954.2	3979.1	3961.7
167.5°	4017.6	4006.5	4006.5	4031.3	4013.9
170°	4062.4	4052.4	4048.8	4073.6	4052.4
172.5°	4093.5	4083.6	4079.8	4104.7	4083.6
175°	4118.4	4108.5	4101.0	4125.9	4104.7
177.5°	4132.1	4122.1	4114.6	4135.8	4114.6
180°	4125.9	4125.9	4125.9	4125.9	4125.9

TEST NUMBER: P917610

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.64	6.31	6.78	7.44	9.01	1.60	2.27	2.74	3.40	4.97
	3H	7.31	7.91	8.46	9.04	10.63	2.78	3.38	3.93	4.51	6.10
	4H	7.91	8.48	9.07	9.62	11.21	3.22	3.79	4.38	4.93	6.52
	6H	8.33	8.85	9.50	9.99	11.60	3.54	4.06	4.70	5.20	6.80
	8H	8.46	8.95	9.62	10.11	11.70	3.62	4.12	4.79	5.27	6.87
	12H	8.51	8.98	9.68	10.13	11.75	3.66	4.13	4.83	5.28	6.90
4H	2H	5.64	6.21	6.80	7.34	8.94	2.18	2.75	3.34	3.88	5.48
	3H	7.46	7.93	8.63	9.09	10.70	3.52	3.99	4.68	5.15	6.76
	4H	8.15	8.58	9.32	9.73	11.36	4.06	4.49	5.23	5.64	7.27
	6H	8.66	9.03	9.83	10.20	11.82	4.47	4.84	5.65	6.01	7.63
	8H	8.83	9.18	10.01	10.34	11.97	4.60	4.94	5.77	6.11	7.74
	12H	8.92	9.24	10.11	10.41	12.05	4.65	4.97	5.84	6.14	7.78
8H	4H	8.10	8.45	9.28	9.61	11.25	4.33	4.68	5.50	5.84	7.47
	6H	8.67	8.95	9.86	10.16	11.79	4.84	5.13	6.04	6.34	7.96
	8H	8.89	9.14	10.09	10.32	11.97	5.03	5.28	6.23	6.47	8.12
	12H	9.02	9.24	10.22	10.42	12.10	5.15	5.37	6.35	6.55	8.23
12H	4H	8.05	8.36	9.24	9.54	11.17	4.33	4.64	5.52	5.82	7.45
	6H	8.64	8.89	9.84	10.08	11.72	4.89	5.14	6.09	6.33	7.97
	8H	8.86	9.08	10.06	10.26	11.94	5.10	5.32	6.30	6.50	8.18

END OF REPORT