

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920609

Luminaire Tested: DFN2DIP-SQ4F0-160D100US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920609
REPORT IS A COMBINATION OF REPORTS P901667 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D100US935-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22162.1 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 241.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920609

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920609

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56
2	91	84	78	72	85	79	73	69	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21
9	52	39	32	27	49	37	30	26	33	28	23	30	25	21	26	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3761	3761	3761
5°	3767	3710	3735
10°	3736	3660	3685
15°	3682	3601	3607
20°	3607	3518	3528
25°	3533	3418	3435
30°	3441	3326	3317
35°	3353	3217	3192
40°	3245	3107	3074
45°	3137	2996	2953
50°	3019	2881	2812
55°	2896	2746	2683
60°	2757	2587	2535
65°	2605	2423	2361
70°	2411	2222	2174
75°	2143	1982	2003
80°	1820	1676	1674
85°	1316	1147	1125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3137 cd/sqm

TEST NUMBER: P920609

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	504.5	2.3
10°-20°	1419.5	6.4
20°-30°	2086.1	9.4
30°-40°	2422.9	10.9
40°-50°	2419.9	10.9
50°-60°	2110.1	9.5
60°-70°	1559.8	7.0
70°-80°	882.5	4.0
80°-90°	238.0	1.1
90°-100°	95.8	0.4
100°-110°	357.2	1.6
110°-120°	947.3	4.3
120°-130°	1571.2	7.1
130°-140°	1669.0	7.5
140°-150°	1551.1	7.0
150°-160°	1247.1	5.6
160°-170°	803.6	3.6
170°-180°	276.6	1.2
0°-30°	4010.1	18.1
0°-40°	6433.0	29.0
0°-60°	10963.0	49.5
0°-90°	13643.3	61.6
90°-120°	1400.3	6.3
90°-150°	6191.6	27.9
90°-180°	8519.0	38.4
0°-180°	22162.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5360	5360	5360	5360	5360	
5°	5360	5340	5283	5324	5314	509
15°	5103	5072	5005	5026	5000	1437
25°	4618	4577	4490	4500	4490	2125
35°	3984	3933	3850	3819	3794	2488
45°	3242	3206	3129	3072	3052	2502
55°	2454	2423	2361	2299	2273	2194
65°	1655	1624	1572	1526	1500	1636
75°	866	856	830	799	809	924
85°	211	206	201	185	180	235
90°	2	25	42	53	57	21
95°	137	67	82	93	90	162
105°	639	702	128	151	160	683
115°	1209	1245	1297	324	172	1190
125°	1709	1737	1777	1792	1798	1524
135°	2115	2149	2168	2189	2185	1634
145°	2454	2452	2487	2502	2492	1535
155°	2702	2683	2708	2721	2704	1245
165°	2847	2834	2841	2855	2841	804
175°	2912	2897	2902	2916	2895	277
180°	2906	2906	2906	2906	2906	

TEST NUMBER: P920609

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5360.3	5360.3	5360.3	5360.3	5360.3
2.5°	5391.5	5365.7	5308.9	5360.3	5350.4
5°	5360.3	5340.1	5283.2	5324.2	5314.3
7.5°	5324.2	5293.6	5236.7	5278.3	5267.8
10°	5267.8	5231.8	5170.0	5211.0	5195.7
12.5°	5190.3	5159.6	5097.8	5123.5	5113.1
15°	5102.7	5072.1	5004.8	5025.6	4999.9
17.5°	4994.5	4963.8	4896.6	4922.2	4896.6
20°	4875.7	4845.2	4772.9	4788.3	4768.0
22.5°	4757.7	4711.2	4643.9	4643.9	4633.5
25°	4618.2	4577.2	4489.7	4499.6	4489.7
27.5°	4463.4	4427.3	4360.6	4345.4	4319.6
30°	4309.2	4267.7	4190.6	4175.2	4154.5
32.5°	4144.1	4113.5	4030.8	3999.7	3978.9
35°	3984.4	3933.0	3850.4	3819.2	3793.6
37.5°	3804.0	3757.5	3674.9	3638.7	3613.1
40°	3618.5	3577.0	3494.4	3448.5	3427.7
42.5°	3438.1	3396.6	3314.5	3262.6	3231.9
45°	3242.3	3206.2	3128.6	3072.2	3051.5
47.5°	3051.5	3015.4	2932.8	2875.9	2845.3
50°	2850.2	2824.5	2752.4	2680.1	2654.5
52.5°	2654.5	2618.4	2551.7	2494.7	2458.7
55°	2453.8	2422.6	2360.8	2299.0	2273.3
57.5°	2252.5	2226.8	2159.6	2097.7	2077.0
60°	2051.2	2031.0	1958.9	1901.9	1886.6
62.5°	1855.5	1819.4	1768.0	1716.6	1695.8
65°	1654.8	1623.6	1572.2	1525.8	1500.0
67.5°	1448.6	1422.4	1376.5	1340.3	1319.6
70°	1257.7	1237.0	1190.5	1154.4	1134.2
72.5°	1062.0	1041.2	1015.5	979.4	964.1
75°	865.6	855.8	829.6	798.9	809.3
77.5°	690.7	669.9	659.5	644.2	628.9
80°	515.7	510.2	499.8	484.5	474.2
82.5°	350.5	350.5	345.6	324.9	324.9
85°	211.1	206.1	201.2	185.4	180.5
87.5°	93.0	82.6	72.2	56.9	51.4
90°	2.0	25.2	41.9	52.7	56.7
92.5°	52.7	44.2	50.5	54.7	56.7
95°	136.6	67.2	81.9	92.6	90.4
97.5°	245.9	73.6	107.1	113.6	115.6
100°	372.3	84.1	119.9	136.6	140.9
102.5°	510.8	506.9	124.1	147.1	153.5
105°	639.2	702.3	128.4	151.3	159.8
107.5°	788.5	840.9	132.6	155.6	164.0
110°	931.5	975.5	368.0	157.8	166.0

TEST NUMBER: P920609

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1066.1	1103.8	1068.2	161.8	168.3
115°	1208.9	1244.7	1297.4	323.8	172.5
117.5°	1333.0	1375.0	1410.9	1110.1	559.3
120°	1471.9	1503.3	1541.3	1566.5	1282.6
122.5°	1589.5	1623.2	1665.3	1677.8	1680.1
125°	1709.3	1736.8	1776.8	1791.5	1797.7
127.5°	1818.7	1848.1	1879.8	1900.8	1902.8
130°	1921.7	1955.5	1978.5	2001.6	1999.7
132.5°	2026.9	2054.3	2077.3	2096.3	2094.3
135°	2115.3	2149.0	2167.7	2188.9	2184.7
137.5°	2207.7	2232.9	2254.1	2275.1	2268.8
140°	2298.0	2315.1	2338.0	2357.0	2346.5
142.5°	2373.9	2388.7	2415.9	2432.6	2422.2
145°	2453.8	2451.6	2487.3	2502.1	2491.6
147.5°	2523.0	2516.8	2552.4	2562.9	2554.8
150°	2590.4	2575.7	2609.4	2621.9	2611.4
152.5°	2647.1	2630.3	2661.9	2674.5	2659.8
155°	2701.8	2683.0	2708.3	2720.8	2704.0
157.5°	2746.0	2729.3	2748.2	2762.9	2746.0
160°	2784.0	2771.2	2784.0	2796.4	2781.7
162.5°	2817.4	2804.9	2815.4	2830.1	2811.2
165°	2846.8	2834.3	2840.6	2855.3	2840.6
167.5°	2870.1	2857.3	2863.9	2878.6	2859.5
170°	2889.0	2876.3	2880.6	2895.3	2876.3
172.5°	2901.5	2889.0	2893.3	2908.0	2889.0
175°	2912.0	2897.3	2901.5	2916.3	2895.3
177.5°	2916.3	2901.5	2903.8	2918.5	2899.5
180°	2905.8	2905.8	2905.8	2905.8	2905.8

TEST NUMBER: P920609

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.89	13.87	13.74	14.74	15.84	12.45	13.42	13.30	14.29	15.39
	3H	14.56	15.44	15.43	16.32	17.44	14.07	14.95	14.94	15.83	16.95
	4H	15.16	15.99	16.04	16.88	18.01	14.66	15.49	15.54	16.38	17.51
	6H	15.57	16.33	16.46	17.23	18.37	15.07	15.83	15.96	16.73	17.87
	8H	15.68	16.41	16.58	17.32	18.46	15.18	15.90	16.08	16.82	17.96
	12H	15.73	16.43	16.64	17.33	18.50	15.22	15.92	16.13	16.82	17.99
4H	2H	13.37	14.19	14.25	15.08	16.22	13.01	13.84	13.90	14.73	15.86
	3H	15.25	15.94	16.14	16.86	18.01	14.84	15.53	15.73	16.45	17.60
	4H	15.97	16.60	16.88	17.52	18.69	15.54	16.18	16.45	17.09	18.27
	6H	16.49	17.04	17.42	17.98	19.15	16.06	16.61	16.98	17.55	18.72
	8H	16.65	17.16	17.57	18.09	19.28	16.21	16.72	17.14	17.66	18.84
	12H	16.73	17.19	17.67	18.14	19.34	16.28	16.74	17.22	17.69	18.89
8H	4H	16.17	16.68	17.10	17.62	18.81	15.80	16.31	16.72	17.24	18.43
	6H	16.82	17.24	17.77	18.21	19.40	16.43	16.85	17.38	17.83	19.02
	8H	17.04	17.41	18.00	18.38	19.59	16.65	17.02	17.61	17.99	19.19
	12H	17.18	17.51	18.14	18.47	19.72	16.77	17.10	17.73	18.06	19.31
12H	4H	16.17	16.62	17.11	17.58	18.77	15.80	16.26	16.74	17.21	18.40
	6H	16.85	17.22	17.81	18.19	19.39	16.48	16.85	17.44	17.82	19.02
	8H	17.10	17.43	18.06	18.39	19.64	16.72	17.05	17.68	18.01	19.26