

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917641

Luminaire Tested: DFN2DIP-SQ4F0-070D140US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917641
REPORT IS A COMBINATION OF REPORTS P901707 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D140US930-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16950.0 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 167.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917641

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917641

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1558	1558	1558
5°	1561	1537	1547
10°	1548	1516	1527
15°	1525	1492	1494
20°	1494	1457	1461
25°	1464	1416	1423
30°	1425	1378	1374
35°	1389	1333	1323
40°	1344	1287	1273
45°	1300	1241	1223
50°	1251	1193	1165
55°	1200	1138	1112
60°	1142	1072	1050
65°	1079	1004	978
70°	999	921	901
75°	888	821	830
80°	754	695	693
85°	545	475	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2067 cd/sqm

TEST NUMBER: P917641

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.0	1.2
10°-20°	588.1	3.5
20°-30°	864.2	5.1
30°-40°	1003.7	5.9
40°-50°	1002.5	5.9
50°-60°	874.2	5.2
60°-70°	646.2	3.8
70°-80°	365.6	2.2
80°-90°	103.3	0.6
90°-100°	127.0	0.7
100°-110°	473.5	2.8
110°-120°	1255.8	7.4
120°-130°	2082.9	12.3
130°-140°	2212.5	13.1
140°-150°	2056.3	12.1
150°-160°	1653.2	9.8
160°-170°	1065.3	6.3
170°-180°	366.7	2.2
0°-30°	1661.3	9.8
0°-40°	2665.1	15.7
0°-60°	4541.7	26.8
0°-90°	5656.8	33.4
90°-120°	1856.4	11.0
90°-150°	8208.1	48.4
90°-180°	11293.0	66.6
0°-180°	16950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2221	2221	2221	2221	2221	
5°	2221	2212	2189	2206	2202	211
15°	2114	2101	2073	2082	2071	595
25°	1913	1896	1860	1864	1860	880
35°	1651	1629	1595	1582	1572	1031
45°	1343	1328	1296	1273	1264	1037
55°	1016	1004	978	952	942	909
65°	686	673	651	632	621	678
75°	359	355	344	331	335	383
85°	88	85	83	77	75	98
90°	3	33	56	70	75	16
95°	181	89	109	123	120	214
105°	847	931	170	201	212	905
115°	1603	1650	1720	429	229	1578
125°	2266	2302	2355	2375	2383	2021
135°	2804	2849	2874	2902	2896	2166
145°	3253	3250	3297	3317	3303	2035
155°	3582	3557	3590	3607	3585	1650
165°	3774	3758	3766	3785	3766	1066
175°	3860	3841	3846	3866	3838	367
180°	3852	3852	3852	3852	3852	

TEST NUMBER: P917641

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2220.6	2220.6	2220.6	2220.6	2220.6
2.5°	2233.6	2222.9	2199.3	2220.6	2216.6
5°	2220.6	2212.3	2188.7	2205.7	2201.6
7.5°	2205.7	2193.0	2169.4	2186.7	2182.4
10°	2182.4	2167.4	2141.8	2158.8	2152.5
12.5°	2150.2	2137.5	2111.9	2122.5	2118.2
15°	2114.0	2101.3	2073.4	2082.0	2071.3
17.5°	2069.1	2056.4	2028.5	2039.2	2028.5
20°	2019.9	2007.3	1977.3	1983.7	1975.3
22.5°	1971.0	1951.7	1923.9	1923.9	1919.5
25°	1913.3	1896.2	1860.0	1864.1	1860.0
27.5°	1849.1	1834.2	1806.5	1800.2	1789.5
30°	1785.3	1768.0	1736.1	1729.7	1721.1
32.5°	1716.8	1704.1	1669.9	1657.0	1648.4
35°	1650.7	1629.4	1595.1	1582.2	1571.6
37.5°	1575.9	1556.6	1522.4	1507.5	1496.8
40°	1499.1	1481.9	1447.6	1428.6	1420.0
42.5°	1424.3	1407.1	1373.1	1351.6	1338.9
45°	1343.2	1328.3	1296.1	1272.8	1264.1
47.5°	1264.1	1249.2	1215.0	1191.4	1178.8
50°	1180.8	1170.1	1140.2	1110.4	1099.7
52.5°	1099.7	1084.8	1057.1	1033.6	1018.6
55°	1016.5	1003.6	978.0	952.4	941.8
57.5°	933.2	922.5	894.6	869.0	860.5
60°	849.8	841.4	811.5	788.0	781.6
62.5°	768.7	753.7	732.5	711.2	702.5
65°	685.6	672.6	651.3	632.1	621.4
67.5°	600.1	589.3	570.2	555.3	546.7
70°	521.1	512.5	493.2	478.3	469.9
72.5°	439.9	431.4	420.7	405.8	399.4
75°	358.6	354.6	343.6	331.0	335.3
77.5°	286.2	277.5	273.2	266.8	260.6
80°	213.6	211.4	207.1	200.7	196.4
82.5°	145.2	145.2	143.2	134.6	134.6
85°	87.5	85.4	83.4	76.8	74.8
87.5°	38.5	34.2	29.9	23.6	21.3
90°	2.6	33.4	55.6	69.9	75.2
92.5°	69.9	58.6	66.9	72.5	75.2
95°	181.1	89.0	108.6	122.8	119.8
97.5°	326.0	97.7	142.0	150.6	153.3
100°	493.5	111.5	158.9	181.1	186.7
102.5°	677.2	671.9	164.5	194.9	203.6
105°	847.3	931.1	170.2	200.6	211.8
107.5°	1045.3	1114.8	175.8	206.2	217.4
110°	1234.9	1293.2	487.9	209.2	220.1

TEST NUMBER: P917641

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1413.3	1463.3	1416.0	214.5	223.1
115°	1602.7	1650.0	1719.9	429.3	228.7
117.5°	1767.2	1822.8	1870.5	1471.6	741.4
120°	1951.3	1992.9	2043.2	2076.6	1700.3
122.5°	2107.1	2151.8	2207.7	2224.3	2227.3
125°	2266.0	2302.4	2355.4	2374.9	2383.2
127.5°	2411.0	2450.1	2492.0	2519.8	2522.5
130°	2547.6	2592.4	2622.8	2653.6	2650.9
132.5°	2687.1	2723.4	2753.9	2779.0	2776.4
135°	2804.2	2848.9	2873.7	2901.8	2896.2
137.5°	2926.7	2960.1	2988.2	3016.0	3007.8
140°	3046.5	3069.0	3099.4	3124.6	3110.7
142.5°	3147.1	3166.6	3202.7	3224.9	3211.0
145°	3253.0	3250.0	3297.4	3317.0	3303.0
147.5°	3344.8	3336.4	3383.8	3397.7	3386.7
150°	3434.1	3414.6	3459.2	3475.8	3461.9
152.5°	3509.2	3487.0	3528.8	3545.7	3526.1
155°	3581.7	3556.9	3590.3	3606.9	3584.7
157.5°	3640.3	3618.1	3643.3	3662.8	3640.3
160°	3690.6	3673.7	3690.6	3707.2	3687.7
162.5°	3735.0	3718.4	3732.4	3751.8	3726.7
165°	3774.0	3757.5	3765.8	3785.3	3765.8
167.5°	3804.8	3788.0	3796.5	3816.1	3790.9
170°	3829.9	3813.1	3818.7	3838.3	3813.1
172.5°	3846.5	3829.9	3835.6	3855.1	3829.9
175°	3860.4	3840.9	3846.5	3866.1	3838.3
177.5°	3866.1	3846.5	3849.5	3869.0	3843.9
180°	3852.1	3852.1	3852.1	3852.1	3852.1



TEST NUMBER: P917641

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.05	7.78	8.14	8.87	10.36	6.61	7.34	7.70	8.42	9.91
	3H	8.71	9.36	9.80	10.46	11.96	8.22	8.87	9.31	9.97	11.47
	4H	9.29	9.91	10.40	11.01	12.52	8.80	9.42	9.90	10.51	12.03
	6H	9.69	10.26	10.80	11.36	12.88	9.19	9.76	10.30	10.86	12.38
	8H	9.79	10.33	10.91	11.45	12.97	9.29	9.83	10.41	10.95	12.47
	12H	9.84	10.35	10.96	11.46	13.00	9.33	9.84	10.45	10.95	12.49
4H	2H	7.50	8.12	8.61	9.21	10.73	7.14	7.76	8.26	8.86	10.37
	3H	9.36	9.87	10.48	11.00	12.52	8.95	9.47	10.07	10.59	12.12
	4H	10.07	10.54	11.19	11.66	13.20	9.64	10.12	10.77	11.23	12.78
	6H	10.58	10.99	11.71	12.12	13.66	10.15	10.56	11.28	11.69	13.23
	8H	10.73	11.11	11.86	12.24	13.79	10.29	10.67	11.42	11.80	13.35
	12H	10.80	11.14	11.95	12.28	13.84	10.35	10.69	11.50	11.83	13.39
8H	4H	10.25	10.64	11.39	11.76	13.32	9.88	10.26	11.01	11.39	12.94
	6H	10.89	11.20	12.04	12.37	13.92	10.50	10.82	11.65	11.99	13.54
	8H	11.11	11.38	12.27	12.53	14.10	10.72	10.99	11.87	12.14	13.71
	12H	11.24	11.48	12.40	12.62	14.23	10.83	11.07	11.99	12.21	13.82
12H	4H	10.23	10.58	11.38	11.72	13.28	9.87	10.21	11.01	11.35	12.91
	6H	10.91	11.19	12.07	12.34	13.91	10.54	10.82	11.70	11.97	13.54
	8H	11.15	11.39	12.32	12.54	14.15	10.77	11.01	11.94	12.16	13.77