

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920622

Luminaire Tested: DFN2DIP-SQ4F0-160D140US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920622
REPORT IS A COMBINATION OF REPORTS P900202 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D140US935-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22377.3 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 272.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920622

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920622

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	24	21	19
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3995	3995	3995
5°	4001	3932	3958
10°	3962	3856	3830
15°	3907	3729	3632
20°	3835	3554	3389
25°	3761	3358	3154
30°	3662	3157	2855
35°	3564	2940	2593
40°	3465	2716	2292
45°	3350	2468	2019
50°	3232	2216	1752
55°	3107	1948	1496
60°	2964	1667	1233
65°	2798	1382	1111
70°	2598	1115	1007
75°	2347	985	919
80°	1982	829	801
85°	1380	558	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3350 cd/sqm

TEST NUMBER: P920622

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	533.6	2.4
10°-20°	1464.9	6.5
20°-30°	2056.6	9.2
30°-40°	2241.8	10.0
40°-50°	2060.5	9.2
50°-60°	1618.2	7.2
60°-70°	1053.3	4.7
70°-80°	542.2	2.4
80°-90°	149.3	0.7
90°-100°	235.9	1.1
100°-110°	749.5	3.3
110°-120°	1282.7	5.7
120°-130°	1686.9	7.5
130°-140°	1893.5	8.5
140°-150°	1856.8	8.3
150°-160°	1557.6	7.0
160°-170°	1033.0	4.6
170°-180°	361.0	1.6
0°-30°	4055.1	18.1
0°-40°	6296.9	28.1
0°-60°	9975.6	44.6
0°-90°	11720.4	52.4
90°-120°	2268.1	10.1
90°-150°	7705.3	34.4
90°-180°	10657.0	47.6
0°-180°	22377.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5694	5694	5694	5694	5694	
5°	5694	5668	5601	5647	5632	540
15°	5415	5358	5184	5086	5034	1526
25°	4916	4751	4410	4200	4122	2261
35°	4236	3973	3520	3195	3081	2651
45°	3463	3117	2576	2210	2087	2674
55°	2633	2231	1674	1366	1268	2353
65°	1778	1360	897	722	706	1762
75°	948	587	412	376	371	1003
85°	221	113	98	98	98	254
90°	3	41	113	106	109	22
95°	168	200	206	206	200	187
105°	692	701	708	714	714	730
115°	1287	1306	1300	1296	1287	1273
125°	1872	1901	1892	1881	1878	1673
135°	2422	2457	2464	2461	2451	1872
145°	2940	2963	2981	2985	2972	1837
155°	3362	3371	3381	3397	3387	1547
165°	3657	3654	3654	3677	3660	1032
175°	3805	3796	3789	3812	3793	362
180°	3812	3812	3812	3812	3812	

TEST NUMBER: P920622

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5693.6	5693.6	5693.6	5693.6	5693.6
2.5°	5719.3	5693.6	5636.7	5688.7	5678.3
5°	5693.6	5667.9	5600.6	5647.1	5631.8
7.5°	5647.1	5616.5	5544.3	5564.5	5538.9
10°	5585.4	5549.3	5446.5	5430.7	5400.0
12.5°	5508.2	5461.8	5322.4	5291.8	5235.0
15°	5415.3	5358.5	5183.6	5085.7	5034.3
17.5°	5307.1	5224.5	5008.1	4894.9	4812.4
20°	5183.6	5080.2	4822.7	4694.2	4580.6
22.5°	5049.6	4930.9	4631.9	4457.0	4379.9
25°	4915.7	4750.6	4410.5	4199.5	4121.9
27.5°	4756.1	4580.6	4204.4	3962.3	3843.7
30°	4586.0	4389.8	3977.6	3715.2	3575.8
32.5°	4421.0	4183.7	3761.6	3452.3	3323.2
35°	4235.6	3972.6	3519.5	3194.7	3081.1
37.5°	4055.2	3771.5	3292.6	2936.7	2808.2
40°	3864.4	3555.6	3055.3	2689.6	2555.7
42.5°	3668.7	3339.0	2818.6	2437.1	2308.6
45°	3462.6	3117.2	2576.4	2210.2	2086.6
47.5°	3266.9	2901.2	2344.7	1978.4	1865.3
50°	3050.4	2684.7	2117.8	1761.9	1654.2
52.5°	2838.9	2452.4	1901.3	1561.3	1463.4
55°	2632.8	2230.9	1674.5	1365.5	1267.7
57.5°	2421.7	2009.6	1473.9	1185.2	1102.6
60°	2205.3	1793.1	1262.2	999.9	917.3
62.5°	1994.2	1582.1	1081.8	834.7	793.8
65°	1777.8	1360.1	896.6	721.6	705.8
67.5°	1571.7	1154.0	721.6	633.6	618.3
70°	1355.2	953.4	597.5	546.1	525.4
72.5°	1149.1	767.5	499.6	458.7	448.2
75°	948.0	587.1	412.2	376.1	371.2
77.5°	747.3	417.1	324.7	303.9	293.6
80°	561.5	299.0	247.1	226.9	226.9
82.5°	391.4	201.2	170.0	159.6	159.6
85°	221.4	113.1	97.9	97.9	97.9
87.5°	82.6	41.0	41.0	36.1	36.1
90°	3.4	41.4	112.6	105.7	109.2
92.5°	71.3	96.5	100.0	103.4	103.4
95°	167.8	200.0	205.7	205.7	200.0
97.5°	279.3	309.2	321.8	321.8	321.8
100°	408.0	434.5	443.6	443.6	440.1
102.5°	543.6	563.2	575.8	579.3	575.8
105°	691.9	701.1	708.0	713.7	713.7
107.5°	839.0	852.8	852.8	855.1	839.0
110°	981.5	999.9	999.9	999.9	990.7

TEST NUMBER: P920622

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1135.5	1155.0	1151.6	1142.4	1135.5
115°	1287.2	1305.6	1299.8	1296.4	1287.2
117.5°	1437.8	1463.1	1447.0	1437.8	1428.6
120°	1589.5	1614.8	1589.5	1589.5	1579.2
122.5°	1727.4	1759.5	1743.5	1734.3	1727.4
125°	1872.2	1900.9	1891.7	1881.4	1877.9
127.5°	2013.5	2049.2	2036.5	2022.7	2013.5
130°	2145.7	2187.1	2181.3	2174.5	2161.8
132.5°	2294.0	2326.2	2328.5	2312.4	2303.2
135°	2421.6	2457.2	2464.1	2460.6	2451.4
137.5°	2564.1	2592.8	2598.6	2596.3	2582.5
140°	2689.3	2718.1	2734.2	2734.2	2721.5
142.5°	2818.0	2846.8	2856.0	2859.5	2846.8
145°	2939.9	2962.9	2981.3	2984.7	2972.1
147.5°	3049.1	3077.8	3091.6	3097.4	3084.7
150°	3161.7	3181.2	3193.9	3204.2	3193.9
152.5°	3261.7	3281.3	3297.4	3309.9	3297.4
155°	3361.7	3370.9	3381.2	3397.3	3387.0
157.5°	3447.9	3454.8	3460.5	3483.5	3467.4
160°	3524.9	3531.8	3535.3	3554.8	3540.9
162.5°	3596.1	3596.1	3599.6	3621.4	3605.3
165°	3657.1	3653.6	3653.6	3676.6	3660.5
167.5°	3712.2	3701.9	3701.9	3724.8	3708.7
170°	3753.6	3744.4	3740.9	3763.9	3744.4
172.5°	3782.4	3773.2	3769.7	3792.7	3773.2
175°	3805.4	3796.1	3789.3	3812.2	3792.7
177.5°	3817.9	3808.8	3801.9	3821.4	3801.9
180°	3812.2	3812.2	3812.2	3812.2	3812.2

TEST NUMBER: P920622

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.19	13.04	13.13	14.00	15.23	8.15	9.00	9.09	9.96	11.20
	3H	13.87	14.63	14.83	15.60	16.86	9.34	10.10	10.30	11.07	12.33
	4H	14.49	15.20	15.46	16.17	17.44	9.79	10.51	10.76	11.48	12.75
	6H	14.91	15.57	15.89	16.55	17.83	10.12	10.78	11.10	11.75	13.04
	8H	15.04	15.67	16.03	16.66	17.94	10.21	10.84	11.19	11.83	13.11
	12H	15.11	15.70	16.10	16.69	17.99	10.25	10.85	11.24	11.83	13.14
4H	2H	12.21	12.93	13.19	13.90	15.17	8.75	9.47	9.73	10.44	11.71
	3H	14.05	14.64	15.03	15.64	16.93	10.10	10.70	11.09	11.70	12.98
	4H	14.74	15.29	15.74	16.28	17.59	10.65	11.20	11.65	12.19	13.50
	6H	15.26	15.73	16.27	16.75	18.05	11.07	11.54	12.08	12.56	13.87
	8H	15.44	15.88	16.45	16.89	18.21	11.20	11.64	12.21	12.65	13.97
	12H	15.54	15.93	16.56	16.96	18.29	11.27	11.67	12.29	12.69	14.02
8H	4H	14.71	15.15	15.72	16.16	17.48	10.94	11.37	11.94	12.38	13.70
	6H	15.28	15.64	16.31	16.69	18.01	11.46	11.82	12.49	12.87	14.19
	8H	15.50	15.82	16.54	16.86	18.20	11.65	11.97	12.69	13.00	14.34
	12H	15.65	15.93	16.69	16.96	18.34	11.77	12.05	12.81	13.08	14.46
12H	4H	14.67	15.06	15.69	16.08	17.41	10.94	11.34	11.97	12.36	13.69
	6H	15.26	15.58	16.30	16.61	17.95	11.51	11.83	12.55	12.86	14.20
	8H	15.48	15.76	16.52	16.79	18.18	11.72	12.00	12.76	13.03	14.41

END OF REPORT