

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917662

Luminaire Tested: DFN2DIP-SQ4F0-080D090US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917662
REPORT IS A COMBINATION OF REPORTS P900118 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D090US930-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12037.8 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 138.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917662
CATALOG NUMBER: DFN2DIP-SQ4F0-080D090US930-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P917662

CATALOG NUMBER: DFN2DIP-SQ4F0-080D090US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46			46
1	97	93	90	86	89	86	83	80	72	70	68	59	57	56	47	46	45	40			40
2	89	82	76	71	82	75	70	66	63	60	57	52	50	47	42	40	39	34			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33	29			29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	26			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22			22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16			16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1892	1892	1892
5°	1895	1862	1874
10°	1876	1826	1813
15°	1850	1766	1720
20°	1816	1683	1604
25°	1781	1590	1493
30°	1734	1495	1352
35°	1688	1392	1228
40°	1641	1286	1085
45°	1586	1168	956
50°	1530	1049	830
55°	1471	922	708
60°	1403	789	584
65°	1325	654	526
70°	1230	528	477
75°	1111	466	435
80°	938	392	379
85°	653	264	289

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1825 cd/sqm



TEST NUMBER: P917662

CATALOG NUMBER: DFN2DIP-SQ4F0-080D090US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	2.1
10°-20°	693.6	5.8
20°-30°	973.7	8.1
30°-40°	1061.4	8.8
40°-50°	975.6	8.1
50°-60°	766.2	6.4
60°-70°	498.7	4.1
70°-80°	256.7	2.1
80°-90°	72.1	0.6
90°-100°	143.6	1.2
100°-110°	456.3	3.8
110°-120°	780.8	6.5
120°-130°	1026.9	8.5
130°-140°	1152.6	9.6
140°-150°	1130.3	9.4
150°-160°	948.2	7.9
160°-170°	628.8	5.2
170°-180°	219.8	1.8
0°-30°	1919.9	15.9
0°-40°	2981.4	24.8
0°-60°	4723.1	39.2
0°-90°	5550.6	46.1
90°-120°	1380.7	11.5
90°-150°	4690.5	39.0
90°-180°	6487.0	53.9
0°-180°	12037.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2696	2696	2696	2696	2696	
5°	2696	2684	2652	2674	2666	256
15°	2564	2537	2454	2408	2384	722
25°	2327	2249	2088	1988	1952	1070
35°	2005	1881	1666	1513	1459	1255
45°	1639	1476	1220	1046	988	1266
55°	1246	1056	793	646	600	1114
65°	842	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	2	25	69	64	66	12
95°	102	122	125	125	122	114
105°	421	427	431	434	434	444
115°	784	795	791	789	784	775
125°	1140	1157	1152	1145	1143	1018
135°	1474	1496	1500	1498	1492	1139
145°	1790	1804	1815	1817	1809	1118
155°	2046	2052	2058	2068	2062	942
165°	2226	2224	2224	2238	2228	628
175°	2316	2311	2307	2321	2309	220
180°	2321	2321	2321	2321	2321	



TEST NUMBER: P917662

CATALOG NUMBER: DFN2DIP-SQ4F0-080D090US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2695.7	2695.7	2695.7	2695.7	2695.7
2.5°	2707.9	2695.7	2668.8	2693.3	2688.4
5°	2695.7	2683.6	2651.7	2673.7	2666.4
7.5°	2673.7	2659.2	2625.0	2634.6	2622.4
10°	2644.4	2627.4	2578.7	2571.2	2556.7
12.5°	2608.0	2586.0	2519.9	2505.4	2478.5
15°	2563.9	2537.0	2454.2	2407.9	2383.5
17.5°	2512.7	2473.6	2371.1	2317.6	2278.4
20°	2454.2	2405.3	2283.4	2222.6	2168.7
22.5°	2390.8	2334.6	2193.1	2110.2	2073.7
25°	2327.4	2249.2	2088.2	1988.3	1951.6
27.5°	2251.8	2168.7	1990.6	1876.0	1819.8
30°	2171.3	2078.4	1883.3	1759.0	1693.0
32.5°	2093.1	1980.8	1781.0	1634.5	1573.4
35°	2005.4	1880.9	1666.3	1512.6	1458.7
37.5°	1919.9	1785.7	1558.9	1390.4	1329.6
40°	1829.7	1683.4	1446.6	1273.4	1210.0
42.5°	1737.0	1580.9	1334.5	1153.9	1093.0
45°	1639.4	1475.9	1219.8	1046.4	988.0
47.5°	1546.8	1373.6	1110.1	936.7	883.1
50°	1444.2	1271.1	1002.7	834.2	783.2
52.5°	1344.1	1161.1	900.2	739.2	692.9
55°	1246.5	1056.3	792.8	646.5	600.2
57.5°	1146.6	951.5	697.8	561.2	522.0
60°	1044.1	849.0	597.6	473.4	434.3
62.5°	944.2	749.0	512.3	395.3	375.9
65°	841.7	643.9	424.4	341.7	334.1
67.5°	744.1	546.4	341.7	299.9	292.8
70°	641.6	451.4	282.9	258.5	248.7
72.5°	544.0	363.4	236.6	217.2	212.2
75°	448.8	278.0	195.2	178.1	175.8
77.5°	353.8	197.5	153.8	143.9	139.0
80°	265.8	141.6	117.0	107.4	107.4
82.5°	185.3	95.2	80.5	75.6	75.6
85°	104.8	53.6	46.3	46.3	46.3
87.5°	39.1	19.4	19.4	17.1	17.1
90°	2.1	25.2	68.6	64.3	66.4
92.5°	43.4	58.8	60.9	62.9	62.9
95°	102.2	121.7	125.2	125.2	121.7
97.5°	170.0	188.2	195.9	195.9	195.9
100°	248.3	264.5	270.0	270.0	268.0
102.5°	330.9	342.8	350.5	352.6	350.5
105°	421.2	426.7	431.0	434.5	434.5
107.5°	510.7	519.1	519.1	520.5	510.7
110°	597.5	608.7	608.7	608.7	603.1



TEST NUMBER: P917662

CATALOG NUMBER: DFN2DIP-SQ4F0-080D090US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	691.2	703.1	701.0	695.4	691.2
115°	783.6	794.8	791.2	789.2	783.6
117.5°	875.2	890.6	880.8	875.2	869.6
120°	967.6	982.9	967.6	967.6	961.2
122.5°	1051.5	1071.1	1061.4	1055.7	1051.5
125°	1139.7	1157.2	1151.6	1145.2	1143.2
127.5°	1225.7	1247.4	1239.7	1231.3	1225.7
130°	1306.2	1331.4	1327.9	1323.6	1316.0
132.5°	1396.4	1416.0	1417.4	1407.6	1402.1
135°	1474.1	1495.7	1500.0	1497.9	1492.3
137.5°	1560.8	1578.3	1581.8	1580.5	1572.1
140°	1637.1	1654.6	1664.3	1664.3	1656.7
142.5°	1715.5	1732.9	1738.5	1740.7	1732.9
145°	1789.7	1803.6	1814.8	1816.9	1809.2
147.5°	1856.1	1873.6	1882.0	1885.5	1877.8
150°	1924.7	1936.6	1944.2	1950.5	1944.2
152.5°	1985.5	1997.4	2007.2	2014.9	2007.2
155°	2046.4	2051.9	2058.3	2068.1	2061.8
157.5°	2098.8	2103.1	2106.6	2120.5	2110.7
160°	2145.7	2149.9	2152.1	2163.9	2155.5
162.5°	2189.1	2189.1	2191.2	2204.5	2194.7
165°	2226.2	2224.1	2224.1	2238.1	2228.3
167.5°	2259.8	2253.5	2253.5	2267.4	2257.6
170°	2285.0	2279.3	2277.3	2291.2	2279.3
172.5°	2302.4	2296.9	2294.7	2308.8	2296.9
175°	2316.4	2310.8	2306.6	2320.7	2308.8
177.5°	2324.1	2318.5	2314.3	2326.2	2314.3
180°	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P917662
 CATALOG NUMBER: DFN2DIP-SQ4F0-080D090US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.00	9.80	9.99	10.80	12.13	4.96	5.76	5.95	6.76	8.09
	3H	10.68	11.39	11.68	12.40	13.75	6.14	6.86	7.15	7.87	9.22
	4H	11.29	11.96	12.31	12.98	14.34	6.59	7.27	7.61	8.29	9.64
	6H	11.71	12.33	12.74	13.35	14.72	6.91	7.54	7.94	8.56	9.93
	8H	11.84	12.43	12.87	13.47	14.83	7.00	7.60	8.04	8.63	10.00
	12H	11.90	12.46	12.94	13.49	14.88	7.05	7.61	8.09	8.64	10.03
4H	2H	9.01	9.69	10.04	10.70	12.06	5.55	6.23	6.58	7.24	8.60
	3H	10.84	11.41	11.88	12.45	13.82	6.90	7.46	7.93	8.51	9.88
	4H	11.54	12.05	12.58	13.09	14.48	7.45	7.96	8.49	9.00	10.39
	6H	12.06	12.50	13.11	13.56	14.94	7.87	8.31	8.92	9.37	10.76
	8H	12.23	12.64	13.28	13.70	15.10	8.00	8.41	9.05	9.46	10.86
	12H	12.33	12.70	13.40	13.77	15.18	8.06	8.43	9.13	9.50	10.91
8H	4H	11.50	11.92	12.55	12.97	14.37	7.73	8.14	8.78	9.19	10.60
	6H	12.07	12.41	13.15	13.51	14.91	8.25	8.59	9.32	9.68	11.08
	8H	12.29	12.59	13.37	13.67	15.09	8.44	8.74	9.52	9.82	11.24
	12H	12.43	12.70	13.52	13.77	15.23	8.56	8.82	9.64	9.89	11.35
12H	4H	11.45	11.83	12.52	12.89	14.30	7.73	8.10	8.80	9.17	10.58
	6H	12.05	12.35	13.13	13.42	14.85	8.30	8.60	9.38	9.67	11.09
	8H	12.27	12.53	13.36	13.61	15.07	8.51	8.77	9.59	9.84	11.30