

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917673

Luminaire Tested: DFN2DIP-SQ4F0-080D120US930-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P917673  
REPORT IS A COMBINATION OF REPORTS P901691 AND P898471  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-080D120US930-FLLONL  
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16142.9 lumens  
Efficiency: N/A  
Efficacy: 100.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 161.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9954  
Total Harmonic Distortion (THDi): 0.076  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P917673  
CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US930-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P917673

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US930-FLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	21
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1781	1781	1781
5°	1784	1756	1768
10°	1769	1733	1745
15°	1743	1705	1708
20°	1708	1666	1670
25°	1673	1618	1626
30°	1629	1575	1571
35°	1587	1523	1511
40°	1536	1471	1455
45°	1485	1419	1398
50°	1430	1364	1331
55°	1371	1300	1270
60°	1305	1225	1200
65°	1233	1147	1118
70°	1142	1052	1029
75°	1015	938	949
80°	862	794	792
85°	623	543	532

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1770 cd/sqm



TEST NUMBER: P917673

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US930-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	238.9	1.5
10°-20°	672.1	4.2
20°-30°	987.7	6.1
30°-40°	1147.1	7.1
40°-50°	1145.7	7.1
50°-60°	999.0	6.2
60°-70°	738.5	4.6
70°-80°	417.8	2.6
80°-90°	116.1	0.7
90°-100°	108.9	0.7
100°-110°	405.9	2.5
110°-120°	1076.4	6.7
120°-130°	1785.3	11.1
130°-140°	1896.5	11.7
140°-150°	1762.5	10.9
150°-160°	1417.0	8.8
160°-170°	913.1	5.7
170°-180°	314.3	1.9
0°-30°	1898.6	11.8
0°-40°	3045.8	18.9
0°-60°	5190.5	32.2
0°-90°	6463.0	40.0
90°-120°	1591.2	9.9
90°-150°	7035.5	43.6
90°-180°	9680.0	60.0
0°-180°	16142.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2538	2538	2538	2538	2538	
5°	2538	2528	2501	2521	2516	241
15°	2416	2402	2370	2379	2367	680
25°	2186	2167	2126	2130	2126	1006
35°	1886	1862	1823	1808	1796	1178
45°	1535	1518	1481	1455	1445	1185
55°	1162	1147	1118	1088	1076	1039
65°	784	769	744	722	710	775
75°	410	405	393	378	383	438
85°	100	98	95	88	85	112
90°	2	29	48	60	64	15
95°	155	76	93	105	103	184
105°	726	798	146	172	182	776
115°	1374	1414	1474	368	196	1352
125°	1942	1974	2019	2036	2043	1732
135°	2404	2442	2463	2487	2482	1857
145°	2788	2786	2826	2843	2831	1744
155°	3070	3049	3077	3092	3073	1415
165°	3235	3221	3228	3245	3228	914
175°	3309	3292	3297	3314	3290	315
180°	3302	3302	3302	3302	3302	



TEST NUMBER: P917673

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US930-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2537.9	2537.9	2537.9	2537.9	2537.9
2.5°	2552.6	2540.5	2513.6	2537.9	2533.2
5°	2537.9	2528.3	2501.4	2520.8	2516.2
7.5°	2520.8	2506.3	2479.4	2499.1	2494.2
10°	2494.2	2477.0	2447.8	2467.2	2460.0
12.5°	2457.4	2442.9	2413.6	2425.8	2420.9
15°	2416.0	2401.5	2369.6	2379.4	2367.3
17.5°	2364.7	2350.2	2318.3	2330.5	2318.3
20°	2308.5	2294.0	2259.8	2267.1	2257.5
22.5°	2252.6	2230.6	2198.7	2198.7	2193.8
25°	2186.5	2167.1	2125.7	2130.4	2125.7
27.5°	2113.3	2096.2	2064.6	2057.3	2045.2
30°	2040.3	2020.6	1984.1	1976.9	1967.0
32.5°	1962.1	1947.6	1908.5	1893.7	1883.9
35°	1886.4	1862.1	1823.0	1808.2	1796.1
37.5°	1801.0	1779.0	1739.9	1722.8	1710.7
40°	1713.3	1693.5	1654.5	1632.7	1622.9
42.5°	1627.8	1608.1	1569.3	1544.7	1530.2
45°	1535.1	1518.0	1481.2	1454.6	1444.8
47.5°	1444.8	1427.7	1388.5	1361.6	1347.1
50°	1349.5	1337.3	1303.1	1268.9	1256.8
52.5°	1256.8	1239.7	1208.1	1181.2	1164.1
55°	1161.7	1147.0	1117.8	1088.5	1076.3
57.5°	1066.5	1054.3	1022.5	993.2	983.3
60°	971.2	961.6	927.4	900.5	893.2
62.5°	878.5	861.4	837.1	812.8	802.9
65°	783.5	768.7	744.4	722.4	710.2
67.5°	685.8	673.4	651.7	634.6	624.8
70°	595.5	585.6	563.7	546.6	537.0
72.5°	502.8	493.0	480.8	463.7	456.5
75°	409.9	405.2	392.8	378.3	383.2
77.5°	327.0	317.2	312.3	305.0	297.7
80°	244.2	241.6	236.7	229.4	224.5
82.5°	166.0	166.0	163.6	153.8	153.8
85°	100.0	97.6	95.3	87.8	85.4
87.5°	44.0	39.1	34.2	26.9	24.4
90°	2.3	28.6	47.7	59.8	64.4
92.5°	59.8	50.2	57.3	62.1	64.4
95°	155.2	76.3	93.0	105.3	102.7
97.5°	279.5	83.7	121.7	129.1	131.3
100°	423.0	95.6	136.2	155.2	160.0
102.5°	580.5	575.9	141.0	167.1	174.5
105°	726.3	798.1	145.9	171.9	181.6
107.5°	895.9	955.5	150.7	176.8	186.4
110°	1058.5	1108.5	418.2	179.3	188.7



TEST NUMBER: P917673

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US930-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1211.5	1254.3	1213.7	183.8	191.2
115°	1373.7	1414.3	1474.1	367.9	196.1
117.5°	1514.7	1562.4	1603.3	1261.3	635.5
120°	1672.5	1708.2	1751.3	1780.0	1457.4
122.5°	1806.1	1844.4	1892.4	1906.6	1909.1
125°	1942.3	1973.5	2018.9	2035.6	2042.7
127.5°	2066.5	2100.0	2136.1	2159.9	2162.2
130°	2183.7	2222.0	2248.1	2274.5	2272.2
132.5°	2303.1	2334.4	2360.5	2382.1	2379.8
135°	2403.6	2441.9	2463.2	2487.3	2482.5
137.5°	2508.6	2537.2	2561.3	2585.1	2578.1
140°	2611.3	2630.6	2656.6	2678.3	2666.4
142.5°	2697.5	2714.3	2745.2	2764.2	2752.3
145°	2788.3	2785.8	2826.3	2843.1	2831.1
147.5°	2866.9	2859.8	2900.4	2912.3	2903.0
150°	2943.5	2926.8	2965.1	2979.3	2967.4
152.5°	3007.9	2988.9	3024.7	3039.1	3022.4
155°	3070.0	3048.7	3077.4	3091.6	3072.6
157.5°	3120.2	3101.2	3122.8	3139.6	3120.2
160°	3163.4	3148.9	3163.4	3177.5	3160.8
162.5°	3201.4	3187.2	3199.1	3215.9	3194.3
165°	3234.9	3220.7	3227.8	3244.6	3227.8
167.5°	3261.3	3246.8	3254.2	3270.9	3249.4
170°	3282.8	3268.4	3273.2	3289.9	3268.4
172.5°	3297.0	3282.8	3287.7	3304.4	3282.8
175°	3308.9	3292.2	3297.0	3313.8	3289.9
177.5°	3313.8	3297.0	3299.6	3316.3	3294.8
180°	3301.9	3301.9	3301.9	3301.9	3301.9



TEST NUMBER: P917673  
 CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US930-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.29	9.07	9.33	10.11	11.52	7.85	8.63	8.89	9.67	11.08
	3H	9.95	10.65	11.00	11.70	13.13	9.46	10.16	10.51	11.21	12.64
	4H	10.54	11.20	11.60	12.25	13.69	10.04	10.70	11.10	11.76	13.19
	6H	10.94	11.55	12.01	12.60	14.05	10.44	11.04	11.51	12.10	13.55
	8H	11.04	11.62	12.11	12.70	14.14	10.54	11.12	11.61	12.19	13.63
	12H	11.09	11.64	12.17	12.71	14.17	10.58	11.13	11.66	12.20	13.66
4H	2H	8.74	9.40	9.81	10.46	11.89	8.39	9.05	9.46	10.11	11.54
	3H	10.61	11.16	11.68	12.24	13.69	10.20	10.75	11.27	11.83	13.28
	4H	11.32	11.83	12.40	12.90	14.37	10.90	11.40	11.98	12.48	13.94
	6H	11.84	12.27	12.92	13.37	14.83	11.40	11.84	12.49	12.93	14.40
	8H	11.99	12.39	13.07	13.48	14.96	11.55	11.95	12.64	13.04	14.52
	12H	12.06	12.42	13.16	13.53	15.01	11.61	11.97	12.71	13.08	14.56
8H	4H	11.51	11.92	12.60	13.01	14.48	11.13	11.54	12.22	12.63	14.11
	6H	12.14	12.48	13.25	13.61	15.08	11.76	12.10	12.87	13.23	14.70
	8H	12.37	12.66	13.48	13.77	15.27	11.97	12.27	13.09	13.38	14.87
	12H	12.50	12.76	13.62	13.86	15.40	12.09	12.34	13.21	13.45	14.99
12H	4H	11.49	11.86	12.60	12.96	14.44	11.13	11.49	12.23	12.59	14.08
	6H	12.17	12.47	13.29	13.58	15.07	11.80	12.10	12.92	13.21	14.70
	8H	12.41	12.67	13.54	13.78	15.31	12.03	12.29	13.16	13.40	14.93