

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923067

Luminaire Tested: DFN2DIP-SQ4F0-060D160US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923067
REPORT IS A COMBINATION OF REPORTS P901724 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D160US940-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18672.4 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 172.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923067

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923067

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	14	13	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1552	1552	1552
5°	1554	1527	1537
10°	1539	1498	1488
15°	1517	1448	1411
20°	1489	1380	1316
25°	1461	1304	1225
30°	1422	1226	1109
35°	1384	1142	1007
40°	1346	1055	890
45°	1301	958	784
50°	1255	861	681
55°	1207	757	581
60°	1151	648	479
65°	1087	537	431
70°	1009	433	391
75°	911	382	357
80°	769	322	311
85°	536	217	237

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2581 cd/sqm

TEST NUMBER: P923067

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.2	1.1
10°-20°	568.9	3.0
20°-30°	798.7	4.3
30°-40°	870.7	4.7
40°-50°	800.3	4.3
50°-60°	628.5	3.4
60°-70°	409.1	2.2
70°-80°	210.6	1.1
80°-90°	62.2	0.3
90°-100°	158.8	0.9
100°-110°	591.9	3.2
110°-120°	1569.8	8.4
120°-130°	2603.6	13.9
130°-140°	2765.6	14.8
140°-150°	2570.3	13.8
150°-160°	2066.5	11.1
160°-170°	1331.6	7.1
170°-180°	458.3	2.5
0°-30°	1574.9	8.4
0°-40°	2445.6	13.1
0°-60°	3874.3	20.7
0°-90°	4556.2	24.4
90°-120°	2320.4	12.4
90°-150°	10259.9	54.9
90°-180°	14116.0	75.6
0°-180°	18672.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2211	2211	2211	2211	2211	
5°	2211	2201	2175	2193	2187	210
15°	2103	2081	2013	1975	1955	593
25°	1909	1845	1713	1631	1601	878
35°	1645	1543	1367	1241	1197	1030
45°	1345	1211	1001	858	810	1039
55°	1022	866	650	530	492	914
65°	690	528	348	280	274	685
75°	368	228	160	146	144	389
85°	86	44	38	38	38	99
90°	3	42	70	87	94	17
95°	226	111	136	154	150	268
105°	1059	1164	213	251	265	1132
115°	2003	2062	2150	537	286	1972
125°	2832	2878	2944	2969	2979	2526
135°	3505	3561	3592	3627	3620	2708
145°	4066	4062	4122	4146	4129	2543
155°	4477	4446	4488	4508	4481	2063
165°	4717	4697	4707	4732	4707	1333
175°	4825	4801	4808	4832	4798	459
180°	4815	4815	4815	4815	4815	

TEST NUMBER: P923067

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2211.3	2211.3	2211.3	2211.3	2211.3
2.5°	2221.3	2211.3	2189.1	2209.3	2205.3
5°	2211.3	2201.3	2175.1	2193.3	2187.3
7.5°	2193.3	2181.3	2153.3	2161.1	2151.2
10°	2169.2	2155.2	2115.3	2109.2	2097.2
12.5°	2139.3	2121.2	2067.1	2055.2	2033.1
15°	2103.2	2081.1	2013.1	1975.1	1955.2
17.5°	2061.2	2029.1	1945.0	1901.0	1869.0
20°	2013.1	1973.0	1873.0	1823.1	1779.0
22.5°	1961.1	1915.0	1798.9	1731.0	1701.0
25°	1909.2	1845.0	1713.0	1631.0	1600.9
27.5°	1847.2	1779.0	1632.9	1538.8	1492.8
30°	1781.1	1704.9	1544.8	1442.9	1388.7
32.5°	1717.0	1624.9	1461.0	1340.8	1290.7
35°	1645.0	1542.9	1366.9	1240.7	1196.6
37.5°	1574.9	1464.7	1278.8	1140.6	1090.7
40°	1500.8	1380.9	1186.6	1044.5	992.6
42.5°	1424.9	1296.8	1094.7	946.5	896.6
45°	1344.8	1210.6	1000.7	858.4	810.4
47.5°	1268.8	1126.8	910.6	768.4	724.4
50°	1184.7	1042.7	822.5	684.3	642.5
52.5°	1102.5	952.4	738.4	606.4	568.4
55°	1022.5	866.5	650.3	530.4	492.3
57.5°	940.6	780.4	572.4	460.3	428.2
60°	856.5	696.4	490.3	388.3	356.2
62.5°	774.5	614.5	420.2	324.2	308.3
65°	690.5	528.2	348.2	280.3	274.1
67.5°	610.4	448.2	280.3	246.1	240.1
70°	526.3	370.2	232.0	212.1	204.0
72.5°	446.3	298.1	194.0	178.2	174.1
75°	368.2	228.0	160.1	146.1	144.2
77.5°	290.3	162.0	126.1	118.1	114.0
80°	218.0	116.1	95.9	88.1	88.1
82.5°	152.0	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	3.3	41.8	69.5	87.3	93.9
92.5°	87.3	73.2	83.6	90.6	93.9
95°	226.3	111.3	135.7	153.5	149.8
97.5°	407.5	122.1	177.5	188.2	191.5
100°	616.9	139.5	198.6	226.3	233.4
102.5°	846.5	839.9	205.6	243.7	254.4
105°	1059.2	1163.9	212.7	250.7	264.7
107.5°	1306.5	1393.5	219.7	257.8	271.8
110°	1543.6	1616.5	609.8	261.4	275.1

TEST NUMBER: P923067

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1766.7	1829.2	1770.0	268.1	278.8
115°	2003.3	2062.4	2149.7	536.6	285.9
117.5°	2208.9	2278.4	2338.1	1839.5	926.8
120°	2439.0	2491.1	2553.9	2595.8	2125.4
122.5°	2633.8	2689.7	2759.6	2780.3	2784.0
125°	2832.4	2877.9	2944.2	2968.6	2978.9
127.5°	3013.6	3062.5	3115.0	3149.8	3153.1
130°	3184.6	3240.4	3278.5	3316.9	3313.6
132.5°	3358.7	3404.2	3442.3	3473.7	3470.4
135°	3505.1	3561.0	3592.1	3627.2	3620.2
137.5°	3658.2	3700.1	3735.2	3770.0	3759.6
140°	3808.0	3836.1	3874.2	3905.7	3888.3
142.5°	3933.8	3958.2	4003.3	4031.1	4013.7
145°	4066.2	4062.5	4121.7	4146.0	4128.7
147.5°	4180.8	4170.4	4229.6	4247.0	4233.3
150°	4292.5	4268.1	4324.0	4344.7	4327.3
152.5°	4386.4	4358.7	4410.8	4432.0	4407.5
155°	4477.0	4446.0	4487.8	4508.5	4480.8
157.5°	4550.3	4522.6	4554.0	4578.4	4550.3
160°	4613.2	4592.0	4613.2	4633.9	4609.4
162.5°	4668.6	4648.0	4665.3	4689.7	4658.3
165°	4717.4	4696.7	4707.1	4731.5	4707.1
167.5°	4755.9	4734.8	4745.6	4769.9	4738.5
170°	4787.3	4766.3	4773.2	4797.7	4766.3
172.5°	4808.0	4787.3	4794.4	4818.8	4787.3
175°	4825.4	4801.0	4808.0	4832.4	4797.7
177.5°	4832.4	4808.0	4811.8	4836.2	4804.7
180°	4815.1	4815.1	4815.1	4815.1	4815.1

TEST NUMBER: P923067

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.62	6.27	6.77	7.41	9.01	1.58	2.24	2.73	3.37	4.97
	3H	7.29	7.87	8.45	9.02	10.63	2.75	3.34	3.91	4.49	6.10
	4H	7.89	8.45	9.06	9.59	11.21	3.20	3.75	4.37	4.90	6.52
	6H	8.31	8.82	9.48	9.97	11.60	3.51	4.02	4.69	5.17	6.80
	8H	8.43	8.92	9.61	10.08	11.70	3.60	4.08	4.77	5.25	6.87
	12H	8.49	8.95	9.67	10.11	11.75	3.63	4.10	4.82	5.25	6.90
4H	2H	5.61	6.17	6.79	7.32	8.94	2.15	2.71	3.33	3.86	5.48
	3H	7.43	7.90	8.61	9.07	10.70	3.49	3.95	4.67	5.13	6.75
	4H	8.12	8.55	9.30	9.71	11.36	4.03	4.46	5.21	5.62	7.27
	6H	8.63	9.00	9.82	10.18	11.82	4.44	4.81	5.63	5.99	7.63
	8H	8.80	9.15	9.99	10.32	11.97	4.57	4.91	5.75	6.08	7.74
	12H	8.89	9.20	10.10	10.39	12.05	4.63	4.94	5.83	6.12	7.78
8H	4H	8.08	8.42	9.26	9.59	11.24	4.30	4.64	5.49	5.82	7.47
	6H	8.64	8.92	9.85	10.14	11.79	4.81	5.10	6.02	6.31	7.96
	8H	8.86	9.10	10.07	10.30	11.97	5.01	5.25	6.22	6.44	8.11
	12H	8.99	9.21	10.21	10.40	12.10	5.12	5.33	6.33	6.52	8.23
12H	4H	8.02	8.33	9.22	9.51	11.17	4.30	4.61	5.50	5.79	7.45
	6H	8.62	8.86	9.83	10.05	11.72	4.86	5.11	6.07	6.30	7.97
	8H	8.83	9.05	10.04	10.24	11.94	5.07	5.28	6.28	6.47	8.18

END OF REPORT