

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923074

Luminaire Tested: DFN2DIP-SQ4F0-070D070US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P923074  
REPORT IS A COMBINATION OF REPORTS P900080 AND P896915  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-070D070US940-RLLFLL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10829.8 lumens  
Efficiency: N/A  
Efficacy: 95.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 113.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9967  
Total Harmonic Distortion (THDi): 0.063  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P923074  
CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US940-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P923074

CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US940-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42			42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36			36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31			31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19			19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14			14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1810	1810	1810
5°	1813	1782	1793
10°	1795	1747	1736
15°	1770	1690	1646
20°	1738	1611	1536
25°	1704	1522	1429
30°	1659	1430	1294
35°	1615	1332	1175
40°	1570	1231	1038
45°	1518	1118	915
50°	1464	1004	794
55°	1408	883	678
60°	1343	755	559
65°	1268	626	503
70°	1177	505	456
75°	1063	446	416
80°	898	376	363
85°	625	252	276

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1553 cd/sqm



TEST NUMBER: P923074

CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	241.8	2.2
10°-20°	663.7	6.1
20°-30°	931.9	8.6
30°-40°	1015.8	9.4
40°-50°	933.6	8.6
50°-60°	733.2	6.8
60°-70°	477.3	4.4
70°-80°	245.7	2.3
80°-90°	68.3	0.6
90°-100°	122.2	1.1
100°-110°	388.1	3.6
110°-120°	664.2	6.1
120°-130°	873.6	8.1
130°-140°	980.5	9.1
140°-150°	961.5	8.9
150°-160°	806.6	7.4
160°-170°	534.9	4.9
170°-180°	187.0	1.7
0°-30°	1837.4	17.0
0°-40°	2853.2	26.3
0°-60°	4520.0	41.7
0°-90°	5311.3	49.0
90°-120°	1174.5	10.8
90°-150°	3990.1	36.8
90°-180°	5519.0	51.0
0°-180°	10829.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2580	2580	2580	2580	2580	
5°	2580	2568	2538	2559	2552	245
15°	2454	2428	2349	2304	2281	691
25°	2227	2152	1998	1903	1868	1024
35°	1919	1800	1595	1448	1396	1201
45°	1569	1412	1167	1002	946	1212
55°	1193	1011	759	619	574	1066
65°	806	616	406	327	320	799
75°	430	266	187	170	168	454
85°	100	51	44	44	44	115
90°	2	21	58	55	56	11
95°	87	104	107	107	104	97
105°	358	363	367	370	370	378
115°	667	676	673	671	667	659
125°	970	984	980	974	972	866
135°	1254	1272	1276	1274	1269	969
145°	1522	1534	1544	1546	1539	951
155°	1741	1746	1751	1759	1754	801
165°	1894	1892	1892	1904	1896	534
175°	1970	1966	1962	1974	1964	187
180°	1974	1974	1974	1974	1974	



TEST NUMBER: P923074

CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2579.8	2579.8	2579.8	2579.8	2579.8
2.5°	2591.4	2579.8	2554.0	2577.6	2572.9
5°	2579.8	2568.1	2537.7	2558.8	2551.8
7.5°	2558.8	2544.9	2512.2	2521.3	2509.7
10°	2530.8	2514.4	2467.8	2460.7	2446.8
12.5°	2495.8	2474.8	2411.6	2397.7	2371.9
15°	2453.7	2427.9	2348.7	2304.4	2281.1
17.5°	2404.7	2367.3	2269.2	2217.9	2180.5
20°	2348.7	2301.9	2185.2	2127.0	2075.5
22.5°	2288.0	2234.3	2098.7	2019.5	1984.6
25°	2227.3	2152.5	1998.4	1902.8	1867.7
27.5°	2155.0	2075.5	1905.1	1795.4	1741.6
30°	2078.0	1989.0	1802.2	1683.4	1620.2
32.5°	2003.1	1895.7	1704.4	1564.2	1505.7
35°	1919.1	1800.0	1594.7	1447.6	1396.1
37.5°	1837.5	1708.9	1491.9	1330.6	1272.5
40°	1751.0	1611.1	1384.4	1218.7	1158.0
42.5°	1662.3	1513.0	1277.1	1104.2	1046.1
45°	1569.0	1412.4	1167.4	1001.5	945.5
47.5°	1480.2	1314.6	1062.4	896.4	845.2
50°	1382.2	1216.5	959.6	798.3	749.6
52.5°	1286.3	1111.2	861.5	707.4	663.1
55°	1192.9	1010.8	758.7	618.8	574.4
57.5°	1097.3	910.5	667.8	537.0	499.6
60°	999.3	812.4	571.9	453.1	415.6
62.5°	903.6	716.8	490.2	378.3	359.6
65°	805.5	616.3	406.3	327.0	319.8
67.5°	712.1	522.9	327.0	287.0	280.2
70°	614.0	431.9	270.7	247.4	238.0
72.5°	520.7	347.8	226.4	207.9	203.1
75°	429.5	266.0	186.7	170.4	168.2
77.5°	338.6	189.0	147.1	137.7	133.0
80°	254.4	135.5	112.0	102.8	102.8
82.5°	177.4	91.1	77.0	72.3	72.3
85°	100.3	51.3	44.3	44.3	44.3
87.5°	37.4	18.5	18.5	16.3	16.3
90°	1.8	21.4	58.3	54.8	56.5
92.5°	36.9	50.0	51.8	53.6	53.6
95°	86.9	103.5	106.6	106.6	103.5
97.5°	144.6	160.1	166.7	166.7	166.7
100°	211.2	225.0	229.7	229.7	227.9
102.5°	281.5	291.6	298.2	300.0	298.2
105°	358.3	363.0	366.6	369.6	369.6
107.5°	434.4	441.6	441.6	442.8	434.4
110°	508.3	517.8	517.8	517.8	513.0



TEST NUMBER: P923074

CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	588.0	598.2	596.4	591.6	588.0
115°	666.6	676.1	673.2	671.4	666.6
117.5°	744.5	757.6	749.3	744.5	739.8
120°	823.0	836.2	823.0	823.0	817.7
122.5°	894.5	911.1	902.9	898.0	894.5
125°	969.5	984.4	979.6	974.3	972.5
127.5°	1042.7	1061.1	1054.6	1047.5	1042.7
130°	1111.2	1132.6	1129.6	1126.1	1119.5
132.5°	1187.9	1204.6	1205.8	1197.5	1192.7
135°	1254.0	1272.4	1276.0	1274.2	1269.4
137.5°	1327.8	1342.6	1345.6	1344.4	1337.3
140°	1392.7	1407.6	1415.9	1415.9	1409.3
142.5°	1459.3	1474.2	1478.9	1480.7	1474.2
145°	1522.4	1534.3	1543.8	1545.6	1539.1
147.5°	1579.0	1593.8	1601.0	1603.9	1597.4
150°	1637.3	1647.3	1653.9	1659.3	1653.9
152.5°	1689.0	1699.2	1707.4	1714.0	1707.4
155°	1740.8	1745.5	1751.0	1759.3	1753.9
157.5°	1785.5	1789.0	1792.0	1803.9	1795.5
160°	1825.3	1828.9	1830.7	1840.8	1833.6
162.5°	1862.2	1862.2	1864.0	1875.3	1867.0
165°	1893.7	1891.9	1891.9	1903.9	1895.5
167.5°	1922.3	1917.0	1917.0	1928.9	1920.6
170°	1943.8	1939.0	1937.2	1949.1	1939.0
172.5°	1958.6	1953.8	1952.0	1964.0	1953.8
175°	1970.5	1965.8	1962.2	1974.1	1964.0
177.5°	1977.1	1972.3	1968.7	1978.9	1968.7
180°	1974.1	1974.1	1974.1	1974.1	1974.1



TEST NUMBER: P923074  
 CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.13	9.95	10.10	10.93	12.22	5.09	5.91	6.06	6.89	8.18
	3H	10.81	11.55	11.79	12.54	13.85	6.28	7.01	7.26	8.00	9.31
	4H	11.42	12.12	12.42	13.11	14.43	6.73	7.42	7.73	8.42	9.74
	6H	11.85	12.49	12.85	13.49	14.82	7.05	7.69	8.06	8.69	10.02
	8H	11.98	12.58	12.99	13.60	14.93	7.14	7.75	8.15	8.76	10.09
	12H	12.04	12.62	13.06	13.63	14.98	7.18	7.76	8.20	8.77	10.12
4H	2H	9.15	9.84	10.15	10.84	12.15	5.69	6.38	6.69	7.38	8.69
	3H	10.98	11.56	11.99	12.58	13.91	7.04	7.62	8.05	8.64	9.97
	4H	11.67	12.20	12.69	13.22	14.57	7.59	8.11	8.60	9.13	10.48
	6H	12.19	12.65	13.22	13.69	15.04	8.01	8.46	9.04	9.50	10.85
	8H	12.37	12.80	13.40	13.83	15.19	8.13	8.56	9.17	9.59	10.96
	12H	12.47	12.85	13.52	13.90	15.27	8.20	8.58	9.25	9.63	11.00
8H	4H	11.64	12.07	12.67	13.10	14.46	7.87	8.29	8.90	9.32	10.69
	6H	12.21	12.56	13.27	13.64	15.00	8.39	8.74	9.44	9.81	11.17
	8H	12.43	12.74	13.49	13.80	15.18	8.58	8.89	9.64	9.95	11.33
	12H	12.57	12.84	13.64	13.90	15.32	8.70	8.97	9.76	10.02	11.45
12H	4H	11.59	11.98	12.64	13.02	14.39	7.87	8.26	8.92	9.30	10.67
	6H	12.19	12.50	13.25	13.56	14.94	8.44	8.75	9.50	9.80	11.19
	8H	12.41	12.68	13.48	13.74	15.16	8.65	8.92	9.71	9.97	11.40