

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917703

Luminaire Tested: DFN2DIP-SQ4F0-090D100US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917703
REPORT IS A COMBINATION OF REPORTS P901658 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D100US930-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14308.5 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 157.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917703

CATALOG NUMBER: DFN2DIP-SQ4F0-090D100US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917703

CATALOG NUMBER: DFN2DIP-SQ4F0-090D100US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44		
1	97	93	89	86	88	85	82	79	71	68	66	57	56	54	45	44	43	38		
2	88	81	76	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32		
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28		
4	74	64	56	50	68	59	52	47	49	44	41	41	37	34	32	30	28	24		
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21		
6	63	51	43	38	58	47	41	36	40	35	31	33	29	26	27	24	22	19		
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17		
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15		
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14		
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2128	2128	2128
5°	2131	2095	2108
10°	2110	2054	2040
15°	2081	1986	1935
20°	2043	1893	1805
25°	2003	1789	1680
30°	1950	1681	1521
35°	1899	1566	1381
40°	1846	1447	1221
45°	1785	1314	1075
50°	1721	1181	933
55°	1655	1038	797
60°	1579	888	657
65°	1491	736	592
70°	1384	594	536
75°	1250	525	489
80°	1056	441	426
85°	735	297	325

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1785 cd/sqm

TEST NUMBER: P917703

CATALOG NUMBER: DFN2DIP-SQ4F0-090D100US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.2	2.0
10°-20°	780.3	5.5
20°-30°	1095.5	7.7
30°-40°	1194.1	8.3
40°-50°	1097.5	7.7
50°-60°	861.9	6.0
60°-70°	561.0	3.9
70°-80°	288.8	2.0
80°-90°	78.6	0.5
90°-100°	90.7	0.6
100°-110°	338.2	2.4
110°-120°	897.0	6.3
120°-130°	1487.8	10.4
130°-140°	1580.4	11.0
140°-150°	1468.8	10.3
150°-160°	1180.9	8.3
160°-170°	760.9	5.3
170°-180°	261.9	1.8
0°-30°	2159.9	15.1
0°-40°	3354.0	23.4
0°-60°	5313.5	37.1
0°-90°	6241.9	43.6
90°-120°	1326.0	9.3
90°-150°	5862.9	41.0
90°-180°	8067.0	56.4
0°-180°	14308.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3033	3033	3033	3033	3033	
5°	3033	3019	2983	3008	3000	288
15°	2884	2854	2761	2709	2682	813
25°	2618	2530	2349	2237	2196	1204
35°	2256	2116	1875	1702	1641	1412
45°	1844	1660	1372	1177	1111	1424
55°	1402	1188	892	727	675	1253
65°	947	724	478	384	376	939
75°	505	313	220	200	198	534
85°	118	60	52	52	52	135
90°	2	24	40	50	54	13
95°	129	64	78	88	86	153
105°	605	665	122	143	151	647
115°	1145	1179	1228	307	163	1127
125°	1619	1645	1682	1696	1702	1444
135°	2003	2035	2053	2073	2069	1547
145°	2324	2322	2355	2369	2359	1453
155°	2558	2541	2564	2576	2560	1179
165°	2696	2684	2690	2704	2690	762
175°	2757	2744	2748	2762	2742	262
180°	2752	2752	2752	2752	2752	

TEST NUMBER: P917703

CATALOG NUMBER: DFN2DIP-SQ4F0-090D100US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3032.7	3032.7	3032.7	3032.7	3032.7
2.5°	3046.4	3032.7	3002.3	3030.1	3024.5
5°	3032.7	3019.0	2983.2	3007.9	2999.7
7.5°	3007.9	2991.6	2953.2	2963.9	2950.2
10°	2975.0	2955.8	2901.1	2892.6	2876.3
12.5°	2933.9	2909.2	2835.0	2818.6	2788.3
15°	2884.4	2854.2	2761.0	2708.8	2681.5
17.5°	2826.8	2782.9	2667.5	2607.2	2563.3
20°	2761.0	2706.0	2568.8	2500.4	2439.8
22.5°	2689.7	2626.5	2467.2	2374.0	2333.0
25°	2618.3	2530.4	2349.3	2236.9	2195.5
27.5°	2533.3	2439.8	2239.5	2110.5	2047.3
30°	2442.7	2338.2	2118.6	1978.9	1904.6
32.5°	2354.7	2228.4	2003.6	1838.8	1770.1
35°	2256.1	2116.0	1874.6	1701.7	1641.1
37.5°	2160.0	2008.9	1753.8	1564.2	1495.8
40°	2058.4	1893.9	1627.4	1432.6	1361.3
42.5°	1954.1	1778.6	1501.3	1298.1	1229.6
45°	1844.4	1660.4	1372.3	1177.2	1111.4
47.5°	1740.1	1545.3	1248.9	1053.8	993.5
50°	1624.8	1430.0	1128.0	938.5	881.1
52.5°	1512.1	1306.3	1012.8	831.6	779.5
55°	1402.3	1188.3	891.9	727.4	675.2
57.5°	1290.0	1070.4	785.1	631.3	587.3
60°	1174.6	955.0	672.4	532.6	488.6
62.5°	1062.3	842.7	576.3	444.7	422.8
65°	946.9	724.5	477.5	384.3	375.9
67.5°	837.1	614.7	384.3	337.5	329.3
70°	721.9	507.8	318.3	290.9	279.8
72.5°	612.0	408.8	266.1	244.3	238.8
75°	504.9	312.7	219.6	200.3	197.7
77.5°	398.0	222.2	172.9	161.9	156.4
80°	299.1	159.3	131.6	120.8	120.8
82.5°	208.5	107.1	90.6	85.0	85.0
85°	117.9	60.3	52.1	52.1	52.1
87.5°	43.9	21.8	21.8	19.2	19.2
90°	1.9	23.9	39.7	49.9	53.6
92.5°	49.9	41.8	47.8	51.8	53.6
95°	129.3	63.6	77.5	87.7	85.6
97.5°	232.8	69.7	101.4	107.5	109.5
100°	352.5	79.7	113.5	129.3	133.4
102.5°	483.7	480.0	117.5	139.3	145.4
105°	605.3	665.0	121.6	143.2	151.3
107.5°	746.7	796.3	125.6	147.3	155.3
110°	882.1	923.7	348.5	149.4	157.2

TEST NUMBER: P917703

CATALOG NUMBER: DFN2DIP-SQ4F0-090D100US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1009.5	1045.2	1011.5	153.2	159.4
115°	1144.8	1178.6	1228.5	306.6	163.4
117.5°	1262.2	1302.0	1336.0	1051.2	529.6
120°	1393.8	1423.5	1459.5	1483.4	1214.5
122.5°	1505.1	1537.0	1576.9	1588.8	1590.9
125°	1618.6	1644.6	1682.4	1696.4	1702.3
127.5°	1722.2	1750.0	1780.0	1799.9	1801.8
130°	1819.7	1851.7	1873.5	1895.4	1893.5
132.5°	1919.3	1945.3	1967.1	1985.0	1983.1
135°	2003.0	2034.9	2052.7	2072.7	2068.7
137.5°	2090.5	2114.4	2134.5	2154.3	2148.4
140°	2176.0	2192.2	2213.9	2231.9	2221.9
142.5°	2247.9	2261.9	2287.6	2303.5	2293.6
145°	2323.6	2321.5	2355.3	2369.3	2359.3
147.5°	2389.1	2383.2	2417.0	2426.9	2419.2
150°	2452.9	2439.0	2470.9	2482.7	2472.8
152.5°	2506.6	2490.7	2520.6	2532.6	2518.6
155°	2558.4	2540.6	2564.5	2576.3	2560.5
157.5°	2600.2	2584.4	2602.4	2616.3	2600.2
160°	2636.2	2624.1	2636.2	2648.0	2634.1
162.5°	2667.8	2656.0	2665.9	2679.9	2661.9
165°	2695.7	2683.9	2689.8	2703.8	2689.8
167.5°	2717.7	2705.6	2711.8	2725.8	2707.8
170°	2735.7	2723.7	2727.7	2741.6	2723.7
172.5°	2747.5	2735.7	2739.7	2753.7	2735.7
175°	2757.4	2743.5	2747.5	2761.5	2741.6
177.5°	2761.5	2747.5	2749.7	2763.6	2745.6
180°	2751.6	2751.6	2751.6	2751.6	2751.6

TEST NUMBER: P917703

CATALOG NUMBER: DFN2DIP-SQ4F0-090D100US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.16	9.94	10.17	10.96	12.32	5.12	5.90	6.13	6.92	8.28
	3H	10.84	11.53	11.86	12.56	13.95	6.30	7.00	7.33	8.03	9.41
	4H	11.44	12.11	12.48	13.14	14.53	6.75	7.41	7.79	8.45	9.84
	6H	11.87	12.48	12.92	13.51	14.91	7.07	7.68	8.12	8.72	10.12
	8H	11.99	12.57	13.05	13.63	15.02	7.16	7.74	8.21	8.79	10.19
	12H	12.06	12.61	13.12	13.65	15.07	7.20	7.75	8.26	8.80	10.22
4H	2H	9.17	9.83	10.22	10.86	12.25	5.71	6.37	6.76	7.40	8.79
	3H	11.00	11.55	12.05	12.61	14.01	7.06	7.61	8.11	8.67	10.07
	4H	11.69	12.20	12.75	13.25	14.67	7.60	8.11	8.66	9.16	10.58
	6H	12.21	12.64	13.28	13.72	15.14	8.02	8.45	9.09	9.53	10.95
	8H	12.39	12.79	13.46	13.86	15.29	8.15	8.55	9.22	9.62	11.05
	12H	12.48	12.85	13.57	13.93	15.37	8.21	8.58	9.30	9.66	11.10
8H	4H	11.66	12.06	12.73	13.13	14.56	7.88	8.28	8.95	9.35	10.79
	6H	12.23	12.56	13.32	13.67	15.10	8.40	8.73	9.49	9.84	11.27
	8H	12.45	12.74	13.54	13.83	15.28	8.59	8.88	9.69	9.98	11.43
	12H	12.58	12.84	13.69	13.93	15.42	8.71	8.97	9.81	10.05	11.55
12H	4H	11.61	11.97	12.69	13.05	14.49	7.89	8.25	8.97	9.33	10.77
	6H	12.20	12.49	13.30	13.59	15.04	8.45	8.74	9.55	9.83	11.29
	8H	12.42	12.68	13.52	13.77	15.26	8.66	8.92	9.76	10.00	11.50