

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917750

Luminaire Tested: DFN2DIP-SQ4F0-100D140US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917750
REPORT IS A COMBINATION OF REPORTS P900194 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D140US930-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17031.6 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 198.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917750

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917750

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2364	2364	2364
5°	2368	2327	2342
10°	2345	2282	2267
15°	2312	2207	2150
20°	2270	2104	2006
25°	2226	1987	1866
30°	2167	1868	1690
35°	2109	1740	1534
40°	2051	1608	1356
45°	1983	1460	1195
50°	1912	1312	1037
55°	1839	1153	885
60°	1754	987	730
65°	1656	818	658
70°	1538	660	596
75°	1389	583	544
80°	1173	491	474
85°	816	330	361

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2842 cd/sqm

TEST NUMBER: P917750

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.8	1.9
10°-20°	866.9	5.1
20°-30°	1217.2	7.1
30°-40°	1326.8	7.8
40°-50°	1219.5	7.2
50°-60°	957.7	5.6
60°-70°	623.4	3.7
70°-80°	320.9	1.9
80°-90°	92.2	0.5
90°-100°	223.4	1.3
100°-110°	709.8	4.2
110°-120°	1214.6	7.1
120°-130°	1597.4	9.4
130°-140°	1793.0	10.5
140°-150°	1758.2	10.3
150°-160°	1474.9	8.7
160°-170°	978.1	5.7
170°-180°	341.9	2.0
0°-30°	2399.9	14.1
0°-40°	3726.7	21.9
0°-60°	5903.9	34.7
0°-90°	6940.3	40.7
90°-120°	2147.7	12.6
90°-150°	7296.4	42.8
90°-180°	10091.0	59.2
0°-180°	17031.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3370	3370	3370	3370	3370	
5°	3370	3354	3315	3342	3333	320
15°	3205	3171	3068	3010	2979	903
25°	2909	2812	2610	2485	2440	1338
35°	2507	2351	2083	1891	1823	1569
45°	2049	1845	1525	1308	1235	1583
55°	1558	1320	991	808	750	1392
65°	1052	805	531	427	418	1043
75°	561	348	244	223	220	593
85°	131	67	58	58	58	150
90°	3	39	107	100	103	17
95°	159	189	195	195	189	177
105°	655	664	670	676	676	691
115°	1219	1236	1231	1228	1219	1206
125°	1773	1800	1791	1782	1778	1584
135°	2293	2327	2333	2330	2321	1772
145°	2784	2806	2823	2826	2814	1739
155°	3183	3192	3202	3217	3207	1465
165°	3463	3460	3460	3482	3466	977
175°	3603	3595	3588	3610	3591	342
180°	3610	3610	3610	3610	3610	

TEST NUMBER: P917750

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3369.6	3369.6	3369.6	3369.6	3369.6
2.5°	3384.8	3369.6	3336.0	3366.7	3360.6
5°	3369.6	3354.4	3314.6	3342.2	3333.0
7.5°	3342.2	3324.0	3281.2	3293.2	3278.1
10°	3305.5	3284.2	3223.4	3214.0	3195.9
12.5°	3260.0	3232.4	3149.9	3131.8	3098.1
15°	3204.9	3171.3	3067.7	3009.8	2979.4
17.5°	3140.9	3092.0	2963.9	2896.9	2848.1
20°	3067.7	3006.6	2854.2	2778.2	2710.9
22.5°	2988.5	2918.3	2741.3	2637.8	2592.2
25°	2909.2	2811.6	2610.3	2485.4	2439.5
27.5°	2814.7	2710.9	2488.3	2345.0	2274.8
30°	2714.1	2597.9	2354.0	2198.8	2116.3
32.5°	2616.5	2476.0	2226.3	2043.1	1966.7
35°	2506.7	2351.2	2082.9	1890.8	1823.4
37.5°	2400.0	2232.0	1948.6	1738.1	1662.0
40°	2287.1	2104.3	1808.2	1591.8	1512.5
42.5°	2171.2	1976.1	1668.2	1442.3	1366.3
45°	2049.3	1844.8	1524.9	1308.1	1234.9
47.5°	1933.5	1717.0	1387.6	1170.8	1103.9
50°	1805.3	1588.9	1253.4	1042.8	979.0
52.5°	1680.1	1451.4	1125.3	924.0	866.1
55°	1558.1	1320.4	991.0	808.2	750.2
57.5°	1433.3	1189.3	872.3	701.4	652.6
60°	1305.1	1061.2	747.1	591.7	542.9
62.5°	1180.2	936.3	640.3	494.1	469.8
65°	1052.1	804.9	530.6	427.1	417.7
67.5°	930.2	683.0	427.1	375.0	365.9
70°	802.0	564.3	353.6	323.2	311.0
72.5°	680.0	454.2	295.7	271.4	265.3
75°	561.0	347.5	243.9	222.6	219.6
77.5°	442.3	246.9	192.2	179.9	173.7
80°	332.2	177.0	146.3	134.3	134.3
82.5°	231.6	119.0	100.6	94.5	94.5
85°	131.0	66.9	57.9	57.9	57.9
87.5°	48.8	24.3	24.3	21.4	21.4
90°	3.3	39.2	106.6	100.1	103.4
92.5°	67.5	91.4	94.7	97.9	97.9
95°	158.9	189.4	194.8	194.8	189.4
97.5°	264.5	292.8	304.8	304.8	304.8
100°	386.4	411.4	420.0	420.0	416.8
102.5°	514.8	533.3	545.3	548.5	545.3
105°	655.2	663.9	670.4	675.8	675.8
107.5°	794.4	807.6	807.6	809.7	794.4
110°	929.4	946.8	946.8	946.8	938.1

TEST NUMBER: P917750

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1075.2	1093.7	1090.5	1081.7	1075.2
115°	1218.9	1236.3	1230.9	1227.6	1218.9
117.5°	1361.5	1385.4	1370.2	1361.5	1352.7
120°	1505.1	1529.1	1505.1	1505.1	1495.3
122.5°	1635.7	1666.1	1651.0	1642.3	1635.7
125°	1772.9	1800.0	1791.3	1781.5	1778.2
127.5°	1906.7	1940.4	1928.4	1915.4	1906.7
130°	2031.8	2071.0	2065.6	2059.0	2047.1
132.5°	2172.2	2202.7	2204.9	2189.6	2180.9
135°	2293.0	2326.8	2333.3	2330.0	2321.3
137.5°	2428.0	2455.2	2460.7	2458.5	2445.4
140°	2546.6	2573.8	2589.1	2589.1	2577.1
142.5°	2668.5	2695.7	2704.4	2707.7	2695.7
145°	2783.8	2805.6	2823.1	2826.3	2814.3
147.5°	2887.2	2914.4	2927.5	2933.0	2921.0
150°	2993.9	3012.4	3024.3	3034.1	3024.3
152.5°	3088.6	3107.1	3122.3	3134.3	3122.3
155°	3183.3	3192.0	3201.8	3217.0	3207.2
157.5°	3264.9	3271.4	3276.8	3298.6	3283.4
160°	3337.8	3344.4	3347.6	3366.1	3353.0
162.5°	3405.3	3405.3	3408.5	3429.2	3414.0
165°	3463.0	3459.7	3459.7	3481.5	3466.2
167.5°	3515.2	3505.4	3505.4	3527.1	3511.9
170°	3554.4	3545.7	3542.4	3564.2	3545.7
172.5°	3581.6	3572.9	3569.6	3591.4	3572.9
175°	3603.4	3594.6	3588.1	3609.9	3591.4
177.5°	3615.3	3606.6	3600.1	3618.5	3600.1
180°	3609.9	3609.9	3609.9	3609.9	3609.9

TEST NUMBER: P917750

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.22	9.98	10.26	11.02	12.42	5.18	5.94	6.22	6.98	8.38
	3H	10.89	11.57	11.94	12.62	14.04	6.36	7.04	7.41	8.09	9.51
	4H	11.50	12.15	12.56	13.20	14.62	6.81	7.45	7.87	8.51	9.93
	6H	11.92	12.52	12.99	13.57	15.01	7.13	7.72	8.20	8.78	10.21
	8H	12.05	12.61	13.13	13.69	15.12	7.22	7.78	8.29	8.85	10.28
	12H	12.11	12.65	13.19	13.71	15.17	7.26	7.79	8.34	8.86	10.31
4H	2H	9.23	9.87	10.29	10.92	12.35	5.77	6.41	6.83	7.46	8.89
	3H	11.06	11.59	12.13	12.67	14.11	7.11	7.65	8.19	8.73	10.17
	4H	11.75	12.24	12.83	13.31	14.77	7.66	8.15	8.74	9.22	10.68
	6H	12.26	12.68	13.35	13.78	15.23	8.07	8.49	9.16	9.59	11.04
	8H	12.44	12.83	13.53	13.92	15.39	8.20	8.60	9.29	9.68	11.15
	12H	12.53	12.89	13.64	13.99	15.46	8.27	8.62	9.37	9.72	11.19
8H	4H	11.71	12.10	12.80	13.19	14.66	7.94	8.33	9.02	9.41	10.88
	6H	12.28	12.60	13.39	13.73	15.20	8.45	8.78	9.56	9.90	11.37
	8H	12.50	12.78	13.61	13.89	15.38	8.64	8.93	9.76	10.04	11.53
	12H	12.64	12.89	13.76	13.99	15.52	8.76	9.01	9.88	10.12	11.64
12H	4H	11.66	12.01	12.76	13.11	14.59	7.94	8.29	9.04	9.39	10.87
	6H	12.25	12.54	13.37	13.65	15.13	8.50	8.79	9.62	9.90	11.38
	8H	12.47	12.72	13.59	13.83	15.35	8.71	8.96	9.83	10.07	11.59