

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917753

Luminaire Tested: DFN2DIP-SQ4F0-100D160US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917753
REPORT IS A COMBINATION OF REPORTS P901731 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D160US930-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20985.8 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 214.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917753

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917753

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2226	2226	2226
5°	2230	2195	2210
10°	2211	2166	2181
15°	2179	2131	2135
20°	2135	2082	2088
25°	2091	2023	2033
30°	2036	1968	1963
35°	1984	1904	1889
40°	1920	1839	1819
45°	1857	1773	1748
50°	1787	1705	1664
55°	1714	1625	1588
60°	1632	1531	1501
65°	1542	1434	1398
70°	1427	1315	1287
75°	1268	1173	1186
80°	1077	992	990
85°	778	679	666

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2361 cd/sqm

TEST NUMBER: P917753

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.6	1.4
10°-20°	840.1	4.0
20°-30°	1234.6	5.9
30°-40°	1433.9	6.8
40°-50°	1432.1	6.8
50°-60°	1248.8	6.0
60°-70°	923.1	4.4
70°-80°	522.3	2.5
80°-90°	145.6	0.7
90°-100°	145.1	0.7
100°-110°	541.2	2.6
110°-120°	1435.3	6.8
120°-130°	2380.5	11.3
130°-140°	2528.6	12.0
140°-150°	2350.1	11.2
150°-160°	1889.4	9.0
160°-170°	1217.5	5.8
170°-180°	419.0	2.0
0°-30°	2373.3	11.3
0°-40°	3807.2	18.1
0°-60°	6488.2	30.9
0°-90°	8079.2	38.5
90°-120°	2121.6	10.1
90°-150°	9380.7	44.7
90°-180°	12907.0	61.5
0°-180°	20985.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3172	3172	3172	3172	3172	
5°	3172	3160	3127	3151	3145	301
15°	3020	3002	2962	2974	2959	851
25°	2733	2709	2657	2663	2657	1258
35°	2358	2328	2279	2260	2245	1473
45°	1919	1898	1852	1818	1806	1481
55°	1452	1434	1397	1361	1345	1298
65°	979	961	930	903	888	968
75°	512	506	491	473	479	547
85°	125	122	119	110	107	139
90°	3	38	64	80	86	19
95°	207	102	124	140	137	245
105°	968	1064	194	229	242	1035
115°	1832	1886	1966	491	261	1803
125°	2590	2631	2692	2714	2724	2310
135°	3205	3256	3284	3316	3310	2476
145°	3718	3714	3768	3791	3775	2325
155°	4093	4065	4103	4122	4097	1886
165°	4313	4294	4304	4326	4304	1219
175°	4412	4390	4396	4418	4386	420
180°	4402	4402	4402	4402	4402	

TEST NUMBER: P917753

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3172.4	3172.4	3172.4	3172.4	3172.4
2.5°	3190.8	3175.6	3141.9	3172.4	3166.5
5°	3172.4	3160.4	3126.8	3151.0	3145.2
7.5°	3151.0	3132.9	3099.2	3123.8	3117.7
10°	3117.7	3096.3	3059.7	3084.0	3075.0
12.5°	3071.7	3053.6	3017.0	3032.3	3026.1
15°	3019.9	3001.8	2962.0	2974.3	2959.1
17.5°	2955.9	2937.8	2897.9	2913.1	2897.9
20°	2885.6	2867.5	2824.8	2833.8	2821.8
22.5°	2815.7	2788.2	2748.4	2748.4	2742.3
25°	2733.2	2708.9	2657.1	2662.9	2657.1
27.5°	2641.6	2620.2	2580.7	2571.7	2556.4
30°	2550.3	2525.7	2480.1	2471.0	2458.7
32.5°	2452.6	2434.5	2385.6	2367.1	2354.8
35°	2358.1	2327.7	2278.8	2260.3	2245.1
37.5°	2251.3	2223.7	2174.9	2153.5	2138.3
40°	2141.5	2116.9	2068.1	2040.9	2028.6
42.5°	2034.7	2010.1	1961.6	1930.9	1912.8
45°	1918.9	1897.5	1851.5	1818.2	1806.0
47.5°	1806.0	1784.6	1735.7	1702.0	1683.9
50°	1686.9	1671.6	1628.9	1586.2	1571.0
52.5°	1571.0	1549.6	1510.1	1476.5	1455.1
55°	1452.2	1433.8	1397.2	1360.6	1345.4
57.5°	1333.1	1317.8	1278.1	1241.5	1229.2
60°	1214.0	1202.0	1159.3	1125.6	1116.6
62.5°	1098.1	1076.8	1046.4	1015.9	1003.6
65°	979.3	960.9	930.5	902.9	887.8
67.5°	857.4	841.8	814.6	793.3	781.0
70°	744.4	732.1	704.6	683.2	671.2
72.5°	628.5	616.2	601.0	579.7	570.5
75°	512.3	506.5	491.0	472.9	479.0
77.5°	408.8	396.5	390.3	381.2	372.2
80°	305.2	302.0	295.8	286.7	280.6
82.5°	207.5	207.5	204.6	192.2	192.2
85°	124.9	122.1	119.1	109.7	106.8
87.5°	55.0	48.8	42.7	33.7	30.4
90°	3.0	38.2	63.5	79.8	85.9
92.5°	79.8	66.9	76.4	82.8	85.9
95°	206.9	101.7	124.1	140.3	137.0
97.5°	372.6	111.6	162.2	172.1	175.1
100°	564.0	127.5	181.6	206.9	213.4
102.5°	774.0	767.9	188.0	222.8	232.6
105°	968.4	1064.1	194.4	229.3	242.1
107.5°	1194.6	1274.1	200.9	235.7	248.5
110°	1411.4	1478.0	557.6	239.0	251.5

TEST NUMBER: P917753

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1615.3	1672.4	1618.3	245.2	254.9
115°	1831.6	1885.7	1965.5	490.6	261.4
117.5°	2019.7	2083.2	2137.7	1681.9	847.3
120°	2230.0	2277.6	2335.1	2373.3	1943.3
122.5°	2408.1	2459.2	2523.1	2542.0	2545.4
125°	2589.7	2631.3	2691.9	2714.2	2723.7
127.5°	2755.4	2800.1	2848.1	2879.9	2882.9
130°	2911.7	2962.7	2997.5	3032.7	3029.6
132.5°	3070.9	3112.5	3147.3	3176.1	3173.1
135°	3204.8	3255.9	3284.3	3316.4	3309.9
137.5°	3344.8	3383.0	3415.1	3446.9	3437.5
140°	3481.7	3507.4	3542.2	3571.0	3555.1
142.5°	3596.7	3619.0	3660.3	3685.6	3669.7
145°	3717.8	3714.3	3768.5	3790.7	3774.9
147.5°	3822.5	3813.1	3867.2	3883.1	3870.5
150°	3924.7	3902.3	3953.5	3972.4	3956.5
152.5°	4010.5	3985.2	4032.9	4052.2	4029.9
155°	4093.4	4065.0	4103.2	4122.1	4096.8
157.5°	4160.4	4135.0	4163.7	4186.1	4160.4
160°	4217.9	4198.5	4217.9	4236.8	4214.4
162.5°	4268.6	4249.7	4265.5	4287.8	4259.1
165°	4313.2	4294.3	4303.7	4326.1	4303.7
167.5°	4348.4	4329.1	4338.9	4361.2	4332.5
170°	4377.1	4357.9	4364.2	4386.5	4357.9
172.5°	4396.0	4377.1	4383.5	4405.9	4377.1
175°	4411.9	4389.6	4396.0	4418.3	4386.5
177.5°	4418.3	4396.0	4399.4	4421.8	4393.0
180°	4402.4	4402.4	4402.4	4402.4	4402.4

TEST NUMBER: P917753

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.90	9.66	9.95	10.72	12.15	8.45	9.22	9.50	10.27	11.70
	3H	10.56	11.24	11.61	12.31	13.75	10.07	10.75	11.12	11.82	13.26
	4H	11.14	11.79	12.21	12.86	14.31	10.65	11.30	11.72	12.36	13.82
	6H	11.54	12.14	12.62	13.21	14.67	11.04	11.64	12.12	12.71	14.17
	8H	11.64	12.21	12.73	13.30	14.76	11.14	11.71	12.23	12.80	14.26
	12H	11.69	12.23	12.78	13.31	14.79	11.18	11.72	12.27	12.80	14.28
4H	2H	9.35	10.00	10.43	11.06	12.52	8.99	9.64	10.07	10.71	12.16
	3H	11.21	11.75	12.29	12.85	14.31	10.80	11.35	11.89	12.44	13.90
	4H	11.92	12.42	13.01	13.51	14.99	11.50	12.00	12.59	13.08	14.57
	6H	12.44	12.87	13.54	13.97	15.45	12.01	12.43	13.10	13.54	15.02
	8H	12.59	12.99	13.69	14.09	15.58	12.15	12.55	13.25	13.65	15.14
	12H	12.66	13.02	13.77	14.13	15.63	12.21	12.57	13.32	13.68	15.18
8H	4H	12.11	12.51	13.21	13.61	15.11	11.74	12.14	12.84	13.23	14.73
	6H	12.75	13.08	13.87	14.22	15.71	12.36	12.69	13.48	13.83	15.32
	8H	12.97	13.26	14.10	14.38	15.89	12.57	12.86	13.70	13.99	15.50
	12H	13.10	13.35	14.23	14.47	16.02	12.69	12.94	13.82	14.06	15.61
12H	4H	12.09	12.46	13.21	13.57	15.07	11.73	12.09	12.84	13.20	14.70
	6H	12.77	13.06	13.90	14.19	15.70	12.40	12.69	13.53	13.81	15.33
	8H	13.02	13.27	14.15	14.39	15.94	12.63	12.89	13.77	14.01	15.56

END OF REPORT