

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917791

Luminaire Tested: DFN2DIP-SQ4F0-110D160US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917791
REPORT IS A COMBINATION OF REPORTS P901734 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D160US930-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20537.4 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 227.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917791

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917791

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	38	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	45	42	35	34	33	33	33	27
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	28	28	24
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	29	26	25	25	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	22	22	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	19	19	16
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	17	17	14
8	53	41	34	29	48	38	31	27	31	26	23	26	22	19	20	17	15	15	15	13
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14	14	14	12
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2601	2601	2601
5°	2605	2560	2577
10°	2579	2510	2494
15°	2544	2428	2365
20°	2497	2314	2206
25°	2448	2186	2053
30°	2384	2055	1859
35°	2320	1914	1688
40°	2256	1768	1492
45°	2181	1606	1314
50°	2104	1443	1141
55°	2023	1268	974
60°	1929	1085	803
65°	1822	899	723
70°	1691	726	656
75°	1527	641	598
80°	1290	540	521
85°	898	363	397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2361 cd/sqm

TEST NUMBER: P917791

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.4	1.7
10°-20°	953.6	4.6
20°-30°	1338.9	6.5
30°-40°	1459.5	7.1
40°-50°	1341.4	6.5
50°-60°	1053.5	5.1
60°-70°	685.7	3.3
70°-80°	353.0	1.7
80°-90°	97.9	0.5
90°-100°	145.1	0.7
100°-110°	541.2	2.6
110°-120°	1435.3	7.0
120°-130°	2380.5	11.6
130°-140°	2528.6	12.3
140°-150°	2350.1	11.4
150°-160°	1889.4	9.2
160°-170°	1217.5	5.9
170°-180°	419.0	2.0
0°-30°	2639.9	12.9
0°-40°	4099.4	20.0
0°-60°	6494.2	31.6
0°-90°	7630.8	37.2
90°-120°	2121.6	10.3
90°-150°	9380.7	45.7
90°-180°	12907.0	62.8
0°-180°	20537.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3707	3707	3707	3707	3707	
5°	3707	3690	3646	3676	3666	351
15°	3525	3488	3374	3311	3277	993
25°	3200	3093	2871	2734	2683	1472
35°	2757	2586	2291	2080	2006	1726
45°	2254	2029	1677	1439	1358	1741
55°	1714	1452	1090	889	825	1532
65°	1157	885	584	470	459	1147
75°	617	382	268	245	242	653
85°	144	74	64	64	64	165
90°	3	38	64	80	86	19
95°	207	102	124	140	137	245
105°	968	1064	194	229	242	1035
115°	1832	1886	1966	491	261	1803
125°	2590	2631	2692	2714	2724	2310
135°	3205	3256	3284	3316	3310	2476
145°	3718	3714	3768	3791	3775	2325
155°	4093	4065	4103	4122	4097	1886
165°	4313	4294	4304	4326	4304	1219
175°	4412	4390	4396	4418	4386	420
180°	4402	4402	4402	4402	4402	

TEST NUMBER: P917791

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3706.6	3706.6	3706.6	3706.6	3706.6
2.5°	3723.3	3706.6	3669.6	3703.4	3696.6
5°	3706.6	3689.9	3646.1	3676.3	3666.4
7.5°	3676.3	3656.4	3609.4	3622.6	3605.8
10°	3636.1	3612.6	3545.7	3535.4	3515.5
12.5°	3585.9	3555.7	3464.9	3445.0	3407.9
15°	3525.4	3488.4	3374.5	3310.8	3277.3
17.5°	3455.0	3401.3	3260.3	3186.6	3132.9
20°	3374.5	3307.3	3139.6	3056.0	2982.0
22.5°	3287.4	3210.1	3015.5	2901.6	2851.3
25°	3200.1	3092.7	2871.3	2733.9	2683.4
27.5°	3096.3	2982.0	2737.1	2579.4	2502.2
30°	2985.5	2857.8	2589.5	2418.6	2327.8
32.5°	2878.1	2723.6	2448.8	2247.5	2163.5
35°	2757.4	2586.2	2291.2	2079.8	2005.8
37.5°	2640.0	2455.3	2143.5	1911.8	1828.2
40°	2515.8	2314.7	1989.1	1750.9	1663.8
42.5°	2388.3	2173.7	1835.0	1586.6	1502.9
45°	2254.2	2029.3	1677.3	1438.8	1358.4
47.5°	2126.8	1888.7	1526.4	1287.9	1214.3
50°	1985.8	1747.8	1378.8	1147.0	1076.9
52.5°	1848.1	1596.5	1237.8	1016.4	952.7
55°	1713.9	1452.4	1090.1	889.0	825.3
57.5°	1576.6	1308.2	959.4	771.6	717.8
60°	1435.7	1167.3	821.7	650.9	597.2
62.5°	1298.3	1030.0	704.3	543.5	516.7
65°	1157.3	885.4	583.7	469.8	459.4
67.5°	1023.2	751.3	469.8	412.5	402.5
70°	882.2	620.7	389.0	355.6	342.0
72.5°	748.0	499.7	325.3	298.6	291.8
75°	617.1	382.2	268.3	244.8	241.7
77.5°	486.5	271.6	211.4	197.9	191.1
80°	365.5	194.7	160.9	147.7	147.7
82.5°	254.8	130.9	110.7	104.0	104.0
85°	144.1	73.7	63.7	63.7	63.7
87.5°	53.7	26.7	26.7	23.5	23.5
90°	3.0	38.2	63.5	79.8	85.9
92.5°	79.8	66.9	76.4	82.8	85.9
95°	206.9	101.7	124.1	140.3	137.0
97.5°	372.6	111.6	162.2	172.1	175.1
100°	564.0	127.5	181.6	206.9	213.4
102.5°	774.0	767.9	188.0	222.8	232.6
105°	968.4	1064.1	194.4	229.3	242.1
107.5°	1194.6	1274.1	200.9	235.7	248.5
110°	1411.4	1478.0	557.6	239.0	251.5

TEST NUMBER: P917791

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1615.3	1672.4	1618.3	245.2	254.9
115°	1831.6	1885.7	1965.5	490.6	261.4
117.5°	2019.7	2083.2	2137.7	1681.9	847.3
120°	2230.0	2277.6	2335.1	2373.3	1943.3
122.5°	2408.1	2459.2	2523.1	2542.0	2545.4
125°	2589.7	2631.3	2691.9	2714.2	2723.7
127.5°	2755.4	2800.1	2848.1	2879.9	2882.9
130°	2911.7	2962.7	2997.5	3032.7	3029.6
132.5°	3070.9	3112.5	3147.3	3176.1	3173.1
135°	3204.8	3255.9	3284.3	3316.4	3309.9
137.5°	3344.8	3383.0	3415.1	3446.9	3437.5
140°	3481.7	3507.4	3542.2	3571.0	3555.1
142.5°	3596.7	3619.0	3660.3	3685.6	3669.7
145°	3717.8	3714.3	3768.5	3790.7	3774.9
147.5°	3822.5	3813.1	3867.2	3883.1	3870.5
150°	3924.7	3902.3	3953.5	3972.4	3956.5
152.5°	4010.5	3985.2	4032.9	4052.2	4029.9
155°	4093.4	4065.0	4103.2	4122.1	4096.8
157.5°	4160.4	4135.0	4163.7	4186.1	4160.4
160°	4217.9	4198.5	4217.9	4236.8	4214.4
162.5°	4268.6	4249.7	4265.5	4287.8	4259.1
165°	4313.2	4294.3	4303.7	4326.1	4303.7
167.5°	4348.4	4329.1	4338.9	4361.2	4332.5
170°	4377.1	4357.9	4364.2	4386.5	4357.9
172.5°	4396.0	4377.1	4383.5	4405.9	4377.1
175°	4411.9	4389.6	4396.0	4418.3	4386.5
177.5°	4418.3	4396.0	4399.4	4421.8	4393.0
180°	4402.4	4402.4	4402.4	4402.4	4402.4

TEST NUMBER: P917791

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.15	9.88	10.21	10.95	12.39	5.11	5.85	6.18	6.91	8.36
	3H	10.82	11.48	11.90	12.55	14.02	6.29	6.95	7.37	8.02	9.49
	4H	11.43	12.05	12.52	13.13	14.60	6.74	7.36	7.82	8.44	9.91
	6H	11.85	12.42	12.95	13.50	14.98	7.06	7.63	8.15	8.71	10.19
	8H	11.98	12.52	13.08	13.62	15.09	7.14	7.69	8.24	8.78	10.26
	12H	12.04	12.55	13.14	13.64	15.14	7.18	7.70	8.29	8.79	10.29
4H	2H	9.16	9.78	10.25	10.85	12.32	5.70	6.32	6.79	7.39	8.86
	3H	10.98	11.50	12.08	12.60	14.08	7.04	7.56	8.14	8.66	10.14
	4H	11.67	12.15	12.78	13.24	14.74	7.58	8.06	8.69	9.15	10.65
	6H	12.19	12.59	13.30	13.71	15.21	8.00	8.41	9.11	9.52	11.02
	8H	12.36	12.74	13.47	13.85	15.36	8.13	8.51	9.24	9.61	11.13
	12H	12.46	12.80	13.58	13.92	15.44	8.19	8.53	9.32	9.65	11.17
8H	4H	11.63	12.01	12.75	13.12	14.63	7.86	8.24	8.97	9.35	10.86
	6H	12.20	12.51	13.33	13.66	15.17	8.38	8.69	9.51	9.84	11.35
	8H	12.42	12.69	13.56	13.82	15.35	8.57	8.84	9.71	9.97	11.50
	12H	12.56	12.80	13.70	13.92	15.49	8.68	8.92	9.83	10.05	11.62
12H	4H	11.58	11.92	12.71	13.04	14.56	7.86	8.20	8.99	9.32	10.84
	6H	12.18	12.45	13.32	13.58	15.11	8.43	8.70	9.56	9.83	11.36
	8H	12.40	12.64	13.54	13.76	15.33	8.63	8.87	9.78	10.00	11.57

END OF REPORT