

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923178

Luminaire Tested: DFN2DIP-SQ4F0-100D060US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923178
REPORT IS A COMBINATION OF REPORTS P900068 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D060US940-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12314.5 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 137.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923178

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923178

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	58
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	53	51	49
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	41	45	40	37	39	36	33
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2586	2586	2586
5°	2590	2545	2562
10°	2564	2496	2479
15°	2529	2414	2351
20°	2482	2301	2194
25°	2434	2174	2041
30°	2370	2043	1848
35°	2307	1903	1678
40°	2243	1758	1484
45°	2169	1597	1307
50°	2092	1435	1134
55°	2011	1261	969
60°	1918	1079	798
65°	1811	894	719
70°	1682	722	652
75°	1519	637	595
80°	1283	537	519
85°	893	361	394

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2169 cd/sqm

TEST NUMBER: P923178

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.4	2.8
10°-20°	948.2	7.7
20°-30°	1331.2	10.8
30°-40°	1451.1	11.8
40°-50°	1333.8	10.8
50°-60°	1047.4	8.5
60°-70°	681.8	5.5
70°-80°	351.0	2.8
80°-90°	94.4	0.8
90°-100°	104.7	0.9
100°-110°	332.7	2.7
110°-120°	569.3	4.6
120°-130°	748.8	6.1
130°-140°	840.5	6.8
140°-150°	824.2	6.7
150°-160°	691.4	5.6
160°-170°	458.5	3.7
170°-180°	160.3	1.3
0°-30°	2624.8	21.3
0°-40°	4076.0	33.1
0°-60°	6457.2	52.4
0°-90°	7584.3	61.6
90°-120°	1006.7	8.2
90°-150°	3420.1	27.8
90°-180°	4730.0	38.4
0°-180°	12314.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3669	3625	3655	3645	349
15°	3505	3468	3355	3292	3259	988
25°	3182	3075	2855	2718	2668	1463
35°	2742	2572	2278	2068	1994	1716
45°	2241	2018	1668	1431	1351	1731
55°	1704	1444	1084	884	821	1523
65°	1151	880	580	467	457	1141
75°	614	380	267	243	240	649
85°	143	73	63	63	63	164
90°	2	18	50	47	48	12
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	

TEST NUMBER: P923178

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.4	3685.4	3685.4	3685.4	3685.4
2.5°	3702.0	3685.4	3648.6	3682.2	3675.5
5°	3685.4	3668.8	3625.2	3655.4	3645.4
7.5°	3655.4	3635.5	3588.8	3601.9	3585.3
10°	3615.4	3592.0	3525.5	3515.2	3495.4
12.5°	3565.5	3535.4	3445.1	3425.3	3388.5
15°	3505.3	3468.5	3355.2	3291.9	3258.7
17.5°	3435.2	3381.8	3241.7	3168.4	3115.0
20°	3355.2	3288.4	3121.7	3038.6	2964.9
22.5°	3268.6	3191.8	2998.2	2885.0	2835.1
25°	3181.9	3075.1	2854.9	2718.3	2668.1
27.5°	3078.5	2964.9	2721.5	2564.7	2488.0
30°	2968.5	2841.4	2574.6	2404.9	2314.6
32.5°	2861.7	2708.0	2434.9	2234.6	2151.1
35°	2741.7	2571.5	2278.1	2068.0	1994.3
37.5°	2624.9	2441.2	2131.3	1900.9	1817.8
40°	2501.4	2301.5	1977.7	1741.0	1654.3
42.5°	2374.7	2161.3	1824.5	1577.5	1494.3
45°	2241.3	2017.7	1667.8	1430.7	1350.7
47.5°	2114.7	1877.9	1517.7	1280.6	1207.4
50°	1974.5	1737.8	1370.8	1140.5	1070.8
52.5°	1837.5	1587.4	1230.7	1010.6	947.3
55°	1704.1	1444.1	1083.9	884.0	820.6
57.5°	1567.6	1300.7	954.0	767.1	713.7
60°	1427.4	1160.7	817.1	647.2	593.8
62.5°	1290.8	1024.0	700.3	540.4	513.8
65°	1150.8	880.4	580.3	467.1	456.8
67.5°	1017.4	747.0	467.1	410.1	400.2
70°	877.2	617.2	386.7	353.5	340.1
72.5°	743.8	496.8	323.4	296.9	290.2
75°	613.6	380.0	266.8	243.4	240.2
77.5°	483.8	270.0	210.2	196.7	190.0
80°	363.4	193.6	160.0	146.9	146.9
82.5°	253.3	130.2	110.0	103.3	103.3
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7



TEST NUMBER: P923178

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1

TEST NUMBER: P923178

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.48	12.41	12.34	13.29	14.39	7.44	8.37	8.30	9.25	10.35
	3H	13.17	14.00	14.04	14.89	16.01	8.64	9.47	9.51	10.36	11.48
	4H	13.78	14.57	14.67	15.46	16.60	9.09	9.88	9.98	10.77	11.91
	6H	14.21	14.94	15.11	15.84	16.99	9.42	10.14	10.32	11.04	12.19
	8H	14.35	15.04	15.25	15.95	17.10	9.51	10.20	10.42	11.12	12.26
	12H	14.41	15.07	15.32	15.98	17.15	9.56	10.22	10.47	11.12	12.30
4H	2H	11.51	12.30	12.40	13.19	14.32	8.05	8.84	8.94	9.73	10.86
	3H	13.35	14.01	14.25	14.93	16.08	9.41	10.06	10.31	10.99	12.14
	4H	14.05	14.65	14.97	15.57	16.74	9.96	10.56	10.88	11.48	12.65
	6H	14.58	15.09	15.50	16.03	17.21	10.39	10.90	11.32	11.84	13.02
	8H	14.76	15.24	15.69	16.17	17.36	10.52	11.00	11.45	11.93	13.13
	12H	14.86	15.29	15.81	16.24	17.44	10.59	11.02	11.54	11.98	13.17
8H	4H	14.03	14.51	14.96	15.44	16.63	10.25	10.73	11.18	11.67	12.86
	6H	14.60	15.00	15.56	15.98	17.17	10.78	11.17	11.73	12.15	13.34
	8H	14.82	15.17	15.79	16.14	17.35	10.97	11.32	11.93	12.29	13.49
	12H	14.97	15.28	15.94	16.24	17.49	11.09	11.40	12.06	12.36	13.62
12H	4H	13.98	14.42	14.93	15.37	16.57	10.26	10.69	11.21	11.65	12.84
	6H	14.58	14.93	15.54	15.90	17.10	10.83	11.18	11.79	12.15	13.35
	8H	14.81	15.11	15.77	16.08	17.33	11.04	11.35	12.01	12.31	13.57