

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923199

Luminaire Tested: DFN2DIP-SQ4F0-100D110US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923199
REPORT IS A COMBINATION OF REPORTS P901678 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D110US940-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17290.2 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 175.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923199

CATALOG NUMBER: DFN2DIP-SQ4F0-100D110US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923199

CATALOG NUMBER: DFN2DIP-SQ4F0-100D110US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	97	93	89	86	89	85	82	79	71	68	66	57	56	55	45	44	43
2	89	81	76	71	81	75	70	66	62	59	56	51	48	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	40	36	34	32
4	74	64	56	51	68	59	52	47	49	45	41	41	37	34	33	30	28
5	68	57	49	44	62	53	46	41	44	39	35	37	33	30	30	27	25
6	63	51	44	38	58	47	41	36	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	37	31	27	30	26	24	25	22	20
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2586	2586	2586
5°	2590	2545	2562
10°	2564	2496	2479
15°	2529	2414	2351
20°	2482	2301	2194
25°	2434	2174	2041
30°	2370	2043	1848
35°	2307	1903	1678
40°	2243	1758	1484
45°	2169	1597	1307
50°	2092	1435	1134
55°	2011	1261	969
60°	1918	1079	798
65°	1811	894	719
70°	1682	722	652
75°	1519	637	595
80°	1283	537	519
85°	893	361	394

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2169 cd/sqm

TEST NUMBER: P923199

CATALOG NUMBER: DFN2DIP-SQ4F0-100D110US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.4	2.0
10°-20°	948.2	5.5
20°-30°	1331.2	7.7
30°-40°	1451.1	8.4
40°-50°	1333.8	7.7
50°-60°	1047.4	6.1
60°-70°	681.8	3.9
70°-80°	351.0	2.0
80°-90°	95.4	0.6
90°-100°	109.2	0.6
100°-110°	406.9	2.4
110°-120°	1079.2	6.2
120°-130°	1789.9	10.4
130°-140°	1901.3	11.0
140°-150°	1767.1	10.2
150°-160°	1420.7	8.2
160°-170°	915.4	5.3
170°-180°	315.1	1.8
0°-30°	2624.8	15.2
0°-40°	4076.0	23.6
0°-60°	6457.2	37.3
0°-90°	7585.3	43.9
90°-120°	1595.3	9.2
90°-150°	7053.7	40.8
90°-180°	9705.0	56.1
0°-180°	17290.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3669	3625	3655	3645	349
15°	3505	3468	3355	3292	3259	988
25°	3182	3075	2855	2718	2668	1463
35°	2742	2572	2278	2068	1994	1716
45°	2241	2018	1668	1431	1351	1731
55°	1704	1444	1084	884	821	1523
65°	1151	880	580	467	457	1141
75°	614	380	267	243	240	649
85°	143	73	63	63	63	164
90°	2	29	48	60	65	16
95°	156	76	93	106	103	184
105°	728	800	146	172	182	778
115°	1377	1418	1478	369	196	1356
125°	1947	1979	2024	2041	2048	1737
135°	2410	2448	2470	2494	2489	1862
145°	2796	2793	2834	2850	2838	1748
155°	3078	3057	3085	3100	3080	1418
165°	3243	3229	3236	3253	3236	916
175°	3317	3301	3306	3322	3298	316
180°	3310	3310	3310	3310	3310	

TEST NUMBER: P923199

CATALOG NUMBER: DFN2DIP-SQ4F0-100D110US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.4	3685.4	3685.4	3685.4	3685.4
2.5°	3702.0	3685.4	3648.6	3682.2	3675.5
5°	3685.4	3668.8	3625.2	3655.4	3645.4
7.5°	3655.4	3635.5	3588.8	3601.9	3585.3
10°	3615.4	3592.0	3525.5	3515.2	3495.4
12.5°	3565.5	3535.4	3445.1	3425.3	3388.5
15°	3505.3	3468.5	3355.2	3291.9	3258.7
17.5°	3435.2	3381.8	3241.7	3168.4	3115.0
20°	3355.2	3288.4	3121.7	3038.6	2964.9
22.5°	3268.6	3191.8	2998.2	2885.0	2835.1
25°	3181.9	3075.1	2854.9	2718.3	2668.1
27.5°	3078.5	2964.9	2721.5	2564.7	2488.0
30°	2968.5	2841.4	2574.6	2404.9	2314.6
32.5°	2861.7	2708.0	2434.9	2234.6	2151.1
35°	2741.7	2571.5	2278.1	2068.0	1994.3
37.5°	2624.9	2441.2	2131.3	1900.9	1817.8
40°	2501.4	2301.5	1977.7	1741.0	1654.3
42.5°	2374.7	2161.3	1824.5	1577.5	1494.3
45°	2241.3	2017.7	1667.8	1430.7	1350.7
47.5°	2114.7	1877.9	1517.7	1280.6	1207.4
50°	1974.5	1737.8	1370.8	1140.5	1070.8
52.5°	1837.5	1587.4	1230.7	1010.6	947.3
55°	1704.1	1444.1	1083.9	884.0	820.6
57.5°	1567.6	1300.7	954.0	767.1	713.7
60°	1427.4	1160.7	817.1	647.2	593.8
62.5°	1290.8	1024.0	700.3	540.4	513.8
65°	1150.8	880.4	580.3	467.1	456.8
67.5°	1017.4	747.0	467.1	410.1	400.2
70°	877.2	617.2	386.7	353.5	340.1
72.5°	743.8	496.8	323.4	296.9	290.2
75°	613.6	380.0	266.8	243.4	240.2
77.5°	483.8	270.0	210.2	196.7	190.0
80°	363.4	193.6	160.0	146.9	146.9
82.5°	253.3	130.2	110.0	103.3	103.3
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	2.3	28.7	47.8	60.0	64.6
92.5°	60.0	50.4	57.4	62.3	64.6
95°	155.6	76.5	93.3	105.5	103.0
97.5°	280.2	83.9	122.0	129.4	131.7
100°	424.1	95.9	136.5	155.6	160.4
102.5°	581.9	577.4	141.3	167.6	175.0
105°	728.2	800.1	146.2	172.4	182.1
107.5°	898.3	958.0	151.1	177.2	186.9
110°	1061.2	1111.3	419.3	179.8	189.1

TEST NUMBER: P923199

CATALOG NUMBER: DFN2DIP-SQ4F0-100D110US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1214.6	1257.5	1216.8	184.3	191.7
115°	1377.2	1417.9	1478.0	368.9	196.5
117.5°	1518.7	1566.5	1607.4	1264.6	637.1
120°	1676.8	1712.6	1755.9	1784.6	1461.2
122.5°	1810.8	1849.1	1897.2	1911.5	1914.1
125°	1947.3	1978.6	2024.1	2040.9	2048.0
127.5°	2071.9	2105.4	2141.5	2165.4	2167.7
130°	2189.3	2227.8	2253.9	2280.4	2278.1
132.5°	2309.1	2340.4	2366.6	2388.2	2385.9
135°	2409.8	2448.2	2469.5	2493.8	2488.9
137.5°	2515.1	2543.8	2567.9	2591.8	2584.7
140°	2618.1	2637.3	2663.5	2685.1	2673.2
142.5°	2704.5	2721.2	2752.3	2771.3	2759.4
145°	2795.5	2792.9	2833.6	2850.4	2838.5
147.5°	2874.3	2867.2	2907.9	2919.8	2910.5
150°	2951.1	2934.4	2972.7	2987.0	2975.0
152.5°	3015.7	2996.6	3032.4	3047.0	3030.2
155°	3078.0	3056.6	3085.3	3099.6	3080.5
157.5°	3128.3	3109.2	3130.9	3147.6	3128.3
160°	3171.5	3157.0	3171.5	3185.7	3169.0
162.5°	3209.6	3195.4	3207.4	3224.2	3202.6
165°	3243.2	3229.0	3236.1	3252.9	3236.1
167.5°	3269.6	3255.2	3262.6	3279.4	3257.8
170°	3291.3	3276.8	3281.6	3298.4	3276.8
172.5°	3305.5	3291.3	3296.1	3312.9	3291.3
175°	3317.4	3300.7	3305.5	3322.3	3298.4
177.5°	3322.3	3305.5	3308.1	3324.8	3303.3
180°	3310.4	3310.4	3310.4	3310.4	3310.4

TEST NUMBER: P923199

CATALOG NUMBER: DFN2DIP-SQ4F0-100D110US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.86	10.64	10.87	11.66	13.02	5.82	6.60	6.83	7.62	8.98
	3H	11.54	12.24	12.56	13.27	14.65	7.01	7.71	8.03	8.73	10.11
	4H	12.15	12.81	13.18	13.84	15.23	7.45	8.12	8.49	9.15	10.53
	6H	12.57	13.18	13.62	14.22	15.61	7.77	8.38	8.82	9.42	10.82
	8H	12.70	13.28	13.75	14.33	15.72	7.86	8.44	8.92	9.49	10.89
	12H	12.76	13.31	13.82	14.36	15.77	7.91	8.46	8.96	9.50	10.92
4H	2H	9.87	10.53	10.92	11.57	12.95	6.41	7.07	7.46	8.11	9.49
	3H	11.70	12.25	12.75	13.31	14.71	7.76	8.31	8.81	9.37	10.77
	4H	12.40	12.90	13.45	13.95	15.37	8.31	8.81	9.36	9.86	11.28
	6H	12.91	13.34	13.98	14.42	15.84	8.72	9.16	9.79	10.23	11.65
	8H	13.09	13.49	14.16	14.56	15.99	8.85	9.26	9.92	10.32	11.75
	12H	13.18	13.55	14.27	14.63	16.07	8.92	9.28	10.00	10.36	11.80
8H	4H	12.36	12.76	13.43	13.83	15.26	8.59	8.99	9.65	10.05	11.49
	6H	12.93	13.26	14.02	14.37	15.80	9.10	9.44	10.19	10.54	11.97
	8H	13.15	13.44	14.25	14.53	15.98	9.30	9.59	10.39	10.68	12.13
	12H	13.29	13.55	14.39	14.63	16.12	9.41	9.67	10.51	10.76	12.24
12H	4H	12.31	12.67	13.39	13.75	15.19	8.59	8.95	9.67	10.03	11.47
	6H	12.90	13.20	14.00	14.29	15.74	9.15	9.45	10.25	10.54	11.99
	8H	13.13	13.38	14.23	14.47	15.96	9.36	9.62	10.46	10.71	12.20

END OF REPORT