

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923211

Luminaire Tested: DFN2DIP-SQ4F0-100D160US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923211
REPORT IS A COMBINATION OF REPORTS P901732 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D160US940-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21704.2 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 214.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923211

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923211

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2586	2586	2586
5°	2590	2545	2562
10°	2564	2496	2479
15°	2529	2414	2351
20°	2482	2301	2194
25°	2434	2174	2041
30°	2370	2043	1848
35°	2307	1903	1678
40°	2243	1758	1484
45°	2169	1597	1307
50°	2092	1435	1134
55°	2011	1261	969
60°	1918	1079	798
65°	1811	894	719
70°	1682	722	652
75°	1519	637	595
80°	1283	537	519
85°	893	361	394

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2581 cd/sqm

TEST NUMBER: P923211

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.4	1.6
10°-20°	948.2	4.4
20°-30°	1331.2	6.1
30°-40°	1451.1	6.7
40°-50°	1333.8	6.1
50°-60°	1047.4	4.8
60°-70°	681.8	3.1
70°-80°	351.0	1.6
80°-90°	98.1	0.5
90°-100°	158.8	0.7
100°-110°	591.9	2.7
110°-120°	1569.8	7.2
120°-130°	2603.6	12.0
130°-140°	2765.6	12.7
140°-150°	2570.3	11.8
150°-160°	2066.5	9.5
160°-170°	1331.6	6.1
170°-180°	458.3	2.1
0°-30°	2624.8	12.1
0°-40°	4076.0	18.8
0°-60°	6457.2	29.8
0°-90°	7588.0	35.0
90°-120°	2320.4	10.7
90°-150°	10259.9	47.3
90°-180°	14116.0	65.0
0°-180°	21704.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3669	3625	3655	3645	349
15°	3505	3468	3355	3292	3259	988
25°	3182	3075	2855	2718	2668	1463
35°	2742	2572	2278	2068	1994	1716
45°	2241	2018	1668	1431	1351	1731
55°	1704	1444	1084	884	821	1523
65°	1151	880	580	467	457	1141
75°	614	380	267	243	240	649
85°	143	73	63	63	63	164
90°	3	42	70	87	94	20
95°	226	111	136	154	150	268
105°	1059	1164	213	251	265	1132
115°	2003	2062	2150	537	286	1972
125°	2832	2878	2944	2969	2979	2526
135°	3505	3561	3592	3627	3620	2708
145°	4066	4062	4122	4146	4129	2543
155°	4477	4446	4488	4508	4481	2063
165°	4717	4697	4707	4732	4707	1333
175°	4825	4801	4808	4832	4798	459
180°	4815	4815	4815	4815	4815	

TEST NUMBER: P923211

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.4	3685.4	3685.4	3685.4	3685.4
2.5°	3702.0	3685.4	3648.6	3682.2	3675.5
5°	3685.4	3668.8	3625.2	3655.4	3645.4
7.5°	3655.4	3635.5	3588.8	3601.9	3585.3
10°	3615.4	3592.0	3525.5	3515.2	3495.4
12.5°	3565.5	3535.4	3445.1	3425.3	3388.5
15°	3505.3	3468.5	3355.2	3291.9	3258.7
17.5°	3435.2	3381.8	3241.7	3168.4	3115.0
20°	3355.2	3288.4	3121.7	3038.6	2964.9
22.5°	3268.6	3191.8	2998.2	2885.0	2835.1
25°	3181.9	3075.1	2854.9	2718.3	2668.1
27.5°	3078.5	2964.9	2721.5	2564.7	2488.0
30°	2968.5	2841.4	2574.6	2404.9	2314.6
32.5°	2861.7	2708.0	2434.9	2234.6	2151.1
35°	2741.7	2571.5	2278.1	2068.0	1994.3
37.5°	2624.9	2441.2	2131.3	1900.9	1817.8
40°	2501.4	2301.5	1977.7	1741.0	1654.3
42.5°	2374.7	2161.3	1824.5	1577.5	1494.3
45°	2241.3	2017.7	1667.8	1430.7	1350.7
47.5°	2114.7	1877.9	1517.7	1280.6	1207.4
50°	1974.5	1737.8	1370.8	1140.5	1070.8
52.5°	1837.5	1587.4	1230.7	1010.6	947.3
55°	1704.1	1444.1	1083.9	884.0	820.6
57.5°	1567.6	1300.7	954.0	767.1	713.7
60°	1427.4	1160.7	817.1	647.2	593.8
62.5°	1290.8	1024.0	700.3	540.4	513.8
65°	1150.8	880.4	580.3	467.1	456.8
67.5°	1017.4	747.0	467.1	410.1	400.2
70°	877.2	617.2	386.7	353.5	340.1
72.5°	743.8	496.8	323.4	296.9	290.2
75°	613.6	380.0	266.8	243.4	240.2
77.5°	483.8	270.0	210.2	196.7	190.0
80°	363.4	193.6	160.0	146.9	146.9
82.5°	253.3	130.2	110.0	103.3	103.3
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	3.3	41.8	69.5	87.3	93.9
92.5°	87.3	73.2	83.6	90.6	93.9
95°	226.3	111.3	135.7	153.5	149.8
97.5°	407.5	122.1	177.5	188.2	191.5
100°	616.9	139.5	198.6	226.3	233.4
102.5°	846.5	839.9	205.6	243.7	254.4
105°	1059.2	1163.9	212.7	250.7	264.7
107.5°	1306.5	1393.5	219.7	257.8	271.8
110°	1543.6	1616.5	609.8	261.4	275.1

TEST NUMBER: P923211

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1766.7	1829.2	1770.0	268.1	278.8
115°	2003.3	2062.4	2149.7	536.6	285.9
117.5°	2208.9	2278.4	2338.1	1839.5	926.8
120°	2439.0	2491.1	2553.9	2595.8	2125.4
122.5°	2633.8	2689.7	2759.6	2780.3	2784.0
125°	2832.4	2877.9	2944.2	2968.6	2978.9
127.5°	3013.6	3062.5	3115.0	3149.8	3153.1
130°	3184.6	3240.4	3278.5	3316.9	3313.6
132.5°	3358.7	3404.2	3442.3	3473.7	3470.4
135°	3505.1	3561.0	3592.1	3627.2	3620.2
137.5°	3658.2	3700.1	3735.2	3770.0	3759.6
140°	3808.0	3836.1	3874.2	3905.7	3888.3
142.5°	3933.8	3958.2	4003.3	4031.1	4013.7
145°	4066.2	4062.5	4121.7	4146.0	4128.7
147.5°	4180.8	4170.4	4229.6	4247.0	4233.3
150°	4292.5	4268.1	4324.0	4344.7	4327.3
152.5°	4386.4	4358.7	4410.8	4432.0	4407.5
155°	4477.0	4446.0	4487.8	4508.5	4480.8
157.5°	4550.3	4522.6	4554.0	4578.4	4550.3
160°	4613.2	4592.0	4613.2	4633.9	4609.4
162.5°	4668.6	4648.0	4665.3	4689.7	4658.3
165°	4717.4	4696.7	4707.1	4731.5	4707.1
167.5°	4755.9	4734.8	4745.6	4769.9	4738.5
170°	4787.3	4766.3	4773.2	4797.7	4766.3
172.5°	4808.0	4787.3	4794.4	4818.8	4787.3
175°	4825.4	4801.0	4808.0	4832.4	4797.7
177.5°	4832.4	4808.0	4811.8	4836.2	4804.7
180°	4815.1	4815.1	4815.1	4815.1	4815.1

TEST NUMBER: P923211

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.87	9.59	9.95	10.67	12.14	4.83	5.55	5.91	6.63	8.10
	3H	10.54	11.19	11.63	12.27	13.76	6.01	6.65	7.10	7.74	9.23
	4H	11.15	11.76	12.25	12.85	14.34	6.46	7.07	7.56	8.15	9.65
	6H	11.57	12.13	12.68	13.22	14.73	6.77	7.33	7.88	8.42	9.93
	8H	11.69	12.23	12.81	13.33	14.84	6.86	7.39	7.97	8.50	10.00
	12H	11.75	12.26	12.87	13.36	14.89	6.90	7.41	8.02	8.51	10.03
4H	2H	8.87	9.48	9.98	10.57	12.07	5.41	6.02	6.52	7.11	8.61
	3H	10.70	11.21	11.81	12.32	13.83	6.75	7.26	7.87	8.38	9.89
	4H	11.39	11.85	12.51	12.96	14.49	7.30	7.77	8.42	8.87	10.40
	6H	11.90	12.30	13.03	13.43	14.95	7.71	8.11	8.84	9.24	10.76
	8H	12.08	12.45	13.20	13.57	15.11	7.84	8.21	8.97	9.33	10.87
	12H	12.17	12.51	13.31	13.64	15.18	7.90	8.24	9.04	9.37	10.91
8H	4H	11.35	11.72	12.47	12.84	14.38	7.57	7.95	8.70	9.07	10.60
	6H	11.92	12.22	13.06	13.38	14.92	8.09	8.40	9.24	9.56	11.09
	8H	12.13	12.40	13.29	13.54	15.10	8.28	8.55	9.43	9.69	11.25
	12H	12.27	12.51	13.43	13.65	15.24	8.40	8.63	9.55	9.77	11.36
12H	4H	11.30	11.63	12.44	12.76	14.31	7.57	7.91	8.72	9.04	10.59
	6H	11.89	12.16	13.04	13.30	14.86	8.14	8.41	9.29	9.55	11.10
	8H	12.11	12.35	13.26	13.48	15.07	8.35	8.58	9.50	9.72	11.31

END OF REPORT