

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917857

Luminaire Tested: DFN2DIP-SQ4F0-140D140US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917857
REPORT IS A COMBINATION OF REPORTS P901719 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D140US930-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22600.0 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 249.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917857

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917857

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US930-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3116	3116	3116
5°	3121	3074	3095
10°	3096	3033	3053
15°	3050	2983	2989
20°	2989	2915	2923
25°	2928	2832	2846
30°	2851	2756	2748
35°	2778	2665	2645
40°	2689	2574	2547
45°	2599	2483	2446
50°	2502	2387	2330
55°	2400	2276	2223
60°	2284	2144	2101
65°	2158	2007	1956
70°	1998	1841	1801
75°	1775	1642	1660
80°	1508	1389	1386
85°	1090	950	932

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2599 cd/sqm

TEST NUMBER: P917857

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	418.0	1.8
10°-20°	1176.1	5.2
20°-30°	1728.5	7.6
30°-40°	2007.5	8.9
40°-50°	2005.0	8.9
50°-60°	1748.3	7.7
60°-70°	1292.4	5.7
70°-80°	731.2	3.2
80°-90°	199.8	0.9
90°-100°	127.0	0.6
100°-110°	473.5	2.1
110°-120°	1255.8	5.6
120°-130°	2082.9	9.2
130°-140°	2212.5	9.8
140°-150°	2056.3	9.1
150°-160°	1653.2	7.3
160°-170°	1065.3	4.7
170°-180°	366.7	1.6
0°-30°	3322.6	14.7
0°-40°	5330.1	23.6
0°-60°	9083.5	40.2
0°-90°	11306.8	50.0
90°-120°	1856.4	8.2
90°-150°	8208.1	36.3
90°-180°	11293.0	50.0
0°-180°	22600.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4441	4441	4441	4441	4441	
5°	4441	4424	4377	4411	4403	422
15°	4228	4202	4147	4164	4143	1191
25°	3826	3792	3720	3728	3720	1761
35°	3301	3259	3190	3164	3143	2062
45°	2686	2657	2592	2546	2528	2073
55°	2033	2007	1956	1905	1884	1818
65°	1371	1345	1303	1264	1243	1356
75°	717	709	687	662	671	766
85°	175	171	167	154	150	195
90°	3	33	56	70	75	21
95°	181	89	109	123	120	214
105°	847	931	170	201	212	905
115°	1603	1650	1720	429	229	1578
125°	2266	2302	2355	2375	2383	2021
135°	2804	2849	2874	2902	2896	2166
145°	3253	3250	3297	3317	3303	2035
155°	3582	3557	3590	3607	3585	1650
165°	3774	3758	3766	3785	3766	1066
175°	3860	3841	3846	3866	3838	367
180°	3852	3852	3852	3852	3852	

TEST NUMBER: P917857

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US930-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4441.3	4441.3	4441.3	4441.3	4441.3
2.5°	4467.1	4445.8	4398.7	4441.3	4433.2
5°	4441.3	4424.5	4377.4	4411.4	4403.3
7.5°	4411.4	4386.1	4338.9	4373.3	4364.7
10°	4364.7	4334.9	4283.7	4317.7	4304.9
12.5°	4300.4	4275.0	4223.8	4245.1	4236.5
15°	4227.9	4202.5	4146.8	4164.1	4142.7
17.5°	4138.2	4112.9	4057.1	4078.4	4057.1
20°	4039.9	4014.5	3954.7	3967.4	3950.6
22.5°	3942.0	3903.5	3847.7	3847.7	3839.2
25°	3826.4	3792.4	3720.0	3728.1	3720.0
27.5°	3698.2	3668.4	3613.1	3600.4	3579.1
30°	3570.4	3536.0	3472.1	3459.5	3442.2
32.5°	3433.6	3408.3	3339.8	3314.0	3296.7
35°	3301.3	3258.7	3190.3	3164.5	3143.1
37.5°	3151.8	3113.3	3044.8	3015.0	2993.6
40°	2998.2	2963.8	2895.3	2857.3	2840.0
42.5°	2848.7	2814.2	2746.3	2703.2	2677.8
45°	2686.4	2656.6	2592.2	2545.5	2528.3
47.5°	2528.3	2498.4	2430.0	2382.9	2357.5
50°	2361.6	2340.3	2280.5	2220.6	2199.3
52.5°	2199.3	2169.4	2114.1	2067.0	2037.2
55°	2033.1	2007.3	1956.1	1904.9	1883.6
57.5°	1866.3	1845.0	1789.3	1738.1	1720.9
60°	1699.6	1682.9	1623.0	1575.9	1563.2
62.5°	1537.4	1507.5	1464.8	1422.3	1405.1
65°	1371.1	1345.2	1302.7	1264.1	1242.8
67.5°	1200.3	1178.5	1140.4	1110.5	1093.3
70°	1042.1	1024.9	986.4	956.5	939.7
72.5°	880.0	862.7	841.4	811.5	798.8
75°	717.3	709.1	687.4	662.0	670.6
77.5°	572.3	555.1	546.4	533.8	521.1
80°	427.3	422.7	414.2	401.5	392.8
82.5°	290.4	290.4	286.3	269.1	269.1
85°	174.9	170.8	166.7	153.6	149.5
87.5°	77.0	68.4	59.8	47.1	42.6
90°	2.6	33.4	55.6	69.9	75.2
92.5°	69.9	58.6	66.9	72.5	75.2
95°	181.1	89.0	108.6	122.8	119.8
97.5°	326.0	97.7	142.0	150.6	153.3
100°	493.5	111.5	158.9	181.1	186.7
102.5°	677.2	671.9	164.5	194.9	203.6
105°	847.3	931.1	170.2	200.6	211.8
107.5°	1045.3	1114.8	175.8	206.2	217.4
110°	1234.9	1293.2	487.9	209.2	220.1

TEST NUMBER: P917857

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1413.3	1463.3	1416.0	214.5	223.1
115°	1602.7	1650.0	1719.9	429.3	228.7
117.5°	1767.2	1822.8	1870.5	1471.6	741.4
120°	1951.3	1992.9	2043.2	2076.6	1700.3
122.5°	2107.1	2151.8	2207.7	2224.3	2227.3
125°	2266.0	2302.4	2355.4	2374.9	2383.2
127.5°	2411.0	2450.1	2492.0	2519.8	2522.5
130°	2547.6	2592.4	2622.8	2653.6	2650.9
132.5°	2687.1	2723.4	2753.9	2779.0	2776.4
135°	2804.2	2848.9	2873.7	2901.8	2896.2
137.5°	2926.7	2960.1	2988.2	3016.0	3007.8
140°	3046.5	3069.0	3099.4	3124.6	3110.7
142.5°	3147.1	3166.6	3202.7	3224.9	3211.0
145°	3253.0	3250.0	3297.4	3317.0	3303.0
147.5°	3344.8	3336.4	3383.8	3397.7	3386.7
150°	3434.1	3414.6	3459.2	3475.8	3461.9
152.5°	3509.2	3487.0	3528.8	3545.7	3526.1
155°	3581.7	3556.9	3590.3	3606.9	3584.7
157.5°	3640.3	3618.1	3643.3	3662.8	3640.3
160°	3690.6	3673.7	3690.6	3707.2	3687.7
162.5°	3735.0	3718.4	3732.4	3751.8	3726.7
165°	3774.0	3757.5	3765.8	3785.3	3765.8
167.5°	3804.8	3788.0	3796.5	3816.1	3790.9
170°	3829.9	3813.1	3818.7	3838.3	3813.1
172.5°	3846.5	3829.9	3835.6	3855.1	3829.9
175°	3860.4	3840.9	3846.5	3866.1	3838.3
177.5°	3866.1	3846.5	3849.5	3869.0	3843.9
180°	3852.1	3852.1	3852.1	3852.1	3852.1

TEST NUMBER: P917857

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.24	12.10	12.19	13.07	14.34	10.79	11.65	11.75	12.63	13.90
	3H	12.90	13.67	13.87	14.66	15.95	12.41	13.18	13.38	14.16	15.46
	4H	13.49	14.22	14.47	15.21	16.51	13.00	13.73	13.98	14.71	16.02
	6H	13.90	14.57	14.89	15.56	16.87	13.39	14.07	14.39	15.06	16.37
	8H	14.00	14.64	15.00	15.65	16.96	13.50	14.14	14.50	15.15	16.46
	12H	14.05	14.66	15.06	15.66	17.00	13.54	14.15	14.55	15.15	16.49
4H	2H	11.70	12.43	12.69	13.41	14.72	11.34	12.07	12.33	13.06	14.36
	3H	13.57	14.18	14.57	15.19	16.51	13.16	13.77	14.16	14.79	16.10
	4H	14.29	14.85	15.29	15.85	17.19	13.86	14.42	14.87	15.43	16.77
	6H	14.81	15.29	15.82	16.32	17.65	14.37	14.85	15.39	15.89	17.22
	8H	14.96	15.41	15.98	16.43	17.78	14.52	14.97	15.54	15.99	17.34
	12H	15.03	15.44	16.07	16.48	17.83	14.58	14.99	15.62	16.03	17.38
8H	4H	14.48	14.93	15.50	15.96	17.31	14.11	14.56	15.12	15.58	16.93
	6H	15.12	15.49	16.16	16.56	17.91	14.74	15.11	15.78	16.17	17.52
	8H	15.34	15.67	16.39	16.72	18.09	14.95	15.28	16.00	16.33	17.70
	12H	15.48	15.77	16.53	16.81	18.22	15.07	15.35	16.12	16.40	17.81
12H	4H	14.47	14.88	15.51	15.91	17.27	14.10	14.51	15.14	15.55	16.90
	6H	15.15	15.48	16.20	16.53	17.90	14.78	15.11	15.83	16.16	17.52
	8H	15.40	15.68	16.45	16.73	18.14	15.02	15.30	16.07	16.35	17.76

END OF REPORT