

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917883

Luminaire Tested: DFN2DIP-SQ4F0-160D100US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917883
REPORT IS A COMBINATION OF REPORTS P901668 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D100US930-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19159.5 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 241.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917883

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917883

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55
2	92	84	79	74	85	79	74	69	69	65	62	59	57	54	51	49	47
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	43	41
4	77	67	59	53	72	62	56	50	55	49	45	48	44	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	27	23	20
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3783	3783	3783
5°	3789	3724	3748
10°	3751	3651	3627
15°	3700	3531	3439
20°	3631	3366	3209
25°	3561	3180	2986
30°	3467	2989	2704
35°	3375	2784	2455
40°	3282	2572	2170
45°	3173	2337	1912
50°	3060	2099	1659
55°	2942	1845	1417
60°	2806	1579	1167
65°	2650	1308	1052
70°	2460	1056	954
75°	2222	932	870
80°	1877	785	758
85°	1306	528	578

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3173 cd/sqm

TEST NUMBER: P917883

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	505.3	2.6
10°-20°	1387.1	7.2
20°-30°	1947.5	10.2
30°-40°	2122.9	11.1
40°-50°	1951.1	10.2
50°-60°	1532.3	8.0
60°-70°	997.4	5.2
70°-80°	513.4	2.7
80°-90°	135.9	0.7
90°-100°	90.7	0.5
100°-110°	338.2	1.8
110°-120°	897.0	4.7
120°-130°	1487.8	7.8
130°-140°	1580.4	8.2
140°-150°	1468.8	7.7
150°-160°	1180.9	6.2
160°-170°	760.9	4.0
170°-180°	261.9	1.4
0°-30°	3839.9	20.0
0°-40°	5962.7	31.1
0°-60°	9446.2	49.3
0°-90°	11092.9	57.9
90°-120°	1326.0	6.9
90°-150°	5862.9	30.6
90°-180°	8067.0	42.1
0°-180°	19159.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5391	5391	5391	5391	5391	
5°	5391	5367	5303	5347	5333	511
15°	5128	5074	4908	4816	4767	1445
25°	4655	4498	4176	3977	3903	2141
35°	4011	3762	3333	3025	2918	2510
45°	3279	2952	2440	2093	1976	2532
55°	2493	2112	1586	1293	1200	2228
65°	1683	1288	849	683	668	1669
75°	898	556	390	356	352	949
85°	210	107	93	93	93	241
90°	2	24	40	50	54	18
95°	129	64	78	88	86	153
105°	605	665	122	143	151	647
115°	1145	1179	1228	307	163	1127
125°	1619	1645	1682	1696	1702	1444
135°	2003	2035	2053	2073	2069	1547
145°	2324	2322	2355	2369	2359	1453
155°	2558	2541	2564	2576	2560	1179
165°	2696	2684	2690	2704	2690	762
175°	2757	2744	2748	2762	2742	262
180°	2752	2752	2752	2752	2752	

TEST NUMBER: P917883

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5391.4	5391.4	5391.4	5391.4	5391.4
2.5°	5415.7	5391.4	5337.5	5386.8	5376.9
5°	5391.4	5367.0	5303.4	5347.4	5332.9
7.5°	5347.4	5318.4	5250.0	5269.2	5244.9
10°	5288.9	5254.8	5157.4	5142.4	5113.4
12.5°	5215.9	5171.9	5039.9	5010.9	4957.1
15°	5127.9	5074.1	4908.4	4815.7	4767.0
17.5°	5025.4	4947.2	4742.3	4635.1	4556.9
20°	4908.4	4810.6	4566.7	4445.1	4337.5
22.5°	4781.6	4669.2	4386.1	4220.5	4147.4
25°	4654.8	4498.4	4176.4	3976.6	3903.2
27.5°	4503.6	4337.5	3981.3	3752.0	3639.7
30°	4342.6	4156.8	3766.4	3518.0	3386.0
32.5°	4186.3	3961.6	3562.0	3269.0	3146.8
35°	4010.8	3761.8	3332.7	3025.2	2917.5
37.5°	3840.0	3571.3	3117.9	2780.8	2659.2
40°	3659.3	3366.9	2893.2	2546.8	2420.0
42.5°	3474.0	3161.8	2669.0	2307.7	2186.1
45°	3278.8	2951.7	2439.7	2092.9	1975.9
47.5°	3093.5	2747.2	2220.2	1873.4	1766.3
50°	2888.5	2542.2	2005.4	1668.4	1566.4
52.5°	2688.2	2322.2	1800.4	1478.5	1385.8
55°	2493.0	2112.5	1585.6	1293.1	1200.4
57.5°	2293.2	1902.9	1395.6	1122.3	1044.1
60°	2088.2	1697.9	1195.2	946.8	868.6
62.5°	1888.4	1498.1	1024.4	790.4	751.6
65°	1683.4	1287.9	849.0	683.3	668.3
67.5°	1488.2	1092.7	683.3	600.0	585.5
70°	1283.3	902.8	565.8	517.1	497.5
72.5°	1088.1	726.8	473.1	434.3	424.4
75°	897.6	556.0	390.3	356.1	351.5
77.5°	707.6	394.9	307.4	287.8	278.0
80°	531.7	283.2	234.0	214.8	214.8
82.5°	370.6	190.5	161.0	151.2	151.2
85°	209.6	107.1	92.7	92.7	92.7
87.5°	78.2	38.8	38.8	34.2	34.2
90°	1.9	23.9	39.7	49.9	53.6
92.5°	49.9	41.8	47.8	51.8	53.6
95°	129.3	63.6	77.5	87.7	85.6
97.5°	232.8	69.7	101.4	107.5	109.5
100°	352.5	79.7	113.5	129.3	133.4
102.5°	483.7	480.0	117.5	139.3	145.4
105°	605.3	665.0	121.6	143.2	151.3
107.5°	746.7	796.3	125.6	147.3	155.3
110°	882.1	923.7	348.5	149.4	157.2



TEST NUMBER: P917883

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1009.5	1045.2	1011.5	153.2	159.4
115°	1144.8	1178.6	1228.5	306.6	163.4
117.5°	1262.2	1302.0	1336.0	1051.2	529.6
120°	1393.8	1423.5	1459.5	1483.4	1214.5
122.5°	1505.1	1537.0	1576.9	1588.8	1590.9
125°	1618.6	1644.6	1682.4	1696.4	1702.3
127.5°	1722.2	1750.0	1780.0	1799.9	1801.8
130°	1819.7	1851.7	1873.5	1895.4	1893.5
132.5°	1919.3	1945.3	1967.1	1985.0	1983.1
135°	2003.0	2034.9	2052.7	2072.7	2068.7
137.5°	2090.5	2114.4	2134.5	2154.3	2148.4
140°	2176.0	2192.2	2213.9	2231.9	2221.9
142.5°	2247.9	2261.9	2287.6	2303.5	2293.6
145°	2323.6	2321.5	2355.3	2369.3	2359.3
147.5°	2389.1	2383.2	2417.0	2426.9	2419.2
150°	2452.9	2439.0	2470.9	2482.7	2472.8
152.5°	2506.6	2490.7	2520.6	2532.6	2518.6
155°	2558.4	2540.6	2564.5	2576.3	2560.5
157.5°	2600.2	2584.4	2602.4	2616.3	2600.2
160°	2636.2	2624.1	2636.2	2648.0	2634.1
162.5°	2667.8	2656.0	2665.9	2679.9	2661.9
165°	2695.7	2683.9	2689.8	2703.8	2689.8
167.5°	2717.7	2705.6	2711.8	2725.8	2707.8
170°	2735.7	2723.7	2727.7	2741.6	2723.7
172.5°	2747.5	2735.7	2739.7	2753.7	2735.7
175°	2757.4	2743.5	2747.5	2761.5	2741.6
177.5°	2761.5	2747.5	2749.7	2763.6	2745.6
180°	2751.6	2751.6	2751.6	2751.6	2751.6

TEST NUMBER: P917883

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.49	13.39	13.38	14.30	15.45	8.45	9.35	9.34	10.26	11.41
	3H	14.18	14.98	15.08	15.90	17.08	9.64	10.45	10.55	11.37	12.55
	4H	14.79	15.55	15.71	16.47	17.67	10.10	10.86	11.02	11.78	12.97
	6H	15.22	15.92	16.15	16.85	18.05	10.42	11.12	11.36	12.05	13.26
	8H	15.35	16.02	16.29	16.96	18.16	10.52	11.18	11.46	12.13	13.33
	12H	15.42	16.05	16.36	16.99	18.22	10.56	11.20	11.51	12.14	13.36
4H	2H	12.52	13.28	13.44	14.20	15.39	9.06	9.82	9.98	10.74	11.93
	3H	14.36	14.99	15.29	15.94	17.15	10.41	11.04	11.35	12.00	13.20
	4H	15.05	15.63	16.00	16.58	17.81	10.97	11.54	11.91	12.49	13.72
	6H	15.58	16.07	16.54	17.04	18.28	11.39	11.88	12.35	12.86	14.09
	8H	15.76	16.22	16.72	17.18	18.43	11.52	11.98	12.48	12.95	14.19
	12H	15.86	16.27	16.84	17.26	18.51	11.59	12.00	12.57	12.99	14.24
8H	4H	15.03	15.49	15.99	16.46	17.70	11.25	11.71	12.21	12.68	13.93
	6H	15.60	15.98	16.59	16.99	18.23	11.78	12.16	12.76	13.16	14.41
	8H	15.82	16.16	16.82	17.15	18.42	11.97	12.30	12.96	13.30	14.56
	12H	15.97	16.26	16.96	17.25	18.56	12.09	12.39	13.09	13.38	14.69
12H	4H	14.98	15.40	15.96	16.38	17.63	11.26	11.68	12.24	12.66	13.91
	6H	15.58	15.91	16.57	16.91	18.17	11.83	12.16	12.82	13.16	14.42
	8H	15.80	16.10	16.80	17.09	18.40	12.04	12.34	13.04	13.33	14.64

END OF REPORT