

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923267

Luminaire Tested: DFN2DIP-SQ4F0-120D100US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923267
REPORT IS A COMBINATION OF REPORTS P901664 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D100US940-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17923.4 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923267

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923267

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42	42	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	36	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	32	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	28	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	25	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	22	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	20	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	18	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3103	3103	3103
5°	3108	3055	3074
10°	3077	2995	2975
15°	3035	2897	2821
20°	2979	2761	2632
25°	2921	2608	2450
30°	2844	2452	2218
35°	2769	2284	2014
40°	2692	2110	1780
45°	2602	1917	1568
50°	2510	1722	1361
55°	2414	1513	1162
60°	2302	1295	958
65°	2174	1073	863
70°	2018	866	782
75°	1823	765	714
80°	1539	644	622
85°	1072	433	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2602 cd/sqm

TEST NUMBER: P923267

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.5	2.3
10°-20°	1137.8	6.3
20°-30°	1597.5	8.9
30°-40°	1741.4	9.7
40°-50°	1600.5	8.9
50°-60°	1256.9	7.0
60°-70°	818.2	4.6
70°-80°	421.2	2.3
80°-90°	112.8	0.6
90°-100°	99.2	0.6
100°-110°	369.9	2.1
110°-120°	981.1	5.5
120°-130°	1627.2	9.1
130°-140°	1728.5	9.6
140°-150°	1606.5	9.0
150°-160°	1291.5	7.2
160°-170°	832.2	4.6
170°-180°	286.4	1.6
0°-30°	3149.8	17.6
0°-40°	4891.2	27.3
0°-60°	7748.6	43.2
0°-90°	9100.7	50.8
90°-120°	1450.3	8.1
90°-150°	6412.5	35.8
90°-180°	8823.0	49.2
0°-180°	17923.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4422	4422	4422	4422	4422	
5°	4422	4403	4350	4386	4375	419
15°	4206	4162	4026	3950	3910	1185
25°	3818	3690	3426	3262	3202	1756
35°	3290	3086	2734	2482	2393	2059
45°	2690	2421	2001	1717	1621	2077
55°	2045	1733	1301	1061	985	1827
65°	1381	1056	696	560	548	1369
75°	736	456	320	292	288	779
85°	172	88	76	76	76	197
90°	2	26	43	55	59	17
95°	141	70	85	96	94	168
105°	662	727	133	157	166	707
115°	1252	1289	1344	335	179	1233
125°	1770	1799	1840	1855	1862	1579
135°	2191	2226	2245	2267	2263	1692
145°	2541	2539	2576	2591	2580	1589
155°	2798	2779	2805	2818	2800	1289
165°	2948	2935	2942	2957	2942	833
175°	3016	3001	3005	3020	2999	287
180°	3009	3009	3009	3009	3009	



TEST NUMBER: P923267

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	4442.5	4422.5	4378.4	4418.7	4410.6
5°	4422.5	4402.6	4350.3	4386.4	4374.6
7.5°	4386.4	4362.6	4306.6	4322.3	4302.3
10°	4338.4	4310.4	4230.5	4218.2	4194.5
12.5°	4278.5	4242.5	4134.1	4110.4	4066.3
15°	4206.4	4162.2	4026.3	3950.3	3910.4
17.5°	4122.3	4058.2	3890.0	3802.2	3738.0
20°	4026.3	3946.1	3746.1	3646.3	3557.9
22.5°	3922.3	3830.2	3597.9	3462.0	3402.1
25°	3818.3	3690.0	3425.9	3262.0	3201.7
27.5°	3694.3	3557.9	3265.8	3077.7	2985.5
30°	3562.2	3409.8	3089.6	2885.8	2777.5
32.5°	3434.0	3249.7	2921.9	2681.6	2581.3
35°	3290.1	3085.8	2733.7	2481.5	2393.2
37.5°	3149.9	2929.5	2557.5	2281.1	2181.3
40°	3001.7	2761.8	2373.3	2089.2	1985.1
42.5°	2849.6	2593.6	2189.4	1893.0	1793.2
45°	2689.6	2421.3	2001.3	1716.8	1620.8
47.5°	2537.5	2253.5	1821.2	1536.8	1448.9
50°	2369.5	2085.4	1645.0	1368.6	1285.0
52.5°	2205.1	1904.9	1476.9	1212.7	1136.8
55°	2045.0	1732.9	1300.6	1060.7	984.7
57.5°	1881.1	1560.9	1144.8	920.6	856.5
60°	1713.0	1392.8	980.4	776.7	712.6
62.5°	1549.1	1228.9	840.3	648.5	616.5
65°	1380.9	1056.5	696.4	560.5	548.2
67.5°	1220.8	896.3	560.5	492.1	480.3
70°	1052.7	740.6	464.1	424.2	408.0
72.5°	892.6	596.2	388.1	356.2	348.2
75°	736.3	456.0	320.2	292.1	288.3
77.5°	580.5	324.0	252.3	236.1	228.0
80°	436.1	232.3	191.9	176.2	176.2
82.5°	304.1	156.2	132.1	123.9	123.9
85°	172.0	87.9	76.0	76.0	76.0
87.5°	64.1	31.8	31.8	28.0	28.0
90°	2.1	26.1	43.4	54.6	58.7
92.5°	54.6	45.7	52.3	56.6	58.7
95°	141.4	69.6	84.8	95.9	93.6
97.5°	254.7	76.2	110.9	117.6	119.8
100°	385.6	87.1	124.1	141.4	145.9
102.5°	529.1	524.9	128.5	152.3	159.0
105°	662.0	727.4	133.0	156.7	165.5
107.5°	816.6	870.9	137.3	161.1	169.9
110°	964.7	1010.3	381.1	163.5	171.9

TEST NUMBER: P923267

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1104.1	1143.2	1106.3	167.6	174.3
115°	1252.1	1289.1	1343.6	335.4	178.7
117.5°	1380.5	1424.1	1461.2	1149.7	579.3
120°	1524.4	1556.9	1596.3	1622.4	1328.4
122.5°	1646.2	1681.1	1724.7	1737.7	1740.0
125°	1770.3	1798.8	1840.1	1855.4	1861.8
127.5°	1883.6	1914.1	1946.9	1968.6	1970.7
130°	1990.3	2025.3	2049.1	2073.0	2071.0
132.5°	2099.2	2127.6	2151.4	2171.0	2169.0
135°	2190.8	2225.6	2245.1	2267.0	2262.6
137.5°	2286.4	2312.6	2334.5	2356.3	2349.7
140°	2380.0	2397.6	2421.4	2441.1	2430.2
142.5°	2458.6	2473.9	2502.1	2519.3	2508.6
145°	2541.4	2539.1	2576.1	2591.3	2580.4
147.5°	2613.0	2606.6	2643.5	2654.4	2645.9
150°	2682.8	2667.6	2702.5	2715.4	2704.6
152.5°	2741.5	2724.2	2756.8	2769.9	2754.7
155°	2798.2	2778.7	2804.9	2817.8	2800.5
157.5°	2843.9	2826.6	2846.3	2861.5	2843.9
160°	2883.3	2870.1	2883.3	2896.2	2880.9
162.5°	2917.9	2904.9	2915.8	2931.1	2911.4
165°	2948.4	2935.4	2941.9	2957.2	2941.9
167.5°	2972.4	2959.2	2966.0	2981.3	2961.5
170°	2992.0	2978.9	2983.3	2998.6	2978.9
172.5°	3005.0	2992.0	2996.5	3011.8	2992.0
175°	3015.9	3000.6	3005.0	3020.3	2998.6
177.5°	3020.3	3005.0	3007.4	3022.6	3002.9
180°	3009.4	3009.4	3009.4	3009.4	3009.4

TEST NUMBER: P923267

CATALOG NUMBER: DFN2DIP-SQ4F0-120D100US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.17	12.00	12.12	12.97	14.23	7.13	7.96	8.08	8.93	10.19
	3H	12.85	13.60	13.82	14.57	15.86	8.32	9.06	9.29	10.04	11.33
	4H	13.46	14.17	14.44	15.15	16.44	8.77	9.48	9.75	10.46	11.75
	6H	13.89	14.54	14.88	15.52	16.83	9.09	9.74	10.08	10.73	12.03
	8H	14.02	14.63	15.01	15.64	16.94	9.18	9.80	10.18	10.80	12.11
	12H	14.08	14.67	15.08	15.66	16.99	9.22	9.81	10.23	10.81	12.14
4H	2H	11.19	11.89	12.17	12.87	14.17	7.73	8.43	8.71	9.41	10.71
	3H	13.02	13.61	14.02	14.62	15.93	9.08	9.67	10.07	10.68	11.98
	4H	13.72	14.25	14.72	15.26	16.59	9.63	10.16	10.63	11.17	12.50
	6H	14.24	14.70	15.25	15.72	17.05	10.05	10.51	11.06	11.53	12.86
	8H	14.41	14.84	15.43	15.86	17.21	10.18	10.61	11.19	11.63	12.97
	12H	14.51	14.90	15.55	15.94	17.28	10.24	10.63	11.28	11.67	13.01
8H	4H	13.68	14.11	14.70	15.13	16.48	9.91	10.34	10.93	11.36	12.70
	6H	14.26	14.61	15.30	15.67	17.01	10.43	10.78	11.47	11.85	13.19
	8H	14.48	14.79	15.52	15.84	17.20	10.62	10.93	11.67	11.98	13.34
	12H	14.62	14.89	15.67	15.93	17.34	10.74	11.02	11.79	12.06	13.46
12H	4H	13.64	14.02	14.67	15.06	16.41	9.92	10.30	10.95	11.34	12.69
	6H	14.23	14.54	15.28	15.59	16.95	10.48	10.79	11.53	11.84	13.20
	8H	14.45	14.73	15.51	15.77	17.18	10.69	10.97	11.74	12.01	13.41