

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923270

Luminaire Tested: DFN2DIP-SQ4F0-120D110US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P923270  
REPORT IS A COMBINATION OF REPORTS P900162 AND P896915  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-120D110US940-RLLFLL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17776.2 lumens  
Efficiency: N/A  
Efficacy: 88.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 200.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P923270  
CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US940-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P923270

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US940-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	46	44	42	38
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	37	34	32	28
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	34	31	28	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25	31	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3103	3103	3103
5°	3108	3055	3074
10°	3077	2995	2975
15°	3035	2897	2821
20°	2979	2761	2632
25°	2921	2608	2450
30°	2844	2452	2218
35°	2769	2284	2014
40°	2692	2110	1780
45°	2602	1917	1568
50°	2510	1722	1361
55°	2414	1513	1162
60°	2302	1295	958
65°	2174	1073	863
70°	2018	866	782
75°	1823	765	714
80°	1539	644	622
85°	1072	433	474

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2602 cd/sqm



TEST NUMBER: P923270

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	414.5	2.3
10°-20°	1137.8	6.4
20°-30°	1597.5	9.0
30°-40°	1741.4	9.8
40°-50°	1600.5	9.0
50°-60°	1256.9	7.1
60°-70°	818.2	4.6
70°-80°	421.2	2.4
80°-90°	116.3	0.7
90°-100°	192.0	1.1
100°-110°	609.9	3.4
110°-120°	1043.8	5.9
120°-130°	1372.7	7.7
130°-140°	1540.8	8.7
140°-150°	1511.0	8.5
150°-160°	1267.5	7.1
160°-170°	840.6	4.7
170°-180°	293.8	1.7
0°-30°	3149.8	17.7
0°-40°	4891.2	27.5
0°-60°	7748.6	43.6
0°-90°	9104.3	51.2
90°-120°	1845.7	10.4
90°-150°	6270.1	35.3
90°-180°	8672.0	48.8
0°-180°	17776.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4422	4422	4422	4422	4422	
5°	4422	4403	4350	4386	4375	419
15°	4206	4162	4026	3950	3910	1185
25°	3818	3690	3426	3262	3202	1756
35°	3290	3086	2734	2482	2393	2059
45°	2690	2421	2001	1717	1621	2077
55°	2045	1733	1301	1061	985	1827
65°	1381	1056	696	560	548	1369
75°	736	456	320	292	288	779
85°	172	88	76	76	76	197
90°	3	34	92	86	89	17
95°	136	163	167	167	163	152
105°	563	570	576	581	581	594
115°	1048	1062	1058	1055	1048	1036
125°	1524	1547	1539	1531	1528	1361
135°	1970	2000	2005	2002	1995	1523
145°	2392	2411	2426	2429	2418	1495
155°	2736	2743	2752	2765	2756	1259
165°	2976	2973	2973	2992	2979	840
175°	3097	3089	3083	3102	3086	294
180°	3102	3102	3102	3102	3102	



TEST NUMBER: P923270

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	4442.5	4422.5	4378.4	4418.7	4410.6
5°	4422.5	4402.6	4350.3	4386.4	4374.6
7.5°	4386.4	4362.6	4306.6	4322.3	4302.3
10°	4338.4	4310.4	4230.5	4218.2	4194.5
12.5°	4278.5	4242.5	4134.1	4110.4	4066.3
15°	4206.4	4162.2	4026.3	3950.3	3910.4
17.5°	4122.3	4058.2	3890.0	3802.2	3738.0
20°	4026.3	3946.1	3746.1	3646.3	3557.9
22.5°	3922.3	3830.2	3597.9	3462.0	3402.1
25°	3818.3	3690.0	3425.9	3262.0	3201.7
27.5°	3694.3	3557.9	3265.8	3077.7	2985.5
30°	3562.2	3409.8	3089.6	2885.8	2777.5
32.5°	3434.0	3249.7	2921.9	2681.6	2581.3
35°	3290.1	3085.8	2733.7	2481.5	2393.2
37.5°	3149.9	2929.5	2557.5	2281.1	2181.3
40°	3001.7	2761.8	2373.3	2089.2	1985.1
42.5°	2849.6	2593.6	2189.4	1893.0	1793.2
45°	2689.6	2421.3	2001.3	1716.8	1620.8
47.5°	2537.5	2253.5	1821.2	1536.8	1448.9
50°	2369.5	2085.4	1645.0	1368.6	1285.0
52.5°	2205.1	1904.9	1476.9	1212.7	1136.8
55°	2045.0	1732.9	1300.6	1060.7	984.7
57.5°	1881.1	1560.9	1144.8	920.6	856.5
60°	1713.0	1392.8	980.4	776.7	712.6
62.5°	1549.1	1228.9	840.3	648.5	616.5
65°	1380.9	1056.5	696.4	560.5	548.2
67.5°	1220.8	896.3	560.5	492.1	480.3
70°	1052.7	740.6	464.1	424.2	408.0
72.5°	892.6	596.2	388.1	356.2	348.2
75°	736.3	456.0	320.2	292.1	288.3
77.5°	580.5	324.0	252.3	236.1	228.0
80°	436.1	232.3	191.9	176.2	176.2
82.5°	304.1	156.2	132.1	123.9	123.9
85°	172.0	87.9	76.0	76.0	76.0
87.5°	64.1	31.8	31.8	28.0	28.0
90°	2.8	33.7	91.7	86.1	88.8
92.5°	58.0	78.6	81.3	84.2	84.2
95°	136.5	162.7	167.4	167.4	162.7
97.5°	227.3	251.6	261.9	261.9	261.9
100°	332.0	353.5	361.0	361.0	358.2
102.5°	442.4	458.2	468.6	471.4	468.6
105°	563.0	570.5	576.1	580.8	580.8
107.5°	682.7	693.9	693.9	695.8	682.7
110°	798.7	813.7	813.7	813.7	806.2



TEST NUMBER: P923270

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	924.0	939.9	937.1	929.6	924.0
115°	1047.5	1062.4	1057.7	1055.0	1047.5
117.5°	1170.0	1190.5	1177.4	1170.0	1162.5
120°	1293.4	1314.0	1293.4	1293.4	1285.0
122.5°	1405.7	1431.8	1418.7	1411.2	1405.7
125°	1523.5	1546.8	1539.4	1531.0	1528.1
127.5°	1638.5	1667.5	1657.2	1646.0	1638.5
130°	1746.1	1779.8	1775.0	1769.4	1759.2
132.5°	1866.7	1892.9	1894.8	1881.7	1874.2
135°	1970.5	1999.5	2005.1	2002.3	1994.8
137.5°	2086.5	2109.9	2114.5	2112.6	2101.5
140°	2188.4	2211.8	2224.9	2224.9	2214.7
142.5°	2293.2	2316.6	2324.1	2326.8	2316.6
145°	2392.3	2411.0	2426.0	2428.8	2418.5
147.5°	2481.2	2504.5	2515.8	2520.4	2510.2
150°	2572.9	2588.7	2599.0	2607.5	2599.0
152.5°	2654.2	2670.0	2683.2	2693.5	2683.2
155°	2735.6	2743.0	2751.5	2764.6	2756.1
157.5°	2805.7	2811.3	2815.9	2834.7	2821.5
160°	2868.4	2874.0	2876.7	2892.7	2881.5
162.5°	2926.3	2926.3	2929.2	2946.9	2933.8
165°	2975.9	2973.1	2973.1	2991.8	2978.7
167.5°	3020.8	3012.4	3012.4	3031.1	3018.0
170°	3054.5	3047.0	3044.2	3062.8	3047.0
172.5°	3077.8	3070.3	3067.6	3086.3	3070.3
175°	3096.6	3089.1	3083.4	3102.2	3086.3
177.5°	3106.8	3099.3	3093.7	3109.7	3093.7
180°	3102.2	3102.2	3102.2	3102.2	3102.2



TEST NUMBER: P923270  
 CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.21	12.05	12.16	13.01	14.27	7.17	8.01	8.12	8.97	10.23
	3H	12.89	13.64	13.85	14.61	15.89	8.36	9.11	9.32	10.08	11.36
	4H	13.50	14.21	14.48	15.19	16.48	8.81	9.52	9.79	10.50	11.78
	6H	13.93	14.58	14.92	15.56	16.86	9.13	9.78	10.12	10.77	12.07
	8H	14.06	14.68	15.05	15.68	16.97	9.22	9.84	10.22	10.84	12.14
	12H	14.12	14.71	15.12	15.70	17.02	9.26	9.86	10.27	10.85	12.17
4H	2H	11.23	11.94	12.21	12.91	14.20	7.77	8.48	8.75	9.45	10.74
	3H	13.06	13.65	14.05	14.66	15.96	9.12	9.71	10.11	10.72	12.02
	4H	13.76	14.29	14.76	15.30	16.62	9.67	10.21	10.67	11.21	12.53
	6H	14.28	14.74	15.29	15.76	17.09	10.09	10.55	11.10	11.57	12.90
	8H	14.45	14.89	15.47	15.90	17.24	10.22	10.65	11.23	11.67	13.00
	12H	14.55	14.94	15.58	15.97	17.32	10.28	10.67	11.31	11.70	13.05
8H	4H	13.72	14.16	14.74	15.17	16.51	9.95	10.38	10.96	11.40	12.74
	6H	14.30	14.65	15.33	15.71	17.05	10.47	10.83	11.51	11.89	13.22
	8H	14.52	14.83	15.56	15.87	17.23	10.66	10.98	11.71	12.02	13.37
	12H	14.66	14.93	15.71	15.97	17.37	10.78	11.06	11.83	12.10	13.49
12H	4H	13.68	14.07	14.71	15.10	16.44	9.96	10.35	10.99	11.38	12.72
	6H	14.27	14.59	15.32	15.63	16.98	10.52	10.83	11.57	11.88	13.23
	8H	14.50	14.77	15.54	15.81	17.21	10.73	11.01	11.78	12.05	13.45