

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923287

Luminaire Tested: DFN2DIP-SQ4F0-140D060US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923287
REPORT IS A COMBINATION OF REPORTS P901594 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D060US940-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15908.1 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923287

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923287

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3620	3620	3620
5°	3626	3564	3587
10°	3590	3494	3471
15°	3541	3380	3292
20°	3475	3221	3071
25°	3408	3043	2858
30°	3318	2861	2587
35°	3230	2665	2350
40°	3140	2462	2077
45°	3036	2236	1830
50°	2928	2008	1588
55°	2816	1765	1356
60°	2686	1511	1117
65°	2536	1252	1007
70°	2354	1010	913
75°	2126	892	833
80°	1796	751	726
85°	1250	505	552

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3036 cd/sqm

TEST NUMBER: P923287

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	483.6	3.0
10°-20°	1327.5	8.3
20°-30°	1863.7	11.7
30°-40°	2031.6	12.8
40°-50°	1867.3	11.7
50°-60°	1466.4	9.2
60°-70°	954.5	6.0
70°-80°	491.3	3.1
80°-90°	128.6	0.8
90°-100°	59.5	0.4
100°-110°	222.0	1.4
110°-120°	588.7	3.7
120°-130°	976.3	6.1
130°-140°	1037.1	6.5
140°-150°	963.9	6.1
150°-160°	774.9	4.9
160°-170°	499.3	3.1
170°-180°	171.9	1.1
0°-30°	3674.8	23.1
0°-40°	5706.4	35.9
0°-60°	9040.1	56.8
0°-90°	10614.5	66.7
90°-120°	870.2	5.5
90°-150°	3847.4	24.2
90°-180°	5294.0	33.3
0°-180°	15908.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5160	5160	5160	5160	5160	
5°	5160	5136	5075	5118	5104	489
15°	4907	4856	4697	4609	4562	1383
25°	4455	4305	3997	3806	3735	2049
35°	3838	3600	3189	2895	2792	2402
45°	3138	2825	2335	2003	1891	2423
55°	2386	2022	1517	1238	1149	2132
65°	1611	1232	812	654	640	1597
75°	859	532	374	341	336	909
85°	201	102	89	89	89	230
90°	1	16	26	33	35	15
95°	85	42	51	58	56	101
105°	397	436	80	94	99	424
115°	751	774	806	201	107	740
125°	1062	1079	1104	1113	1117	947
135°	1314	1335	1347	1360	1358	1015
145°	1525	1523	1546	1555	1548	954
155°	1679	1667	1683	1691	1680	774
165°	1769	1761	1765	1774	1765	500
175°	1810	1800	1803	1812	1799	172
180°	1806	1806	1806	1806	1806	

TEST NUMBER: P923287

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5159.6	5159.6	5159.6	5159.6	5159.6
2.5°	5182.9	5159.6	5108.1	5155.2	5145.7
5°	5159.6	5136.3	5075.3	5117.5	5103.6
7.5°	5117.5	5089.7	5024.3	5042.7	5019.4
10°	5061.5	5028.8	4935.7	4921.3	4893.5
12.5°	4991.6	4949.5	4823.2	4795.4	4744.0
15°	4907.4	4855.9	4697.4	4608.7	4562.2
17.5°	4809.4	4734.5	4538.4	4435.8	4361.0
20°	4697.4	4603.7	4370.5	4254.0	4151.0
22.5°	4576.0	4468.5	4197.5	4039.0	3969.2
25°	4454.6	4305.0	3996.9	3805.6	3735.3
27.5°	4310.0	4151.0	3810.1	3590.7	3483.2
30°	4155.9	3978.1	3604.6	3366.7	3240.4
32.5°	4006.3	3791.3	3408.8	3128.5	3011.6
35°	3838.4	3600.1	3189.4	2895.1	2792.0
37.5°	3674.9	3417.7	2983.8	2661.3	2544.9
40°	3502.0	3222.1	2768.8	2437.4	2316.0
42.5°	3324.7	3025.9	2554.3	2208.5	2092.0
45°	3137.8	2824.8	2334.9	2002.9	1891.0
47.5°	2960.5	2629.1	2124.8	1792.9	1690.3
50°	2764.3	2432.9	1919.1	1596.7	1499.1
52.5°	2572.6	2222.3	1723.0	1414.9	1326.2
55°	2385.9	2021.7	1517.4	1237.5	1148.8
57.5°	2194.6	1821.1	1335.6	1074.1	999.3
60°	1998.4	1624.9	1143.9	906.1	831.3
62.5°	1807.2	1433.7	980.4	756.4	719.3
65°	1611.1	1232.5	812.4	653.9	639.5
67.5°	1424.2	1045.8	653.9	574.2	560.3
70°	1228.1	864.0	541.4	494.9	476.1
72.5°	1041.3	695.5	452.8	415.6	406.3
75°	859.0	532.1	373.5	340.8	336.4
77.5°	677.3	378.0	294.3	275.4	266.0
80°	508.8	271.0	223.9	205.6	205.6
82.5°	354.7	182.3	154.1	144.6	144.6
85°	200.6	102.5	88.6	88.6	88.6
87.5°	74.8	37.2	37.2	32.7	32.7
90°	1.2	15.7	26.0	32.7	35.2
92.5°	32.7	27.5	31.3	34.0	35.2
95°	84.9	41.7	50.9	57.6	56.2
97.5°	152.8	45.7	66.5	70.6	71.9
100°	231.3	52.3	74.5	84.9	87.5
102.5°	317.4	315.0	77.1	91.4	95.4
105°	397.2	436.4	79.7	94.0	99.3
107.5°	490.0	522.5	82.4	96.7	101.9
110°	578.9	606.2	228.7	98.1	103.2

TEST NUMBER: P923287

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	662.5	685.9	663.7	100.5	104.6
115°	751.3	773.5	806.2	201.3	107.2
117.5°	828.3	854.4	876.7	689.8	347.5
120°	914.6	934.2	957.8	973.4	797.0
122.5°	987.7	1008.6	1034.8	1042.6	1044.0
125°	1062.2	1079.2	1104.0	1113.2	1117.0
127.5°	1130.2	1148.4	1168.1	1181.2	1182.4
130°	1194.2	1215.1	1229.4	1243.8	1242.6
132.5°	1259.5	1276.6	1290.8	1302.6	1301.4
135°	1314.5	1335.4	1347.0	1360.2	1357.5
137.5°	1371.8	1387.5	1400.7	1413.7	1409.9
140°	1428.0	1438.6	1452.9	1464.6	1458.1
142.5°	1475.2	1484.3	1501.3	1511.6	1505.1
145°	1524.8	1523.4	1545.6	1554.8	1548.3
147.5°	1567.8	1563.9	1586.1	1592.6	1587.5
150°	1609.7	1600.5	1621.5	1629.2	1622.7
152.5°	1644.9	1634.5	1654.0	1662.0	1652.8
155°	1678.9	1667.2	1682.9	1690.7	1680.2
157.5°	1706.4	1695.9	1707.7	1716.9	1706.4
160°	1729.9	1722.0	1729.9	1737.7	1728.6
162.5°	1750.7	1742.9	1749.4	1758.6	1746.9
165°	1769.1	1761.3	1765.1	1774.3	1765.1
167.5°	1783.4	1775.6	1779.6	1788.8	1776.9
170°	1795.3	1787.3	1790.0	1799.1	1787.3
172.5°	1803.0	1795.3	1797.9	1807.1	1795.3
175°	1809.5	1800.4	1803.0	1812.1	1799.1
177.5°	1812.1	1803.0	1804.4	1813.6	1801.8
180°	1805.6	1805.6	1805.6	1805.6	1805.6

TEST NUMBER: P923287

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.06	14.05	13.87	14.88	15.89	9.03	10.01	9.83	10.84	11.85
	3H	14.76	15.64	15.58	16.48	17.52	10.23	11.11	11.05	11.94	12.99
	4H	15.38	16.21	16.21	17.05	18.11	10.68	11.52	11.52	12.36	13.41
	6H	15.81	16.58	16.66	17.43	18.49	11.01	11.78	11.86	12.63	13.70
	8H	15.94	16.67	16.80	17.54	18.61	11.11	11.84	11.97	12.71	13.77
	12H	16.01	16.71	16.88	17.57	18.66	11.16	11.85	12.02	12.71	13.81
4H	2H	13.10	13.94	13.94	14.78	15.83	9.64	10.48	10.48	11.32	12.37
	3H	14.95	15.64	15.80	16.52	17.59	11.01	11.70	11.86	12.57	13.64
	4H	15.65	16.28	16.52	17.15	18.25	11.56	12.19	12.43	13.06	14.16
	6H	16.18	16.72	17.06	17.62	18.72	11.99	12.53	12.87	13.43	14.53
	8H	16.36	16.87	17.24	17.76	18.87	12.12	12.63	13.01	13.52	14.63
	12H	16.47	16.92	17.37	17.83	18.95	12.20	12.65	13.10	13.56	14.68
8H	4H	15.63	16.14	16.51	17.03	18.14	11.86	12.36	12.74	13.25	14.37
	6H	16.21	16.63	17.12	17.56	18.67	12.38	12.80	13.29	13.73	14.84
	8H	16.43	16.80	17.35	17.72	18.85	12.57	12.95	13.50	13.87	15.00
	12H	16.58	16.90	17.50	17.82	19.00	12.70	13.03	13.62	13.94	15.13
12H	4H	15.59	16.05	16.49	16.96	18.07	11.87	12.32	12.77	13.23	14.35
	6H	16.18	16.56	17.10	17.48	18.61	12.43	12.80	13.35	13.73	14.86
	8H	16.41	16.74	17.34	17.66	18.84	12.65	12.98	13.57	13.90	15.08

END OF REPORT