

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923312

Luminaire Tested: DFN2DIP-SQ4F0-140D140US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923312
REPORT IS A COMBINATION OF REPORTS P900199 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D140US940-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23407.4 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 249.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923312

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923312

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3408	3408	3408
5°	3414	3362	3385
10°	3386	3317	3340
15°	3336	3263	3269
20°	3269	3188	3197
25°	3202	3098	3113
30°	3118	3014	3006
35°	3039	2915	2893
40°	2941	2815	2786
45°	2843	2715	2676
50°	2736	2610	2548
55°	2625	2489	2432
60°	2498	2344	2298
65°	2361	2196	2140
70°	2185	2014	1970
75°	1942	1796	1815
80°	1649	1519	1516
85°	1192	1039	1019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3108 cd/sqm

TEST NUMBER: P923312

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	457.2	2.0
10°-20°	1286.4	5.5
20°-30°	1890.5	8.1
30°-40°	2195.7	9.4
40°-50°	2192.9	9.4
50°-60°	1912.2	8.2
60°-70°	1413.5	6.0
70°-80°	799.7	3.4
80°-90°	222.3	0.9
90°-100°	244.3	1.0
100°-110°	776.3	3.3
110°-120°	1328.4	5.7
120°-130°	1747.1	7.5
130°-140°	1961.0	8.4
140°-150°	1923.0	8.2
150°-160°	1613.2	6.9
160°-170°	1069.8	4.6
170°-180°	373.9	1.6
0°-30°	3634.0	15.5
0°-40°	5829.7	24.9
0°-60°	9934.8	42.4
0°-90°	12370.3	52.8
90°-120°	2349.0	10.0
90°-150°	7980.2	34.1
90°-180°	11037.0	47.2
0°-180°	23407.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4858	4858	4858	4858	4858	
5°	4858	4839	4788	4825	4816	461
15°	4624	4596	4535	4554	4531	1302
25°	4185	4148	4069	4078	4069	1926
35°	3611	3564	3489	3461	3438	2255
45°	2938	2906	2835	2784	2765	2268
55°	2224	2195	2139	2083	2060	1988
65°	1500	1471	1425	1383	1359	1483
75°	784	776	752	724	733	837
85°	191	187	182	168	164	213
90°	4	43	117	110	113	23
95°	174	207	213	213	207	193
105°	717	726	733	739	739	756
115°	1333	1352	1346	1343	1333	1319
125°	1939	1969	1959	1948	1945	1733
135°	2508	2545	2552	2548	2539	1938
145°	3045	3069	3088	3091	3078	1902
155°	3482	3491	3502	3518	3508	1603
165°	3788	3784	3784	3808	3791	1068
175°	3941	3932	3924	3948	3928	374
180°	3948	3948	3948	3948	3948	

TEST NUMBER: P923312

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4857.6	4857.6	4857.6	4857.6	4857.6
2.5°	4885.8	4862.5	4811.0	4857.6	4848.7
5°	4857.6	4839.2	4787.7	4824.9	4815.9
7.5°	4824.9	4797.1	4745.6	4783.2	4773.8
10°	4773.8	4741.1	4685.1	4722.3	4708.4
12.5°	4703.4	4675.7	4619.7	4643.0	4633.6
15°	4624.1	4596.4	4535.4	4554.3	4531.0
17.5°	4526.1	4498.3	4437.3	4460.6	4437.3
20°	4418.5	4390.8	4325.3	4339.2	4320.9
22.5°	4311.4	4269.3	4208.3	4208.3	4199.0
25°	4185.1	4147.9	4068.6	4077.5	4068.6
27.5°	4044.8	4012.2	3951.7	3937.8	3914.5
30°	3905.1	3867.4	3797.5	3783.7	3764.8
32.5°	3755.4	3727.7	3652.8	3624.6	3605.7
35°	3610.7	3564.2	3489.3	3461.1	3437.7
37.5°	3447.2	3405.1	3330.2	3297.5	3274.2
40°	3279.2	3241.5	3166.6	3125.1	3106.2
42.5°	3115.6	3078.0	3003.6	2956.6	2928.8
45°	2938.2	2905.5	2835.2	2784.1	2765.3
47.5°	2765.3	2732.6	2657.7	2606.2	2578.5
50°	2582.9	2559.7	2494.2	2428.8	2405.5
52.5°	2405.5	2372.8	2312.3	2260.8	2228.1
55°	2223.7	2195.4	2139.4	2083.4	2060.1
57.5°	2041.2	2017.9	1957.0	1901.0	1882.1
60°	1858.9	1840.6	1775.1	1723.6	1709.7
62.5°	1681.5	1648.8	1602.1	1555.6	1536.8
65°	1499.6	1471.3	1424.8	1382.6	1359.3
67.5°	1312.8	1289.0	1247.3	1214.6	1195.8
70°	1139.8	1121.0	1078.9	1046.2	1027.8
72.5°	962.4	943.5	920.2	887.6	873.7
75°	784.5	775.6	751.8	724.1	733.4
77.5°	625.9	607.1	597.6	583.8	569.9
80°	467.3	462.4	453.0	439.1	429.6
82.5°	317.6	317.6	313.2	294.4	294.4
85°	191.3	186.8	182.4	168.0	163.5
87.5°	84.3	74.8	65.5	51.5	46.5
90°	3.6	42.9	116.6	109.5	113.1
92.5°	73.8	100.0	103.5	107.1	107.1
95°	173.8	207.1	213.0	213.0	207.1
97.5°	289.3	320.2	333.3	333.3	333.3
100°	422.6	450.0	459.4	459.4	455.8
102.5°	563.0	583.3	596.4	599.9	596.4
105°	716.6	726.1	733.3	739.1	739.1
107.5°	868.9	883.2	883.2	885.6	868.9
110°	1016.5	1035.5	1035.5	1035.5	1026.0



TEST NUMBER: P923312

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1176.0	1196.2	1192.7	1183.1	1176.0
115°	1333.1	1352.2	1346.2	1342.6	1333.1
117.5°	1489.1	1515.3	1498.6	1489.1	1479.5
120°	1646.2	1672.4	1646.2	1646.2	1635.5
122.5°	1789.0	1822.3	1805.7	1796.2	1789.0
125°	1939.0	1968.7	1959.2	1948.5	1944.9
127.5°	2085.4	2122.3	2109.2	2094.9	2085.4
130°	2222.2	2265.1	2259.1	2252.0	2238.9
132.5°	2375.8	2409.1	2411.5	2394.9	2385.3
135°	2507.9	2544.9	2552.0	2548.4	2538.9
137.5°	2655.5	2685.3	2691.3	2688.9	2674.6
140°	2785.3	2815.0	2831.7	2831.7	2818.6
142.5°	2918.6	2948.4	2957.9	2961.5	2948.4
145°	3044.7	3068.6	3087.6	3091.2	3078.1
147.5°	3157.8	3187.6	3201.9	3207.8	3194.7
150°	3274.4	3294.7	3307.8	3318.5	3307.8
152.5°	3378.1	3398.3	3415.0	3428.0	3415.0
155°	3481.6	3491.1	3501.8	3518.5	3507.8
157.5°	3570.9	3578.0	3584.0	3607.8	3591.1
160°	3650.7	3657.8	3661.4	3681.6	3667.2
162.5°	3724.4	3724.4	3728.0	3750.6	3733.9
165°	3787.5	3784.0	3784.0	3807.8	3791.1
167.5°	3844.6	3833.9	3833.9	3857.7	3841.0
170°	3887.5	3878.0	3874.4	3898.2	3878.0
172.5°	3917.3	3907.7	3904.2	3928.0	3907.7
175°	3941.1	3931.6	3924.4	3948.2	3928.0
177.5°	3954.1	3944.7	3937.5	3957.7	3937.5
180°	3948.2	3948.2	3948.2	3948.2	3948.2

TEST NUMBER: P923312

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.80	12.69	12.74	13.64	14.87	11.36	12.25	12.29	13.20	14.43
	3H	13.47	14.27	14.41	15.22	16.48	12.98	13.78	13.92	14.73	15.99
	4H	14.06	14.81	15.02	15.78	17.04	13.57	14.32	14.53	15.28	16.55
	6H	14.47	15.16	15.44	16.13	17.40	13.97	14.66	14.94	15.63	16.90
	8H	14.57	15.23	15.55	16.22	17.49	14.07	14.73	15.05	15.72	16.99
	12H	14.62	15.25	15.61	16.23	17.53	14.11	14.74	15.10	15.72	17.02
4H	2H	12.27	13.02	13.23	13.98	15.25	11.91	12.67	12.88	13.63	14.89
	3H	14.14	14.77	15.11	15.76	17.04	13.73	14.36	14.71	15.36	16.63
	4H	14.86	15.43	15.84	16.42	17.72	14.44	15.01	15.42	16.00	17.30
	6H	15.38	15.88	16.38	16.89	18.18	14.95	15.44	15.94	16.45	17.75
	8H	15.53	16.00	16.53	17.00	18.31	15.10	15.56	16.09	16.56	17.88
	12H	15.61	16.03	16.62	17.05	18.37	15.16	15.58	16.18	16.60	17.92
8H	4H	15.06	15.52	16.05	16.53	17.84	14.68	15.14	15.68	16.15	17.46
	6H	15.70	16.08	16.72	17.12	18.44	15.31	15.70	16.33	16.74	18.05
	8H	15.92	16.26	16.95	17.29	18.62	15.53	15.86	16.56	16.90	18.23
	12H	16.06	16.35	17.09	17.38	18.75	15.64	15.94	16.68	16.97	18.34
12H	4H	15.05	15.46	16.06	16.48	17.80	14.68	15.10	15.69	16.12	17.43
	6H	15.73	16.06	16.76	17.10	18.43	15.35	15.69	16.38	16.72	18.05
	8H	15.97	16.27	17.01	17.30	18.67	15.59	15.89	16.63	16.92	18.29