

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923318

Luminaire Tested: DFN2DIP-SQ4F0-140D160US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923318
REPORT IS A COMBINATION OF REPORTS P900218 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D160US940-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23238.8 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 265.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923318

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923318

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3620	3620	3620
5°	3626	3564	3587
10°	3590	3494	3471
15°	3541	3380	3292
20°	3475	3221	3071
25°	3408	3043	2858
30°	3318	2861	2587
35°	3230	2665	2350
40°	3140	2462	2077
45°	3036	2236	1830
50°	2928	2008	1588
55°	2816	1765	1356
60°	2686	1511	1117
65°	2536	1252	1007
70°	2354	1010	913
75°	2126	892	833
80°	1796	751	726
85°	1250	505	552

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3551 cd/sqm

TEST NUMBER: P923318

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	483.6	2.1
10°-20°	1327.5	5.7
20°-30°	1863.7	8.0
30°-40°	2031.6	8.7
40°-50°	1867.3	8.0
50°-60°	1466.4	6.3
60°-70°	954.5	4.1
70°-80°	491.3	2.1
80°-90°	138.2	0.6
90°-100°	279.2	1.2
100°-110°	887.2	3.8
110°-120°	1518.3	6.5
120°-130°	1996.8	8.6
130°-140°	2241.4	9.6
140°-150°	2197.9	9.5
150°-160°	1843.7	7.9
160°-170°	1222.7	5.3
170°-180°	427.4	1.8
0°-30°	3674.8	15.8
0°-40°	5706.4	24.6
0°-60°	9040.1	38.9
0°-90°	10624.1	45.7
90°-120°	2684.7	11.6
90°-150°	9120.8	39.2
90°-180°	12615.0	54.3
0°-180°	23238.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5160	5160	5160	5160	5160	
5°	5160	5136	5075	5118	5104	489
15°	4907	4856	4697	4609	4562	1383
25°	4455	4305	3997	3806	3735	2049
35°	3838	3600	3189	2895	2792	2402
45°	3138	2825	2335	2003	1891	2423
55°	2386	2022	1517	1238	1149	2132
65°	1611	1232	812	654	640	1597
75°	859	532	374	341	336	909
85°	201	102	89	89	89	230
90°	4	49	133	125	129	23
95°	199	237	244	244	237	221
105°	819	830	838	845	845	864
115°	1524	1545	1539	1534	1524	1507
125°	2216	2250	2239	2227	2223	1980
135°	2866	2909	2917	2913	2902	2216
145°	3480	3507	3529	3533	3518	2174
155°	3979	3990	4002	4021	4009	1832
165°	4329	4325	4325	4352	4333	1221
175°	4504	4494	4485	4513	4489	428
180°	4513	4513	4513	4513	4513	

TEST NUMBER: P923318

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5159.6	5159.6	5159.6	5159.6	5159.6
2.5°	5182.9	5159.6	5108.1	5155.2	5145.7
5°	5159.6	5136.3	5075.3	5117.5	5103.6
7.5°	5117.5	5089.7	5024.3	5042.7	5019.4
10°	5061.5	5028.8	4935.7	4921.3	4893.5
12.5°	4991.6	4949.5	4823.2	4795.4	4744.0
15°	4907.4	4855.9	4697.4	4608.7	4562.2
17.5°	4809.4	4734.5	4538.4	4435.8	4361.0
20°	4697.4	4603.7	4370.5	4254.0	4151.0
22.5°	4576.0	4468.5	4197.5	4039.0	3969.2
25°	4454.6	4305.0	3996.9	3805.6	3735.3
27.5°	4310.0	4151.0	3810.1	3590.7	3483.2
30°	4155.9	3978.1	3604.6	3366.7	3240.4
32.5°	4006.3	3791.3	3408.8	3128.5	3011.6
35°	3838.4	3600.1	3189.4	2895.1	2792.0
37.5°	3674.9	3417.7	2983.8	2661.3	2544.9
40°	3502.0	3222.1	2768.8	2437.4	2316.0
42.5°	3324.7	3025.9	2554.3	2208.5	2092.0
45°	3137.8	2824.8	2334.9	2002.9	1891.0
47.5°	2960.5	2629.1	2124.8	1792.9	1690.3
50°	2764.3	2432.9	1919.1	1596.7	1499.1
52.5°	2572.6	2222.3	1723.0	1414.9	1326.2
55°	2385.9	2021.7	1517.4	1237.5	1148.8
57.5°	2194.6	1821.1	1335.6	1074.1	999.3
60°	1998.4	1624.9	1143.9	906.1	831.3
62.5°	1807.2	1433.7	980.4	756.4	719.3
65°	1611.1	1232.5	812.4	653.9	639.5
67.5°	1424.2	1045.8	653.9	574.2	560.3
70°	1228.1	864.0	541.4	494.9	476.1
72.5°	1041.3	695.5	452.8	415.6	406.3
75°	859.0	532.1	373.5	340.8	336.4
77.5°	677.3	378.0	294.3	275.4	266.0
80°	508.8	271.0	223.9	205.6	205.6
82.5°	354.7	182.3	154.1	144.6	144.6
85°	200.6	102.5	88.6	88.6	88.6
87.5°	74.8	37.2	37.2	32.7	32.7
90°	4.1	49.0	133.3	125.2	129.2
92.5°	84.4	114.3	118.3	122.4	122.4
95°	198.6	236.7	243.5	243.5	236.7
97.5°	330.6	366.0	380.9	380.9	380.9
100°	483.0	514.2	525.1	525.1	521.0
102.5°	643.5	666.6	681.5	685.6	681.5
105°	818.9	829.8	838.0	844.8	844.8
107.5°	993.1	1009.4	1009.4	1012.2	993.1
110°	1161.8	1183.6	1183.6	1183.6	1172.7



TEST NUMBER: P923318

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1344.1	1367.3	1363.2	1352.3	1344.1
115°	1523.7	1545.4	1538.6	1534.5	1523.7
117.5°	1701.9	1731.8	1712.8	1701.9	1691.0
120°	1881.5	1911.4	1881.5	1881.5	1869.2
122.5°	2044.7	2082.9	2063.8	2052.9	2044.7
125°	2216.2	2250.1	2239.3	2227.0	2222.9
127.5°	2383.5	2425.6	2410.6	2394.3	2383.5
130°	2539.9	2588.9	2582.1	2573.9	2558.9
132.5°	2715.4	2753.5	2756.2	2737.2	2726.3
135°	2866.4	2908.6	2916.8	2912.7	2901.8
137.5°	3035.1	3069.1	3076.0	3073.2	3056.9
140°	3183.4	3217.4	3236.5	3236.5	3221.5
142.5°	3335.8	3369.8	3380.7	3384.8	3369.8
145°	3480.0	3507.2	3528.9	3533.0	3518.1
147.5°	3609.2	3643.3	3659.6	3666.4	3651.4
150°	3742.5	3765.7	3780.7	3792.9	3780.7
152.5°	3860.9	3884.0	3903.1	3918.0	3903.1
155°	3979.3	3990.1	4002.4	4021.4	4009.2
157.5°	4081.3	4089.5	4096.2	4123.4	4104.5
160°	4172.4	4180.6	4184.7	4207.8	4191.5
162.5°	4256.8	4256.8	4260.9	4286.7	4267.6
165°	4328.9	4324.8	4324.8	4352.0	4333.0
167.5°	4394.2	4382.0	4382.0	4409.2	4390.1
170°	4443.1	4432.2	4428.2	4455.4	4432.2
172.5°	4477.2	4466.3	4462.2	4489.4	4466.3
175°	4504.4	4493.5	4485.3	4512.6	4489.4
177.5°	4519.4	4508.5	4500.3	4523.5	4500.3
180°	4512.6	4512.6	4512.6	4512.6	4512.6

TEST NUMBER: P923318

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.21	12.01	12.21	13.02	14.35	7.17	7.97	8.17	8.98	10.31
	3H	12.89	13.61	13.90	14.62	15.98	8.36	9.07	9.37	10.09	11.44
	4H	13.50	14.18	14.53	15.20	16.56	8.81	9.48	9.83	10.50	11.87
	6H	13.93	14.55	14.96	15.57	16.94	9.13	9.75	10.16	10.77	12.15
	8H	14.05	14.64	15.09	15.68	17.05	9.22	9.81	10.26	10.85	12.22
	12H	14.12	14.68	15.16	15.71	17.10	9.26	9.82	10.31	10.86	12.25
4H	2H	11.23	11.90	12.26	12.92	14.28	7.77	8.44	8.80	9.46	10.82
	3H	13.06	13.62	14.10	14.67	16.04	9.12	9.68	10.15	10.72	12.10
	4H	13.75	14.27	14.80	15.30	16.70	9.66	10.18	10.71	11.21	12.61
	6H	14.27	14.71	15.32	15.77	17.17	10.08	10.52	11.14	11.58	12.98
	8H	14.45	14.86	15.50	15.91	17.32	10.21	10.62	11.27	11.68	13.08
	12H	14.54	14.91	15.62	15.98	17.40	10.27	10.65	11.35	11.71	13.13
8H	4H	13.72	14.13	14.77	15.18	16.59	9.94	10.35	11.00	11.41	12.82
	6H	14.29	14.63	15.37	15.72	17.13	10.46	10.80	11.54	11.90	13.30
	8H	14.51	14.81	15.59	15.89	17.31	10.65	10.95	11.74	12.03	13.46
	12H	14.65	14.91	15.74	15.98	17.45	10.77	11.03	11.86	12.11	13.58
12H	4H	13.67	14.04	14.74	15.11	16.52	9.95	10.32	11.02	11.39	12.80
	6H	14.26	14.56	15.35	15.64	17.07	10.51	10.81	11.60	11.89	13.32
	8H	14.49	14.75	15.57	15.82	17.29	10.72	10.98	11.81	12.06	13.53

END OF REPORT