

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923336

Luminaire Tested: DFN2DIP-SQ4F0-160D100US940-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P923336  
REPORT IS A COMBINATION OF REPORTS P900147 AND P896915  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-160D100US940-FLLFLL  
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 22016.3 lumens  
Efficiency: N/A  
Efficacy: 91.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 241.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P923336  
CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US940-FLLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P923336

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US940-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	69	69	69	64
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	61	60	58	61	60	58	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	54	51	49	45
3	84	74	67	61	79	70	63	58	62	57	52	55	50	47	48	45	42	48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	32	38	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	35	31	28	25
7	60	48	40	34	56	45	38	32	40	34	30	36	31	27	32	28	25	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3895	3895	3895
5°	3902	3842	3868
10°	3870	3791	3817
15°	3813	3729	3736
20°	3736	3643	3653
25°	3659	3540	3558
30°	3563	3445	3436
35°	3473	3332	3306
40°	3361	3218	3184
45°	3249	3103	3058
50°	3127	2983	2912
55°	2999	2844	2779
60°	2855	2679	2626
65°	2698	2509	2445
70°	2497	2301	2252
75°	2219	2053	2075
80°	1885	1736	1733
85°	1362	1188	1165

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3249 cd/sqm



TEST NUMBER: P923336

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US940-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	522.5	2.4
10°-20°	1470.1	6.7
20°-30°	2160.5	9.8
30°-40°	2509.3	11.4
40°-50°	2506.2	11.4
50°-60°	2185.3	9.9
60°-70°	1615.4	7.3
70°-80°	914.0	4.2
80°-90°	249.2	1.1
90°-100°	174.5	0.8
100°-110°	554.5	2.5
110°-120°	948.9	4.3
120°-130°	1247.9	5.7
130°-140°	1400.8	6.4
140°-150°	1373.6	6.2
150°-160°	1152.3	5.2
160°-170°	764.1	3.5
170°-180°	267.1	1.2
0°-30°	4153.2	18.9
0°-40°	6662.5	30.3
0°-60°	11354.0	51.6
0°-90°	14132.7	64.2
90°-120°	1677.9	7.6
90°-150°	5700.1	25.9
90°-180°	7884.0	35.8
0°-180°	22016.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5552	5552	5552	5552	5552	
5°	5552	5531	5472	5514	5504	527
15°	5285	5253	5183	5205	5178	1488
25°	4783	4740	4650	4660	4650	2201
35°	4127	4073	3988	3955	3929	2577
45°	3358	3321	3240	3182	3160	2592
55°	2541	2509	2445	2381	2354	2272
65°	1714	1682	1628	1580	1554	1694
75°	896	886	859	827	838	957
85°	219	214	208	192	187	244
90°	3	31	83	78	81	21
95°	124	148	152	152	148	138
105°	512	519	524	528	528	540
115°	952	966	962	959	952	942
125°	1385	1406	1400	1392	1389	1238
135°	1791	1818	1823	1820	1814	1385
145°	2175	2192	2206	2208	2199	1359
155°	2487	2494	2501	2513	2506	1145
165°	2705	2703	2703	2720	2708	763
175°	2815	2808	2803	2820	2806	267
180°	2820	2820	2820	2820	2820	



TEST NUMBER: P923336

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US940-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5551.5	5551.5	5551.5	5551.5	5551.5
2.5°	5583.8	5557.1	5498.3	5551.5	5541.3
5°	5551.5	5530.6	5471.6	5514.2	5503.9
7.5°	5514.2	5482.4	5423.5	5466.5	5455.8
10°	5455.8	5418.4	5354.5	5396.9	5381.0
12.5°	5375.4	5343.7	5279.6	5306.3	5295.5
15°	5284.7	5253.1	5183.3	5204.9	5178.3
17.5°	5172.6	5140.9	5071.2	5097.8	5071.2
20°	5049.7	5018.0	4943.2	4959.1	4938.1
22.5°	4927.4	4879.3	4809.5	4809.5	4798.8
25°	4783.0	4740.5	4649.8	4660.1	4649.8
27.5°	4622.6	4585.3	4516.2	4500.4	4473.7
30°	4462.9	4419.9	4340.0	4324.2	4302.7
32.5°	4291.9	4260.2	4174.6	4142.4	4120.9
35°	4126.6	4073.3	3987.7	3955.4	3928.9
37.5°	3939.7	3891.5	3806.0	3768.5	3742.0
40°	3747.6	3704.6	3619.1	3571.5	3550.0
42.5°	3560.8	3517.7	3432.7	3379.0	3347.2
45°	3358.0	3320.6	3240.2	3181.8	3160.3
47.5°	3160.3	3122.9	3037.4	2978.5	2946.8
50°	2951.9	2925.3	2850.5	2775.7	2749.1
52.5°	2749.1	2711.8	2642.7	2583.7	2546.4
55°	2541.3	2509.0	2445.0	2381.0	2354.4
57.5°	2332.9	2306.2	2236.6	2172.6	2151.1
60°	2124.4	2103.5	2028.7	1969.8	1953.9
62.5°	1921.6	1884.3	1831.0	1777.8	1756.3
65°	1713.8	1681.5	1628.3	1580.2	1553.5
67.5°	1500.3	1473.1	1425.6	1388.1	1366.6
70°	1302.6	1281.1	1233.0	1195.6	1174.7
72.5°	1099.8	1078.3	1051.8	1014.3	998.5
75°	896.5	886.4	859.2	827.4	838.2
77.5°	715.3	693.8	683.1	667.2	651.3
80°	534.0	528.4	517.6	501.8	491.1
82.5°	363.0	363.0	357.9	336.4	336.4
85°	218.6	213.5	208.4	192.0	186.9
87.5°	96.3	85.5	74.7	58.9	53.2
90°	2.6	30.6	83.3	78.2	80.8
92.5°	52.7	71.4	74.0	76.5	76.5
95°	124.1	147.9	152.2	152.2	147.9
97.5°	206.6	228.7	238.1	238.1	238.1
100°	301.8	321.4	328.1	328.1	325.7
102.5°	402.2	416.6	426.0	428.5	426.0
105°	511.8	518.6	523.7	528.0	528.0
107.5°	620.6	630.9	630.9	632.6	620.6
110°	726.1	739.7	739.7	739.7	732.9



TEST NUMBER: P923336

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US940-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	840.0	854.4	851.9	845.1	840.0
115°	952.3	965.8	961.6	959.0	952.3
117.5°	1063.6	1082.4	1070.4	1063.6	1056.8
120°	1175.8	1194.5	1175.8	1175.8	1168.2
122.5°	1277.8	1301.6	1289.8	1283.0	1277.8
125°	1385.0	1406.2	1399.5	1391.8	1389.3
127.5°	1489.6	1515.9	1506.5	1496.4	1489.6
130°	1587.3	1617.9	1613.7	1608.6	1599.3
132.5°	1697.0	1720.8	1722.5	1710.7	1703.8
135°	1791.4	1817.8	1822.8	1820.3	1813.5
137.5°	1896.8	1918.1	1922.3	1920.7	1910.4
140°	1989.5	2010.7	2022.7	2022.7	2013.3
142.5°	2084.7	2106.0	2112.7	2115.3	2106.0
145°	2174.8	2191.8	2205.5	2208.0	2198.6
147.5°	2255.6	2276.9	2287.1	2291.3	2282.0
150°	2339.0	2353.4	2362.8	2370.3	2362.8
152.5°	2412.3	2427.3	2439.3	2448.6	2439.3
155°	2486.9	2493.7	2501.3	2513.2	2505.5
157.5°	2550.6	2555.7	2560.0	2577.0	2565.1
160°	2607.6	2612.7	2615.2	2629.7	2619.5
162.5°	2660.3	2660.3	2662.8	2679.0	2667.1
165°	2705.4	2702.8	2702.8	2719.8	2707.9
167.5°	2746.2	2738.5	2738.5	2755.6	2743.6
170°	2776.8	2770.0	2767.4	2784.5	2770.0
172.5°	2798.0	2791.2	2788.6	2805.7	2791.2
175°	2815.0	2808.3	2803.2	2820.1	2805.7
177.5°	2824.4	2817.6	2812.5	2826.9	2812.5
180°	2820.1	2820.1	2820.1	2820.1	2820.1



TEST NUMBER: P923336  
 CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US940-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.22	14.23	14.05	15.08	16.13	12.78	13.78	13.60	14.63	15.69
	3H	14.90	15.80	15.74	16.66	17.74	14.41	15.31	15.25	16.17	17.25
	4H	15.50	16.35	16.35	17.21	18.30	15.00	15.85	15.86	16.72	17.81
	6H	15.91	16.69	16.77	17.56	18.67	15.41	16.19	16.27	17.06	18.17
	8H	16.02	16.77	16.89	17.66	18.76	15.52	16.26	16.39	17.15	18.26
	12H	16.07	16.79	16.95	17.67	18.80	15.56	16.28	16.44	17.16	18.29
4H	2H	13.70	14.55	14.56	15.42	16.51	13.35	14.20	14.21	15.06	16.16
	3H	15.59	16.30	16.46	17.19	18.30	15.18	15.89	16.05	16.79	17.89
	4H	16.31	16.96	17.19	17.85	18.98	15.89	16.53	16.77	17.43	18.56
	6H	16.84	17.40	17.73	18.32	19.45	16.40	16.97	17.30	17.88	19.02
	8H	16.99	17.52	17.89	18.43	19.58	16.55	17.08	17.46	17.99	19.14
	12H	17.07	17.55	17.99	18.48	19.63	16.62	17.10	17.55	18.03	19.18
8H	4H	16.52	17.04	17.42	17.95	19.10	16.14	16.67	17.04	17.58	18.73
	6H	17.16	17.59	18.09	18.55	19.70	16.78	17.21	17.70	18.16	19.31
	8H	17.38	17.77	18.32	18.71	19.88	16.99	17.38	17.93	18.32	19.49
	12H	17.53	17.87	18.47	18.80	20.02	17.12	17.45	18.06	18.39	19.61
12H	4H	16.51	16.98	17.43	17.91	19.07	16.14	16.62	17.06	17.55	18.70
	6H	17.19	17.58	18.13	18.52	19.69	16.82	17.20	17.76	18.15	19.32
	8H	17.44	17.78	18.38	18.72	19.94	17.06	17.40	18.00	18.34	19.56