

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923346

Luminaire Tested: DFN2DIP-SQ4F0-160D120US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923346
REPORT IS A COMBINATION OF REPORTS P900184 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D120US940-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21597.2 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 256.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923346

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US940-RLFL

Luminous Intensity Polar Plot



TEST NUMBER: P923346

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4138	4138	4138
5°	4144	4073	4099
10°	4103	3994	3967
15°	4046	3862	3762
20°	3972	3681	3510
25°	3895	3478	3266
30°	3792	3269	2957
35°	3692	3045	2685
40°	3589	2813	2374
45°	3470	2556	2091
50°	3347	2295	1815
55°	3218	2017	1550
60°	3069	1726	1277
65°	2898	1431	1151
70°	2691	1155	1043
75°	2430	1020	951
80°	2053	858	829
85°	1429	578	632

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3470 cd/sqm

TEST NUMBER: P923346

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	552.6	2.6
10°-20°	1517.1	7.0
20°-30°	2130.0	9.9
30°-40°	2321.8	10.8
40°-50°	2134.0	9.9
50°-60°	1675.9	7.8
60°-70°	1090.9	5.1
70°-80°	561.5	2.6
80°-90°	153.0	0.7
90°-100°	209.4	1.0
100°-110°	665.4	3.1
110°-120°	1138.7	5.3
120°-130°	1497.5	6.9
130°-140°	1680.9	7.8
140°-150°	1648.3	7.6
150°-160°	1382.7	6.4
160°-170°	917.0	4.2
170°-180°	320.5	1.5
0°-30°	4199.7	19.4
0°-40°	6521.6	30.2
0°-60°	10331.5	47.8
0°-90°	12136.8	56.2
90°-120°	2013.4	9.3
90°-150°	6840.1	31.7
90°-180°	9460.0	43.8
0°-180°	21597.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5897	5897	5897	5897	5897	
5°	5897	5870	5800	5848	5833	559
15°	5608	5550	5368	5267	5214	1580
25°	5091	4920	4568	4349	4269	2341
35°	4387	4114	3645	3309	3191	2746
45°	3586	3228	2668	2289	2161	2769
55°	2727	2310	1734	1414	1313	2437
65°	1841	1409	928	747	731	1825
75°	982	608	427	390	384	1038
85°	229	117	101	101	101	263
90°	3	37	100	94	97	21
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	

TEST NUMBER: P923346

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5896.7	5896.7	5896.7	5896.7	5896.7
2.5°	5923.3	5896.7	5837.8	5891.6	5880.8
5°	5896.7	5870.0	5800.4	5848.5	5832.7
7.5°	5848.5	5816.8	5742.1	5763.0	5736.5
10°	5784.6	5747.3	5640.8	5624.4	5592.6
12.5°	5704.7	5656.7	5512.3	5480.5	5421.7
15°	5608.5	5549.6	5368.5	5267.1	5213.8
17.5°	5496.4	5410.9	5186.7	5069.5	4984.0
20°	5368.5	5261.4	4994.7	4861.7	4744.0
22.5°	5229.7	5106.8	4797.1	4616.0	4536.1
25°	5091.0	4920.0	4567.9	4349.3	4269.0
27.5°	4925.7	4744.0	4354.4	4103.7	3980.8
30°	4749.6	4546.4	4119.4	3847.7	3703.4
32.5°	4578.7	4332.9	3895.8	3575.4	3441.7
35°	4386.7	4114.4	3645.0	3308.7	3191.0
37.5°	4199.9	3906.0	3410.1	3041.4	2908.4
40°	4002.3	3682.4	3164.3	2785.5	2646.9
42.5°	3799.6	3458.1	2919.2	2524.0	2390.9
45°	3586.1	3228.3	2668.4	2289.0	2161.1
47.5°	3383.4	3004.7	2428.3	2049.0	1931.8
50°	3159.2	2780.4	2193.3	1824.8	1713.2
52.5°	2940.1	2539.9	1969.2	1617.0	1515.6
55°	2726.7	2310.5	1734.2	1414.3	1313.0
57.5°	2508.1	2081.3	1526.4	1227.4	1141.9
60°	2283.9	1857.1	1307.2	1035.5	950.0
62.5°	2065.4	1638.5	1120.4	864.5	822.1
65°	1841.2	1408.6	928.5	747.3	730.9
67.5°	1627.7	1195.2	747.3	656.2	640.3
70°	1403.6	987.4	618.8	565.6	544.1
72.5°	1190.1	794.9	517.5	475.0	464.2
75°	981.8	608.1	426.9	389.5	384.4
77.5°	773.9	431.9	336.3	314.8	304.1
80°	581.5	309.7	255.9	235.0	235.0
82.5°	405.4	208.4	176.1	165.3	165.3
85°	229.3	117.2	101.4	101.4	101.4
87.5°	85.5	42.4	42.4	37.4	37.4
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5



TEST NUMBER: P923346

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1

TEST NUMBER: P923346

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.65	13.54	13.56	14.46	15.64	8.61	9.50	9.52	10.42	11.60
	3H	14.34	15.13	15.26	16.06	17.27	9.81	10.60	10.73	11.53	12.74
	4H	14.95	15.70	15.89	16.64	17.85	10.26	11.01	11.20	11.94	13.16
	6H	15.38	16.07	16.33	17.01	18.24	10.58	11.27	11.53	12.21	13.44
	8H	15.51	16.16	16.47	17.12	18.35	10.68	11.33	11.63	12.29	13.52
	12H	15.58	16.20	16.54	17.15	18.40	10.72	11.34	11.68	12.30	13.55
4H	2H	12.68	13.42	13.62	14.36	15.58	9.22	9.96	10.16	10.90	12.12
	3H	14.52	15.14	15.47	16.10	17.34	10.57	11.19	11.52	12.16	13.39
	4H	15.21	15.78	16.17	16.74	18.00	11.12	11.69	12.08	12.65	13.91
	6H	15.74	16.22	16.71	17.21	18.46	11.55	12.03	12.52	13.02	14.27
	8H	15.91	16.37	16.89	17.35	18.62	11.68	12.13	12.65	13.11	14.38
	12H	16.01	16.42	17.01	17.42	18.69	11.75	12.15	12.74	13.15	14.43
8H	4H	15.19	15.64	16.16	16.62	17.89	11.41	11.86	12.39	12.84	14.11
	6H	15.76	16.13	16.76	17.15	18.42	11.93	12.31	12.93	13.33	14.60
	8H	15.98	16.31	16.99	17.32	18.60	12.12	12.46	13.13	13.46	14.75
	12H	16.12	16.41	17.13	17.42	18.75	12.25	12.54	13.26	13.54	14.87
12H	4H	15.14	15.55	16.13	16.55	17.82	11.42	11.83	12.41	12.82	14.10
	6H	15.73	16.06	16.74	17.07	18.36	11.98	12.31	12.99	13.32	14.61
	8H	15.96	16.25	16.97	17.25	18.59	12.20	12.49	13.21	13.49	14.82

END OF REPORT