

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920339

Luminaire Tested: DFN2DIP-SQ4F0-060D160US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920339
REPORT IS A COMBINATION OF REPORTS P901724 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D160US935-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18029.3 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 172.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920339

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920339

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	14	13	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1498	1498	1498
5°	1501	1475	1484
10°	1486	1446	1436
15°	1465	1399	1362
20°	1438	1333	1271
25°	1410	1259	1183
30°	1373	1184	1071
35°	1337	1103	972
40°	1299	1019	859
45°	1256	925	757
50°	1212	831	657
55°	1165	730	561
60°	1111	625	462
65°	1049	518	417
70°	974	418	378
75°	880	369	345
80°	743	311	300
85°	517	209	229

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2493 cd/sqm

TEST NUMBER: P920339

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	1.1
10°-20°	549.3	3.0
20°-30°	771.2	4.3
30°-40°	840.7	4.7
40°-50°	772.7	4.3
50°-60°	606.8	3.4
60°-70°	395.0	2.2
70°-80°	203.3	1.1
80°-90°	60.1	0.3
90°-100°	153.3	0.9
100°-110°	571.5	3.2
110°-120°	1515.7	8.4
120°-130°	2513.9	13.9
130°-140°	2670.3	14.8
140°-150°	2481.8	13.8
150°-160°	1995.3	11.1
160°-170°	1285.7	7.1
170°-180°	442.5	2.5
0°-30°	1520.7	8.4
0°-40°	2361.4	13.1
0°-60°	3740.9	20.7
0°-90°	4399.3	24.4
90°-120°	2240.5	12.4
90°-150°	9906.5	54.9
90°-180°	13630.0	75.6
0°-180°	18029.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	3	40	67	84	91	17
95°	218	108	131	148	145	259
105°	1023	1124	205	242	256	1093
115°	1934	1991	2076	518	276	1904
125°	2735	2779	2843	2866	2876	2439
135°	3384	3438	3468	3502	3496	2614
145°	3926	3922	3980	4003	3986	2456
155°	4323	4293	4333	4353	4326	1992
165°	4555	4535	4545	4568	4545	1287
175°	4659	4636	4642	4666	4632	443
180°	4649	4649	4649	4649	4649	

TEST NUMBER: P920339

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	3.2	40.4	67.1	84.3	90.7
92.5°	84.3	70.7	80.7	87.5	90.7
95°	218.5	107.5	131.0	148.2	144.6
97.5°	393.5	117.9	171.3	181.8	184.9
100°	595.6	134.7	191.7	218.5	225.3
102.5°	817.3	811.0	198.5	235.3	245.6
105°	1022.7	1123.8	205.3	242.1	255.6
107.5°	1261.5	1345.5	212.1	248.9	262.4
110°	1490.5	1560.8	588.8	252.4	265.6

TEST NUMBER: P920339

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1705.8	1766.2	1709.0	258.9	269.2
115°	1934.3	1991.4	2075.7	518.1	276.0
117.5°	2132.9	2199.9	2257.5	1776.2	894.8
120°	2355.0	2405.3	2466.0	2506.4	2052.2
122.5°	2543.1	2597.0	2664.5	2684.5	2688.1
125°	2734.9	2778.8	2842.8	2866.3	2876.3
127.5°	2909.8	2957.0	3007.7	3041.3	3044.5
130°	3074.9	3128.8	3165.5	3202.7	3199.5
132.5°	3243.0	3286.9	3323.7	3354.1	3350.9
135°	3384.4	3438.4	3468.4	3502.3	3495.5
137.5°	3532.2	3572.6	3606.5	3640.1	3630.1
140°	3676.9	3704.0	3740.8	3771.2	3754.4
142.5°	3798.3	3821.9	3865.4	3892.2	3875.4
145°	3926.2	3922.5	3979.7	4003.2	3986.5
147.5°	4036.8	4026.8	4084.0	4100.8	4087.5
150°	4144.7	4121.1	4175.1	4195.0	4178.3
152.5°	4235.3	4208.6	4258.9	4279.3	4255.7
155°	4322.8	4292.8	4333.2	4353.2	4326.4
157.5°	4393.6	4366.8	4397.1	4420.7	4393.6
160°	4454.3	4433.9	4454.3	4474.3	4450.7
162.5°	4507.8	4487.9	4504.6	4528.2	4497.9
165°	4554.9	4535.0	4544.9	4568.5	4544.9
167.5°	4592.1	4571.7	4582.1	4605.6	4575.3
170°	4622.4	4602.1	4608.8	4632.4	4602.1
172.5°	4642.4	4622.4	4629.2	4652.8	4622.4
175°	4659.2	4635.6	4642.4	4666.0	4632.4
177.5°	4666.0	4642.4	4646.0	4669.6	4639.2
180°	4649.2	4649.2	4649.2	4649.2	4649.2

TEST NUMBER: P920339

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.50	6.15	6.65	7.29	8.89	1.46	2.11	2.61	3.25	4.85
	3H	7.16	7.75	8.33	8.90	10.51	2.63	3.22	3.79	4.37	5.98
	4H	7.77	8.33	8.94	9.47	11.09	3.07	3.63	4.24	4.78	6.40
	6H	8.18	8.70	9.36	9.85	11.47	3.39	3.90	4.56	5.05	6.68
	8H	8.31	8.80	9.49	9.96	11.58	3.47	3.96	4.65	5.13	6.74
	12H	8.37	8.83	9.55	9.99	11.63	3.51	3.97	4.69	5.13	6.77
4H	2H	5.49	6.05	6.67	7.20	8.81	2.03	2.59	3.21	3.74	5.35
	3H	7.31	7.77	8.49	8.95	10.58	3.37	3.83	4.55	5.00	6.63
	4H	8.00	8.43	9.18	9.59	11.23	3.91	4.34	5.09	5.50	7.14
	6H	8.51	8.87	9.70	10.06	11.69	4.32	4.69	5.51	5.87	7.51
	8H	8.68	9.02	9.87	10.20	11.85	4.45	4.79	5.63	5.96	7.61
	12H	8.77	9.08	9.97	10.27	11.93	4.50	4.81	5.71	6.00	7.66
8H	4H	7.95	8.30	9.14	9.47	11.12	4.18	4.52	5.37	5.69	7.35
	6H	8.52	8.80	9.72	10.02	11.67	4.69	4.97	5.90	6.19	7.84
	8H	8.74	8.98	9.95	10.18	11.85	4.88	5.13	6.09	6.32	7.99
	12H	8.87	9.09	10.08	10.28	11.98	5.00	5.21	6.21	6.40	8.10
12H	4H	7.90	8.21	9.10	9.39	11.05	4.18	4.49	5.38	5.67	7.33
	6H	8.49	8.74	9.70	9.93	11.60	4.74	4.99	5.95	6.18	7.85
	8H	8.71	8.92	9.92	10.12	11.82	4.95	5.16	6.16	6.35	8.05

END OF REPORT