

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920373

Luminaire Tested: DFN2DIP-SQ4F0-070D160US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920373
REPORT IS A COMBINATION OF REPORTS P901725 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D160US935-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19604.9 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 183.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920373

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920373

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	28	27
3	78	68	61	56	69	62	56	51	49	45	41	37	34	32	26	25	23
4	71	60	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	53	43	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	23	43	32	26	22	26	21	18	20	17	14	15	12	11
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1646	1646	1646
5°	1648	1623	1634
10°	1635	1601	1612
15°	1611	1575	1578
20°	1578	1539	1543
25°	1546	1496	1503
30°	1505	1455	1451
35°	1467	1407	1397
40°	1420	1359	1345
45°	1373	1311	1292
50°	1321	1260	1230
55°	1267	1202	1174
60°	1206	1132	1109
65°	1140	1060	1033
70°	1055	972	951
75°	938	867	876
80°	796	734	732
85°	576	502	492

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2493 cd/sqm

TEST NUMBER: P920373

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.7	1.1
10°-20°	621.0	3.2
20°-30°	912.7	4.7
30°-40°	1060.0	5.4
40°-50°	1058.7	5.4
50°-60°	923.2	4.7
60°-70°	682.4	3.5
70°-80°	386.1	2.0
80°-90°	110.1	0.6
90°-100°	153.3	0.8
100°-110°	571.5	2.9
110°-120°	1515.7	7.7
120°-130°	2513.9	12.8
130°-140°	2670.3	13.6
140°-150°	2481.8	12.7
150°-160°	1995.3	10.2
160°-170°	1285.7	6.6
170°-180°	442.5	2.3
0°-30°	1754.4	8.9
0°-40°	2814.4	14.4
0°-60°	4796.3	24.5
0°-90°	5974.9	30.5
90°-120°	2240.5	11.4
90°-150°	9906.5	50.5
90°-180°	13630.0	69.5
0°-180°	19604.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	3	40	67	84	91	18
95°	218	108	131	148	145	259
105°	1023	1124	205	242	256	1093
115°	1934	1991	2076	518	276	1904
125°	2735	2779	2843	2866	2876	2439
135°	3384	3438	3468	3502	3496	2614
145°	3926	3922	3980	4003	3986	2456
155°	4323	4293	4333	4353	4326	1992
165°	4555	4535	4545	4568	4545	1287
175°	4659	4636	4642	4666	4632	443
180°	4649	4649	4649	4649	4649	

TEST NUMBER: P920373

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.0	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.2	2153.5	2142.2
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1564.9	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.5	857.0	832.2	825.4
62.5°	811.7	796.0	773.5	751.0	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	3.2	40.4	67.1	84.3	90.7
92.5°	84.3	70.7	80.7	87.5	90.7
95°	218.5	107.5	131.0	148.2	144.6
97.5°	393.5	117.9	171.3	181.8	184.9
100°	595.6	134.7	191.7	218.5	225.3
102.5°	817.3	811.0	198.5	235.3	245.6
105°	1022.7	1123.8	205.3	242.1	255.6
107.5°	1261.5	1345.5	212.1	248.9	262.4
110°	1490.5	1560.8	588.8	252.4	265.6

TEST NUMBER: P920373

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1705.8	1766.2	1709.0	258.9	269.2
115°	1934.3	1991.4	2075.7	518.1	276.0
117.5°	2132.9	2199.9	2257.5	1776.2	894.8
120°	2355.0	2405.3	2466.0	2506.4	2052.2
122.5°	2543.1	2597.0	2664.5	2684.5	2688.1
125°	2734.9	2778.8	2842.8	2866.3	2876.3
127.5°	2909.8	2957.0	3007.7	3041.3	3044.5
130°	3074.9	3128.8	3165.5	3202.7	3199.5
132.5°	3243.0	3286.9	3323.7	3354.1	3350.9
135°	3384.4	3438.4	3468.4	3502.3	3495.5
137.5°	3532.2	3572.6	3606.5	3640.1	3630.1
140°	3676.9	3704.0	3740.8	3771.2	3754.4
142.5°	3798.3	3821.9	3865.4	3892.2	3875.4
145°	3926.2	3922.5	3979.7	4003.2	3986.5
147.5°	4036.8	4026.8	4084.0	4100.8	4087.5
150°	4144.7	4121.1	4175.1	4195.0	4178.3
152.5°	4235.3	4208.6	4258.9	4279.3	4255.7
155°	4322.8	4292.8	4333.2	4353.2	4326.4
157.5°	4393.6	4366.8	4397.1	4420.7	4393.6
160°	4454.3	4433.9	4454.3	4474.3	4450.7
162.5°	4507.8	4487.9	4504.6	4528.2	4497.9
165°	4554.9	4535.0	4544.9	4568.5	4544.9
167.5°	4592.1	4571.7	4582.1	4605.6	4575.3
170°	4622.4	4602.1	4608.8	4632.4	4602.1
172.5°	4642.4	4622.4	4629.2	4652.8	4622.4
175°	4659.2	4635.6	4642.4	4666.0	4632.4
177.5°	4666.0	4642.4	4646.0	4669.6	4639.2
180°	4649.2	4649.2	4649.2	4649.2	4649.2

TEST NUMBER: P920373

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.87	7.58	7.97	8.68	10.20	6.42	7.13	7.53	8.23	9.76
	3H	8.52	9.15	9.64	10.27	11.81	8.03	8.66	9.15	9.78	11.32
	4H	9.10	9.71	10.23	10.82	12.37	8.61	9.21	9.73	10.32	11.87
	6H	9.50	10.05	10.63	11.17	12.73	9.00	9.55	10.13	10.67	12.23
	8H	9.60	10.13	10.74	11.26	12.81	9.10	9.63	10.24	10.76	12.31
	12H	9.64	10.15	10.79	11.27	12.85	9.14	9.64	10.28	10.76	12.34
4H	2H	7.31	7.91	8.44	9.03	10.57	6.95	7.56	8.09	8.67	10.22
	3H	9.17	9.67	10.31	10.81	12.37	8.76	9.26	9.90	10.40	11.96
	4H	9.88	10.34	11.02	11.47	13.05	9.45	9.92	10.60	11.04	12.62
	6H	10.39	10.78	11.54	11.94	13.51	9.96	10.35	11.10	11.50	13.07
	8H	10.54	10.91	11.68	12.05	13.64	10.10	10.47	11.25	11.61	13.20
	12H	10.60	10.94	11.77	12.09	13.69	10.15	10.49	11.32	11.64	13.24
8H	4H	10.06	10.43	11.21	11.57	13.16	9.68	10.06	10.83	11.20	12.79
	6H	10.69	11.00	11.86	12.18	13.77	10.31	10.61	11.48	11.80	13.38
	8H	10.91	11.18	12.09	12.34	13.95	10.52	10.79	11.70	11.95	13.56
	12H	11.04	11.28	12.22	12.44	14.07	10.63	10.86	11.81	12.03	13.66
12H	4H	10.04	10.38	11.21	11.53	13.12	9.67	10.01	10.84	11.16	12.75
	6H	10.72	10.99	11.89	12.15	13.76	10.35	10.62	11.52	11.78	13.38
	8H	10.96	11.19	12.14	12.35	13.99	10.58	10.81	11.76	11.97	13.61

END OF REPORT