

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925771

Luminaire Tested: DFN2DIP-SQ4F0-060D080US950-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P925771  
REPORT IS A COMBINATION OF REPORTS P901616 AND P898471  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-060D080US950-RLLONL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12421.1 lumens  
Efficiency: N/A  
Efficacy: 113.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 109.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.946  
Total Harmonic Distortion (THDi): 0.132  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925771  
CATALOG NUMBER: DFN2DIP-SQ4F0-060D080US950-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P925771

CATALOG NUMBER: DFN2DIP-SQ4F0-060D080US950-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	67	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19			
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15			
8	53	42	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1660	1660	1660
5°	1663	1634	1645
10°	1646	1602	1591
15°	1623	1550	1509
20°	1593	1477	1408
25°	1563	1395	1310
30°	1521	1312	1186
35°	1481	1222	1077
40°	1440	1129	952
45°	1392	1025	839
50°	1343	921	728
55°	1291	809	622
60°	1231	693	512
65°	1163	574	462
70°	1080	463	418
75°	975	409	382
80°	823	344	333
85°	573	231	253

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1392 cd/sqm



TEST NUMBER: P925771

CATALOG NUMBER: DFN2DIP-SQ4F0-060D080US950-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.7	1.8
10°-20°	608.7	4.9
20°-30°	854.5	6.9
30°-40°	931.5	7.5
40°-50°	856.2	6.9
50°-60°	672.4	5.4
60°-70°	437.7	3.5
70°-80°	225.3	1.8
80°-90°	62.0	0.5
90°-100°	84.9	0.7
100°-110°	316.6	2.5
110°-120°	839.7	6.8
120°-130°	1392.7	11.2
130°-140°	1479.4	11.9
140°-150°	1374.9	11.1
150°-160°	1105.4	8.9
160°-170°	712.3	5.7
170°-180°	245.2	2.0
0°-30°	1684.9	13.6
0°-40°	2616.4	21.1
0°-60°	4144.9	33.4
0°-90°	4869.9	39.2
90°-120°	1241.3	10.0
90°-150°	5488.3	44.2
90°-180°	7551.0	60.8
0°-180°	12421.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2366	2366	2366	2366	2366	
5°	2366	2355	2327	2346	2340	224
15°	2250	2226	2154	2113	2092	634
25°	2042	1974	1833	1745	1713	939
35°	1760	1651	1462	1327	1280	1102
45°	1439	1295	1071	918	867	1111
55°	1094	927	696	567	527	978
65°	739	565	372	300	293	732
75°	394	244	171	156	154	417
85°	92	47	41	41	41	106
90°	2	22	37	47	50	12
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P925771

CATALOG NUMBER: DFN2DIP-SQ4F0-060D080US950-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2365.7	2365.7	2365.7	2365.7	2365.7
2.5°	2376.4	2365.7	2342.1	2363.6	2359.3
5°	2365.7	2355.0	2327.1	2346.5	2340.1
7.5°	2346.5	2333.7	2303.7	2312.1	2301.4
10°	2320.7	2305.7	2263.1	2256.5	2243.7
12.5°	2288.7	2269.4	2211.5	2198.8	2175.1
15°	2250.1	2226.4	2153.8	2113.1	2091.7
17.5°	2205.2	2170.8	2080.9	2033.8	1999.6
20°	2153.8	2110.8	2003.9	1950.5	1903.2
22.5°	2098.1	2048.8	1924.6	1851.9	1819.9
25°	2042.5	1973.9	1832.6	1745.0	1712.7
27.5°	1976.2	1903.2	1747.0	1646.3	1597.1
30°	1905.5	1824.0	1652.7	1543.7	1485.8
32.5°	1836.9	1738.4	1563.0	1434.4	1380.8
35°	1759.9	1650.7	1462.4	1327.4	1280.2
37.5°	1685.0	1567.0	1368.1	1220.3	1166.8
40°	1605.7	1477.4	1269.5	1117.5	1061.9
42.5°	1524.4	1387.4	1171.1	1012.6	959.2
45°	1438.7	1295.2	1070.6	918.3	867.0
47.5°	1357.4	1205.5	974.2	822.1	775.0
50°	1267.5	1115.5	880.0	732.1	687.4
52.5°	1179.5	1019.0	790.0	648.7	608.1
55°	1094.0	927.0	695.8	567.4	526.7
57.5°	1006.3	834.9	612.4	492.5	458.1
60°	916.3	745.1	524.5	415.5	381.1
62.5°	828.6	657.4	449.5	346.9	329.8
65°	738.7	565.1	372.5	299.8	293.3
67.5°	653.0	479.5	299.8	263.3	256.9
70°	563.1	396.1	248.2	227.0	218.3
72.5°	477.5	318.9	207.6	190.6	186.2
75°	393.9	243.9	171.2	156.3	154.3
77.5°	310.5	173.3	134.9	126.3	122.0
80°	233.3	124.2	102.7	94.3	94.3
82.5°	162.7	83.6	70.6	66.3	66.3
85°	92.0	47.0	40.6	40.6	40.6
87.5°	34.3	17.1	17.1	15.0	15.0
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P925771

CATALOG NUMBER: DFN2DIP-SQ4F0-060D080US950-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P925771  
 CATALOG NUMBER: DFN2DIP-SQ4F0-060D080US950-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.82	8.57	8.87	9.62	11.04	3.78	4.53	4.83	5.58	7.00
	3H	9.50	10.17	10.56	11.23	12.67	4.97	5.64	6.03	6.70	8.13
	4H	10.11	10.74	11.18	11.80	13.25	5.41	6.05	6.49	7.11	8.56
	6H	10.53	11.11	11.61	12.18	13.63	5.73	6.31	6.81	7.38	8.84
	8H	10.65	11.21	11.74	12.29	13.74	5.82	6.37	6.90	7.46	8.91
	12H	10.71	11.24	11.80	12.32	13.79	5.86	6.39	6.95	7.46	8.94
4H	2H	7.83	8.46	8.91	9.53	10.97	4.37	5.01	5.45	6.07	7.51
	3H	9.66	10.18	10.74	11.27	12.73	5.71	6.24	6.80	7.33	8.79
	4H	10.35	10.83	11.44	11.91	13.39	6.26	6.74	7.35	7.82	9.30
	6H	10.86	11.28	11.96	12.38	13.85	6.68	7.09	7.77	8.19	9.67
	8H	11.04	11.43	12.14	12.52	14.01	6.80	7.19	7.90	8.29	9.77
	12H	11.13	11.48	12.25	12.59	14.09	6.87	7.22	7.98	8.32	9.82
8H	4H	10.31	10.70	11.41	11.79	13.28	6.54	6.92	7.64	8.02	9.51
	6H	10.88	11.20	12.00	12.33	13.82	7.05	7.37	8.17	8.51	10.00
	8H	11.10	11.38	12.22	12.50	14.00	7.25	7.52	8.37	8.64	10.15
	12H	11.24	11.48	12.37	12.60	14.14	7.36	7.61	8.49	8.72	10.26
12H	4H	10.26	10.61	11.37	11.72	13.21	6.54	6.89	7.65	8.00	9.49
	6H	10.85	11.13	11.98	12.25	13.76	7.10	7.38	8.23	8.50	10.01
	8H	11.07	11.32	12.20	12.43	13.98	7.31	7.56	8.44	8.67	10.22