

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925792

Luminaire Tested: DFN2DIP-SQ4F0-060D160US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925792
REPORT IS A COMBINATION OF REPORTS P900203 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D160US950-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19176.3 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 172.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925792

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925792

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32
2	85	78	72	67	76	70	65	61	55	52	49	42	39	37	29	28	27
3	77	68	61	56	69	61	55	51	49	44	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	38	35	33	30	27	23	21	19
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	21	19	17
6	60	48	40	34	53	43	37	32	35	30	26	26	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	18	16	16	13	12
9	47	35	28	23	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	32	25	21	40	29	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1563	1563	1563
5°	1565	1541	1552
10°	1553	1521	1531
15°	1530	1496	1499
20°	1499	1462	1466
25°	1468	1420	1427
30°	1430	1382	1378
35°	1393	1337	1326
40°	1348	1291	1277
45°	1304	1245	1227
50°	1255	1197	1168
55°	1203	1141	1115
60°	1145	1075	1054
65°	1082	1007	981
70°	1002	923	904
75°	890	824	832
80°	756	697	695
85°	547	476	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3798 cd/sqm

TEST NUMBER: P925792

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.6	1.1
10°-20°	589.8	3.1
20°-30°	866.8	4.5
30°-40°	1006.7	5.2
40°-50°	1005.5	5.2
50°-60°	876.7	4.6
60°-70°	648.1	3.4
70°-80°	366.7	1.9
80°-90°	110.5	0.6
90°-100°	298.7	1.6
100°-110°	949.2	4.9
110°-120°	1624.4	8.5
120°-130°	2136.3	11.1
130°-140°	2397.9	12.5
140°-150°	2351.4	12.3
150°-160°	1972.5	10.3
160°-170°	1308.1	6.8
170°-180°	457.2	2.4
0°-30°	1666.2	8.7
0°-40°	2673.0	13.9
0°-60°	4555.2	23.8
0°-90°	5680.5	29.6
90°-120°	2872.3	15.0
90°-150°	9757.9	50.9
90°-180°	13496.0	70.4
0°-180°	19176.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2227	2227	2227	2227	2227	
5°	2227	2219	2195	2212	2208	211
15°	2120	2108	2080	2088	2078	597
25°	1919	1902	1866	1870	1866	883
35°	1656	1634	1600	1587	1576	1034
45°	1347	1332	1300	1276	1268	1040
55°	1020	1007	981	955	945	912
65°	688	675	653	634	623	680
75°	360	356	345	332	336	384
85°	88	86	84	77	75	98
90°	4	52	143	134	138	19
95°	212	253	260	260	253	236
105°	876	888	897	904	904	925
115°	1630	1653	1646	1642	1630	1612
125°	2371	2407	2396	2383	2378	2119
135°	3067	3112	3120	3116	3104	2370
145°	3723	3752	3776	3780	3764	2326
155°	4257	4269	4282	4302	4289	1960
165°	4631	4627	4627	4656	4636	1306
175°	4819	4807	4799	4828	4803	458
180°	4828	4828	4828	4828	4828	

TEST NUMBER: P925792

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2229.5	2205.8	2227.2	2223.1
5°	2227.2	2218.8	2195.2	2212.2	2208.1
7.5°	2212.2	2199.5	2175.9	2193.2	2188.9
10°	2188.9	2173.9	2148.1	2165.2	2158.8
12.5°	2156.6	2143.8	2118.2	2128.9	2124.6
15°	2120.2	2107.5	2079.5	2088.2	2077.5
17.5°	2075.2	2062.5	2034.6	2045.2	2034.6
20°	2025.9	2013.2	1983.2	1989.6	1981.2
22.5°	1976.9	1957.5	1929.6	1929.6	1925.3
25°	1918.9	1901.9	1865.5	1869.6	1865.5
27.5°	1854.6	1839.6	1811.8	1805.5	1794.9
30°	1790.6	1773.2	1741.2	1734.8	1726.2
32.5°	1721.9	1709.2	1674.8	1661.9	1653.3
35°	1655.6	1634.2	1599.9	1586.9	1576.2
37.5°	1580.6	1561.2	1527.0	1511.9	1501.2
40°	1503.5	1486.2	1452.0	1432.9	1424.2
42.5°	1428.5	1411.3	1377.2	1355.6	1342.9
45°	1347.2	1332.2	1299.9	1276.5	1267.9
47.5°	1267.9	1252.9	1218.6	1195.0	1182.2
50°	1184.3	1173.6	1143.7	1113.6	1102.9
52.5°	1102.9	1087.9	1060.2	1036.6	1021.6
55°	1019.5	1006.6	980.9	955.2	944.6
57.5°	936.0	925.3	897.3	871.7	863.0
60°	852.3	843.9	814.0	790.3	783.9
62.5°	770.9	755.9	734.6	713.2	704.6
65°	687.5	674.7	653.3	633.9	623.2
67.5°	601.9	591.0	571.9	556.9	548.3
70°	522.6	514.0	494.6	479.7	471.3
72.5°	441.2	432.6	422.0	407.0	400.6
75°	359.7	355.7	344.7	332.0	336.3
77.5°	287.0	278.4	274.0	267.7	261.3
80°	214.3	212.0	207.7	201.3	197.0
82.5°	145.7	145.7	143.6	135.0	135.0
85°	87.7	85.7	83.6	77.0	75.0
87.5°	38.6	34.3	30.0	23.7	21.4
90°	4.4	52.4	142.6	133.9	138.2
92.5°	90.2	122.3	126.6	131.0	131.0
95°	212.5	253.3	260.5	260.5	253.3
97.5°	353.6	391.5	407.5	407.5	407.5
100°	516.7	550.2	561.8	561.8	557.4
102.5°	688.4	713.2	729.1	733.5	729.1
105°	876.2	887.8	896.6	903.8	903.8
107.5°	1062.5	1079.9	1079.9	1082.9	1062.5
110°	1243.0	1266.2	1266.2	1266.2	1254.6

TEST NUMBER: P925792

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1438.0	1462.8	1458.4	1446.7	1438.0
115°	1630.1	1653.4	1646.1	1641.7	1630.1
117.5°	1820.8	1852.8	1832.4	1820.8	1809.2
120°	2012.9	2044.9	2012.9	2012.9	1999.8
122.5°	2187.5	2228.4	2207.9	2196.3	2187.5
125°	2371.0	2407.3	2395.7	2382.6	2378.2
127.5°	2549.9	2595.1	2579.0	2561.6	2549.9
130°	2717.4	2769.7	2762.5	2753.7	2737.7
132.5°	2905.1	2945.9	2948.7	2928.4	2916.8
135°	3066.6	3111.8	3120.5	3116.1	3104.5
137.5°	3247.1	3283.5	3290.8	3287.9	3270.4
140°	3405.8	3442.1	3462.5	3462.5	3446.5
142.5°	3568.8	3605.2	3616.8	3621.2	3605.2
145°	3723.1	3752.2	3775.5	3779.8	3763.8
147.5°	3861.3	3897.8	3915.2	3922.5	3906.4
150°	4003.9	4028.7	4044.8	4057.8	4044.8
152.5°	4130.6	4155.3	4175.8	4191.7	4175.8
155°	4257.2	4268.9	4281.9	4302.3	4289.3
157.5°	4366.4	4375.1	4382.4	4411.5	4391.2
160°	4463.9	4472.6	4477.0	4501.7	4484.3
162.5°	4554.1	4554.1	4558.5	4586.2	4565.7
165°	4631.3	4626.9	4626.9	4656.0	4635.7
167.5°	4701.1	4688.1	4688.1	4717.1	4696.7
170°	4753.5	4741.9	4737.6	4766.7	4741.9
172.5°	4789.9	4778.3	4773.9	4803.0	4778.3
175°	4819.0	4807.4	4798.6	4827.8	4803.0
177.5°	4835.1	4823.4	4814.6	4839.5	4814.6
180°	4827.8	4827.8	4827.8	4827.8	4827.8

TEST NUMBER: P925792

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.57	7.27	7.68	8.38	9.92	6.12	6.83	7.24	7.94	9.47
	3H	8.22	8.85	9.34	9.97	11.52	7.73	8.36	8.85	9.48	11.03
	4H	8.80	9.40	9.93	10.52	12.08	8.31	8.91	9.44	10.03	11.58
	6H	9.20	9.75	10.34	10.87	12.44	8.70	9.25	9.84	10.37	11.94
	8H	9.30	9.82	10.44	10.96	12.52	8.80	9.32	9.94	10.46	12.02
	12H	9.34	9.84	10.49	10.97	12.56	8.83	9.33	9.98	10.46	12.05
4H	2H	7.01	7.61	8.15	8.73	10.28	6.65	7.25	7.79	8.37	9.93
	3H	8.86	9.36	10.01	10.51	12.08	8.46	8.96	9.60	10.10	11.67
	4H	9.58	10.04	10.72	11.17	12.76	9.15	9.61	10.30	10.74	12.33
	6H	10.09	10.48	11.24	11.64	13.22	9.65	10.05	10.81	11.20	12.78
	8H	10.23	10.60	11.39	11.75	13.35	9.80	10.16	10.95	11.31	12.91
	12H	10.30	10.64	11.47	11.79	13.40	9.85	10.19	11.02	11.35	12.95
8H	4H	9.76	10.13	10.91	11.28	12.87	9.38	9.75	10.54	10.90	12.50
	6H	10.39	10.69	11.56	11.88	13.48	10.01	10.31	11.18	11.50	13.09
	8H	10.61	10.88	11.79	12.04	13.66	10.22	10.48	11.40	11.65	13.27
	12H	10.74	10.97	11.92	12.14	13.78	10.33	10.56	11.51	11.73	13.37
12H	4H	9.74	10.07	10.91	11.23	12.83	9.37	9.70	10.54	10.86	12.46
	6H	10.42	10.68	11.60	11.85	13.47	10.05	10.31	11.23	11.48	13.09
	8H	10.66	10.89	11.84	12.05	13.70	10.28	10.51	11.46	11.67	13.32