

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925793

Luminaire Tested: DFN2DIP-SQ4F0-060D160US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925793
REPORT IS A COMBINATION OF REPORTS P901723 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D160US950-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20778.1 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 172.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925793

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925793

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21
4	70	60	52	47	63	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	23	19	18	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1563	1563	1563
5°	1565	1541	1552
10°	1553	1521	1531
15°	1530	1496	1499
20°	1499	1462	1466
25°	1468	1420	1427
30°	1430	1382	1378
35°	1393	1337	1326
40°	1348	1291	1277
45°	1304	1245	1227
50°	1255	1197	1168
55°	1203	1141	1115
60°	1145	1075	1054
65°	1082	1007	981
70°	1002	923	904
75°	890	824	832
80°	756	697	695
85°	547	476	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2762 cd/sqm

TEST NUMBER: P925793

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.6	1.0
10°-20°	589.8	2.8
20°-30°	866.8	4.2
30°-40°	1006.7	4.8
40°-50°	1005.5	4.8
50°-60°	876.7	4.2
60°-70°	648.1	3.1
70°-80°	366.7	1.8
80°-90°	105.9	0.5
90°-100°	169.9	0.8
100°-110°	633.2	3.0
110°-120°	1679.4	8.1
120°-130°	2785.4	13.4
130°-140°	2958.8	14.2
140°-150°	2749.9	13.2
150°-160°	2210.8	10.6
160°-170°	1424.6	6.9
170°-180°	490.3	2.4
0°-30°	1666.2	8.0
0°-40°	2673.0	12.9
0°-60°	4555.2	21.9
0°-90°	5675.8	27.3
90°-120°	2482.5	11.9
90°-150°	10976.6	52.8
90°-180°	15102.0	72.7
0°-180°	20778.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2227	2227	2227	2227	2227	
5°	2227	2219	2195	2212	2208	211
15°	2120	2108	2080	2088	2078	597
25°	1919	1902	1866	1870	1866	883
35°	1656	1634	1600	1587	1576	1034
45°	1347	1332	1300	1276	1268	1040
55°	1020	1007	981	955	945	912
65°	688	675	653	634	623	680
75°	360	356	345	332	336	384
85°	88	86	84	77	75	98
90°	4	45	74	93	100	19
95°	242	119	145	164	160	287
105°	1133	1245	228	268	283	1211
115°	2143	2206	2300	574	306	2110
125°	3030	3079	3150	3176	3187	2703
135°	3750	3810	3843	3881	3873	2897
145°	4350	4346	4410	4436	4417	2721
155°	4790	4756	4801	4823	4794	2207
165°	5047	5025	5036	5062	5036	1426
175°	5162	5136	5144	5170	5133	491
180°	5151	5151	5151	5151	5151	

TEST NUMBER: P925793

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2229.5	2205.8	2227.2	2223.1
5°	2227.2	2218.8	2195.2	2212.2	2208.1
7.5°	2212.2	2199.5	2175.9	2193.2	2188.9
10°	2188.9	2173.9	2148.1	2165.2	2158.8
12.5°	2156.6	2143.8	2118.2	2128.9	2124.6
15°	2120.2	2107.5	2079.5	2088.2	2077.5
17.5°	2075.2	2062.5	2034.6	2045.2	2034.6
20°	2025.9	2013.2	1983.2	1989.6	1981.2
22.5°	1976.9	1957.5	1929.6	1929.6	1925.3
25°	1918.9	1901.9	1865.5	1869.6	1865.5
27.5°	1854.6	1839.6	1811.8	1805.5	1794.9
30°	1790.6	1773.2	1741.2	1734.8	1726.2
32.5°	1721.9	1709.2	1674.8	1661.9	1653.3
35°	1655.6	1634.2	1599.9	1586.9	1576.2
37.5°	1580.6	1561.2	1527.0	1511.9	1501.2
40°	1503.5	1486.2	1452.0	1432.9	1424.2
42.5°	1428.5	1411.3	1377.2	1355.6	1342.9
45°	1347.2	1332.2	1299.9	1276.5	1267.9
47.5°	1267.9	1252.9	1218.6	1195.0	1182.2
50°	1184.3	1173.6	1143.7	1113.6	1102.9
52.5°	1102.9	1087.9	1060.2	1036.6	1021.6
55°	1019.5	1006.6	980.9	955.2	944.6
57.5°	936.0	925.3	897.3	871.7	863.0
60°	852.3	843.9	814.0	790.3	783.9
62.5°	770.9	755.9	734.6	713.2	704.6
65°	687.5	674.7	653.3	633.9	623.2
67.5°	601.9	591.0	571.9	556.9	548.3
70°	522.6	514.0	494.6	479.7	471.3
72.5°	441.2	432.6	422.0	407.0	400.6
75°	359.7	355.7	344.7	332.0	336.3
77.5°	287.0	278.4	274.0	267.7	261.3
80°	214.3	212.0	207.7	201.3	197.0
82.5°	145.7	145.7	143.6	135.0	135.0
85°	87.7	85.7	83.6	77.0	75.0
87.5°	38.6	34.3	30.0	23.7	21.4
90°	3.5	44.7	74.3	93.4	100.5
92.5°	93.4	78.3	89.4	96.9	100.5
95°	242.1	119.1	145.2	164.2	160.3
97.5°	436.0	130.6	189.8	201.4	204.9
100°	660.0	149.2	212.5	242.1	249.7
102.5°	905.6	898.6	220.0	260.7	272.2
105°	1133.2	1245.2	227.5	268.3	283.2
107.5°	1397.8	1490.8	235.1	275.8	290.8
110°	1651.5	1729.4	652.4	279.7	294.3

TEST NUMBER: P925793

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1890.1	1956.9	1893.6	286.9	298.3
115°	2143.3	2206.5	2299.9	574.1	305.9
117.5°	2363.2	2437.6	2501.4	1968.0	991.5
120°	2609.4	2665.1	2732.4	2777.1	2273.9
122.5°	2817.8	2877.6	2952.3	2974.5	2978.5
125°	3030.3	3078.9	3149.8	3176.0	3187.0
127.5°	3224.1	3276.4	3332.6	3369.8	3373.3
130°	3407.0	3466.7	3507.5	3548.6	3545.1
132.5°	3593.3	3642.0	3682.7	3716.4	3712.9
135°	3750.0	3809.8	3843.0	3880.6	3873.0
137.5°	3913.8	3958.5	3996.1	4033.3	4022.3
140°	4074.1	4104.1	4144.8	4178.5	4159.9
142.5°	4208.6	4234.7	4283.0	4312.7	4294.0
145°	4350.2	4346.2	4409.6	4435.6	4417.1
147.5°	4472.8	4461.8	4525.1	4543.7	4529.0
150°	4592.4	4566.2	4626.0	4648.2	4629.6
152.5°	4692.8	4663.2	4719.0	4741.6	4715.4
155°	4789.7	4756.5	4801.3	4823.4	4793.8
157.5°	4868.2	4838.5	4872.1	4898.2	4868.2
160°	4935.4	4912.8	4935.4	4957.6	4931.4
162.5°	4994.8	4972.6	4991.1	5017.3	4983.7
165°	5046.9	5024.8	5035.9	5062.0	5035.9
167.5°	5088.2	5065.5	5077.1	5103.1	5069.6
170°	5121.7	5099.2	5106.7	5132.8	5099.2
172.5°	5143.9	5121.7	5129.3	5155.4	5121.7
175°	5162.5	5136.3	5143.9	5170.0	5132.8
177.5°	5170.0	5143.9	5147.9	5174.0	5140.3
180°	5151.4	5151.4	5151.4	5151.4	5151.4



TEST NUMBER: P925793

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.24	6.93	7.37	8.05	9.61	5.80	6.49	6.93	7.61	9.17
	3H	7.89	8.51	9.03	9.64	11.22	7.40	8.02	8.54	9.15	10.73
	4H	8.48	9.06	9.62	10.19	11.77	7.98	8.57	9.13	9.70	11.28
	6H	8.87	9.41	10.03	10.54	12.14	8.37	8.91	9.52	10.04	11.64
	8H	8.97	9.48	10.13	10.63	12.22	8.47	8.98	9.63	10.13	11.72
	12H	9.02	9.50	10.18	10.64	12.25	8.51	8.99	9.67	10.13	11.74
4H	2H	6.68	7.27	7.84	8.40	9.98	6.33	6.91	7.48	8.04	9.63
	3H	8.54	9.03	9.70	10.18	11.78	8.13	8.62	9.29	9.77	11.37
	4H	9.25	9.70	10.41	10.84	12.46	8.82	9.27	9.99	10.42	12.03
	6H	9.76	10.14	10.92	11.31	12.91	9.32	9.71	10.49	10.88	12.48
	8H	9.90	10.26	11.07	11.42	13.04	9.47	9.83	10.63	10.99	12.61
	12H	9.97	10.30	11.15	11.47	13.09	9.52	9.85	10.70	11.02	12.64
8H	4H	9.43	9.79	10.60	10.95	12.57	9.05	9.41	10.22	10.57	12.19
	6H	10.06	10.36	11.25	11.56	13.17	9.68	9.97	10.86	11.17	12.79
	8H	10.28	10.54	11.47	11.72	13.36	9.89	10.15	11.08	11.33	12.96
	12H	10.41	10.63	11.60	11.81	13.48	10.00	10.22	11.19	11.40	13.07
12H	4H	9.41	9.73	10.59	10.90	12.53	9.04	9.37	10.22	10.54	12.16
	6H	10.09	10.35	11.28	11.53	13.16	9.72	9.97	10.91	11.15	12.79
	8H	10.32	10.55	11.52	11.73	13.40	9.94	10.17	11.14	11.35	13.02

END OF REPORT