

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925837

Luminaire Tested: DFN2DIP-SQ4F0-080D070US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925837
REPORT IS A COMBINATION OF REPORTS P901601 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D070US950-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14166.9 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 123.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925837

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925837

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2084	2084	2084
5°	2087	2055	2069
10°	2070	2028	2042
15°	2040	1995	1999
20°	1999	1949	1954
25°	1958	1894	1903
30°	1906	1843	1838
35°	1858	1782	1769
40°	1798	1721	1703
45°	1738	1660	1636
50°	1673	1596	1558
55°	1604	1522	1486
60°	1527	1433	1405
65°	1443	1342	1308
70°	1336	1231	1205
75°	1187	1098	1110
80°	1008	929	927
85°	729	635	623

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1738 cd/sqm

TEST NUMBER: P925837

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	2.0
10°-20°	786.4	5.6
20°-30°	1155.7	8.2
30°-40°	1342.3	9.5
40°-50°	1340.6	9.5
50°-60°	1169.0	8.3
60°-70°	864.1	6.1
70°-80°	488.9	3.5
80°-90°	133.0	0.9
90°-100°	74.3	0.5
100°-110°	277.0	2.0
110°-120°	734.8	5.2
120°-130°	1218.6	8.6
130°-140°	1294.5	9.1
140°-150°	1203.1	8.5
150°-160°	967.2	6.8
160°-170°	623.3	4.4
170°-180°	214.5	1.5
0°-30°	2221.6	15.7
0°-40°	3563.9	25.2
0°-60°	6073.6	42.9
0°-90°	7559.6	53.4
90°-120°	1086.1	7.7
90°-150°	4802.2	33.9
90°-180°	6607.0	46.6
0°-180°	14166.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2970	2970	2970	2970	2970	
5°	2970	2958	2927	2950	2944	282
15°	2827	2810	2773	2784	2770	796
25°	2558	2536	2487	2493	2487	1177
35°	2207	2179	2133	2116	2102	1378
45°	1796	1776	1733	1702	1691	1386
55°	1359	1342	1308	1274	1259	1215
65°	917	900	871	845	831	906
75°	480	474	460	443	448	512
85°	117	114	112	103	100	130
90°	2	20	32	41	44	13
95°	106	52	64	72	70	125
105°	496	545	100	117	124	530
115°	938	965	1006	251	134	923
125°	1326	1347	1378	1390	1394	1182
135°	1641	1667	1681	1698	1694	1267
145°	1903	1902	1929	1941	1932	1190
155°	2096	2081	2100	2110	2097	966
165°	2208	2198	2203	2215	2203	624
175°	2259	2247	2250	2262	2246	215
180°	2254	2254	2254	2254	2254	

TEST NUMBER: P925837

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2969.6	2969.6	2969.6	2969.6	2969.6
2.5°	2986.9	2972.7	2941.2	2969.6	2964.2
5°	2969.6	2958.4	2927.0	2949.7	2944.2
7.5°	2949.7	2932.7	2901.2	2924.2	2918.5
10°	2918.5	2898.4	2864.2	2886.9	2878.5
12.5°	2875.5	2858.5	2824.2	2838.4	2832.7
15°	2827.0	2810.0	2772.7	2784.2	2770.0
17.5°	2767.0	2750.0	2712.7	2727.0	2712.7
20°	2701.3	2684.3	2644.3	2652.8	2641.5
22.5°	2635.8	2610.0	2572.7	2572.7	2567.0
25°	2558.5	2535.8	2487.4	2492.8	2487.4
27.5°	2472.8	2452.8	2415.8	2407.3	2393.1
30°	2387.4	2364.3	2321.7	2313.2	2301.6
32.5°	2295.9	2278.9	2233.1	2215.9	2204.4
35°	2207.4	2178.9	2133.1	2115.9	2101.7
37.5°	2107.4	2081.6	2035.9	2015.9	2001.7
40°	2004.7	1981.6	1936.0	1910.5	1898.9
42.5°	1904.8	1881.7	1836.3	1807.4	1790.6
45°	1796.3	1776.3	1733.2	1702.0	1690.6
47.5°	1690.6	1670.5	1624.8	1593.3	1576.3
50°	1579.1	1564.8	1524.8	1484.8	1470.6
52.5°	1470.6	1450.6	1413.6	1382.2	1362.1
55°	1359.4	1342.1	1307.9	1273.7	1259.4
57.5°	1247.9	1233.7	1196.4	1162.2	1150.6
60°	1136.4	1125.2	1085.2	1053.7	1045.2
62.5°	1027.9	1008.0	979.5	951.0	939.5
65°	916.8	899.5	871.0	845.2	831.0
67.5°	802.5	788.0	762.5	742.6	731.1
70°	696.8	685.3	659.6	639.6	628.3
72.5°	588.3	576.9	562.6	542.6	534.1
75°	479.6	474.1	459.6	442.7	448.4
77.5°	382.6	371.1	365.4	356.9	348.4
80°	285.7	282.7	276.9	268.5	262.6
82.5°	194.2	194.2	191.5	179.9	179.9
85°	117.0	114.2	111.5	102.7	100.0
87.5°	51.5	45.8	40.0	31.5	28.5
90°	1.5	19.6	32.5	40.8	44.0
92.5°	40.8	34.2	39.1	42.5	44.0
95°	105.9	52.1	63.5	71.8	70.1
97.5°	190.7	57.1	83.1	88.1	89.7
100°	288.8	65.3	92.9	105.9	109.2
102.5°	396.2	393.1	96.3	114.1	119.1
105°	495.8	544.7	99.5	117.3	123.9
107.5°	611.5	652.2	102.8	120.7	127.3
110°	722.6	756.6	285.4	122.4	128.8



TEST NUMBER: P925837

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	826.9	856.1	828.5	125.5	130.5
115°	937.7	965.4	1006.2	251.2	133.8
117.5°	1033.9	1066.5	1094.3	861.0	433.8
120°	1141.6	1166.0	1195.5	1215.0	994.8
122.5°	1232.8	1258.9	1291.7	1301.4	1303.1
125°	1325.8	1347.0	1378.1	1389.5	1394.3
127.5°	1410.6	1433.4	1458.0	1474.3	1475.8
130°	1490.5	1516.7	1534.5	1552.5	1551.0
132.5°	1572.1	1593.4	1611.2	1625.9	1624.4
135°	1640.6	1666.7	1681.3	1697.7	1694.5
137.5°	1712.2	1731.9	1748.3	1764.6	1759.7
140°	1782.4	1795.5	1813.4	1828.1	1819.9
142.5°	1841.2	1852.7	1873.8	1886.7	1878.6
145°	1903.2	1901.5	1929.2	1940.6	1932.5
147.5°	1956.8	1952.1	1979.7	1987.8	1981.5
150°	2009.1	1997.8	2023.9	2033.5	2025.4
152.5°	2053.1	2040.1	2064.6	2074.4	2063.0
155°	2095.6	2081.0	2100.5	2110.2	2097.3
157.5°	2129.8	2116.8	2131.5	2143.0	2129.8
160°	2159.3	2149.4	2159.3	2168.9	2157.5
162.5°	2185.2	2175.5	2183.6	2195.1	2180.4
165°	2208.0	2198.4	2203.2	2214.6	2203.2
167.5°	2226.1	2216.1	2221.2	2232.6	2218.0
170°	2240.8	2230.9	2234.2	2245.6	2230.9
172.5°	2250.5	2240.8	2244.1	2255.4	2240.8
175°	2258.6	2247.1	2250.5	2261.8	2245.6
177.5°	2261.8	2250.5	2252.2	2263.7	2248.9
180°	2253.7	2253.7	2253.7	2253.7	2253.7

TEST NUMBER: P925837

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.14	11.03	11.07	11.98	13.20	9.70	10.59	10.62	11.53	12.76
	3H	11.81	12.61	12.75	13.56	14.81	11.32	12.12	12.26	13.07	14.32
	4H	12.40	13.16	13.35	14.12	15.37	11.91	12.66	12.86	13.62	14.88
	6H	12.80	13.50	13.77	14.47	15.74	12.30	13.00	13.27	13.97	15.24
	8H	12.91	13.58	13.88	14.56	15.82	12.41	13.07	13.38	14.06	15.32
	12H	12.96	13.60	13.94	14.57	15.86	12.45	13.09	13.43	14.06	15.35
4H	2H	10.61	11.36	11.57	12.32	13.58	10.25	11.01	11.21	11.97	13.22
	3H	12.48	13.11	13.45	14.10	15.37	12.07	12.70	13.04	13.69	14.96
	4H	13.20	13.78	14.18	14.76	16.05	12.77	13.35	13.75	14.34	15.63
	6H	13.72	14.22	14.71	15.22	16.52	13.29	13.79	14.28	14.79	16.08
	8H	13.87	14.34	14.86	15.34	16.64	13.44	13.90	14.43	14.90	16.21
	12H	13.95	14.37	14.96	15.38	16.70	13.50	13.92	14.51	14.94	16.25
8H	4H	13.40	13.86	14.39	14.86	16.17	13.02	13.49	14.01	14.49	15.79
	6H	14.04	14.42	15.05	15.46	16.77	13.65	14.04	14.67	15.08	16.38
	8H	14.26	14.60	15.28	15.63	16.95	13.87	14.21	14.89	15.23	16.56
	12H	14.40	14.69	15.42	15.72	17.08	13.98	14.28	15.01	15.31	16.67
12H	4H	13.39	13.81	14.40	14.82	16.13	13.02	13.44	14.03	14.45	15.76
	6H	14.07	14.41	15.09	15.43	16.76	13.69	14.03	14.72	15.06	16.38
	8H	14.31	14.61	15.34	15.63	17.00	13.93	14.23	14.96	15.25	16.62