

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925855

Luminaire Tested: DFN2DIP-SQ4F0-080D110US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925855
REPORT IS A COMBINATION OF REPORTS P901674 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D110US950-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16876.3 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 154.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925855

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925855

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	38		
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33		
2	87	80	74	70	79	73	68	64	60	56	53	48	45	43	36	35	34	28		
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	33	31	29	24		
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21		
5	67	56	48	43	61	51	45	40	43	38	34	34	31	28	27	24	22	19		
6	62	50	43	37	56	46	39	35	38	33	30	31	27	25	24	22	20	17		
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15		
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	20	18	16	13		
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12		
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2213	2213	2213
5°	2217	2179	2193
10°	2195	2136	2122
15°	2165	2066	2012
20°	2125	1969	1877
25°	2084	1860	1747
30°	2029	1749	1582
35°	1975	1629	1436
40°	1920	1505	1270
45°	1856	1367	1119
50°	1790	1228	971
55°	1722	1079	829
60°	1642	924	683
65°	1550	765	615
70°	1439	618	558
75°	1300	546	509
80°	1098	459	443
85°	765	309	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1899 cd/sqm

TEST NUMBER: P925855

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	1.8
10°-20°	811.5	4.8
20°-30°	1139.4	6.8
30°-40°	1242.0	7.4
40°-50°	1141.5	6.8
50°-60°	896.5	5.3
60°-70°	583.5	3.5
70°-80°	300.4	1.8
80°-90°	82.9	0.5
90°-100°	116.8	0.7
100°-110°	435.4	2.6
110°-120°	1154.6	6.8
120°-130°	1915.0	11.3
130°-140°	2034.2	12.1
140°-150°	1890.5	11.2
150°-160°	1519.9	9.0
160°-170°	979.4	5.8
170°-180°	337.1	2.0
0°-30°	2246.6	13.3
0°-40°	3488.6	20.7
0°-60°	5526.6	32.7
0°-90°	6493.4	38.5
90°-120°	1706.7	10.1
90°-150°	7546.4	44.7
90°-180°	10383.0	61.5
0°-180°	16876.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3154	3154	3154	3154	3154	
5°	3154	3140	3103	3128	3120	299
15°	3000	2969	2872	2818	2789	845
25°	2723	2632	2444	2327	2284	1252
35°	2347	2201	1950	1770	1707	1469
45°	1918	1727	1427	1224	1156	1481
55°	1459	1236	928	756	702	1303
65°	985	754	497	400	391	976
75°	525	325	228	208	206	555
85°	123	63	54	54	54	141
90°	2	31	51	64	69	16
95°	166	82	100	113	110	197
105°	779	856	156	184	195	832
115°	1474	1517	1581	395	210	1451
125°	2083	2117	2166	2183	2191	1858
135°	2578	2619	2642	2668	2663	1992
145°	2991	2988	3032	3050	3037	1871
155°	3293	3270	3301	3316	3296	1517
165°	3470	3454	3462	3480	3462	980
175°	3549	3531	3536	3554	3529	338
180°	3542	3542	3542	3542	3542	

TEST NUMBER: P925855

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3154.3	3154.3	3154.3	3154.3	3154.3
2.5°	3168.5	3154.3	3122.8	3151.5	3145.8
5°	3154.3	3140.1	3102.8	3128.5	3120.1
7.5°	3128.5	3111.6	3071.6	3082.9	3068.5
10°	3094.3	3074.4	3017.4	3008.6	2991.6
12.5°	3051.7	3025.9	2948.6	2931.6	2900.2
15°	3000.1	2968.7	2871.7	2817.5	2789.0
17.5°	2940.1	2894.4	2774.5	2711.8	2666.0
20°	2871.7	2814.5	2671.9	2600.7	2537.6
22.5°	2797.5	2731.8	2566.2	2469.2	2426.5
25°	2723.3	2631.9	2443.5	2326.6	2283.6
27.5°	2634.9	2537.6	2329.3	2195.2	2129.4
30°	2540.7	2431.9	2203.6	2058.3	1981.0
32.5°	2449.2	2317.8	2084.0	1912.6	1841.1
35°	2346.6	2200.9	1949.8	1770.0	1706.9
37.5°	2246.6	2089.5	1824.1	1627.0	1555.8
40°	2141.0	1969.8	1692.7	1490.1	1415.8
42.5°	2032.5	1849.9	1561.5	1350.2	1278.9
45°	1918.3	1726.9	1427.4	1224.5	1156.1
47.5°	1809.9	1607.3	1299.0	1096.1	1033.4
50°	1689.9	1487.4	1173.3	976.1	916.4
52.5°	1572.8	1358.6	1053.3	865.0	810.8
55°	1458.6	1236.0	927.7	756.5	702.3
57.5°	1341.7	1113.3	816.5	656.6	610.8
60°	1221.7	993.4	699.3	553.9	508.2
62.5°	1104.8	876.4	599.4	462.5	439.8
65°	984.9	753.5	496.7	399.8	390.9
67.5°	870.7	639.4	399.8	351.0	342.6
70°	750.8	528.2	331.0	302.5	291.1
72.5°	636.6	425.2	276.9	254.1	248.3
75°	525.2	325.3	228.4	208.4	205.7
77.5°	414.0	231.1	179.9	168.4	162.7
80°	311.0	165.7	136.9	125.6	125.6
82.5°	216.8	111.4	94.2	88.4	88.4
85°	122.7	62.7	54.2	54.2	54.2
87.5°	45.7	22.7	22.7	20.0	20.0
90°	2.5	30.7	51.1	64.2	69.1
92.5°	64.2	53.9	61.4	66.7	69.1
95°	166.5	81.9	99.8	112.9	110.2
97.5°	299.7	89.8	130.5	138.4	140.9
100°	453.7	102.6	146.1	166.5	171.6
102.5°	622.6	617.7	151.2	179.3	187.2
105°	779.0	856.0	156.5	184.4	194.8
107.5°	961.1	1024.9	161.6	189.6	200.0
110°	1135.4	1189.0	448.6	192.3	202.3

TEST NUMBER: P925855

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1299.4	1345.3	1301.8	197.2	205.1
115°	1473.5	1517.0	1581.3	394.7	210.3
117.5°	1624.8	1675.9	1719.7	1353.0	681.6
120°	1793.9	1832.3	1878.5	1909.2	1563.2
122.5°	1937.3	1978.3	2029.7	2045.0	2047.8
125°	2083.3	2116.8	2165.5	2183.4	2191.1
127.5°	2216.6	2252.5	2291.1	2316.7	2319.2
130°	2342.3	2383.4	2411.3	2439.7	2437.3
132.5°	2470.4	2503.9	2531.9	2555.0	2552.6
135°	2578.2	2619.2	2642.0	2668.0	2662.7
137.5°	2690.8	2721.5	2747.3	2772.9	2765.3
140°	2800.9	2821.6	2849.6	2872.7	2859.9
142.5°	2893.4	2911.3	2944.5	2964.9	2952.2
145°	2990.8	2988.0	3031.5	3049.6	3036.8
147.5°	3075.1	3067.5	3111.0	3123.8	3113.8
150°	3157.3	3139.3	3180.3	3195.6	3182.8
152.5°	3226.3	3205.9	3244.3	3259.8	3241.9
155°	3293.0	3270.1	3300.8	3316.1	3295.7
157.5°	3346.8	3326.4	3349.6	3367.5	3346.8
160°	3393.1	3377.5	3393.1	3408.3	3390.3
162.5°	3433.8	3418.7	3431.4	3449.4	3426.3
165°	3469.8	3454.5	3462.2	3480.1	3462.2
167.5°	3498.0	3482.6	3490.5	3508.4	3485.3
170°	3521.2	3505.7	3510.8	3528.8	3505.7
172.5°	3536.4	3521.2	3526.4	3544.3	3521.2
175°	3549.2	3531.2	3536.4	3554.4	3528.8
177.5°	3554.4	3536.4	3539.1	3557.1	3534.0
180°	3541.6	3541.6	3541.6	3541.6	3541.6

TEST NUMBER: P925855

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.74	9.48	9.80	10.54	11.97	4.70	5.44	5.76	6.50	7.93
	3H	10.42	11.08	11.48	12.14	13.59	5.88	6.55	6.95	7.61	9.06
	4H	11.02	11.65	12.10	12.72	14.17	6.33	6.96	7.41	8.03	9.48
	6H	11.44	12.02	12.53	13.09	14.56	6.65	7.23	7.73	8.30	9.76
	8H	11.57	12.12	12.66	13.21	14.67	6.74	7.29	7.83	8.37	9.83
	12H	11.63	12.15	12.72	13.23	14.72	6.78	7.30	7.87	8.38	9.86
4H	2H	8.75	9.38	9.83	10.44	11.90	5.29	5.92	6.37	6.98	8.44
	3H	10.57	11.10	11.66	12.19	13.66	6.63	7.15	7.72	8.25	9.72
	4H	11.27	11.75	12.36	12.83	14.32	7.18	7.66	8.27	8.74	10.23
	6H	11.78	12.19	12.88	13.30	14.78	7.59	8.00	8.69	9.11	10.59
	8H	11.96	12.34	13.06	13.44	14.94	7.72	8.10	8.82	9.20	10.70
	12H	12.05	12.40	13.17	13.51	15.01	7.78	8.13	8.90	9.24	10.74
8H	4H	11.23	11.61	12.33	12.71	14.21	7.45	7.84	8.56	8.94	10.43
	6H	11.79	12.11	12.92	13.25	14.75	7.97	8.29	9.09	9.43	10.92
	8H	12.01	12.29	13.15	13.41	14.93	8.16	8.44	9.29	9.56	11.07
	12H	12.15	12.40	13.29	13.51	15.07	8.28	8.52	9.41	9.64	11.19
12H	4H	11.18	11.52	12.30	12.64	14.14	7.45	7.80	8.57	8.91	10.42
	6H	11.77	12.05	12.90	13.17	14.68	8.02	8.30	9.15	9.42	10.93
	8H	11.99	12.23	13.12	13.35	14.90	8.23	8.47	9.36	9.59	11.14