

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920490

Luminaire Tested: DFN2DIP-SQ4F0-110D070US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920490
REPORT IS A COMBINATION OF REPORTS P900088 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D070US935-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13384.3 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 157.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920490

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920490

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	58	56
2	92	85	79	74	86	80	74	70	70	66	63	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	36	32	35	32	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2747	2747	2747
5°	2751	2704	2721
10°	2724	2651	2633
15°	2686	2564	2497
20°	2637	2444	2330
25°	2586	2309	2168
30°	2517	2170	1963
35°	2451	2022	1783
40°	2383	1868	1576
45°	2304	1696	1388
50°	2222	1524	1205
55°	2136	1339	1029
60°	2038	1146	848
65°	1924	950	764
70°	1786	767	692
75°	1613	677	632
80°	1362	570	551
85°	949	383	419

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2304 cd/sqm

TEST NUMBER: P920490

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.9	2.7
10°-20°	1007.1	7.5
20°-30°	1413.9	10.6
30°-40°	1541.3	11.5
40°-50°	1416.6	10.6
50°-60°	1112.5	8.3
60°-70°	724.2	5.4
70°-80°	372.8	2.8
80°-90°	100.6	0.8
90°-100°	117.9	0.9
100°-110°	374.8	2.8
110°-120°	641.3	4.8
120°-130°	843.5	6.3
130°-140°	946.7	7.1
140°-150°	928.4	6.9
150°-160°	778.8	5.8
160°-170°	516.5	3.9
170°-180°	180.5	1.3
0°-30°	2787.9	20.8
0°-40°	4329.1	32.3
0°-60°	6858.3	51.2
0°-90°	8055.8	60.2
90°-120°	1134.1	8.5
90°-150°	3852.7	28.8
90°-180°	5328.0	39.8
0°-180°	13384.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3914	3914	3914	3914	3914	
5°	3914	3897	3850	3882	3872	371
15°	3723	3684	3564	3496	3461	1049
25°	3380	3266	3032	2887	2834	1554
35°	2912	2731	2420	2196	2118	1823
45°	2381	2143	1771	1520	1435	1838
55°	1810	1534	1151	939	872	1617
65°	1222	935	616	496	485	1212
75°	652	404	283	259	255	689
85°	152	78	67	67	67	175
90°	2	21	56	53	55	13
95°	84	100	103	103	100	93
105°	346	350	354	357	357	365
115°	644	653	650	648	644	637
125°	936	950	946	941	939	837
135°	1211	1229	1232	1230	1226	936
145°	1470	1481	1491	1492	1486	918
155°	1681	1685	1691	1699	1694	774
165°	1828	1827	1827	1838	1830	516
175°	1903	1898	1895	1906	1896	181
180°	1906	1906	1906	1906	1906	

TEST NUMBER: P920490

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3914.4	3914.4	3914.4	3914.4	3914.4
2.5°	3932.0	3914.4	3875.3	3911.0	3903.9
5°	3914.4	3896.7	3850.5	3882.4	3871.9
7.5°	3882.4	3861.3	3811.7	3825.7	3807.9
10°	3840.0	3815.1	3744.5	3733.5	3712.5
12.5°	3786.9	3755.0	3659.2	3638.1	3599.0
15°	3723.0	3684.0	3563.7	3496.4	3461.0
17.5°	3648.7	3591.9	3443.0	3365.2	3308.5
20°	3563.7	3492.6	3315.6	3227.3	3149.1
22.5°	3471.6	3390.0	3184.5	3064.2	3011.2
25°	3379.5	3266.0	3032.3	2887.2	2833.8
27.5°	3269.8	3149.1	2890.5	2724.0	2642.5
30°	3152.9	3018.0	2734.6	2554.2	2458.3
32.5°	3039.4	2876.2	2586.1	2373.4	2284.7
35°	2912.0	2731.2	2419.7	2196.4	2118.2
37.5°	2788.0	2592.9	2263.6	2019.0	1930.7
40°	2656.8	2444.5	2100.6	1849.1	1757.0
42.5°	2522.2	2295.6	1937.8	1675.5	1587.2
45°	2380.6	2143.0	1771.3	1519.5	1434.6
47.5°	2246.0	1994.6	1612.0	1360.1	1282.4
50°	2097.1	1845.7	1456.0	1211.3	1137.3
52.5°	1951.7	1686.0	1307.2	1073.4	1006.1
55°	1810.0	1533.8	1151.2	938.8	871.6
57.5°	1665.0	1381.6	1013.2	814.8	758.0
60°	1516.1	1232.8	867.8	687.4	630.7
62.5°	1371.1	1087.7	743.8	573.9	545.7
65°	1222.2	935.0	616.4	496.1	485.2
67.5°	1080.6	793.4	496.1	435.6	425.1
70°	931.7	655.5	410.8	375.5	361.2
72.5°	790.0	527.7	343.5	315.3	308.2
75°	651.7	403.6	283.4	258.6	255.2
77.5°	513.8	286.8	223.3	209.0	201.8
80°	386.0	205.6	169.9	156.0	156.0
82.5°	269.1	138.3	116.9	109.8	109.8
85°	152.2	77.8	67.2	67.2	67.2
87.5°	56.7	28.2	28.2	24.8	24.8
90°	1.7	20.7	56.3	52.9	54.6
92.5°	35.6	48.3	50.0	51.7	51.7
95°	83.9	100.0	102.9	102.9	100.0
97.5°	139.7	154.5	160.9	160.9	160.9
100°	204.0	217.2	221.8	221.8	220.1
102.5°	271.8	281.5	287.9	289.6	287.9
105°	345.9	350.5	354.0	356.9	356.9
107.5°	419.5	426.4	426.4	427.6	419.5
110°	490.8	500.0	500.0	500.0	495.3

TEST NUMBER: P920490

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	567.7	577.6	575.8	571.2	567.7
115°	643.6	652.8	650.0	648.2	643.6
117.5°	718.8	731.5	723.5	718.8	714.3
120°	794.7	807.4	794.7	794.7	789.5
122.5°	863.7	879.8	871.8	867.1	863.7
125°	936.1	950.5	945.9	940.7	939.0
127.5°	1006.8	1024.6	1018.3	1011.4	1006.8
130°	1072.9	1093.6	1090.7	1087.3	1080.9
132.5°	1147.0	1163.1	1164.2	1156.2	1151.6
135°	1210.8	1228.6	1232.1	1230.3	1225.7
137.5°	1282.0	1296.4	1299.2	1298.1	1291.2
140°	1344.7	1359.1	1367.1	1367.1	1360.8
142.5°	1409.0	1423.4	1428.0	1429.7	1423.4
145°	1470.0	1481.4	1490.6	1492.4	1486.1
147.5°	1524.6	1538.9	1545.8	1548.7	1542.4
150°	1580.9	1590.6	1597.0	1602.1	1597.0
152.5°	1630.8	1640.6	1648.6	1655.0	1648.6
155°	1680.8	1685.4	1690.7	1698.7	1693.5
157.5°	1724.0	1727.4	1730.3	1741.8	1733.7
160°	1762.5	1765.9	1767.6	1777.4	1770.5
162.5°	1798.1	1798.1	1799.8	1810.7	1802.7
165°	1828.5	1826.8	1826.8	1838.3	1830.2
167.5°	1856.1	1851.0	1851.0	1862.4	1854.4
170°	1876.8	1872.2	1870.5	1882.0	1872.2
172.5°	1891.2	1886.5	1884.8	1896.3	1886.5
175°	1902.6	1898.1	1894.6	1906.1	1896.3
177.5°	1909.0	1904.4	1900.9	1910.7	1900.9
180°	1906.1	1906.1	1906.1	1906.1	1906.1

TEST NUMBER: P920490

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.57	12.49	12.44	13.38	14.50	7.53	8.45	8.40	9.34	10.46
	3H	13.26	14.08	14.14	14.98	16.13	8.73	9.55	9.61	10.45	11.60
	4H	13.88	14.65	14.78	15.56	16.71	9.18	9.96	10.08	10.86	12.02
	6H	14.31	15.02	15.22	15.93	17.10	9.51	10.22	10.42	11.13	12.30
	8H	14.44	15.12	15.36	16.04	17.21	9.60	10.28	10.52	11.21	12.38
	12H	14.50	15.15	15.43	16.07	17.26	9.65	10.30	10.57	11.22	12.41
4H	2H	11.60	12.38	12.50	13.28	14.44	8.14	8.92	9.04	9.82	10.98
	3H	13.44	14.09	14.36	15.02	16.19	9.50	10.15	10.41	11.08	12.25
	4H	14.14	14.73	15.07	15.66	16.86	10.05	10.64	10.98	11.57	12.77
	6H	14.67	15.17	15.61	16.13	17.32	10.48	10.98	11.42	11.94	13.14
	8H	14.84	15.32	15.79	16.27	17.48	10.61	11.08	11.55	12.03	13.24
	12H	14.95	15.37	15.91	16.34	17.55	10.68	11.10	11.64	12.07	13.29
8H	4H	14.12	14.59	15.06	15.54	16.75	10.34	10.81	11.28	11.76	12.97
	6H	14.69	15.08	15.66	16.07	17.28	10.86	11.25	11.83	12.24	13.45
	8H	14.91	15.25	15.89	16.23	17.46	11.06	11.40	12.03	12.38	13.61
	12H	15.06	15.36	16.03	16.33	17.61	11.18	11.48	12.16	12.46	13.73
12H	4H	14.07	14.50	15.03	15.46	16.68	10.35	10.78	11.31	11.74	12.96
	6H	14.67	15.01	15.64	15.99	17.22	10.91	11.26	11.89	12.24	13.47
	8H	14.89	15.20	15.87	16.17	17.45	11.13	11.43	12.11	12.41	13.68

END OF REPORT