

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920516

Luminaire Tested: DFN2DIP-SQ4F0-110D160US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920516
REPORT IS A COMBINATION OF REPORTS P900213 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D160US935-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21568.8 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 227.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920516

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920516

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US935-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	53	54	49	46	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2586	2586	2586
5°	2590	2550	2568
10°	2569	2516	2534
15°	2531	2476	2480
20°	2480	2418	2425
25°	2429	2350	2362
30°	2366	2287	2281
35°	2305	2212	2195
40°	2231	2136	2113
45°	2157	2060	2030
50°	2076	1980	1933
55°	1991	1888	1845
60°	1895	1779	1743
65°	1791	1666	1623
70°	1658	1528	1495
75°	1473	1363	1377
80°	1252	1152	1151
85°	905	789	773

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3430 cd/sqm

TEST NUMBER: P920516

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.9	1.6
10°-20°	975.9	4.5
20°-30°	1434.2	6.6
30°-40°	1665.7	7.7
40°-50°	1663.7	7.7
50°-60°	1450.7	6.7
60°-70°	1072.4	5.0
70°-80°	606.7	2.8
80°-90°	172.5	0.8
90°-100°	269.6	1.3
100°-110°	856.6	4.0
110°-120°	1466.0	6.8
120°-130°	1928.1	8.9
130°-140°	2164.2	10.0
140°-150°	2122.2	9.8
150°-160°	1780.2	8.3
160°-170°	1180.6	5.5
170°-180°	412.7	1.9
0°-30°	2757.0	12.8
0°-40°	4422.7	20.5
0°-60°	7537.0	34.9
0°-90°	9388.6	43.5
90°-120°	2592.3	12.0
90°-150°	8806.7	40.8
90°-180°	12180.0	56.5
0°-180°	21568.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3671	3632	3660	3654	350
15°	3508	3487	3441	3455	3437	988
25°	3175	3147	3087	3094	3087	1461
35°	2739	2704	2647	2626	2608	1711
45°	2229	2204	2151	2112	2098	1720
55°	1687	1666	1623	1580	1563	1508
65°	1138	1116	1081	1049	1031	1125
75°	595	588	570	549	556	635
85°	145	142	138	127	124	162
90°	4	47	129	121	125	21
95°	192	229	235	235	229	213
105°	791	801	809	816	816	834
115°	1471	1492	1486	1482	1471	1455
125°	2140	2173	2162	2150	2146	1912
135°	2768	2808	2816	2812	2802	2139
145°	3360	3386	3407	3411	3397	2099
155°	3842	3853	3864	3883	3871	1768
165°	4180	4176	4176	4202	4184	1179
175°	4349	4339	4331	4357	4335	413
180°	4357	4357	4357	4357	4357	

TEST NUMBER: P920516

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.2	3685.2	3685.2	3685.2	3685.2
2.5°	3706.6	3688.9	3649.9	3685.2	3678.4
5°	3685.2	3671.3	3632.2	3660.4	3653.6
7.5°	3660.4	3639.4	3600.3	3628.8	3621.7
10°	3621.7	3596.8	3554.4	3582.5	3572.0
12.5°	3568.3	3547.2	3504.8	3522.4	3515.3
15°	3508.1	3487.0	3440.8	3455.1	3437.4
17.5°	3433.7	3412.7	3366.4	3384.1	3366.4
20°	3352.1	3331.0	3281.4	3291.9	3278.1
22.5°	3270.9	3238.9	3192.7	3192.7	3185.5
25°	3175.0	3146.9	3086.7	3093.5	3086.7
27.5°	3068.6	3043.8	2997.9	2987.4	2969.8
30°	2962.6	2934.0	2881.0	2870.5	2856.2
32.5°	2849.0	2828.0	2771.2	2749.8	2735.5
35°	2739.3	2704.0	2647.1	2625.7	2608.0
37.5°	2615.2	2583.3	2526.5	2501.6	2484.0
40°	2487.8	2459.2	2402.4	2370.8	2356.6
42.5°	2363.7	2335.1	2278.7	2243.0	2222.0
45°	2229.1	2204.2	2150.9	2112.2	2097.9
47.5°	2097.9	2073.1	2016.3	1977.2	1956.1
50°	1959.5	1941.9	1892.2	1842.6	1825.0
52.5°	1825.0	1800.1	1754.3	1715.1	1690.3
55°	1687.0	1665.5	1623.1	1580.5	1562.9
57.5°	1548.6	1530.9	1484.7	1442.2	1427.9
60°	1410.2	1396.4	1346.7	1307.6	1297.1
62.5°	1275.7	1250.9	1215.5	1180.2	1165.9
65°	1137.6	1116.2	1080.9	1049.0	1031.3
67.5°	995.9	977.9	946.3	921.5	907.2
70°	864.7	850.4	818.5	793.7	779.7
72.5°	730.1	715.8	698.2	673.4	662.8
75°	595.1	588.4	570.3	549.3	556.5
77.5°	474.8	460.5	453.4	442.9	432.4
80°	354.6	350.8	343.6	333.1	326.0
82.5°	241.0	241.0	237.6	223.3	223.3
85°	145.2	141.7	138.4	127.4	124.1
87.5°	63.9	56.7	49.6	39.1	35.3
90°	4.0	47.3	128.7	120.9	124.8
92.5°	81.5	110.4	114.3	118.2	118.2
95°	191.7	228.6	235.1	235.1	228.6
97.5°	319.2	353.4	367.8	367.8	367.8
100°	466.3	496.5	507.0	507.0	503.1
102.5°	621.3	643.7	658.1	662.0	658.1
105°	790.7	801.2	809.2	815.7	815.7
107.5°	958.9	974.6	974.6	977.3	958.9
110°	1121.8	1142.8	1142.8	1142.8	1132.3

TEST NUMBER: P920516

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1297.8	1320.2	1316.2	1305.7	1297.8
115°	1471.2	1492.2	1485.7	1481.7	1471.2
117.5°	1643.3	1672.1	1653.8	1643.3	1632.8
120°	1816.7	1845.5	1816.7	1816.7	1804.8
122.5°	1974.3	2011.1	1992.7	1982.2	1974.3
125°	2139.8	2172.6	2162.1	2150.3	2146.4
127.5°	2301.4	2342.1	2327.6	2311.9	2301.4
130°	2452.5	2499.7	2493.2	2485.3	2470.8
132.5°	2621.9	2658.7	2661.3	2642.9	2632.4
135°	2767.7	2808.4	2816.3	2812.4	2801.9
137.5°	2930.6	2963.4	2970.0	2967.3	2951.6
140°	3073.8	3106.6	3125.0	3125.0	3110.5
142.5°	3220.9	3253.7	3264.2	3268.2	3253.7
145°	3360.1	3386.4	3407.4	3411.4	3396.9
147.5°	3484.9	3517.8	3533.5	3540.1	3525.6
150°	3613.6	3636.0	3650.5	3662.3	3650.5
152.5°	3727.9	3750.2	3768.7	3783.1	3768.7
155°	3842.2	3852.7	3864.5	3882.9	3871.1
157.5°	3940.7	3948.6	3955.2	3981.4	3963.1
160°	4028.7	4036.6	4040.6	4062.9	4047.1
162.5°	4110.1	4110.1	4114.1	4139.1	4120.6
165°	4179.8	4175.8	4175.8	4202.1	4183.8
167.5°	4242.8	4231.0	4231.0	4257.3	4238.9
170°	4290.1	4279.6	4275.7	4302.0	4279.6
172.5°	4323.0	4312.5	4308.5	4334.8	4312.5
175°	4349.2	4338.7	4330.8	4357.2	4334.8
177.5°	4363.7	4353.2	4345.3	4367.7	4345.3
180°	4357.2	4357.2	4357.2	4357.2	4357.2

TEST NUMBER: P920516

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.95	10.76	10.96	11.78	13.14	9.51	10.32	10.52	11.34	12.70
	3H	11.61	12.34	12.64	13.37	14.75	11.12	11.85	12.15	12.88	14.26
	4H	12.20	12.89	13.24	13.92	15.31	11.71	12.39	12.74	13.43	14.81
	6H	12.60	13.23	13.65	14.27	15.67	12.10	12.73	13.15	13.77	15.17
	8H	12.71	13.31	13.76	14.36	15.76	12.21	12.81	13.25	13.86	15.26
	12H	12.76	13.33	13.81	14.37	15.79	12.25	12.82	13.30	13.86	15.28
4H	2H	10.41	11.09	11.45	12.13	13.51	10.05	10.74	11.09	11.77	13.16
	3H	12.27	12.85	13.32	13.91	15.31	11.87	12.44	12.91	13.50	14.90
	4H	12.99	13.51	14.04	14.56	15.99	12.57	13.09	13.62	14.14	15.56
	6H	13.51	13.96	14.57	15.03	16.45	13.07	13.52	14.14	14.60	16.02
	8H	13.66	14.08	14.72	15.14	16.58	13.22	13.64	14.28	14.71	16.14
	12H	13.73	14.11	14.81	15.19	16.63	13.28	13.66	14.36	14.74	16.18
8H	4H	13.18	13.60	14.25	14.67	16.10	12.81	13.23	13.87	14.29	15.73
	6H	13.82	14.16	14.90	15.27	16.70	13.43	13.78	14.52	14.89	16.32
	8H	14.04	14.34	15.13	15.44	16.89	13.65	13.95	14.74	15.04	16.49
	12H	14.17	14.44	15.27	15.53	17.02	13.76	14.03	14.86	15.12	16.61
12H	4H	13.17	13.55	14.25	14.63	16.07	12.80	13.18	13.88	14.26	15.70
	6H	13.85	14.15	14.94	15.24	16.69	13.47	13.78	14.57	14.87	16.32
	8H	14.09	14.36	15.19	15.44	16.94	13.71	13.98	14.81	15.06	16.56