

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925966

Luminaire Tested: DFN2DIP-SQ4F0-110D120US950-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P925966  
REPORT IS A COMBINATION OF REPORTS P900178 AND P896915  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-110D120US950-RLLFLL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 19051.4 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 195.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925966  
CATALOG NUMBER: DFN2DIP-SQ4F0-110D120US950-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P925966  
 CATALOG NUMBER: DFN2DIP-SQ4F0-110D120US950-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47	47	47	47
1	98	93	90	86	90	86	83	80	72	70	68	59	58	57	48	47	46	40	40	40	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35	35	35	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26	26	26	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23	23	23	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23	20	20	20	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16	16	16	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15	15	15	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14	14	14	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3043	3043	3043
5°	3048	2996	3015
10°	3018	2937	2918
15°	2976	2841	2767
20°	2921	2708	2582
25°	2865	2558	2402
30°	2789	2405	2175
35°	2715	2240	1975
40°	2640	2069	1746
45°	2552	1880	1538
50°	2462	1688	1335
55°	2367	1484	1140
60°	2258	1270	939
65°	2132	1052	846
70°	1979	850	767
75°	1787	750	700
80°	1510	631	610
85°	1051	425	464

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2850 cd/sqm



TEST NUMBER: P925966

CATALOG NUMBER: DFN2DIP-SQ4F0-110D120US950-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	406.5	2.1
10°-20°	1115.9	5.9
20°-30°	1566.7	8.2
30°-40°	1707.7	9.0
40°-50°	1569.6	8.2
50°-60°	1232.7	6.5
60°-70°	802.4	4.2
70°-80°	413.0	2.2
80°-90°	115.7	0.6
90°-100°	224.0	1.2
100°-110°	711.8	3.7
110°-120°	1218.2	6.4
120°-130°	1602.1	8.4
130°-140°	1798.3	9.4
140°-150°	1763.5	9.3
150°-160°	1479.3	7.8
160°-170°	981.0	5.1
170°-180°	342.9	1.8
0°-30°	3089.0	16.2
0°-40°	4796.8	25.2
0°-60°	7599.1	39.9
0°-90°	8930.2	46.9
90°-120°	2154.1	11.3
90°-150°	7318.0	38.4
90°-180°	10121.0	53.1
0°-180°	19051.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4337	4337	4337	4337	4337	
5°	4337	4318	4266	4302	4290	411
15°	4125	4082	3949	3874	3835	1162
25°	3744	3619	3360	3199	3140	1722
35°	3226	3026	2681	2434	2347	2019
45°	2638	2374	1963	1684	1590	2037
55°	2006	1700	1276	1040	966	1792
65°	1354	1036	683	550	538	1343
75°	722	447	314	286	283	764
85°	169	86	74	74	74	194
90°	3	39	107	100	104	19
95°	159	190	195	195	190	177
105°	657	666	672	678	678	693
115°	1222	1240	1234	1231	1222	1209
125°	1778	1805	1797	1787	1784	1589
135°	2300	2334	2340	2337	2328	1778
145°	2792	2814	2831	2835	2823	1745
155°	3193	3201	3211	3226	3217	1470
165°	3473	3470	3470	3492	3476	980
175°	3614	3605	3599	3620	3602	343
180°	3620	3620	3620	3620	3620	



TEST NUMBER: P925966

CATALOG NUMBER: DFN2DIP-SQ4F0-110D120US950-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4337.2	4337.2	4337.2	4337.2	4337.2
2.5°	4356.7	4337.2	4293.9	4333.4	4325.5
5°	4337.2	4317.6	4266.4	4301.8	4290.1
7.5°	4301.8	4278.4	4223.5	4238.9	4219.3
10°	4254.7	4227.2	4148.9	4136.8	4113.6
12.5°	4196.0	4160.6	4054.4	4031.0	3987.7
15°	4125.2	4081.9	3948.6	3874.1	3834.9
17.5°	4042.8	3979.9	3815.0	3728.7	3665.8
20°	3948.6	3869.9	3673.8	3575.9	3489.3
22.5°	3846.6	3756.2	3528.5	3395.2	3336.4
25°	3744.5	3618.8	3359.8	3199.0	3139.9
27.5°	3623.0	3489.3	3202.8	3018.3	2927.9
30°	3493.5	3344.0	3030.0	2830.0	2723.9
32.5°	3367.7	3186.9	2865.4	2629.8	2531.5
35°	3226.5	3026.2	2681.0	2433.7	2347.0
37.5°	3089.1	2873.0	2508.2	2237.0	2139.2
40°	2943.8	2708.5	2327.5	2048.8	1946.8
42.5°	2794.6	2543.6	2147.2	1856.5	1758.6
45°	2637.7	2374.5	1962.7	1683.6	1589.6
47.5°	2488.6	2210.0	1786.1	1507.0	1420.9
50°	2323.7	2045.1	1613.3	1342.2	1260.1
52.5°	2162.5	1868.1	1448.4	1189.4	1114.7
55°	2005.5	1699.5	1275.5	1040.2	965.7
57.5°	1844.8	1530.8	1122.7	902.9	839.9
60°	1679.9	1365.9	961.5	761.7	698.8
62.5°	1519.1	1205.2	824.2	635.9	604.6
65°	1354.2	1036.0	683.0	549.7	537.6
67.5°	1197.3	879.1	549.7	482.6	471.0
70°	1032.3	726.3	455.2	416.0	400.2
72.5°	875.3	584.7	380.6	349.4	341.4
75°	722.1	447.2	314.0	286.5	282.8
77.5°	569.3	317.8	247.4	231.5	223.6
80°	427.7	227.8	188.2	172.9	172.9
82.5°	298.1	153.2	129.6	121.6	121.6
85°	168.7	86.2	74.5	74.5	74.5
87.5°	62.9	31.2	31.2	27.5	27.5
90°	3.2	39.3	106.9	100.5	103.7
92.5°	67.6	91.7	94.9	98.3	98.3
95°	159.3	189.9	195.4	195.4	189.9
97.5°	265.2	293.6	305.7	305.7	305.7
100°	387.5	412.6	421.3	421.3	418.0
102.5°	516.3	534.8	546.8	550.2	546.8
105°	657.1	665.8	672.4	677.8	677.8
107.5°	796.8	809.9	809.9	812.0	796.8
110°	932.2	949.6	949.6	949.6	940.9



TEST NUMBER: P925966

CATALOG NUMBER: DFN2DIP-SQ4F0-110D120US950-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1078.4	1097.0	1093.7	1085.0	1078.4
115°	1222.5	1240.0	1234.5	1231.2	1222.5
117.5°	1365.5	1389.5	1374.2	1365.5	1356.8
120°	1509.6	1533.6	1509.6	1509.6	1499.8
122.5°	1640.6	1671.1	1655.9	1647.1	1640.6
125°	1778.1	1805.3	1796.7	1786.8	1783.5
127.5°	1912.4	1946.2	1934.1	1921.1	1912.4
130°	2037.8	2077.1	2071.7	2065.1	2053.1
132.5°	2178.6	2209.3	2211.4	2196.1	2187.4
135°	2299.8	2333.7	2340.3	2336.9	2328.2
137.5°	2435.2	2462.5	2467.9	2465.7	2452.6
140°	2554.1	2581.4	2596.7	2596.7	2584.7
142.5°	2676.4	2703.7	2712.4	2715.7	2703.7
145°	2792.1	2813.9	2831.4	2834.7	2822.7
147.5°	2895.8	2923.1	2936.2	2941.7	2929.6
150°	3002.8	3021.3	3033.3	3043.2	3033.3
152.5°	3097.7	3116.2	3131.6	3143.6	3131.6
155°	3192.7	3201.4	3211.3	3226.5	3216.7
157.5°	3274.6	3281.1	3286.5	3308.4	3293.1
160°	3347.7	3354.3	3357.5	3376.1	3362.9
162.5°	3415.3	3415.3	3418.7	3439.4	3424.1
165°	3473.2	3470.0	3470.0	3491.7	3476.5
167.5°	3525.6	3515.8	3515.8	3537.6	3522.4
170°	3564.9	3556.1	3552.9	3574.7	3556.1
172.5°	3592.2	3583.4	3580.2	3602.0	3583.4
175°	3614.0	3605.3	3598.8	3620.5	3602.0
177.5°	3626.1	3617.3	3610.7	3629.3	3610.7
180°	3620.5	3620.5	3620.5	3620.5	3620.5



TEST NUMBER: P925966  
 CATALOG NUMBER: DFN2DIP-SQ4F0-110D120US950-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.72	11.53	11.72	12.53	13.85	6.69	7.49	7.68	8.49	9.81
	3H	12.41	13.13	13.41	14.13	15.47	7.87	8.59	8.87	9.60	10.94
	4H	13.02	13.70	14.03	14.71	16.05	8.32	9.00	9.34	10.01	11.36
	6H	13.44	14.07	14.46	15.08	16.44	8.64	9.27	9.67	10.28	11.64
	8H	13.57	14.16	14.60	15.19	16.55	8.73	9.33	9.76	10.36	11.72
	12H	13.63	14.20	14.66	15.22	16.60	8.78	9.34	9.81	10.37	11.75
4H	2H	10.74	11.42	11.76	12.43	13.78	7.28	7.96	8.30	8.97	10.32
	3H	12.57	13.14	13.60	14.18	15.54	8.63	9.20	9.66	10.23	11.59
	4H	13.27	13.78	14.30	14.81	16.20	9.18	9.70	10.21	10.73	12.11
	6H	13.78	14.23	14.83	15.28	16.66	9.60	10.04	10.64	11.09	12.47
	8H	13.96	14.38	15.01	15.42	16.82	9.73	10.14	10.77	11.19	12.58
	12H	14.06	14.43	15.12	15.49	16.89	9.79	10.16	10.85	11.23	12.62
8H	4H	13.23	13.65	14.28	14.69	16.09	9.46	9.87	10.50	10.92	12.31
	6H	13.80	14.15	14.87	15.23	16.63	9.98	10.32	11.05	11.41	12.80
	8H	14.02	14.32	15.10	15.40	16.81	10.17	10.47	11.25	11.54	12.95
	12H	14.16	14.43	15.24	15.50	16.95	10.29	10.55	11.37	11.62	13.07
12H	4H	13.18	13.56	14.25	14.62	16.02	9.46	9.84	10.53	10.90	12.30
	6H	13.78	14.08	14.85	15.15	16.56	10.03	10.33	11.10	11.40	12.81
	8H	14.00	14.27	15.08	15.33	16.79	10.24	10.50	11.32	11.57	13.02