

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926015

Luminaire Tested: DFN2DIP-SQ4F0-140D060US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926015
REPORT IS A COMBINATION OF REPORTS P901594 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D060US950-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17019.3 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926015

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926015

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71
1	102	98	94	91	96	93	89	86	82	80	78		73	71	69		64
2	94	86	80	75	88	82	76	72	73	69	65		65	62	59		57
3	86	77	69	64	81	72	66	61	65	60	56		58	54	51		51
4	79	68	60	54	74	65	58	52	58	53	48		52	48	44		46
5	73	61	53	47	68	58	51	45	52	47	42		47	42	39		42
6	67	55	47	41	63	53	45	40	48	42	37		43	38	34		38
7	62	50	42	37	59	48	41	36	43	37	33		39	34	31		35
8	58	46	38	33	55	44	37	32	40	34	30		36	31	28		33
9	54	42	35	30	51	40	33	29	37	31	27		33	29	25		30
10	51	39	32	27	48	37	31	26	34	28	24		31	26	23		28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3873	3873	3873
5°	3879	3813	3837
10°	3841	3739	3714
15°	3788	3616	3522
20°	3718	3446	3286
25°	3646	3256	3058
30°	3550	3061	2768
35°	3456	2851	2514
40°	3360	2634	2222
45°	3248	2392	1958
50°	3133	2149	1699
55°	3013	1889	1451
60°	2873	1616	1195
65°	2713	1339	1077
70°	2519	1081	976
75°	2275	955	891
80°	1922	803	777
85°	1337	540	591

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3248 cd/sqm

TEST NUMBER: P926015

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	517.3	3.0
10°-20°	1420.2	8.3
20°-30°	1993.9	11.7
30°-40°	2173.5	12.8
40°-50°	1997.7	11.7
50°-60°	1568.9	9.2
60°-70°	1021.2	6.0
70°-80°	525.7	3.1
80°-90°	137.6	0.8
90°-100°	63.7	0.4
100°-110°	237.5	1.4
110°-120°	629.8	3.7
120°-130°	1044.5	6.1
130°-140°	1109.5	6.5
140°-150°	1031.2	6.1
150°-160°	829.1	4.9
160°-170°	534.2	3.1
170°-180°	183.9	1.1
0°-30°	3931.5	23.1
0°-40°	6105.0	35.9
0°-60°	9671.6	56.8
0°-90°	11356.0	66.7
90°-120°	930.9	5.5
90°-150°	4116.2	24.2
90°-180°	5663.0	33.3
0°-180°	17019.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5520	5520	5520	5520	5520	
5°	5520	5495	5430	5475	5460	523
15°	5250	5195	5026	4931	4881	1479
25°	4766	4606	4276	4072	3996	2192
35°	4106	3852	3412	3097	2987	2570
45°	3357	3022	2498	2143	2023	2593
55°	2552	2163	1623	1324	1229	2281
65°	1724	1319	869	700	684	1709
75°	919	569	400	365	360	972
85°	215	110	95	95	95	246
90°	1	17	28	35	38	16
95°	91	45	54	62	60	108
105°	425	467	85	101	106	454
115°	804	828	862	215	115	791
125°	1136	1155	1181	1191	1195	1014
135°	1406	1429	1441	1455	1452	1086
145°	1631	1630	1654	1663	1656	1020
155°	1796	1784	1800	1809	1798	828
165°	1893	1884	1888	1898	1888	535
175°	1936	1926	1929	1939	1925	184
180°	1932	1932	1932	1932	1932	



TEST NUMBER: P926015

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5520.0	5520.0	5520.0	5520.0	5520.0
2.5°	5544.9	5520.0	5464.9	5515.3	5505.2
5°	5520.0	5495.1	5429.9	5475.0	5460.1
7.5°	5475.0	5445.2	5375.3	5395.0	5370.1
10°	5415.1	5380.1	5280.5	5265.0	5235.4
12.5°	5340.3	5295.3	5160.1	5130.4	5075.4
15°	5250.2	5195.1	5025.5	4930.7	4880.9
17.5°	5145.3	5065.3	4855.4	4745.7	4665.6
20°	5025.5	4925.3	4675.7	4551.2	4441.0
22.5°	4895.6	4780.7	4490.8	4321.1	4246.4
25°	4765.8	4605.7	4276.1	4071.5	3996.2
27.5°	4611.1	4441.0	4076.3	3841.5	3726.5
30°	4446.2	4256.0	3856.4	3601.9	3466.7
32.5°	4286.1	4056.1	3647.0	3347.0	3221.9
35°	4106.5	3851.6	3412.2	3097.4	2987.1
37.5°	3931.6	3656.5	3192.2	2847.2	2722.6
40°	3746.6	3447.2	2962.2	2607.7	2477.8
42.5°	3556.9	3237.3	2732.7	2362.8	2238.2
45°	3357.0	3022.1	2498.0	2142.8	2023.1
47.5°	3167.3	2812.8	2273.2	1918.1	1808.4
50°	2957.4	2602.9	2053.2	1708.2	1603.8
52.5°	2752.3	2377.6	1843.3	1513.7	1418.8
55°	2552.5	2162.9	1623.4	1324.0	1229.0
57.5°	2347.9	1948.3	1428.9	1149.1	1069.1
60°	2138.0	1738.4	1223.8	969.4	889.3
62.5°	1933.5	1533.8	1048.9	809.3	769.6
65°	1723.6	1318.6	869.2	699.6	684.2
67.5°	1523.7	1118.9	699.6	614.3	599.4
70°	1313.8	924.3	579.3	529.5	509.3
72.5°	1114.1	744.1	484.4	444.7	434.6
75°	919.0	569.3	399.6	364.6	359.8
77.5°	724.6	404.4	314.8	294.7	284.6
80°	544.4	289.9	239.5	220.0	220.0
82.5°	379.5	195.0	164.9	154.7	154.7
85°	214.6	109.7	94.8	94.8	94.8
87.5°	80.0	39.8	39.8	35.0	35.0
90°	1.3	16.8	27.9	35.0	37.7
92.5°	35.0	29.4	33.5	36.3	37.7
95°	90.8	44.6	54.5	61.6	60.1
97.5°	163.5	48.9	71.2	75.6	76.9
100°	247.5	55.9	79.7	90.8	93.6
102.5°	339.6	337.0	82.5	97.8	102.1
105°	424.9	466.9	85.3	100.6	106.3
107.5°	524.2	559.0	88.1	103.4	109.0
110°	619.3	648.5	244.7	104.9	110.4

TEST NUMBER: P926015

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	708.7	733.8	710.1	107.5	111.9
115°	803.7	827.5	862.5	215.3	114.7
117.5°	886.2	914.1	938.0	738.0	371.8
120°	978.5	999.4	1024.7	1041.4	852.7
122.5°	1056.7	1079.1	1107.1	1115.4	1116.9
125°	1136.4	1154.6	1181.1	1191.0	1195.1
127.5°	1209.1	1228.7	1249.7	1263.7	1265.0
130°	1277.6	1300.0	1315.3	1330.7	1329.4
132.5°	1347.5	1365.7	1381.0	1393.6	1392.3
135°	1406.3	1428.7	1441.1	1455.2	1452.4
137.5°	1467.6	1484.4	1498.5	1512.5	1508.4
140°	1527.7	1539.1	1554.4	1566.9	1560.0
142.5°	1578.2	1588.0	1606.2	1617.2	1610.3
145°	1631.3	1629.8	1653.6	1663.4	1656.4
147.5°	1677.3	1673.1	1696.9	1703.8	1698.4
150°	1722.2	1712.3	1734.8	1743.1	1736.1
152.5°	1759.8	1748.7	1769.6	1778.1	1768.2
155°	1796.2	1783.7	1800.5	1808.8	1797.6
157.5°	1825.6	1814.4	1827.0	1836.8	1825.6
160°	1850.8	1842.3	1850.8	1859.1	1849.3
162.5°	1873.0	1864.7	1871.7	1881.5	1868.9
165°	1892.6	1884.3	1888.4	1898.3	1888.4
167.5°	1908.0	1899.6	1903.9	1913.7	1901.0
170°	1920.7	1912.2	1915.1	1924.8	1912.2
172.5°	1929.0	1920.7	1923.5	1933.3	1920.7
175°	1936.0	1926.1	1929.0	1938.7	1924.8
177.5°	1938.7	1929.0	1930.4	1940.2	1927.7
180°	1931.8	1931.8	1931.8	1931.8	1931.8

TEST NUMBER: P926015

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.30	14.29	14.11	15.11	16.12	9.26	10.25	10.07	11.07	12.09
	3H	14.99	15.88	15.81	16.71	17.75	10.46	11.35	11.28	12.18	13.22
	4H	15.61	16.45	16.45	17.29	18.34	10.92	11.75	11.76	12.59	13.65
	6H	16.05	16.81	16.89	17.66	18.73	11.25	12.02	12.10	12.87	13.93
	8H	16.18	16.91	17.04	17.78	18.84	11.34	12.07	12.20	12.94	14.01
	12H	16.25	16.94	17.11	17.80	18.89	11.39	12.09	12.26	12.95	14.04
4H	2H	13.34	14.17	14.18	15.01	16.06	9.88	10.71	10.72	11.55	12.60
	3H	15.18	15.88	16.04	16.75	17.82	11.24	11.93	12.09	12.81	13.88
	4H	15.89	16.52	16.75	17.39	18.48	11.80	12.43	12.66	13.30	14.39
	6H	16.41	16.96	17.29	17.85	18.95	12.23	12.77	13.11	13.66	14.76
	8H	16.60	17.10	17.48	17.99	19.10	12.36	12.86	13.24	13.75	14.87
	12H	16.70	17.16	17.60	18.07	19.18	12.43	12.89	13.33	13.80	14.91
8H	4H	15.87	16.37	16.75	17.26	18.37	12.09	12.60	12.97	13.49	14.60
	6H	16.44	16.86	17.35	17.79	18.91	12.62	13.04	13.53	13.97	15.08
	8H	16.66	17.03	17.58	17.96	19.09	12.81	13.18	13.73	14.11	15.23
	12H	16.81	17.14	17.73	18.05	19.24	12.94	13.26	13.86	14.18	15.36
12H	4H	15.83	16.28	16.73	17.19	18.31	12.10	12.56	13.01	13.47	14.59
	6H	16.42	16.79	17.34	17.72	18.84	12.67	13.04	13.59	13.96	15.09
	8H	16.65	16.98	17.57	17.89	19.07	12.89	13.21	13.81	14.13	15.31