

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920562

Luminaire Tested: DFN2DIP-SQ4F0-140D070US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920562
REPORT IS A COMBINATION OF REPORTS P900092 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D070US935-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15579.8 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 196
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920562

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920562

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3496	3496	3496
5°	3501	3441	3463
10°	3467	3374	3351
15°	3419	3263	3178
20°	3356	3110	2965
25°	3291	2938	2759
30°	3204	2762	2498
35°	3119	2573	2269
40°	3032	2377	2005
45°	2932	2159	1767
50°	2828	1939	1533
55°	2719	1705	1309
60°	2593	1459	1079
65°	2449	1209	972
70°	2273	976	881
75°	2053	862	804
80°	1734	725	701
85°	1207	488	533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2932 cd/sqm

TEST NUMBER: P920562

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	466.9	3.0
10°-20°	1281.8	8.2
20°-30°	1799.5	11.6
30°-40°	1961.6	12.6
40°-50°	1802.9	11.6
50°-60°	1415.9	9.1
60°-70°	921.6	5.9
70°-80°	474.4	3.0
80°-90°	126.5	0.8
90°-100°	117.9	0.8
100°-110°	374.8	2.4
110°-120°	641.3	4.1
120°-130°	843.5	5.4
130°-140°	946.7	6.1
140°-150°	928.4	6.0
150°-160°	778.8	5.0
160°-170°	516.5	3.3
170°-180°	180.5	1.2
0°-30°	3548.2	22.8
0°-40°	5509.8	35.4
0°-60°	8728.7	56.0
0°-90°	10251.3	65.8
90°-120°	1134.1	7.3
90°-150°	3852.7	24.7
90°-180°	5328.0	34.2
0°-180°	15579.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4982	4982	4982	4982	4982	
5°	4982	4959	4900	4941	4928	472
15°	4738	4689	4536	4450	4405	1335
25°	4301	4157	3859	3675	3607	1978
35°	3706	3476	3080	2795	2696	2320
45°	3030	2728	2254	1934	1826	2340
55°	2304	1952	1465	1195	1109	2059
65°	1556	1190	784	631	618	1542
75°	829	514	361	329	325	877
85°	194	99	86	86	86	222
90°	2	21	56	53	55	15
95°	84	100	103	103	100	93
105°	346	350	354	357	357	365
115°	644	653	650	648	644	637
125°	936	950	946	941	939	837
135°	1211	1229	1232	1230	1226	936
145°	1470	1481	1491	1492	1486	918
155°	1681	1685	1691	1699	1694	774
165°	1828	1827	1827	1838	1830	516
175°	1903	1898	1895	1906	1896	181
180°	1906	1906	1906	1906	1906	

TEST NUMBER: P920562

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4981.9	4981.9	4981.9	4981.9	4981.9
2.5°	5004.4	4981.9	4932.1	4977.6	4968.5
5°	4981.9	4959.4	4900.5	4941.3	4927.8
7.5°	4941.3	4914.4	4851.3	4869.0	4846.6
10°	4887.2	4855.6	4765.7	4751.8	4725.0
12.5°	4819.7	4779.1	4657.1	4630.3	4580.6
15°	4738.4	4688.6	4535.6	4450.0	4405.0
17.5°	4643.7	4571.5	4382.0	4283.0	4210.8
20°	4535.6	4445.2	4219.9	4107.5	4008.0
22.5°	4418.4	4314.6	4053.0	3899.9	3832.5
25°	4301.2	4156.7	3859.3	3674.6	3606.6
27.5°	4161.5	4008.0	3678.9	3467.0	3363.2
30°	4012.8	3841.1	3480.4	3250.8	3128.8
32.5°	3868.3	3660.7	3291.4	3020.7	2907.8
35°	3706.2	3476.1	3079.5	2795.4	2695.9
37.5°	3548.3	3300.0	2881.0	2569.6	2457.2
40°	3381.4	3111.1	2673.4	2353.5	2236.3
42.5°	3210.1	2921.7	2466.3	2132.4	2020.0
45°	3029.8	2727.5	2254.4	1933.9	1825.8
47.5°	2858.5	2538.6	2051.6	1731.1	1632.1
50°	2669.1	2349.1	1853.0	1541.7	1447.4
52.5°	2484.0	2145.8	1663.6	1366.1	1280.5
55°	2303.7	1952.1	1465.2	1194.9	1109.2
57.5°	2119.0	1758.3	1289.6	1037.1	964.8
60°	1929.6	1568.9	1104.5	874.9	802.6
62.5°	1745.0	1384.3	946.7	730.4	694.6
65°	1555.6	1190.1	784.5	631.4	617.5
67.5°	1375.2	1009.8	631.4	554.4	541.0
70°	1185.8	834.2	522.8	477.9	459.7
72.5°	1005.5	671.6	437.2	401.3	392.3
75°	829.4	513.8	360.7	329.1	324.8
77.5°	653.9	365.0	284.1	266.0	256.8
80°	491.3	261.7	216.2	198.5	198.5
82.5°	342.5	176.0	148.8	139.7	139.7
85°	193.7	99.0	85.6	85.6	85.6
87.5°	72.2	35.9	35.9	31.6	31.6
90°	1.7	20.7	56.3	52.9	54.6
92.5°	35.6	48.3	50.0	51.7	51.7
95°	83.9	100.0	102.9	102.9	100.0
97.5°	139.7	154.5	160.9	160.9	160.9
100°	204.0	217.2	221.8	221.8	220.1
102.5°	271.8	281.5	287.9	289.6	287.9
105°	345.9	350.5	354.0	356.9	356.9
107.5°	419.5	426.4	426.4	427.6	419.5
110°	490.8	500.0	500.0	500.0	495.3

TEST NUMBER: P920562

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	567.7	577.6	575.8	571.2	567.7
115°	643.6	652.8	650.0	648.2	643.6
117.5°	718.8	731.5	723.5	718.8	714.3
120°	794.7	807.4	794.7	794.7	789.5
122.5°	863.7	879.8	871.8	867.1	863.7
125°	936.1	950.5	945.9	940.7	939.0
127.5°	1006.8	1024.6	1018.3	1011.4	1006.8
130°	1072.9	1093.6	1090.7	1087.3	1080.9
132.5°	1147.0	1163.1	1164.2	1156.2	1151.6
135°	1210.8	1228.6	1232.1	1230.3	1225.7
137.5°	1282.0	1296.4	1299.2	1298.1	1291.2
140°	1344.7	1359.1	1367.1	1367.1	1360.8
142.5°	1409.0	1423.4	1428.0	1429.7	1423.4
145°	1470.0	1481.4	1490.6	1492.4	1486.1
147.5°	1524.6	1538.9	1545.8	1548.7	1542.4
150°	1580.9	1590.6	1597.0	1602.1	1597.0
152.5°	1630.8	1640.6	1648.6	1655.0	1648.6
155°	1680.8	1685.4	1690.7	1698.7	1693.5
157.5°	1724.0	1727.4	1730.3	1741.8	1733.7
160°	1762.5	1765.9	1767.6	1777.4	1770.5
162.5°	1798.1	1798.1	1799.8	1810.7	1802.7
165°	1828.5	1826.8	1826.8	1838.3	1830.2
167.5°	1856.1	1851.0	1851.0	1862.4	1854.4
170°	1876.8	1872.2	1870.5	1882.0	1872.2
172.5°	1891.2	1886.5	1884.8	1896.3	1886.5
175°	1902.6	1898.1	1894.6	1906.1	1896.3
177.5°	1909.0	1904.4	1900.9	1910.7	1900.9
180°	1906.1	1906.1	1906.1	1906.1	1906.1

TEST NUMBER: P920562

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.87	13.85	13.68	14.68	15.71	8.83	9.81	9.64	10.64	11.67
	3H	14.56	15.44	15.39	16.28	17.34	10.03	10.90	10.86	11.75	12.81
	4H	15.18	16.00	16.03	16.85	17.92	10.49	11.31	11.33	12.16	13.23
	6H	15.61	16.37	16.47	17.23	18.31	10.82	11.58	11.67	12.43	13.52
	8H	15.75	16.47	16.61	17.34	18.43	10.91	11.63	11.78	12.51	13.59
	12H	15.81	16.50	16.69	17.37	18.48	10.96	11.65	11.83	12.52	13.62
4H	2H	12.90	13.73	13.75	14.58	15.65	9.44	10.27	10.30	11.12	12.19
	3H	14.75	15.44	15.61	16.32	17.40	10.81	11.49	11.67	12.38	13.46
	4H	15.45	16.08	16.33	16.96	18.07	11.36	11.99	12.24	12.87	13.98
	6H	15.98	16.52	16.87	17.42	18.54	11.79	12.33	12.68	13.23	14.35
	8H	16.16	16.66	17.05	17.56	18.69	11.92	12.43	12.82	13.32	14.45
	12H	16.27	16.72	17.18	17.63	18.77	12.00	12.45	12.91	13.37	14.50
8H	4H	15.43	15.93	16.32	16.83	17.96	11.66	12.16	12.55	13.06	14.18
	6H	16.01	16.42	16.93	17.36	18.49	12.18	12.60	13.10	13.54	14.66
	8H	16.23	16.59	17.16	17.53	18.67	12.37	12.74	13.30	13.68	14.82
	12H	16.38	16.70	17.31	17.62	18.82	12.50	12.82	13.43	13.75	14.94
12H	4H	15.39	15.84	16.30	16.76	17.89	11.67	12.12	12.58	13.04	14.17
	6H	15.98	16.35	16.91	17.28	18.43	12.23	12.60	13.16	13.53	14.68
	8H	16.21	16.54	17.15	17.46	18.66	12.45	12.77	13.38	13.70	14.90