

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920563

Luminaire Tested: DFN2DIP-SQ4F0-140D070US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920563
REPORT IS A COMBINATION OF REPORTS P901612 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D070US935-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16212.6 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 196
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920563

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920563

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91		79	79	79		68
1	101	97	93	90	95	91	88	85	80	78	76		71	69	67		61
2	93	86	80	75	87	81	75	71	71	67	64		63	60	57		55
3	85	76	69	63	80	72	65	60	63	58	54		56	52	49		49
4	78	68	60	54	73	64	57	52	57	51	47		50	46	43		44
5	72	61	53	47	67	57	50	45	51	45	41		46	41	37		40
6	67	55	47	41	62	52	45	39	46	41	36		41	37	33		37
7	62	50	42	36	58	47	40	35	42	36	32		38	33	30		34
8	58	45	38	32	54	43	36	31	39	33	29		35	30	27		31
9	54	42	34	29	51	40	33	28	36	30	26		32	27	24		29
10	50	38	31	26	47	37	30	25	33	28	24		30	25	22		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3496	3496	3496
5°	3501	3441	3463
10°	3467	3374	3351
15°	3419	3263	3178
20°	3356	3110	2965
25°	3291	2938	2759
30°	3204	2762	2498
35°	3119	2573	2269
40°	3032	2377	2005
45°	2932	2159	1767
50°	2828	1939	1533
55°	2719	1705	1309
60°	2593	1459	1079
65°	2449	1209	972
70°	2273	976	881
75°	2053	862	804
80°	1734	725	701
85°	1207	488	533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2932 cd/sqm

TEST NUMBER: P920563

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	466.9	2.9
10°-20°	1281.8	7.9
20°-30°	1799.5	11.1
30°-40°	1961.6	12.1
40°-50°	1802.9	11.1
50°-60°	1415.9	8.7
60°-70°	921.6	5.7
70°-80°	474.4	2.9
80°-90°	124.7	0.8
90°-100°	67.1	0.4
100°-110°	250.0	1.5
110°-120°	663.1	4.1
120°-130°	1099.8	6.8
130°-140°	1168.3	7.2
140°-150°	1085.8	6.7
150°-160°	872.9	5.4
160°-170°	562.5	3.5
170°-180°	193.6	1.2
0°-30°	3548.2	21.9
0°-40°	5509.8	34.0
0°-60°	8728.7	53.8
0°-90°	10249.5	63.2
90°-120°	980.2	6.0
90°-150°	4334.1	26.7
90°-180°	5963.0	36.8
0°-180°	16212.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4982	4982	4982	4982	4982	
5°	4982	4959	4900	4941	4928	472
15°	4738	4689	4536	4450	4405	1335
25°	4301	4157	3859	3675	3607	1978
35°	3706	3476	3080	2795	2696	2320
45°	3030	2728	2254	1934	1826	2340
55°	2304	1952	1465	1195	1109	2059
65°	1556	1190	784	631	618	1542
75°	829	514	361	329	325	877
85°	194	99	86	86	86	222
90°	1	18	29	37	40	15
95°	96	47	57	65	63	113
105°	448	492	90	106	112	478
115°	846	871	908	227	121	833
125°	1196	1216	1244	1254	1258	1067
135°	1481	1504	1517	1532	1529	1144
145°	1718	1716	1741	1751	1744	1074
155°	1891	1878	1896	1904	1893	872
165°	1993	1984	1988	1999	1988	563
175°	2038	2028	2031	2041	2027	194
180°	2034	2034	2034	2034	2034	

TEST NUMBER: P920563

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4981.9	4981.9	4981.9	4981.9	4981.9
2.5°	5004.4	4981.9	4932.1	4977.6	4968.5
5°	4981.9	4959.4	4900.5	4941.3	4927.8
7.5°	4941.3	4914.4	4851.3	4869.0	4846.6
10°	4887.2	4855.6	4765.7	4751.8	4725.0
12.5°	4819.7	4779.1	4657.1	4630.3	4580.6
15°	4738.4	4688.6	4535.6	4450.0	4405.0
17.5°	4643.7	4571.5	4382.0	4283.0	4210.8
20°	4535.6	4445.2	4219.9	4107.5	4008.0
22.5°	4418.4	4314.6	4053.0	3899.9	3832.5
25°	4301.2	4156.7	3859.3	3674.6	3606.6
27.5°	4161.5	4008.0	3678.9	3467.0	3363.2
30°	4012.8	3841.1	3480.4	3250.8	3128.8
32.5°	3868.3	3660.7	3291.4	3020.7	2907.8
35°	3706.2	3476.1	3079.5	2795.4	2695.9
37.5°	3548.3	3300.0	2881.0	2569.6	2457.2
40°	3381.4	3111.1	2673.4	2353.5	2236.3
42.5°	3210.1	2921.7	2466.3	2132.4	2020.0
45°	3029.8	2727.5	2254.4	1933.9	1825.8
47.5°	2858.5	2538.6	2051.6	1731.1	1632.1
50°	2669.1	2349.1	1853.0	1541.7	1447.4
52.5°	2484.0	2145.8	1663.6	1366.1	1280.5
55°	2303.7	1952.1	1465.2	1194.9	1109.2
57.5°	2119.0	1758.3	1289.6	1037.1	964.8
60°	1929.6	1568.9	1104.5	874.9	802.6
62.5°	1745.0	1384.3	946.7	730.4	694.6
65°	1555.6	1190.1	784.5	631.4	617.5
67.5°	1375.2	1009.8	631.4	554.4	541.0
70°	1185.8	834.2	522.8	477.9	459.7
72.5°	1005.5	671.6	437.2	401.3	392.3
75°	829.4	513.8	360.7	329.1	324.8
77.5°	653.9	365.0	284.1	266.0	256.8
80°	491.3	261.7	216.2	198.5	198.5
82.5°	342.5	176.0	148.8	139.7	139.7
85°	193.7	99.0	85.6	85.6	85.6
87.5°	72.2	35.9	35.9	31.6	31.6
90°	1.4	17.7	29.4	36.9	39.7
92.5°	36.9	30.9	35.3	38.3	39.7
95°	95.6	47.0	57.3	64.8	63.3
97.5°	172.1	51.6	75.0	79.6	80.9
100°	260.6	58.9	83.9	95.6	98.6
102.5°	357.6	354.8	86.9	103.0	107.5
105°	447.5	491.6	89.8	105.9	111.8
107.5°	551.9	588.7	92.8	108.9	114.9
110°	652.1	682.9	257.6	110.5	116.2



TEST NUMBER: P920563

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	746.3	772.7	747.7	113.2	117.8
115°	846.3	871.2	908.1	226.7	120.8
117.5°	933.1	962.5	987.7	777.1	391.5
120°	1030.3	1052.3	1078.9	1096.6	897.8
122.5°	1112.6	1136.2	1165.8	1174.5	1176.0
125°	1196.5	1215.7	1243.7	1254.0	1258.3
127.5°	1273.1	1293.6	1315.9	1330.6	1332.0
130°	1345.2	1368.8	1384.9	1401.2	1399.8
132.5°	1418.8	1438.0	1454.1	1467.4	1466.0
135°	1480.7	1504.2	1517.4	1532.2	1529.3
137.5°	1545.3	1563.1	1577.9	1592.6	1588.2
140°	1608.6	1620.5	1636.6	1649.8	1642.5
142.5°	1661.7	1672.1	1691.1	1702.8	1695.5
145°	1717.7	1716.1	1741.1	1751.4	1744.1
147.5°	1766.1	1761.8	1786.7	1794.1	1788.3
150°	1813.3	1803.0	1826.6	1835.3	1828.0
152.5°	1853.0	1841.2	1863.3	1872.2	1861.9
155°	1891.3	1878.1	1895.7	1904.5	1892.8
157.5°	1922.2	1910.5	1923.7	1934.1	1922.2
160°	1948.8	1939.8	1948.8	1957.5	1947.1
162.5°	1972.2	1963.4	1970.7	1981.1	1967.8
165°	1992.8	1984.1	1988.4	1998.7	1988.4
167.5°	2009.1	2000.1	2004.7	2015.0	2001.7
170°	2022.3	2013.4	2016.4	2026.7	2013.4
172.5°	2031.1	2022.3	2025.3	2035.6	2022.3
175°	2038.4	2028.1	2031.1	2041.3	2026.7
177.5°	2041.3	2031.1	2032.6	2043.0	2029.6
180°	2034.0	2034.0	2034.0	2034.0	2034.0

TEST NUMBER: P920563

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.66	13.61	13.50	14.47	15.54	8.62	9.57	9.46	10.43	11.50
	3H	14.35	15.20	15.21	16.07	17.17	9.82	10.67	10.67	11.54	12.64
	4H	14.97	15.77	15.84	16.65	17.76	10.28	11.08	11.15	11.95	13.06
	6H	15.40	16.14	16.28	17.02	18.14	10.60	11.34	11.49	12.22	13.35
	8H	15.53	16.23	16.42	17.13	18.26	10.70	11.40	11.59	12.30	13.42
	12H	15.60	16.27	16.50	17.16	18.31	10.75	11.41	11.64	12.31	13.46
4H	2H	12.69	13.50	13.57	14.37	15.48	9.23	10.04	10.11	10.91	12.02
	3H	14.54	15.20	15.42	16.11	17.24	10.60	11.26	11.48	12.17	13.29
	4H	15.24	15.84	16.14	16.75	17.90	11.15	11.76	12.05	12.66	13.81
	6H	15.76	16.29	16.68	17.21	18.37	11.58	12.10	12.49	13.03	14.18
	8H	15.94	16.43	16.86	17.35	18.52	11.71	12.20	12.62	13.12	14.28
	12H	16.05	16.49	16.98	17.43	18.60	11.78	12.22	12.71	13.16	14.33
8H	4H	15.22	15.70	16.13	16.62	17.79	11.44	11.93	12.36	12.85	14.02
	6H	15.79	16.19	16.73	17.16	18.32	11.96	12.37	12.91	13.33	14.50
	8H	16.01	16.37	16.96	17.32	18.51	12.16	12.51	13.11	13.47	14.65
	12H	16.16	16.47	17.11	17.42	18.65	12.28	12.60	13.24	13.54	14.78
12H	4H	15.17	15.61	16.11	16.55	17.72	11.45	11.89	12.39	12.83	14.00
	6H	15.77	16.12	16.72	17.08	18.26	12.02	12.37	12.97	13.33	14.51
	8H	16.00	16.31	16.95	17.26	18.49	12.23	12.55	13.19	13.49	14.73